

AMP MTA .100" IDC Headers

RoHS Compliant This product is RoHS compliant.
FRICTION LOCK HEADERS

- Posts: Copper alloy, tin plated or gold over nickel • RoHS Compliant per Tyco Electronics documentation
- Housing: UL94V-0 rated, polyester, natural color

FLAT & NARROW FLAT HEADERS

- Housing: UL94V-0 rated, polyester, natural color
- Posts: Copper alloy, tin plated
- RoHS compliant per Tyco Electronics documentation



Flat For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	AMP Part No.	Fig.	No. of Pos.	Price Each		
				1	10	100
Straight Post						
571-6404522	640452-2	A	2			
571-6404523	640452-3	A	3			
571-6404524	640452-4	A	4			
571-640452-5	640452-5	A	5			
571-6404526	640452-6	A	6			
571-6404527	640452-7	A	7			
571-6404528	640452-8	A	8			
571-16404520	1-640452-0	A	10			
571-16404522	1-640452-2	A	12			
571-16404524	1-640452-4	A	14			
571-16404526	1-640452-6	A	16			
Right Angle Post						
571-6404532	640453-2	B	2			
571-6404533	640453-3	B	3			
571-6404534	640453-4	B	4			
571-6404535	640453-5	B	5			
571-6404536	640453-6	B	6			
571-6404537	640453-7	B	7			
571-6404538	640453-8	B	8			
571-6404539	640453-9	B	9			
571-16404530	1-640453-0	B	10			
571-16404532	1-640453-2	B	12			
571-16404534	1-640453-4	B	14			
571-16404536	1-640453-6	B	16			

Narrow Flat For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	AMP Part No.	Fig.	No. of Pos.	Price Each		
				1	10	100
Straight Post						
571-3-644456-2	3-644456-2	A	2			
571-3-644456-3	3-644456-3	A	3			
571-3-644456-4	3-644456-4	A	4			
571-3-644456-5	3-644456-5	A	5			
571-3-644456-6	3-644456-6	A	6			
571-3-644456-7	3-644456-7	A	7			
571-3-644456-8	3-644456-8	A	8			
571-3-644456-9	3-644456-9	A	9			
571-4-644456-0	4-644456-0	A	10			
571-4-644456-4	4-644456-4	A	14			
571-4-644456-6	4-644456-6	A	16			
Straight Post with Retentive Leg						
571-3-644695-2	3-644695-2	A	2			
571-3-644695-3	3-644695-3	A	3			
571-3-644695-4	3-644695-4	A	4			
571-3-644695-5	3-644695-5	A	5			
571-3-644695-6	3-644695-6	A	6			
571-3-644695-8	3-644695-8	A	8			
571-3-644695-9	3-644695-9	A	9			
Right Angle Post						
571-3-644457-2	3-644457-2	B	2			
571-3-644457-3	3-644457-3	B	3			
571-3-644457-4	3-644457-4	B	4			
571-3-644457-5	3-644457-5	B	5			
571-3-644457-6	3-644457-6	B	6			
571-3-644457-8	3-644457-8	B	8			

SHROUDED HEADERS

- Housing: UL94V-0 rated, polyester, natural color • RoHS Compliant per Tyco Electronics documentation
- Posts: Copper alloy, tin plated

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	AMP Part No.	Fig.	No. of Pos.	Price Each		
				1	10	100
Straight Post						
571-2-644486-2	2-644486-2	C	2			
571-2-644486-3	2-644486-3	C	3			
571-2-644486-4	2-644486-4	C	4			
571-2-644486-5	2-644486-5	C	5			
571-2-644486-6	2-644486-6	C	6			
571-2-644486-7	2-644486-7	C	7			
571-2-644486-8	2-644486-8	C	8			
571-2-644486-9	2-644486-9	C	9			
571-3-644486-0	3-644486-0	C	10			
571-3-644486-4	3-644486-4	C	14			
Right Angle Post						
571-2-644488-2	2-644488-2	D	2			
571-2-644488-3	2-644488-3	D	3			
571-2-644488-4	2-644488-4	D	4			
571-2-644488-5	2-644488-5	D	5			
571-2-644488-7	2-644488-7	D	7			

MOUSER STOCK NO.	AMP Part No.	Fig.	No. of Pos.	Price Each		
				1	10	100
Straight Post, Tin Plated						
571-6404562	640456-2	E	2			
571-6404563	640456-3	E	3			
571-6404564	640456-4	E	4			
571-6404565	640456-5	E	5			
571-6404566	640456-6	E	6			
571-6404567	640456-7	E	7			
571-6404568	640456-8	E	8			
571-6404569	640456-9	E	9			
571-16404560	1-640456-0	E	10			
571-16404562	1-640456-2	E	12			
571-16404564	1-640456-4	E	14			
571-16404566	1-640456-6	E	16			
Straight Post, Gold Plated						
571-3-641215-2	3-641215-2	E	2			
571-3-641215-3	3-641215-3	E	3			
571-3-641215-4	3-641215-4	E	4			
571-3-641215-5	3-641215-5	E	5			
571-3-641215-6	3-641215-6	E	6			
571-3-641215-7	3-641215-7	E	7			
571-3-641215-8	3-641215-8	E	8			
571-4-641215-0	4-641215-0	E	10			
571-4-641215-2	4-641215-2	E	12			
571-4-641215-4	4-641215-4	E	14			
571-4-641215-6	4-641215-6	E	16			
Right Angle Post, Tin Plated						
571-6404572	640457-2	F	2			
571-6404573	640457-3	F	3			
571-6404574	640457-4	F	4			
571-6404575	640457-5	F	5			
571-6404576	640457-6	F	6			
571-6404577	640457-7	F	7			
571-6404578	640457-8	F	8			
571-6404579	640457-9	F	9			
571-16404570	1-640457-0	F	10			
571-16404572	1-640457-2	F	12			
571-16404574	1-640457-4	F	14			
571-16404576	1-640457-6	F	16			
Right Angle Post, Gold Plated						
571-3-641216-5	3-641216-5	F	5			
571-4-641216-0	4-641216-0	F	10			
571-4-641216-2	4-641216-2	F	12			
571-4-641216-6	4-641216-6	F	16			

POLARIZED HEADERS

- Housing: UL94V-0 rated, polyester, natural color • RoHS Compliant per Tyco Electronics documentation
- Posts: Copper alloy, tin plated or gold over nickel
- No 16 Position in Gold

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	AMP Part No.	Fig.	No. of Pos.	Price Each		
				1	10	100
Straight Post, Tin Plated						
571-640454-2	640454-2	E	2			
571-640454-3	640454-3	E	3			
571-640454-4	640454-4	E	4			
571-640454-5	640454-5	E	5			
571-640454-6	640454-6	E	6			
571-640454-7	640454-7	E	7			
571-640454-8	640454-8	E	8			
571-640454-9	640454-9	E	9			
571-16404540	1-640454-0	E	10			
571-16404542	1-640454-2	E	12			
571-16404544	1-640454-4	E	14			
571-16404546	1-640454-6	E	16			
Straight Post, Gold Plated						
571-3-641213-2	3-641213-2	E	2			
571-3-641213-3	3-641213-3	E	3			
571-3-641213-4	3-641213-4	E	4			
571-3-641213-5	3-641213-5	E	5			
571-3-641213-6	3-641213-6	E	6			
571-3-641213-8	3-641213-8	E	8			
571-4-641213-0	4-641213-0	E	10			
571-4-641213-4	4-641213-4	E	14			
Right Angle Post, Tin Plated						
571-6404552	640455-2	F	2			
571-6404553	640455-3	F	3			
571-6404554	640455-4	F	4			
571-6404555	640455-5	F	5			
571-6404556	640455-6	F	6			
571-640455-7	640455-7	F	7			
571-6404558	640455-8	F	8			
571-6404559	640455-9	F	9			
571-16404550	1-640455-0	F	10			
Right Angle Post, Gold Plated						
571-3-641214-2	3-641214-2	F	2			
571-4-641216-0	4-641216-0	F	10			
571-4-641214-2	4-641214-2	F	12			

