

CARLING TECHNOLOGIES Pushbutton Switches



CARLING 170/172 SERIES HEAVY ACTION PUSHBUTTON SWITCHES

- Features:**
- Power Rating: 15A @ 125VAC, 10A @ 250VAC
 - Actuator Style: Nickel Plated Pushbutton
 - Actuator Material: Brass / Nickel Plate
 - Actuation Force: 2.5 lbs.
 - Mounting Hole Dimensions: .500" diameter; 12.70 mm diameter
 - Mounting Method: Bushing Mount



For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	Carling Tech. Part No.	Fig.	Circuit	Termination	Price Each			
					1	25	50	100
691-170	170	A	SP, ON-(OFF)	Screw Term.				
691-172	172	A	SP, OFF-(ON)	Screw Term.				

CARLING 641 SERIES MAINTAINED PUSHBUTTON SWITCHES

- Features:**
- Power Rating: 5A @ 125VAC, 2A @ 250VAC
 - Actuator Style: Nickel Plated Pushbutton
 - Actuator Material: Brass / Nickel Plate
 - Actuation Force: 3-3.5 lbs.
 - Mounting Hole Dimensions: .500" diameter; 12.70 mm diameter
 - Mounting Method: Bushing Mount



For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	Carling Tech. Part No.	Fig.	Circuit	Termination	Price Each			
					1	25	50	100
691-64111210	64111210	B	SP, ON-OFF	Solder Lug				
691-64112210	64112210	B	DP, ON-OFF	Solder Lug				
691-64111220	64111220	B	SP, ON-ON	Solder Lug				
691-64112220	64112220	B	DP, ON-ON	Solder Lug				

CARLING 110/316 SERIES HEAVY DUTY PUSHBUTTON SWITCHES

- Features:**
- Actuator Style: Nickel Plated Pushbutton
 - Actuator Material: Brass / Nickel Plate
 - Actuation Force: 3-3.5 lbs.
 - Mounting Hole Dimensions: .500" diameter; 12.70 mm diameter
 - Mounting Method: Bushing Mount



For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	Carling Tech. Part No.	Fig.	Circuit	Termination	Price Each			
					1	25	50	100
Power Rating: 6A @ 125V 3A @ 250V								
691-110-P	110-P	C	SP, OFF-ON	Solder Lug (end)				
691-110-SP	110-SP	C	SP, OFF-ON	Screw Term. (#6-32NC-2)				
691-111-PM-ON	111-PM-ON	C	SP, ON-(OFF)	Wire Leads				
Power Rating: 3A @ 125V 1A @ 250V								
691-112-P	112P	C	SP, ON-ON	Solder Lug (end)				
691-316-PP	316-PP	C	DP, ON-ON	Solder Lug (end)				
691-316-B-PP	316-B-PP	D	DP, ON-ON	Solder Lug (bottom)				

CARLING P26/27 SERIES MOMENTARY PUSHBUTTON SWITCHES

- Features:**
- Power Rating: 6A @ 125VAC; 3A @ 250VAC; 3/4A 125V
 - Actuation Force: P26 - 13 oz.; P27 - 26 oz.
 - Mounting Hole Dimensions: .500" diameter; 12.70 mm diameter
 - Mounting Method: Bushing Mount



For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	Carling Tech. Part No.	Fig.	Circuit	Termination	Button Style/Color	Price Each			
						1	25	50	100
691-P26A-1D-BL	P26A-1D-BL	E	SP, OFF-(ON)	Solder Lug	Nylon/Black				
691-P26A-1D-RND-MTL	P26A-1D-RND-MTL	E	SP, OFF-(ON)	Solder Lug	Round/Metal				
691-P26L-1D-RND-MTL	P26L-1D-RND-MTL	E	SP, ON-(OFF)	Solder Lug	Round/Metal				
691-P27A-BL	P27A-BL	F	SP, OFF-(ON)	Solder Lug	Nylon/Black				
691-P27B-BL	P27B-BL	F	SP, OFF-(ON)	.250 Q.C. Tab	Nylon/Black				
691-P27L-BL	P27L-BL	F	SP, ON-(OFF)	Solder Lug	Nylon/Black				

CARLING P SERIES HEAVY DUTY PUSHBUTTON SWITCHES

- Features:**
- Power Rating: PA351 - 15A @ 125VAC, 10A @ 250VAC; PA951 - 15A @ 125VAC, 10A @ 250VAC, 10A(6) 250Vμ T85
 - Actuator Style: Nickel Plated Pushbutton
 - Actuator Material: Brass / Nickel Plate
 - Actuation Force: 3-5 lbs.
 - Mounting Hole Dimensions: .550" diameter; 13.97 mm diameter
 - Mounting Method: Bushing Mount



For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	Carling Tech. Part No.	Fig.	Circuit	Termination	Price Each			
					1	25	50	100
691-PA351	PA351	G	SP, ON-OFF	.250 Q.C. Tab				
* 691-PA951	PA951	G	SP, ON-OFF	.250 Q.C. Tab				

