

C&K Toggle Switches



C&K GT SERIES: SEALED ULTRAMINIATURE TOGGLE SWITCHES

- Contact Material: Gold Terminal Plating
- Internal O-ring seal standard with all actuators
- Epoxy sealed termination
- Lead Free

- Contact Rating: 0.4VA @ 20VAC or DC max.
- Case and actuator material: Glass filled nylon (UL 94V-0)
- Body Height: .210"



For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	C&K Part No.	Fig.	Contact Form	Circuit	Mounting Type	Actuator/Bushing Height	Contact Material	Price Each			
								1	25	50	100
611-GT11MSCBE	GT11MSCBE	A	SPDT	On-On	Surface mount	.50"/.063"	Gold				
611-GT11MABE	GT11MABE	B	SPDT	On-On	R/A PC thru-hole	.50"/.063"	Gold				
611-GT12MABE	GT12MABE	B	SPST	Off-On	R/A PC thru-hole	.150"/.063"	Gold				
611-GT12MCBE	GT12MCBE	C	SPDT	Off-None-On	Thru-hole	.150"/.063"	Gold				

C&K E SERIES: SEALED MINIATURE TOGGLE SWITCHES

- Contact Material: Cu alloy, w/ Au plate over Ni plate, Au plate terminal
- Epoxy sealed termination
- Actuator material: Chrome plated brass
- Internal O-ring seal standard with all actuators

- Contact Rating: 0.4VA @ 20VAC or DC max.
- Case and bushing material: Glass filled nylon
- Unthreaded bushing



RoHS Compliant

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	C&K Part No.	Fig.	Contact Form	Circuit	Mounting Type	Bushing Height	Price Each			
							1	25	50	100
Standard Round Actuator (.300" High)										
611-E101-001	E101MD1ABE	D	SPDT	On-None-On	R/A PC thru-hole	.250"				
611-E101-002	E101MD1AV2BE	E	SPDT	On-None-On	Vertical R/A PC thru-hole	.250"				
611-E101-006	E101MD1CBE	F	SPDT	On-None-On	PC thru-hole	.250"				
611-E103-002	E103MD1AV2BE	E	SPDT	On-Off-On	Vertical R/A PC thru-hole	.250"				
611-E201-002	E201MD1AV2BE	E	DPDT	On-None-On	Vertical R/A PC thru-hole	.250"				
611-E203-002	E203MD1AV2BE	E	DPDT	On-Off-On	Vertical R/A PC thru-hole	.250"				
Long Round Actuator (.500" High)										
611-E101-003	E101SD1CBE	F	SPDT	On-None-On	PC thru-hole	.250"				
611-E103-005	E103SD1ABE	D	SPDT	On-Off-On	R/A PC thru-hole	.250"				
611-E201-003	E201SD1CBE	F	DPDT	On-None-On	PC thru-hole	.250"				

C&K ET SERIES: SEALED SUBMINIATURE TOGGLE SWITCHES

- Contact Material: B- Cu alloy, w/ Au plate over Ni plate, Au plate terminal
K- Cu alloy, w/ Au plate over Ni plate, SnPb plate terminal
G- Coin Ag, w/ Au plate over Ni plate, Au plate terminal
- Epoxy sealed termination
- Actuator material: Chrome plated brass
- Internal O-ring seal standard with all actuators

- Contact Rating: B & K- 0.4VA @ 20VAC or DC max.
G- 0.4VA @ 20VAC or DC max. or
5A @ 120VAC; 2A @ 250VAC
- Case and bushing material: Glass filled nylon
- Unthreaded bushing



RoHS Compliant

() = Momentary

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	C&K Part No.	Fig.	Contact Form	Circuit	Mounting Type	Bushing Height	Contact Material	Price Each			
								1	25	50	100
Standard Round Actuator (.240" High)											
611-ET01-011	ET01MD1ABE	G	SPDT	On-On	R/A PC thru-hole	.177"	B				
611-ET01-006	ET01MD1AGE	G	SPDT	On-On	R/A PC thru-hole	.177"	G				
611-ET01-002	ET01MD1AVBE	E	SPDT	On-On	R/A PC thru-hole	.177"	B				
611-ET01-001	ET01MD1CBE	F	SPDT	On-On	PC thru-hole	.177"	B				
611-ET01-013	ET01MD1V3BE	H	SPDT	On-On	V bracket	.177"	B				
611-ET03-011	ET03MD1ABE	G	SPDT	On-Off-On	R/A PC thru-hole	.177"	B				
611-ET08-011	ET08MD1ABE	G	SPDT	On-(On)	R/A PC thru-hole	.177"	B				
Round Actuator (.320" High)											
611-ET01-005	ET01LD1CBE	F	SPDT	On-On	PC thru-hole	.177"	B				
Long Round Actuator (.400" High)											
611-ET01-003	ET01SD1CBE	F	SPDT	On-On	PC thru-hole	.177"	B				
611-ET01-004	ET01SD1ABE	G	SPDT	On-On	R/A PC thru-hole	.177"	B				

C&K T SERIES: SEALED SUBMINIATURE TOGGLE SWITCHES

- Contact Material: B- Cu alloy, w/ Au plate over Ni plate, Au plate terminal
Q- Cu alloy, w/ Ag plate, Ag plate terminal
- Actuator material: Chrome plated brass
- Housing material: Stainless steel

- Contact Rating: B- 0.4VA @ 20VAC or DC max.
Q- 5A @ 120VAC; 2A @ 250VAC
- Bushing material: Nickel plated brass
- Case material: Glass filled nylon or DAP



RoHS Compliant

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	C&K Part No.	Fig.	Contact Form	Circuit	Mounting Type	Bushing Height	Contact Material	Price Each			
								1	25	50	100
Standard Round Actuator (.370" High), Threaded Bushing											
611-T101-001	T101SHCQE	I	SPDT	On-On	PC thru-hole	.220" flat	Q				
611-T103-001	T103SHCQE	I	SPDT	On-Off-On	PC thru-hole	.220" flat	Q				
611-T102SHZQE	T102SHZQE	J	SPDT	Off-None-On	Solder lug	.220" flat	Q				
611-T103-002	T103SHZQE	J	SPDT	On-Off-On	Solder lug	.220" flat	Q				
Short Round Actuator (.210" High), Unthreaded Bushing											
611-T101-004	T101MH9ABE	G	SPDT	On-On	R/A PC thru-hole	.220" flat	B				
611-T101-005	T101MH9AVBE	E	SPDT	On-On	R/A PC thru-hole	.220" flat	B				

DIMENSIONS: in.

(SPDT Shown)

C&K Toggle Switches