

TEXAS INSTRUMENTS Analog ICs

Products may be RoHS compliant.
Check mouser.com for RoHS status.

TEXAS INSTRUMENTS
Authorized Distributor

TEXAS INSTRUMENTS ANALOG-TO-DIGITAL CONVERTERS (ADCS) (CONT.)

For quantities 500 and up, call for quote.

MOUSER STOCK NO.	TI Part No.	Package	Res.	No. of Input Chan.	Architecture	INL (Max) (+/-LSB)	DNL (Max) (+/-LSB)	Sample Rate	Consumption (Typ) (mW)	Price Each			
										1	25	100	250
595-TLC2543CDB	TLC2543CDB	SSOP-20	12	11	SAR	0.5	0.5	66kSPS	5				
595-TLC2543CDW	TLC2543CDW	SOIC-20	12	11	SAR	0.5	0.5	66kSPS	5				
595-TLC2543CFN	TLC2543CFN	PLCC-20	12	11	SAR	0.5	0.5	66kSPS	5				
595-TLC2543CN	TLC2543CN	PDIP-20	12	11	SAR	0.5	0.5	66kSPS	5				
595-TLC2543IDB	TLC2543IDB	SSOP-20	12	11	SAR	0.5	0.5	66kSPS	5				
595-TLC2543IDW	TLC2543IDW	SOIC-20	12	11	SAR	0.5	0.5	66kSPS	5				
595-TLC2543IFN	TLC2543IFN	PLCC-20	12	11	SAR	0.5	0.5	66kSPS	5				
595-TLC2543IN	TLC2543IN	PDIP-20	12	11	SAR	0.5	0.5	66kSPS	5				
595-TLV2543CDW	TLV2543CDW	SOIC-20	12	11	SAR	1	1	66kSPS	3.3				
595-TLV2543IDB	TLV2543IDB	SSOP-20	12	11	SAR	1	1	66kSPS	3.3				
595-TLV2553IDW	TLV2553IDW	SOIC-20	12	11	SAR	1	1	200kSPS	2.43				
595-TLV2553IPW	TLV2553IPW	TSSOP-20	12	11	SAR	1	1	200kSPS	2.43				
595-TLV2556IPW	TLV2556IPW	TSSOP-20	12	11	SAR	1	1	200kSPS	2.43				
595-ADS5474IPFP	ADS5474IPFP	HTQFP-80	14	1	Pipeline	1	0.7	400MSPS	2500				
595-ADS5547IRGZT	ADS5547IRGZT	QFN 48	14	1	Pipeline	3.5	0.5	210MSPS	1375				
595-ADS61B49IRGZ25	ADS61B49IRGZ25	QFN-48	14	1	Pipeline	5	1	250MSPS	690				
595-TLC3545ID	TLC3545ID	SOIC-8	14	1	SAR	1	1	200kSPS	17.5				
595-TLC7135CN	TLC7135CN	PDIP-28	14	1	Dual-Slope	0.5	0.01	3kSPS	5				
595-TLC3578IPW	TLC3578IPW	TSSOP-24	14	8	SAR	1.5	1	200kSPS	29				
595-ADS1100A0IDBVT	ADS1100A0IDBVT	SOT-23-6	16	1	Delta-Sigma	0.003	1	128SPS	0.27				
595-ADS1100A1IDBVT	ADS1100A1IDBVT	SOT-23-6	16	1	Delta-Sigma	0.003	1	128SPS	0.27				
595-ADS1100A2IDBVT	ADS1100A2IDBVT	SOT-23-6	16	1	Delta-Sigma	0.003	1	128SPS	0.27				
595-ADS1100A5IDBVT	ADS1100A5IDBVT	SOT-23-6	16	1	Delta-Sigma	0.003	1	128SPS	0.27				
595-ADS1110A0IDBVT	ADS1110A0IDBVT	SOT-23-6	16	1	Delta-Sigma	0.004	1	128SPS	0.72				
595-ADS1110A1IDBVT	ADS1110A1IDBVT	SOT-23-6	16	1	Delta-Sigma	0.004	1	128SPS	0.72				
595-ADS1110A5IDBVT	ADS1110A5IDBVT	SOT-23-6	16	1	Delta-Sigma	0.004	1	128SPS	0.72				
595-ADS1110A7IDBVT	ADS1110A7IDBVT	SOT-23-6	16	1	Delta-Sigma	0.004	1	128SPS	0.72				
595-ADS1208IPW	ADS1208IPW	TSSOP-16	16	1	Delta-Sigma, Mod	8	1	40kSPS	64				
595-ADS1602IPFBT	ADS1602IPFBT	TQFP-48	16	1	Delta-Sigma	0.75	0.25	2.5MSPS	530				
595-ADS1610IPAPT	ADS1610IPAPT	HTQFP-64	16	1	Delta-Sigma	0.4	0.5	10MSPS	960				
595-ADS5485IRGC25	ADS5485IRGC25	QFN-64	16	1	Pipeline	10	1	200MSPS	2160				
595-ADS8320E/250	ADS8320E/250	MSOP-8	16	1	SAR	8	2	100kSPS	1.95				
595-ADS8320EB/250	ADS8320EB/250	MSOP-8	16	1	SAR	8	2	100kSPS	1.95				
595-ADS8321E/250	ADS8321E/250	MSOP-8	16	1	SAR	8	2	100kSPS	5.5				
595-ADS8321EB/250	ADS8321EB/250	MSOP-8	16	1	SAR	8	2	100kSPS	5.5				
595-ADS8325IBDGKT	ADS8325IBDGKT	MSOP-8	16	1	SAR	4	2	100kSPS	2.25				
595-ADS8326IBDGKT	ADS8326IBDGKT	MSOP-8	16	1	SAR	1.5	1	250kSPS	10				
595-ADS8326IDGKT	ADS8326IDGKT	MSOP-8	16	1	SAR	1.5	1	250kSPS	10				
595-ADS8327IBPW	ADS8327IBPW	TSSOP-16	16	1	SAR	2	1	500kSPS	15				
595-ADS8327IPW	ADS8327IPW	TSSOP-16	16	1	SAR	2	1	500kSPS	15				
595-ADS8329IRSAT	ADS8329IRSAT	QFN-16	16	1	SAR	1.75	1	1MSPS	15.5				
595-ADS8370IBRHPT	ADS8370IBRHPT	QFN-28	16	1	SAR	1.25	0.75	600kSPS	110				
595-ADS8370IRHPT	ADS8370IRHPT	QFN-28	16	1	SAR	1.25	0.75	600kSPS	110				
595-ADS8401IPFBT	ADS8401IPFBT	TQFP-48	16	1	SAR	3.5	2.0/-1.0	1.25MSPS	155				
595-ADS8422IBPFBT	ADS8422IBPFBT	TQFP-48	16	1	SAR	2	-1.0,1.5	4MSPS	155				
595-ADS8422IPFBT	ADS8422IPFBT	TQFP-48	16	1	SAR	2	-1.0,1.5	4MSPS	155				
595-ADS8472IRGZT	ADS8472IRGZT	QFN-48	16	1	SAR	0.65	0.5	1MSPS	225				
595-ADS8505IDW	ADS8505IDW	SOIC-28	16	1	SAR	3	1	250kSPS	70				
595-ADS8507IBDW	ADS8507IBDW	SOIC-28	16	1	SAR	1.5	1.5	40kSPS	24				
595-ADS8507IDW	ADS8507IDW	SOIC-28	16	1	SAR	1.5	1.5	40kSPS	24				
595-ADS8509IDB	ADS8509IDB	SSOP-28	16	1	SAR	2	1	250kSPS	70				
595-ADS8509IDW	ADS8509IDW	SOIC-20	16	1	SAR	2	1	250kSPS	70				
595-ADS8515IDBR	ADS8515IDBR	SSOP-28	16	1	SAR	2	1	250kSPS	100				
595-ADS1205IRGET	ADS1205IRGET	QFN-24	16	2	Delta-Sigma, Mod	3	1	40kSPS	59				
595-ADS1209SPW	ADS1209SPW	TSSOP-24	16	2	Delta-Sigma, Mod	8	1	40kSPS	65.5				
595-ADS8330IBRSAT	ADS8330IBRSAT	QFN-16	16	2	SAR	1.75	1	1MSPS	15.5				
595-ADS1112IDGST	ADS1112IDGST	MSOP-10	16	3	Delta-Sigma	0.004	1	240SPS	0.675				
595-ADS8331IBRGSET	ADS8331IBRGSET	VQFN-24	16	4	SAR	2	2	500kSPS	39				
595-ADS8331IRGET	ADS8331IRGET	VQFN-24	16	4	SAR	2	2	500kSPS	39				
595-ADS8364Y/250	ADS8364Y/250	TQFP-64	16	6	SAR	8	1.5	250kSPS	413				
595-ADS1178IPAPT	ADS1178IPAPT	HTQFP-64	16	8	Delta-Sigma	0.0045	1	52kSPS	245				
595-ADS1230IPW	ADS1230IPW	TSSOP-16	20	1	Delta-Sigma	0.0006	1	80SPS	2.9				
595-ADS1250U	ADS1250U	SOIC-16	20	1	Delta-Sigma	0.0012	1	25kSPS	75				
595-ADS1212P	ADS1212P	PDIP-18	22	1	Delta-Sigma	0.0015	1	6.25kSPS	1.4				
595-ADS1212U	ADS1212U	SOP-18	22	1	Delta-Sigma	0.0015	1	6.25kSPS	1.4				
595-ADS1213E	ADS1213E	SSOP-28	22	4	Delta-Sigma	0.0015	1	6.25kSPS	1.4				
595-ADS1213P	ADS1213P	PDIP-24	22	4	Delta-Sigma	0.0015	1	6.25kSPS	1.4				
595-ADS1213U	ADS1213U	SOIC-24	22	4	Delta-Sigma	0.0015	1	6.25kSPS	1.4				
595-ADS1210P	ADS1210P	PDIP-18	24	1	Delta-Sigma	0.0015	1	16kSPS	27.5				
595-ADS1210U	ADS1210U	SOP-18	24	1	Delta-Sigma	0.0015	1	16kSPS	27.5				
595-ADS1225IRGVT	ADS1225IRGVT	QFN-16	24	1	Delta-Sigma	0.0005	1	100SPS	1.6				
595-ADS1251U	ADS1251U	SOIC-8	24	1	Delta-Sigma	0.0002	1	20kSPS	7.5				
595-ADS1252U	ADS1252U	SOIC-8	24	1	Delta-Sigma	0.0003	1	41kSPS	40				
595-ADS1255IDBT	ADS1255IDBT	SSOP-20	24	1	Delta-Sigma	0.0003	2	30kSPS	36				
595-ADS1259BIPW	ADS1259BIPW	TSSOP-20	24	1	Delta-Sigma	-	-	14.4kSPS	13				
595-ADS1259IPW	ADS1259IPW	TSSOP-20	24	1	Delta-Sigma	-	-	14.4kSPS	13				
595-ADS1271IPW	ADS1271IPW	TSSOP-16	24	1	Delta-Sigma	0.0006	1	105kSPS	92				
595-ADS1226IRGVT	ADS1226IRGVT	QFN-16	24	2	Delta-Sigma	0.0005	1	100SPS	1.6				
595-ADS1232IPW	ADS1232IPW	TSSOP-24	24	2	Delta-Sigma	0.0002	1	80SPS	2.1				
595-ADS1211E	ADS1211E	SSOP-28	24	4	Delta-Sigma	0.0015	1	16kSPS	27.5				
595-ADS1211P	ADS1211P	PDIP-24	24	4	Delta-Sigma	0.0015	1	16kSPS	27.5				
595-ADS1211U	ADS1211U	SOIC-24	24	4	Delta-Sigma	0.0015	1	16kSPS	27.5				