

TEXAS INSTRUMENTS Operational Amplifiers

TEXAS INSTRUMENTS
Authorized Distributor

RoHS Compliant This product is RoHS compliant.

For quantities of 500 and up, call for quote.

Amplifier ICs

Texas Instruments

PRECISION AMPLIFIERS

MOUSER STOCK NO.	TI Part No.	Package	No. of Channels	Total Supply Voltage Min/Max (+5V=5, ±5v=10)	Iq per Channel (Max) (mA)	GBW (Typ) (MHz)	Slew Rate (Typ) (V/us)	VIO (25°C) (Max) (mV)	Price Each					
									1	25	100	250		
Low Power														
595-TLV2221IDBVT	TLV2221IDBVT	SOT-5	1	10	0.15	0.48	0.18	3						
595-TLV2231CDBVT	TLV2231CDBVT	SOT-5	1	10	1.2	1.9	1.25	3						
595-TLV2711CDBVR	TLV2711CDBVR	SOT-5	1	10	0.025	0.065	0.025	3						
595-TLV2711CDBVT	TLV2711CDBVT	SOT-5	1	10	0.025	0.065	0.025	3						
595-TLV2721CDBVT	TLV2721CDBVT	SOT-5	1	10	0.15	0.51	0.18	3						
595-TLV2721IDBVR	TLV2721IDBVR	SOT-5	1	10	0.15	0.51	0.18	3						
595-TLV2241IDBVT	TLV2241IDBVT	SOT-5	1	12	0.0012	0.0055	0.002	3						
595-TLV271CD	TLV271CD	SOIC-8	1	15	0.66	3	2.4	5						
595-TLV271IDBVR	TLV271IDBVR	SOT-5	1	15	0.66	3	2.4	5						
595-TLV271IDBVT	TLV271IDBVT	SOT-5	1	15	0.66	3	2.4	5						
595-TLV271IDG4	TLV271IDG4	SOIC-8	1	15	0.66	3	2.4	5						
595-TLC27L1BCD	TLC27L1BCD	SOIC-8	1	16	0.017	0.085	0.03	2						
595-TLV2370IDBVR	TLV2370IDBVR	SOT-6	1	16	0.56	2.4	2	4.5						
595-TLV2370IDBVT	TLV2370IDBVT	SOT-6	1	16	0.56	2.4	2	4.5						
595-TLV2371IDBVR	TLV2371IDBVR	SOT-5	1	16	0.56	2.4	2	4.5						
595-TLV2371IDBVT	TLV2371IDBVT	SOT-5	1	16	0.56	2.4	2	4.5						
595-TLV2371IDR	TLV2371IDR	SOIC-8	1	16	0.56	2.4	2	4.5						
595-TLV2381IDBVT	TLV2381IDBVT	SOT-5	1	16	0.01	0.160	0.06	4.5						
595-TLV2381IDG4	TLV2381IDG4	SOIC-8	1	16	0.01	0.160	0.06	4.5						
595-TLV2401CDBVT	TLV2401CDBVT	SOT-5	1	16	0.00095	0.0055	0.0025	1.2						
595-TLV2401ID	TLV2401ID	SOIC-8	1	16	0.00095	0.0055	0.0025	1.2						
595-TLV2401IDBVT	TLV2401IDBVT	SOT-5	1	16	0.00095	0.0055	0.0025	1.2						
595-TLV27L1CDBVT	TLV27L1CDBVT	SOT-5	1	16	0.011	0.160	0.06	4.5						
595-TLV2402IDGKR	TLV2402IDGKR	MSOP-8	2	2.5/16	0.00095	0.0055	0.0025	1.2						
595-TLV2762ID	TLV2762ID	SOIC-8	2	3.6	0.028	0.5	0.2	3.5						
595-TLV2763IDGS	TLV2763IDGS	VSSOP-10	2	3.6	0.028	0.5	0.2	3.5						
595-TLV2763IDGSR	TLV2763IDGSR	VSSOP-10	2	3.6	0.028	0.5	0.2	3.5						
595-OPA2369AIDCNT	OPA2369AIDCNT	SSOP-8	2	5.5	0.001	0.012	0.005	0.75						
595-OPA2369AIDGKT	OPA2369AIDGKT	VSSOP-8	2	5.5	0.001	0.012	0.005	0.75						
595-OPA2379AID	OPA2379AID	SOIC-8	2	5.5	0.0055	0.09	0.03	1.5						
595-TLV2452ID	TLV2452ID	SOIC-8	2	6	0.035	0.22	0.11	1.5						
595-TLV2252AID	TLV2252AID	SOIC-8	2	8	0.0625	0.187	0.1	0.85						
595-TLV2252AIPW	TLV2252AIPW	TSSOP-8	2	8	0.0625	0.187	0.1	0.85						
595-TLV2322IPW	TLV2322IPW	TSSOP-8	2	8	0.017	0.027	0.02	9						
595-TLV2332ID	TLV2332ID	SOIC-8	2	8	0.25	0.3	0.38	9						
595-TLV2342ID	TLV2342ID	SOIC-8	2	8	1.5	0.79	2.1	9						
595-TLV2432AIPW	TLV2432AIPW	TSSOP-8	2	10	0.125	0.5	0.25	0.95						
595-TLV2432CD	TLV2432CD	SOIC-8	2	10	0.125	0.5	0.25	2						
595-TLV2432ID	TLV2432ID	SOIC-8	2	10	0.125	0.5	0.25	2						
595-TLV2442CD	TLV2442CD	SOIC-8	2	10	1.1	1.75	1.3	2						
595-TLV272CDGK	TLV272CDGK	VSSOP-8	2	15	0.66	3	2.4	5						
595-TLV272ID	TLV272ID	SOIC-8	2	15	0.66	3	2.4	5						
595-TLV272IDGK	TLV272IDGK	VSSOP-8	2	15	0.66	3	2.4	5						
595-TLV272IDGKR	TLV272IDGKR	VSSOP-8	2	15	0.66	3	2.4	5						
595-TLV272IDR	TLV272IDR	SOIC-8	2	15	0.66	3	2.4	5						
595-TLC2252AID	TLC2252AID	SOIC-8	2	16	0.0625	0.2	0.12	0.85						
595-TLC2252CD	TLC2252CD	SOIC-8	2	16	0.0625	0.2	0.12	1.5						
595-TLC2252ID	TLC2252ID	SOIC-8	2	16	0.0625	0.2	0.12	1.5						
595-TLC27L2ACD	TLC27L2ACD	SOIC-8	2	16	0.017	0.085	0.03	5						
595-TLC27L2AID	TLC27L2AID	SOIC-8	2	16	0.017	0.085	0.03	5						
595-TLC27L2AIDR	TLC27L2AIDR	SOIC-8	2	16	0.017	0.085	0.03	5						
595-TLC27L2BCD	TLC27L2BCD	SOIC-8	2	16	0.017	0.085	0.03	2						
595-TLC27L2BCDR	TLC27L2BCDR	SOIC-8	2	16	0.017	0.085	0.03	2						
595-TLC27L2CD	TLC27L2CD	SOIC-8	2	16	0.017	0.085	0.03	10						
595-TLC27L2ID	TLC27L2ID	SOIC-8	2	16	0.017	0.085	0.03	10						
595-TLV2372ID	TLV2372ID	SOIC-8	2	16	0.56	2.4	2	4.5						
595-TLV2372IDGK	TLV2372IDGK	VSSOP-8	2	16	0.56	2.4	2	4.5						
595-TLV2372IDGKR	TLV2372IDGKR	VSSOP-8	2	16	0.56	2.4	2	4.5						
595-TLV2372IDR	TLV2372IDR	SOIC-8	2	16	0.56	2.4	2	4.5						
595-TLV2382ID	TLV2382ID	SOIC-8	2	16	0.01	0.160	0.06	4.5						
595-TLV2402CDGK	TLV2402CDGK	VSSOP-8	2	16	0.00095	0.0055	0.0025	1.2						
595-TLV2402IDG4	TLV2402IDG4	SOIC-8	2	16	0.00095	0.0055	0.0025	1.2						
595-TLV27L2CDGK	TLV27L2CDGK	VSSOP-8	2	16	0.01	0.160	0.06	4.5						
595-TLV27L2IDGK	TLV27L2IDGK	VSSOP-8	2	16	0.01	0.160	0.06	4.5						
595-TLV27L2IDR	TLV27L2IDR	SOIC-8	2	16	0.01	0.160	0.06	4.5						
595-TLV2764ID	TLV2764ID	SOIC-14	4	3.6	0.028	0.5	0.2	3.5						
595-TLV2764IPW	TLV2764IPW	TSSOP-14	4	3.6	0.028	0.5	0.2	3.5						
595-TLV2764IPWG4	TLV2764IPWG4	TSSOP-14	4	3.6	0.028	0.5	0.2	3.5						
595-TLV2765CD	TLV2765CD	SOIC-16	4	3.6	0.028	0.5	0.2	3.5						
595-TLV2454AID	TLV2454AID	SOIC-14	4	6	0.035	0.22	0.12	1						
595-TLV2454AIPW	TLV2454AIPW	TSSOP-14	4	6	0.035	0.22	0.12	1						
595-TLV2454AIPWR	TLV2454AIPWR	TSSOP-14	4	6	0.035	0.22	0.12	1						
595-TLV2254AID	TLV2254AID	SOIC-14	4	8	0.0625	0.187	0.1	0.85						
595-TLV2254AIPW	TLV2254AIPW	TSSOP-14	4	8	0.0625	0.187	0.1	0.85						
595-TLV2434AID	TLV2434AID	SOIC-14	4	10	0.125	0.5	0.25	0.95						
595-TLV2434ID	TLV2434ID	SOIC-14	4	10	0.125	0.5	0.25	2						
595-TLV2444AID	TLV2444AID	SOIC-14	4	10	0.725	1.75	1.3	0.95						
595-TLV2444AIPW	TLV2444AIPW	TSSOP-14	4	10	0.725	1.75	1.3	0.95						
595-TLV2244ID	TLV2244ID	SOIC-14	4	12	0.0012	0.0055	0.002	3						
595-TLV2244IPW	TLV2244IPW	TSSOP-14	4	12	0.0012	0.0055	0.002	3						
595-TLV274CD	TLV274CD	SOIC-14	4	15	0.66	3	2.4	5						
595-TLV274IDR	TLV274IDR	SOIC-14	4	15	0.66	3	2.4	5						
595-TLV274IPW	TLV274IPW	TSSOP-14	4	15	0.66	3	2.4	5						
595-TLC1079CD	TLC1079CD	SOIC-14	4	16	0.017	0.085	32	0.85						
595-TLC2254AIDR	TLC2254AIDR	SOIC-14	4	16	0.0625	0.2	0.12	0.85						
595-TLC2254ID	TLC2254ID	SOIC-14	4	16	0.0625	0.2	0.12	1.5						
595-TLC27L4ACD	TLC27L4ACD	SOIC-14	4	16	0.017	0.085	0.03	5						
595-TLC27L4AID	TLC27L4AID	SOIC-14	4	16	0.017	0.085	0.03	5						