

TEXAS INSTRUMENTS Operational Amplifiers



TEXAS INSTRUMENTS
Authorized Distributor



This product is RoHS compliant.

STANDARD LINEAR AMPLIFIERS

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	TI Part No.	Package	No. of Channels	Total Supply Voltage Min/Max (+5V=5, ±5v=10)	Iq per Channel (Max) (mA)	GBW (Typ) (MHz)	Slew Rate (Typ) (V/us)	VIO (25°C) (Max) (mV)	Price Each			
									1	25	100	250
595-OPA237NA/250	OPA237NA/250	SOT-5	1	2.7	0.35	1.5	0.5	0.75				
595-OPA237UA	OPA237UA	SOIC-8	1	2.7	0.35	1.5	0.5	0.75				
595-TLC271AID	TLC271AID	SOIC-8	1	3	1.6	1.7	3.6	5				
595-TLC271BCD	TLC271BCD	SOIC-8	1	3	1.6	1.7	3.6	2				
595-TLC271CD	TLC271CD	SOIC-8	1	3	1.6	1.7	3.6	10				
595-TLC271CDR	TLC271CDR	SOIC-8	1	3	1.6	1.7	3.6	10				
595-TLC271CPWR	TLC271CPWR	TSSOP-8	1	3	1.6	1.7	3.6	10				
595-TLC271ID	TLC271ID	SOIC-8	1	3	1.6	1.7	3.6	10				
595-OP07CD	OP07CD	SOIC-8	1	6	5	0.6	0.3	0.15				
595-TL061ACD	TL061ACD	SOIC-8	1	7	0.25	1	3.5	6				
595-TL061CD	TL061CD	SOIC-8	1	7	0.25	1	3.5	15				
595-TL061IDR	TL061IDR	SOIC-8	1	7	0.25	1	3.5	15				
595-TL071CD	TL071CD	SOIC-8	1	7	2.5	3	13	10				
595-TL071CPSR	TL071CPSR	SOP-8	1	7	2.5	3	13	10				
595-TL071ID	TL071ID	SOIC-8	1	7	2.5	3	13	10				
595-TL081ACD	TL081ACD	SOIC-8	1	7	2.8	3	13	6				
595-TL081BCD	TL081BCD	SOIC-8	1	7	2.8	3	13	3				
595-TL081CD	TL081CD	SOIC-8	1	7	2.8	3	13	15				
595-TL081ID	TL081ID	SOIC-8	1	7	2.8	3	13	15				
595-OPA454AIDDA	OPA454AIDDA	HSOP-8	1	10	4	2.5	13	4				
595-TL031CD	TL031CD	SOIC-8	1	10	0.28	1.1	5.1	1.5				
595-TL031ID	TL031ID	SOIC-8	1	10	0.28	1.1	5.1	1.5				
595-TL051ACD	TL051ACD	SOIC-8	1	10	3.2	3.1	20	0.8				
595-TL051CD	TL051CD	SOIC-8	1	10	3.2	3.1	20	1.5				
595-TLC252CD	TLC252CD	SOIC-8	2	1.4	1.6	1.7	3.6	10				
595-TLC25M2ACD	TLC25M2ACD	SOIC-8	2	1.4	0.28	0.525	0.43	5				
595-OPA2336E/250	OPA2336E/250	VSSOP-8	2	2.3	0.032	0.1	0.03	0.125				
595-OPA2336U	OPA2336U	SOIC-8	2	2.3	0.032	0.1	0.03	0.125				
595-OPA2336UA	OPA2336UA	SOIC-8	2	2.3	0.032	0.1	0.03	0.125				
595-OPA2237UA	OPA2237UA	SOIC-8	2	2.7	0.35	1.5	0.5	0.75				
595-TLC272AID	TLC272AID	SOIC-8	2	3	1.6	1.7	3.6	5				
595-TLC272BID	TLC272BID	SOIC-8	2	3	1.6	1.7	3.6	2				
595-TLC272CD	TLC272CD	SOIC-8	2	3	1.6	1.7	3.6	10				
595-TLC272CPW	TLC272CPW	TSSOP-8	2	3	1.6	1.7	3.6	10				
595-TLC272CPWR	TLC272CPWR	TSSOP-8	2	3	1.6	1.7	3.6	10				
595-TLC272ID	TLC272ID	SOIC-8	2	3	1.6	1.7	3.6	10				
595-TLC27M2ACD	TLC27M2ACD	SOIC-8	2	3	0.28	0.525	0.43	5				
595-TLC27M2AID	TLC27M2AID	SOIC-8	2	3	0.28	0.525	0.43	5				
595-TLC27M2BCD	TLC27M2BCD	SOIC-8	2	3	0.28	0.525	0.43	2				
595-TLC27M2BID	TLC27M2BID	SOIC-8	2	3	0.28	0.525	0.43	2				
595-TLC27M2CD	TLC27M2CD	SOIC-8	2	3	0.28	0.525	0.43	10				
595-TLC27M2ID	TLC27M2ID	SOIC-8	2	3	0.28	0.525	0.43	10				
595-TLC27M2IPW	TLC27M2IPW	TSSOP-8	2	3	0.28	0.525	0.43	10				
595-OPA2130UA	OPA2130UA	SOIC-8	2	4.5	0.65	1	2	1				
595-TL062ACD	TL062ACD	SOIC-8	2	7	0.25	1	3.5	6				
595-TL062ACDR	TL062ACDR	SOIC-8	2	7	0.25	1	3.5	6				
595-TL062CD	TL062CD	SOIC-8	2	7	0.25	1	3.5	15				
595-TL062CPSR	TL062CPSR	SOP-8	2	7	0.25	1	3.5	15				
595-TL062CPW	TL062CPW	TSSOP-8	2	7	0.25	1	3.5	15				
595-TL062ID	TL062ID	SOIC-8	2	7	0.25	1	3.5	15				
595-TL062IDR	TL062IDR	SOIC-8	2	7	0.25	1	3.5	15				
595-TL072ACD	TL072ACD	SOIC-8	2	7	2.5	3	13	6				
595-TL072BCD	TL072BCD	SOIC-8	2	7	2.5	3	13	3				
595-TL072BCDR	TL072BCDR	SOIC-8	2	7	2.5	3	13	3				
595-TL072CD	TL072CD	SOIC-8	2	7	2.5	3	13	10				
595-TL072CPWR	TL072CPWR	TSSOP-8	2	7	2.5	3	13	10				
595-TL072ID	TL072ID	SOIC-8	2	7	2.5	3	13	10				
595-TL082ACD	TL082ACD	SOIC-8	2	7	2.8	3	13	6				
595-TL082BCD	TL082BCD	SOIC-8	2	7	2.8	3	13	3				
595-TL082CD	TL082CD	SOIC-8	2	7	2.8	3	13	15				
595-TL082CPSR	TL082CPSR	SOP-8	2	7	2.8	3	13	15				
595-TL082ID	TL082ID	SOIC-8	2	7	2.8	3	13	15				
595-TL082IPWR	TL082IPWR	TSSOP-8	2	7	2.8	3	13	15				
595-TL032ACD	TL032ACD	SOIC-8	2	10	0.28	1.1	5.1	0.8				
595-TL032AIDR	TL032AIDR	SOIC-8	2	10	0.28	1.1	5.1	0.8				
595-TL032CD	TL032CD	SOIC-8	2	10	0.28	1.1	5.1	1.5				
595-TL032IDR	TL032IDR	SOIC-8	2	10	0.28	1.1	5.1	1.5				
595-TL052ACDR	TL052ACDR	SOIC-8	2	10	2.8	3	20.7	0.8				
595-TL052AID	TL052AID	SOIC-8	2	10	2.8	3	20.7	0.8				
595-TL052CD	TL052CD	SOIC-8	2	10	2.8	3	20.7	1.5				
595-TL052IDR	TL052IDR	SOIC-8	2	10	2.8	3	20.7	1.5				
595-TLC274BID	TLC274BID	SOIC-14	4	3	1.6	1.7	3.6	2				
595-TLC274CD	TLC274CD	SOIC-14	4	3	1.6	1.7	3.6	10				
595-TLC27M4ACD	TLC27M4ACD	SOIC-14	4	3	0.28	0.525	0.43	5				
595-TLC27M4AID	TLC27M4AID	SOIC-14	4	3	0.28	0.525	0.43	5				
595-TLC27M4BCD	TLC27M4BCD	SOIC-14	4	3	0.28	0.525	0.43	2				
595-TLC27M4BID	TLC27M4BID	SOIC-14	4	3	0.28	0.525	0.43	2				
595-TLC27M4CD	TLC27M4CD	SOIC-14	4	3	0.28	0.525	0.43	10				
595-TLC27M4ID	TLC27M4ID	SOIC-14	4	3	0.28	0.525	0.43	10				
595-TLC27M9CD	TLC27M9CD	SOIC-14	4	3	0.28	0.525	0.43	0.9				
595-OPA4130UA	OPA4130UA	SOIC-14	4	4.5	0.65	1	2	1				
595-TL064ACD	TL064ACD	SOIC-14	4	7	0.25	1	3.5	6				
595-TL064BCD	TL064BCD	SOIC-14	4	7	0.25	1	3.5	3				
595-TL064CD	TL064CD	SOIC-14	4	7	0.25	1	3.5	15				
595-TL064CNSR	TL064CNSR	SOP-14	4	7	0.25	1	3.5	15				