

DIODES INC. Linear Voltage Regulators



This product is RoHS compliant.

DIODES INC. LINEAR VOLTAGE REGULATORS

MOUSER STOCK NO.	Diodes Inc. Part No.	Type	Package	Max. Input Voltage	Output Voltage	Dropout Voltage	Max. Output Current	Price Each			Reel Qty.	Price Per Piece
								1	25	100		
621-AP130-15RG-7	AP130-15RG-7	Low Dropout	SC59R-3L	7V	1.5V	0.5V	0.35A				3000	
621-AP130-18SAG-7	AP130-18SAG-7	Low Dropout	SOT-23	7V	1.8V	0.5V	0.35A				3000	
621-AP130-20SAG-7	AP130-20SAG-7	Low Dropout	SOT-23	7V	2.0V	0.5V	0.35A				3000	
621-AP130-20WL-7	AP130-20WL-7	Low Dropout	SC59	7V	2.0V	0.5V	0.35A				3000	
621-AP130-30SAG-7	AP130-30SAG-7	Low Dropout	SOT-23	7V	3.0V	0.5V	0.35A				3000	
621-AP130-33YRL-13	AP130-33YRL-13	Low Dropout	SOT89R	7V	3.3V	0.5V	0.35A				2500	
621-AP130-35RG-7	AP130-35RG-7	Low Dropout	SC59R-3L	7V	3.5V	0.5V	0.35A				3000	
621-AP131-20WL-7	AP131-20WL-7	Low Dropout	SC59	7V	2.0V	0.5V	0.35A				3000	
621-AP131-28WL-7	AP131-28WL-7	Low Dropout	SC59	7V	2.8V	0.5V	0.35A				3000	
621-AP131-30WL-7	AP131-30WL-7	Low Dropout	SC59	7V	3.0V	0.5V	0.35A				3000	
621-AP131-33WL-7	AP131-33WL-7	Low Dropout	SC59	7V	3.3V	0.5V	0.35A				3000	
621-AP131-35WL-7	AP131-35WL-7	Low Dropout	SC59	7V	3.5V	0.5V	0.35A				3000	
621-AP139-25WL-7	AP139-25WL-7	Low Dropout	SC59	7V	2.5V	0.5V	0.3A				3000	
621-AP139-30WL-7	AP139-30WL-7	Low Dropout	SC59	7V	3.0V	0.5V	0.3A				3000	
621-AP139-35WL-7	AP139-35WL-7	Low Dropout	SC59	7V	3.5V	0.5V	0.3A				3000	
621-AP1184K518L-U	AP1184K518L-U	High-eff. Quasi-LDO	TO263-5L	16V/18V	1.8V	0.85V	4A				-	-
621-AP1184K533L-13	AP1184K533L-13	High-eff. Quasi-LDO	TO263-5L	16V/18V	3.3V	0.85V	4A				800	
621-AP1184K5L-13	AP1184K5L-13	High-eff. Quasi-LDO	TO263-5L	16V/18V	Adjustable	0.85V	4A				800	
621-AP1184T518L-U	AP1184T518L-U	High-eff. Quasi-LDO	TO220-5L	16V/18V	1.8V	0.85V	4A				-	-
621-AP1186K518L-U	AP1186K518L-U	High-eff. Quasi-LDO	TO263-5L	16V	1.8V	0.5V	1.5A				-	-
621-AP1186K533L-13	AP1186K533L-13	High-eff. Quasi-LDO	TO263-5L	16V	3.3V	0.5V	1.5A				800	
621-AP1186K5L-13	AP1186K5L-13	High-eff. Quasi-LDO	TO263-5L	16V	Adjustable	0.5V	1.5A				800	
621-AP1186T515L-U	AP1186T515L-U	High-eff. Quasi-LDO	TO220-5L	16V	1.5V	0.5V	1.5A				-	-
621-AP1186T525L-U	AP1186T525L-U	High-eff. Quasi-LDO	TO220-5L	16V	2.5V	0.5V	1.5A				-	-
621-AP1084D18L-13	AP1084D18L-13	Quasi-LDO	TO252-3L	12V	1.8V	1.4V	5A				2500	
621-AP1084D33L-13	AP1084D33L-13	Quasi-LDO	TO252-3L	12V	3.3V	1.4V	5A				2500	
621-AP1084D50L-13	AP1084D50L-13	Quasi-LDO	TO252-3L	12V	5.0V	1.4V	5A				2500	
621-AP1084DL-13	AP1084DL-13	Quasi-LDO	TO252-3L	12V	Adjustable	1.4V	5A				2500	
621-AP1084K18L-13	AP1084K18L-13	Quasi-LDO	TO263-3L	12V	1.8V	1.4V	5A				800	
621-AP1084K33L-13	AP1084K33L-13	Quasi-LDO	TO263-3L	12V	3.3V	1.4V	5A				800	
621-AP1084K50L-13	AP1084K50L-13	Quasi-LDO	TO263-3L	12V	5.0V	1.4V	5A				800	
621-AP1084KL-13	AP1084KL-13	Quasi-LDO	TO263-3L	12V	Adjustable	1.4V	5A				800	
621-AP1084T33L-U	AP1084T33L-U	Quasi-LDO	TO220-3L	12V	3.3V	1.4V	5A				-	-
621-AP1084TL-U	AP1084TL-U	Quasi-LDO	TO220-3L	12V	Adjustable	1.4V	5A				-	-
621-AP1086D15L-13	AP1086D15L-13	Quasi-LDO	TO252-3L	12V	1.5V	1.4V	1.5A				2500	
621-AP1086D18L-13	AP1086D18L-13	Quasi-LDO	TO252-3L	12V	1.8V	1.4V	1.5A				2500	
621-AP1086D25L-13	AP1086D25L-13	Quasi-LDO	TO252-3L	12V	2.5V	1.4V	1.5A				2500	
621-AP1086D33L-13	AP1086D33L-13	Quasi-LDO	TO252-3L	12V	3.3V	1.4V	1.5A				2500	
621-AP1086DL-13	AP1086DL-13	Quasi-LDO	TO252-3L	12V	Adjustable	1.4V	1.5A				2500	
621-AP1086K18L-13	AP1086K18L-13	Quasi-LDO	TO263-3L	12V	1.8V	1.4V	1.5A				800	
621-AP1086K33L-13	AP1086K33L-13	Quasi-LDO	TO263-3L	12V	3.3V	1.4V	1.5A				800	
621-AP1086KL-13	AP1086KL-13	Quasi-LDO	TO263-3L	12V	Adjustable	1.4V	1.5A				800	
621-AP1086T33L-U	AP1086T33L-U	Quasi-LDO	TO220-3L	12V	3.3V	1.4V	1.5A				-	-
621-AP1086TL-U	AP1086TL-U	Quasi-LDO	TO220-3L	12V	Adjustable	1.4V	1.5A				-	-
621-AP1115AY18L-13	AP1115AY18L-13	Quasi-LDO	SOT-89	18V	1.8V	1.3V	600mA				2500	
621-AP1115AY33L-13	AP1115AY33L-13	Quasi-LDO	SOT-89	18V	3.3V	1.3V	600mA				2500	
621-AP1115AYL-13	AP1115AYL-13	Quasi-LDO	SOT-89	18V	Adjustable	1.3V	600mA				2500	
621-AP1115BY18L-13	AP1115BY18L-13	Quasi-LDO	SOT-89	18V	1.8V	1.3V	600mA				2500	
621-AP1115BY33L-13	AP1115BY33L-13	Quasi-LDO	SOT-89	18V	3.3V	1.3V	600mA				2500	
621-AP1115BYL-13	AP1115BYL-13	Quasi-LDO	SOT-89	18V	Adjustable	1.3V	600mA				2500	
621-AP1117D15L-13	AP1117D15L-13	Quasi-LDO	TO252-3L	12V	1.5V	1.4V	1A				2500	
621-AP1117D18L-13	AP1117D18L-13	Quasi-LDO	TO252-3L	12V	1.8V	1.4V	1A				2500	
621-AP1117D25L-13	AP1117D25L-13	Quasi-LDO	TO252-3L	12V	2.5V	1.4V	1A				2500	
621-AP1117D33L-13	AP1117D33L-13	Quasi-LDO	TO252-3L	12V	3.3V	1.4V	1A				2500	
621-AP1117DL-13	AP1117DL-13	Quasi-LDO	TO252-3L	12V	Adjustable	1.4V	1A				2500	
621-AP1117E15G-13	AP1117E15G-13	Quasi-LDO	SOT223-3L	12V	1.5V	1.4V	1A				2500	
621-AP1117E18G-13	AP1117E18G-13	Quasi-LDO	SOT223-3L	12V	1.8V	1.4V	1A				2500	
621-AP1117E25G-13	AP1117E25G-13	Quasi-LDO	SOT223-3L	12V	2.5V	1.4V	1A				2500	
621-AP1117E33G-13	AP1117E33G-13	Quasi-LDO	SOT223-3L	12V	3.3V	1.4V	1A				2500	
621-AP1117E50G-13	AP1117E50G-13	Quasi-LDO	SOT223-3L	12V	5.0V	1.4V	1A				2500	
621-AP1117EG-13	AP1117EG-13	Quasi-LDO	SOT223-3L	12V	Adjustable	1.4V	1A				2500	
621-AP1117K18L-13	AP1117K18L-13	Quasi-LDO	TO263-3L	12V	1.8V	1.4V	1A				800	
621-AP1117K33L-13	AP1117K33L-13	Quasi-LDO	TO263-3L	12V	3.3V	1.4V	1A				800	
621-AP1117KL-13	AP1117KL-13	Quasi-LDO	TO263-3L	12V	Adjustable	1.4V	1A				800	
621-AP1117T33L-U	AP1117T33L-U	Quasi-LDO	TO220-3L	12V	3.3V	1.4V	1A				-	-
621-AP1117TL-U	AP1117TL-U	Quasi-LDO	TO220-3L	12V	Adjustable	1.4V	1A				-	-
621-AP1117Y33L-13	AP1117Y33L-13	Quasi-LDO	SOT89-3L	12V	3.3V	1.4V	1A				2500	
621-AP1117YL-13	AP1117YL-13	Quasi-LDO	SOT89-3L	12V	Adjustable	1.4V	1A				2500	
621-AP1121ASL-13	AP1121ASL-13	Quasi-LDO	SOP-8L	18V	3.3V/2.5V	1.3V	1A				2500	
621-AP1122EG-13	AP1122EG-13	Quasi-LDO	SOT223-3L	12V	1.2V	1.3V	1A				2500	
621-AP1122YL-13	AP1122YL-13	Quasi-LDO	SOT89-3L	12V	1.2V	1.3V	1A				2500	