

TEXAS INSTRUMENTS Power Management ICs

SINGLE CHANNEL LDOs (CONT.)

Products may be RoHS compliant. Check mouser.com for RoHS status.

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	Texas Instruments Part No.	Package	Iout	Vdo (Typ) (mV)	Iq (Typ) (mA)	Vin (Min.)	Vin (Max.)	Accuracy (%)	Output Capacitor (µF)	Output Capacitor Type	Price Each			
											1	25	100	250
595-TPS77030DBVT	TPS77030DBVT	SOT-23-5	0.05	57	0.017	3.057	10	3	4.7	Tantalum				
595-TPS77033DBVR	TPS77033DBVR	SOT-23-5	0.05	48	0.017	3.348	10	3	4.7	Tantalum				
595-TPS77050DBVT	TPS77050DBVT	SOT-23-5	0.05	35	0.017	5.035	10	3	4.7	Tantalum				
595-TPS79718DCKR	TPS79718DCKR	SC70-5	0.05	105	0.0012	1.8	5.5	4	0.47	Ceramic				
595-TPS79730DCKR	TPS79730DCKR	SC70-5	0.05	110	0.0012	1.8	5.5	4	0.47	Ceramic				
595-TPS79733DCKR	TPS79733DCKR	SC70-5	0.05	105	0.0012	1.8	5.5	4	0.47	Ceramic				
595-TPS71501DCKR	TPS71501DCKR	SC70-5	0.05	415	0.0032	2.5	24	4	0.47	Ceramic				
595-TPS71518DCKR	TPS71518DCKR	SC70-5	0.05	415	0.0032	2.5	24	4	0.47	Ceramic				
595-TPS71519DCKR	TPS71519DCKR	SC70-5	0.05	415	0.0032	2.5	24	4	0.47	Ceramic				
595-TPS71523DCKR	TPS71523DCKR	SC70-5	0.05	415	0.0032	2.5	24	4	0.47	Ceramic				
595-TPS71525DCKR	TPS71525DCKR	SC70-5	0.05	415	0.0032	2.5	24	4	0.47	Ceramic				
595-TPS71530DCKR	TPS71530DCKR	SC70-5	0.05	415	0.0032	2.5	24	4	0.47	Ceramic				
595-TPS71533DCKR	TPS71533DCKR	SC70-5	0.05	415	0.0032	2.5	24	4	0.47	Ceramic				
595-TPS715345DCKR	TPS715345DCKR	SC70-5	0.05	415	0.0032	2.5	24	4	0.47	Ceramic				
595-TPS71550DCKR	TPS71550DCKR	SC70-5	0.05	415	0.0032	2.5	24	4	0.47	Ceramic				
595-TPS715A01DRBT	TPS715A01DRBT	SON-8	0.08	670	0.0032	2.5	24	4	0.47	Ceramic				
595-TPS715A33DRVR	TPS715A33DRVR	SON-6	0.08	670	0.0032	2.5	24	4	0.47	Ceramic				
595-REG101NA-5/250	REG101NA-5/250	REG101NA-5/250	0.1	60	0.4	1.8	10	1.5	-	Capacitor Free				
595-REG101UA-2.5	REG101UA-2.5	SOIC-8	0.1	60	0.4	1.8	10	1.5	-	Capacitor Free				
595-TPS76201DBVR	TPS76201DBVR	SOT-23-5	0.1	100	0.022	2.7	10	-	4.7	Tantalum				
595-TPS76901DBVR	TPS76901DBVR	SOT-23-5	0.1	71	0.018	2.7	10	3	4.7	Tantalum				
595-TPS76912DBVR	TPS76912DBVR	SOT-23-5	0.1	71	0.018	2.7	10	3	4.7	Tantalum				
595-TPS76912DBVT	TPS76912DBVT	SOT-23-5	0.1	71	0.018	2.7	10	3	4.7	Tantalum				
595-TPS76915DBVT	TPS76915DBVT	SOT-23-5	0.1	71	0.018	2.7	10	3	4.7	Tantalum				
595-TPS76918DBVR	TPS76918DBVR	SOT-23-5	0.1	71	0.018	2.7	10	3	4.7	Tantalum				
595-TPS76925DBVR	TPS76925DBVR	SOT-23-5	0.1	71	0.018	2.7	10	3	4.7	Tantalum				
595-TPS76933DBVR	TPS76933DBVR	SOT-23-5	0.1	98	0.018	3.398	10	3	4.7	Tantalum				
595-TPS78918DBVT	TPS78918DBVT	SOT-23-5	0.1	115	0.018	2.7	13.5	-	4.7	Tantalum				
595-TPS78925DBVT	TPS78925DBVT	SOT-23-5	0.1	115	0.018	2.7	13.5	-	4.7	Tantalum				
595-TPS79101DBVR	TPS79101DBVR	SOT-23-6	0.1	38	0.185	2.7	5.5	2	1	Ceramic				
595-TPS79118DBVR	TPS79118DBVR	SOT-23-5	0.1	38	0.185	2.7	5.5	2	1	Ceramic				
595-TPS79133DBVR	TPS79133DBVR	SOT-23-5	0.1	50	0.185	2.7	5.5	2	1	Ceramic				
595-TPS79133DBVT	TPS79133DBVT	SOT-23-5	0.1	50	0.185	2.7	5.5	2	1	Ceramic				
595-TPS79147DBVT	TPS79147DBVT	SOT-23-5	0.1	38	0.185	2.7	5.5	2	1	Ceramic				
595-TPS79201DBVR	TPS79201DBVR	SOT-23-6	0.1	55	0.185	2.7	5.5	2	1	Ceramic				
595-TPS79225DBVR	TPS79225DBVR	SOT-23-5	0.1	55	0.185	2.7	5.5	2	1	Ceramic				
595-TPS79230DBVR	TPS79230DBVR	SOT-23-5	0.1	55	0.185	2.7	5.5	2	1	Ceramic				
595-TPS79230DBVT	TPS79230DBVT	SOT-23-5	0.1	55	0.185	2.7	5.5	2	1	Ceramic				
595-TPS76130DBVT	TPS76130DBVT	SOT-23-5	0.1	170	0.09	3.35	16	2	4.7	Tantalum				
595-TPS76133DBVR	TPS76133DBVR	SOT-23-5	0.1	170	0.09	3.68	16	2	4.7	Tantalum				
595-TPS76150DBVR	TPS76150DBVR	SOT-23-5	0.1	170	0.09	5.38	16	2	4.7	Tantalum				
595-TPS76928DBVT	TPS76928DBVT	SOT-23-5	0.1	122	0.018	2.922	10	3	4.7	Tantalum				
595-LP2981-28DBVR	LP2981-28DBVR	SOT-23-5	0.1	200	0.6	2.2	16	1.25	4.7	Tantalum				
595-LP2981-30DBVR	LP2981-30DBVR	SOT-23-5	0.1	200	0.6	2.2	16	1.25	4.7	Tantalum				
595-LP2981-33DBVR	LP2981-33DBVR	SOT-23-5	0.1	200	0.6	2.2	16	1.25	4.7	Tantalum				
595-LP2981A-28DBVR	LP2981A-28DBVR	SOT-23-5	0.1	200	0.6	2.2	16	0.75	4.7	Tantalum				
595-LP2981A-28DBVT	LP2981A-28DBVT	SOT-23-5	0.1	200	0.6	2.2	16	0.75	4.7	Tantalum				
595-LP2981A-30DBVR	LP2981A-30DBVR	SOT-23-5	0.1	200	0.6	2.2	16	0.75	4.7	Tantalum				
595-LP2981A-33DBVR	LP2981A-33DBVR	SOT-23-5	0.1	200	0.6	2.2	16	0.75	4.7	Tantalum				
595-TPS73101DBVR	TPS73101DBVR	SOT-23-5	0.15	30	0.4	1.7	5.5	1	-	Capacitor Free				
595-TPS73101DBVT	TPS73101DBVT	SOT-23-5	0.15	30	0.4	1.7	5.5	1	-	Capacitor Free				
595-TPS731125DBVT	TPS731125DBVT	SOT-23-5	0.15	30	0.4	1.7	5.5	-	-	Capacitor Free				
595-TPS73118DBVT	TPS73118DBVT	SOT-23-5	0.15	30	0.4	1.9	5.5	1	-	Capacitor Free				
595-TPS73125DBVT	TPS73125DBVT	SOT-23-5	0.15	30	0.4	2.6	5.5	1	-	Capacitor Free				
595-TPS73133DBVT	TPS73133DBVT	SOT-23-5	0.15	30	0.4	3.4	5.5	1	-	Capacitor Free				
595-TPS77133DGK	TPS77133DGK	MSOP-8	0.15	115	0.09	3.415	10	2	10	Tantalum				
595-TPS78330DDCT	TPS78330DDCT	TSOT-23-5	0.15	130	0.0005	2.2	5.5	2	1	Ceramic				
595-TPS71709DSE	TPS71709DSE	SON-6	0.15	170	0.05	2.5	6.5	3	1	Ceramic				
595-TPS71709DSE	TPS71709DSE	SON-6	0.15	170	0.05	2.5	6.5	3	1	Ceramic				
595-TPS71710DCKR	TPS71710DCKR	SC70-5	0.15	170	0.05	2.5	6.5	3	1	Ceramic				
595-TPS71713DCKR	TPS71713DCKR	SC70-5	0.15	170	0.05	2.5	6.5	3	1	Ceramic				
595-TPS71715DCKR	TPS71715DCKR	SC70-5	0.15	170	0.05	2.5	6.5	3	1	Ceramic				
595-TPS71719DCKR	TPS71719DCKR	SC70-5	0.15	170	0.05	2.5	6.5	3	1	Ceramic				
595-TPS71725DCKR	TPS71725DCKR	SC70-5	0.15	170	0.05	2.5	6.5	3	1	Ceramic				
595-TPS71730DCKR	TPS71730DCKR	SC70-5	0.15	170	0.05	2.5	6.5	3	1	Ceramic				
595-TPS71733DSE	TPS71733DSE	SON-6	0.15	170	0.05	2.5	6.5	3	1	Ceramic				
595-TPS71733DSE	TPS71733DSE	SON-6	0.15	170	0.05	2.5	6.5	3	1	Ceramic				
595-TPS71750DSE	TPS71750DSE	WSO-6	0.15	170	0.05	2.5	6.5	3	1	Ceramic				
595-TPS72101DBVT	TPS72101DBVT	SOT-23-5	0.15	150	0.09	1.8	5.5	3	0.1	Ceramic				
595-TPS72116DBVT	TPS72116DBVT	SOT-23-5	0.15	150	0.09	1.9	5.5	3	0.1	Ceramic				
595-TPS72118DBVT	TPS72118DBVT	SOT-23-5	0.15	150	0.09	2.1	5.5	3	0.1	Ceramic				
595-TPS76301DBVR	TPS76301DBVR	SOT-23-5	0.15	180	0.085	2.7	10	3	4.7	Tantalum				
595-TPS76316DBVR	TPS76316DBVR	SOT-23-5	0.15	180	0.085	2.7	10	3	4.7	Tantalum				
595-TPS76318DBVT	TPS76318DBVT	SOT-23-5	0.15	180	0.085	2.7	10	3	4.7	Tantalum				
595-TPS76350DBVR	TPS76350DBVR	SOT-23-5	0.15	180	0.085	5.18	10	3	4.7	Tantalum				
595-TPS78833DBVR	TPS78833DBVR	SOT-23-5	0.15	150	0.018	2.7	10	3	4.7	Ceramic				
595-SN105125DBVR	SN105125DBVR	SOT-23-5	0.15	1000	0.15	3	5.25	2	1	Ceramic				
595-TL750L05CD	TL750L05CD	SOIC-8	0.15	600	1	6	26	4	10	Tantalum				
595-TL750L05CLP	TL750L05CLP	TO-92-3	0.15	600	1	6	26	4	10	Tantalum				
595-TL750L08CD	TL750L08CD	SOIC-8	0.15	600	1	9	26	4	10	Tantalum				
595-TL750L10CD	TL750L10CD	SOIC-8	0.15	600	1	11	26	4	10	Tantalum				
595-TL750L12CD	TL750L12CD	SOIC-8	0.15	600	1	13	26	4	10	Tantalum				
595-TL751L05CD	TL751L05CD	SOIC-8	0.15	600	1	6	26	4	10	Tantalum				
595-TL751L10CD	TL751L10CD	SOIC-8	0.15	600	1	11	26	4	10	Tantalum				
595-TL751L10CP	TL751L10CP	PDIP-8	0.15	600	1	11	26	4	10	Tantalum				
595-TPS76325DBVR	TPS76325DBVR	SOT-23-5	0.15	360	0.085	2.7	10	3	4.7	Tantalum				
595-TPS76325DBVT	TPS76325DBVT	SOT-23-5	0.15	360	0.085	2.7	10	3	4.7	Tantalum				
595-TPS76328DBVT	TPS76328DBVT	SOT-23-5	0.15	339	0.085	3.149	10	3	4.7	Tantalum				