

TEXAS INSTRUMENTS Power Management ICs

Products may be RoHS compliant. Check mouser.com for RoHS status.

SINGLE CHANNEL LDOs (CONT.)

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	Texas Instruments Part No.	Package	Iout (Max.)	Vdo (Typ) (mV)	Iq (Typ) (mA)	Vin (Min.)	Vin (Max.)	Accuracy (%)	Output Capacitor (µF)	Output Capacitor Type	Price Each			
											1	25	100	250
595-TPS76330DBVT	TPS76330DBVT	SOT-23-5	0.15	322	0.085	3.322	10	3	4.7	Tantalum				
595-TPS76333DBVVR	TPS76333DBVVR	SOT-23-5	0.15	300	0.085	3.3	10	3	4.7	Tantalum				
595-TPS76433DBVVR	TPS76433DBVVR	SOT-23-5	0.15	300	0.085	3.3	10	3	4.7	Tantalum				
595-TPS728185315DRVVT	TPS728185315DRVVT	SON-6	0.2	0.23	0.045	2.7	6.5	3	-	Ceramic				
595-TPS73001DBVT	TPS73001DBVT	SOT-23-6	0.2	120	0.18	2.7	5.5	2	2.2	Ceramic				
595-TPS73018DBVT	TPS73018DBVT	SOT-23-5	0.2	120	0.18	2.7	5.5	2	2.2	Ceramic				
595-TPS79301DBVVR	TPS79301DBVVR	SOT-23-6	0.2	77	0.18	2.7	5.5	2	2.2	Ceramic				
595-TPS79318DBVVR	TPS79318DBVVR	SOT-23-5	0.2	77	0.18	2.7	5.5	2	2.2	Ceramic				
595-TPS79325DBVVR	TPS79325DBVVR	SOT-23-5	0.2	77	0.18	2.7	5.5	2	2.2	Ceramic				
595-TPS79330DBVVR	TPS79330DBVVR	SOT-23-5	0.2	112	0.18	2.7	5.5	2	2.2	Ceramic				
595-TPS79333DBVVR	TPS79333DBVVR	SOT-23-5	0.2	102	0.18	2.7	5.5	2	2.2	Ceramic				
595-TPS79901DDCR	TPS79901DDCR	TO/SOT-5	0.2	90	0.04	2.7	6.5	2	2.2	Ceramic				
595-TPS79901DRVVT	TPS79901DRVVT	SON-6	0.2	90	0.04	2.7	6.5	2	2.2	Ceramic				
595-TPS79912YZUT	TPS79912YZUT	DSBGA-5	0.2	100	0.04	2.7	6.5	2	2.2	Ceramic				
595-TPS79913DDCR	TPS79913DDCR	TO/SOT-5	0.2	100	0.04	2.7	6.5	2	2.2	Ceramic				
595-TPS79915DDCT	TPS79915DDCT	TO/SOT-5	0.2	100	0.04	2.7	6.5	2	2.2	Ceramic				
595-TPS79918DDCR	TPS79918DDCR	TO/SOT-5	0.2	100	0.04	2.7	6.5	2	2.2	Ceramic				
595-TPS799195DRVVR	TPS799195DRVVR	SON-6	0.2	100	0.04	2.7	6.5	2	2.2	Ceramic				
595-TPS79920YZUT	TPS79920YZUT	DSBGA-5	0.2	100	0.04	2.7	6.5	2	2.2	Ceramic				
595-TPS79925DDCT	TPS79925DDCT	TO/SOT-5	0.2	100	0.04	2.7	6.5	2	2.2	Ceramic				
595-TPS799275YZUR	TPS799275YZUR	DSBGA-5	0.2	100	0.04	2.7	6.5	2	2.2	Ceramic				
595-TPS79927DDCR	TPS79927DDCR	TO/SOT-5	0.2	100	0.04	2.7	6.5	2	2.2	Ceramic				
595-TPS79927DRVVT	TPS79927DRVVT	SON-6	0.2	100	0.04	2.7	6.5	2	2.2	Ceramic				
595-TPS799285YZUR	TPS799285YZUR	DSBGA-5	0.2	100	0.04	2.7	6.5	2	2.2	Ceramic				
595-TPS79928DRVVT	TPS79928DRVVT	SON-6	0.2	100	0.04	2.7	6.5	2	2.2	Ceramic				
595-TPS79928YZUT	TPS79928YZUT	DSBGA-5	0.2	100	0.04	2.7	6.5	2	2.2	Ceramic				
595-TPS79930DDCT	TPS79930DDCT	TO/SOT-5	0.2	100	0.04	2.7	6.5	2	2.2	Ceramic				
595-TPS79933DDCR	TPS79933DDCR	TO/SOT-5	0.2	90	0.04	2.7	6.5	2	2.2	Ceramic				
595-TPS79933DRVVR	TPS79933DRVVR	SON-6	0.2	90	0.04	2.7	6.5	2	2.2	Ceramic				
595-TPS79945YZUR	TPS79945YZUR	DSBGA-5	0.2	100	0.04	2.7	6.5	2	2.2	Ceramic				
595-TPS73025DBVT	TPS73025DBVT	SOT-23-5	0.2	120	0.18	2.7	5.5	2	2.2	Ceramic				
595-TPS730285YZQR	TPS730285YZQR	DSBGA-5	0.2	120	0.18	2.7	5.5	2	2.2	Ceramic				
595-TPS73028DBVT	TPS73028DBVT	SOT-23-5	0.2	120	0.18	2.7	5.5	2	2.2	Ceramic				
595-TPS73028YZQR	TPS73028YZQR	DSBGA-5	0.2	120	0.18	2.7	5.5	2	2.2	Ceramic				
595-TPS73030DBVT	TPS73030DBVT	SOT-23-5	0.2	120	0.18	2.7	5.5	2	2.2	Ceramic				
595-TPS73033DBVVR	TPS73033DBVVR	SOT-23-5	0.2	120	0.18	2.7	5.5	2	2.2	Ceramic				
595-TPS793285DBVVR	TPS793285DBVVR	SOT-23-5	0.2	120	0.18	2.7	5.5	2	2.2	Ceramic				
595-TPS79328DBVVR	TPS79328DBVVR	SOT-23-5	0.2	120	0.18	2.7	5.5	2	2.2	Ceramic				
595-TPS79328YZQT	TPS79328YZQT	DSBGA-5	0.2	120	0.18	2.7	5.5	2	2.2	Ceramic				
595-TPS72301DBVT	TPS72301DBVT	SOT-23-5	0.2	280	0.13	-10	-2.7	2	2.2	Ceramic				
595-TPS72325DBVT	TPS72325DBVT	SOT-23-5	0.2	280	0.13	-10	-3	2	2.2	Ceramic				
595-TPS73201DBVT	TPS73201DBVT	SOT-23-5	0.25	40	0.4	1.7	5.5	1	-	Capacitor Free				
595-TPS73201DCQ	TPS73201DCQ	SOT-223-6	0.25	40	0.4	1.7	5.5	1	-	Capacitor Free				
595-TPS73201DRBT	TPS73201DRBT	SON-8	0.25	40	0.4	1.7	5.5	1	-	Capacitor Free				
595-TPS73218DCQR	TPS73218DCQR	SOT-223-6	0.25	40	0.4	1.95	5.5	1	-	Capacitor Free				
595-TPS73233DBVT	TPS73233DBVT	SOT-23-5	0.25	40	0.4	3.45	5.5	1	-	Capacitor Free				
595-TPS73233DCQ	TPS73233DCQ	SOT-223-6	0.25	40	0.4	3.45	5.5	1	-	Capacitor Free				
595-REG102GA-2.85	REG102GA-2.85	SOT-223-6	0.25	150	0.4	1.8	12	1.5	-	Capacitor Free				
595-REG102UA-3	REG102UA-3	SOIC-8	0.25	150	0.4	1.8	12	1.5	-	Capacitor Free				
595-TPS7201QD	TPS7201QD	SOIC-8	0.25	190	0.18	310	-10	-	-	Tantalum				
595-TPS7250QD	TPS7250QD	SOIC-8	0.25	190	0.18	5.41	10	2	10	Tantalum				
595-TPS76650DR	TPS76650DR	SOIC-8	0.25	140	0.033	5.14	10	-	4.7	Tantalum				
595-TPS77333DGK	TPS77333DGK	MSOP-8	0.25	200	0.09	3.5	10	2	10	Tantalum				
595-TPS79401DCQ	TPS79401DCQ	SOT-223-6	0.25	145	0.172	2.7	5.5	3	2.2	Ceramic				
595-TPS79401DGNT	TPS79401DGNT	MSOP PowerPAD-8	0.25	145	0.172	2.7	5.5	3	2.2	Ceramic				
595-TPS79418DGNT	TPS79418DGNT	MSOP PowerPAD-8	0.25	145	0.172	2.7	5.5	3	2.2	Ceramic				
595-TPS79425DCQ	TPS79425DCQ	SOT-223-6	0.25	145	0.172	2.7	5.5	3	2.2	Ceramic				
595-TPS79425DGNT	TPS79425DGNT	MSOP PowerPAD-8	0.25	145	0.172	2.7	5.5	3	2.2	Ceramic				
595-TPS79428DGNT	TPS79428DGNT	MSOP PowerPAD-8	0.25	155	0.172	2.7	5.5	3	2.2	Ceramic				
595-TPS79433DCQR	TPS79433DCQR	SOT-223-6	0.25	145	0.172	2.7	5.5	3	2.2	Ceramic				
595-TPS79433DGNR	TPS79433DGNR	MSOP PowerPAD-8	0.25	145	0.172	2.7	5.5	3	2.2	Ceramic				
595-TPS76628D	TPS76628D	SOIC-8	0.25	310	0.033	3.11	10	-	4.7	Tantalum				
595-TPS76633D	TPS76633D	SOIC-8	0.25	230	0.033	3.53	10	-	4.7	Tantalum				
595-TPS73601DBVT	TPS73601DBVT	SOT-23-5	0.4	75	0.3	1.7	5.5	1	-	Capacitor Free				
595-TPS73601DCQ	TPS73601DCQ	SOT-223-6	0.4	75	0.3	1.7	5.5	1	-	Capacitor Free				
595-TPS73601DCQR	TPS73601DCQR	SOT-223-6	0.4	75	0.3	1.7	5.5	1	-	Capacitor Free				
595-TPS73601DRBR	TPS73601DRBR	SON-8	0.4	75	0.3	1.7	5.5	1	-	Capacitor Free				
595-TPS736125DRBT	TPS736125DRBT	SON-8	0.4	75	0.3	1.7	5.5	1	-	Capacitor Free				
595-TPS73625DBVT	TPS73625DBVT	SOT-23-5	0.4	75	0.3	2.7	5.5	1	-	Capacitor Free				
595-TPS73625DCQ	TPS73625DCQ	SOT-223-6	0.4	75	0.3	2.7	5.5	1	-	Capacitor Free				
595-TPS73633DBVT	TPS73633DBVT	SOT-23-5	0.4	75	0.3	3.5	5.5	1	-	Capacitor Free				
595-REG113NA-3.3/3K	REG113NA-3.3/3K	SOT-23-5	0.4	250	0.4	1.8	10	1.5	-	Capacitor Free				
595-REG113NA-5/3K	REG113NA-5/3K	SOT-23-5	0.4	250	0.4	1.8	10	1.5	-	Capacitor Free				
595-TPS79501DCQ	TPS79501DCQ	SOT-223-6	0.5	105	0.265	2.7	5.5	3	1	Ceramic				
595-TPS79501DRBR	TPS79501DRBR	SON-8	0.5	105	0.265	2.7	5.5	3	1	Ceramic				
595-TPS79518DCQ	TPS79518DCQ	SOT-223-6	0.5	105	0.265	2.7	5.5	3	1	Ceramic				
595-TPS79530DCQ	TPS79530DCQ	SOT-223-6	0.5	110	0.265	2.7	5.5	3	1	Ceramic				
595-TPS79533DCQ	TPS79533DCQ	SOT-223-6	0.5	105	0.265	2.7	5.5	3	1	Ceramic				
595-TPS7301QDR	TPS7301QDR	SOIC-8	0.5	146	0.29	2.47	10	-	10	Tantalum				
595-TPS7350QD	TPS7350QD	SOIC-8	0.5	146	0.29	5.33	10	-	10	Tantalum				
595-TPS77501PWP	TPS77501PWP	HTSSOP-20	0.5	169	0.087	2.7	10	2	10	Tantalum				
595-TPS77533D	TPS77533D	SOIC-8	0.5	169	0.087	3.469	10	2	10	Tantalum				
595-TPS77601D	TPS77601D	SOIC-8	0.5	169	0.087	2.7	10	2	10	Tantalum				
595-TPS77618D	TPS77618D	SOIC-8	0.5	169	0.087	2.7	10	2	10	Tantalum				
595-TPS77633D	TPS77633D	SOIC-8	0.5	169	0.087	3.469	10	2	10	Tantalum				
595-TPS77633PWP	TPS77633PWP	HTSSOP-20	0.5	169	0.087	3.469	10	2	10	Tantalum				
595-UCC284DP-5	UCC284DP-5	SOIC-8	0.5	200	0.2	-5.2	-16	-	4.7	Tantalum				
595-UCC384DP-12	UCC384DP-12	SOIC-8	0.5	150	0.2	-12.05	-15	2.5	4.7	Tantalum				