


# DIODES INC. Zener Diodes



RoHS Compliant This product is RoHS compliant.

## DIODES INC. ZENER DIODES - SMD



RoHS Compliant

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Diodes Inc. Part No.	Case Type	Nom. Volt. (V)	Power Rating (W)	Test Curr. (mA)	Price Each			
						1	10	100	500
<b>BZT Series; SOD-123</b>									
621-BZT52C2V4-F	BZT52C2V4-F	SOD-123	2.4	0.5	5				
621-BZT52C2V7-F	BZT52C2V7-F	SOD-123	2.7	0.5	5				
621-BZT52C3V0-F	BZT52C3V0-F	SOD-123	3	0.5	5				
621-BZT52C3V3-F	BZT52C3V3-F	SOD-123	3.3	0.5	5				
621-BZT52C3V6-F	BZT52C3V6-F	SOD-123	3.6	0.5	5				
621-BZT52C3V9-F	BZT52C3V9-F	SOD-123	3.9	0.5	5				
621-BZT52C4V3-F	BZT52C4V3-F	SOD-123	4.3	0.5	5				
621-BZT52C4V7-F	BZT52C4V7-F	SOD-123	4.7	0.5	5				
621-BZT52C5V1-F	BZT52C5V1-F	SOD-123	5.1	0.5	5				
621-BZT52C5V6-F	BZT52C5V6-F	SOD-123	5.6	0.5	5				
621-BZT52C6V2-F	BZT52C6V2-F	SOD-123	6.2	0.5	5				
621-BZT52C6V8-F	BZT52C6V8-F	SOD-123	6.8	0.5	5				
621-BZT52C7V5-F	BZT52C7V5-F	SOD-123	7.5	0.5	5				
621-BZT52C8V2-F	BZT52C8V2-F	SOD-123	8.2	0.5	5				
621-BZT52C9V1-F	BZT52C9V1-F	SOD-123	9.1	0.5	5				
621-BZT52C10-F	BZT52C10-F	SOD-123	10	0.5	5				
621-BZT52C11-F	BZT52C11-F	SOD-123	11	0.5	5				
621-BZT52C12-F	BZT52C12-F	SOD-123	12	0.5	5				
621-BZT52C15-F	BZT52C15-F	SOD-123	15	0.5	5				
621-BZT52C16-F	BZT52C16-F	SOD-123	16	0.5	5				
621-BZT52C18-F	BZT52C18-F	SOD-123	18	0.5	5				
621-BZT52C20-F	BZT52C20-F	SOD-123	20	0.5	5				
621-BZT52C24-F	BZT52C24-F	SOD-123	24	0.5	5				
621-BZT52C27-F	BZT52C27-F	SOD-123	27	0.5	5				
621-BZT52C33-F	BZT52C33-F	SOD-123	33	0.5	2				
<b>MMSZ Series; SOD-123</b>									
621-MMSZ5221B-F	MMSZ5221B-F	SOD-123	2.4	0.5	20				
621-MMSZ5223B-F	MMSZ5223B-F	SOD-123	2.7	0.5	20				
621-MMSZ5225B-F	MMSZ5225B-F	SOD-123	3	0.5	20				
621-MMSZ5226B-F	MMSZ5226B-F	SOD-123	3.3	0.5	20				
621-MMSZ5227B-F	MMSZ5227B-F	SOD-123	3.6	0.5	20				
621-MMSZ5228B-F	MMSZ5228B-F	SOD-123	3.9	0.5	20				
621-MMSZ5229B-F	MMSZ5229B-F	SOD-123	4.3	0.5	20				
621-MMSZ5230B-F	MMSZ5230B-F	SOD-123	4.7	0.5	20				
621-MMSZ5231B-F	MMSZ5231B-F	SOD-123	5.1	0.5	20				
621-MMSZ5232B-F	MMSZ5232B-F	SOD-123	5.6	0.5	20				
621-MMSZ5234B-F	MMSZ5234B-F	SOD-123	6.2	0.5	20				
621-MMSZ5235B-F	MMSZ5235B-F	SOD-123	6.8	0.5	20				
621-MMSZ5236B-F	MMSZ5236B-F	SOD-123	7.5	0.5	20				
621-MMSZ5237B-F	MMSZ5237B-F	SOD-123	8.2	0.5	20				
621-MMSZ5239B-F	MMSZ5239B-F	SOD-123	9.1	0.5	20				
621-MMSZ5240B-F	MMSZ5240B-F	SOD-123	10	0.5	20				
621-MMSZ5241B-F	MMSZ5241B-F	SOD-123	11	0.5	20				
621-MMSZ5242B-F	MMSZ5242B-F	SOD-123	12	0.5	20				
621-MMSZ5243B-F	MMSZ5243B-F	SOD-123	13	0.5	9.5				
621-MMSZ5245B-F	MMSZ5245B-F	SOD-123	15	0.5	8.5				
621-MMSZ5246B-F	MMSZ5246B-F	SOD-123	16	0.5	7.8				
621-MMSZ5248B-F	MMSZ5248B-F	SOD-123	18	0.5	7				
621-MMSZ5250B-F	MMSZ5250B-F	SOD-123	20	0.5	6.2				
621-MMSZ5251B-F	MMSZ5251B-F	SOD-123	22	0.5	5.6				
621-MMSZ5252B-F	MMSZ5252B-F	SOD-123	24	0.5	5.2				
621-MMSZ5254B-F	MMSZ5254B-F	SOD-123	27	0.5	5				
621-MMSZ5255B-F	MMSZ5255B-F	SOD-123	28	0.5	4.5				
621-MMSZ5256B-F	MMSZ5256B-F	SOD-123	30	0.5	4.2				
621-MMSZ5257B-F	MMSZ5257B-F	SOD-123	33	0.5	3.8				
621-MMSZ5258B-F	MMSZ5258B-F	SOD-123	36	0.5	3.4				
621-MMSZ5259B-F	MMSZ5259B-F	SOD-123	39	0.5	3.2				
<b>BZT Series; SOD-323</b>									
621-BZT52C2V4S-F	BZT52C2V4S-F	SOD-323	2.4	0.2	5				
621-BZT52C2V7S-F	BZT52C2V7S-F	SOD-323	2.7	0.2	5				
621-BZT52C3V0S-F	BZT52C3V0S-F	SOD-323	3	0.2	5				
621-BZT52C3V3S-F	BZT52C3V3S-F	SOD-323	3.3	0.2	5				
621-BZT52C3V6S-F	BZT52C3V6S-F	SOD-323	3.6	0.2	5				
621-BZT52C3V9S-F	BZT52C3V9S-F	SOD-323	3.9	0.2	5				
621-BZT52C4V3S-F	BZT52C4V3S-F	SOD-323	4.3	0.2	5				
621-BZT52C4V7S-F	BZT52C4V7S-F	SOD-323	4.7	0.2	5				
621-BZT52C5V1S-F	BZT52C5V1S-F	SOD-323	5.1	0.2	5				
621-BZT52C5V6S-F	BZT52C5V6S-F	SOD-323	5.6	0.2	5				
621-BZT52C6V2S-F	BZT52C6V2S-F	SOD-323	6.2	0.2	5				
621-BZT52C6V8S-F	BZT52C6V8S-F	SOD-323	6.8	0.2	5				
621-BZT52C7V5S-F	BZT52C7V5S-F	SOD-323	7.5	0.2	5				
621-BZT52C8V2S-F	BZT52C8V2S-F	SOD-323	8.2	0.2	5				
621-BZT52C9V1S-F	BZT52C9V1S-F	SOD-323	9.1	0.2	5				
621-BZT52C10S-F	BZT52C10S-F	SOD-323	10	0.2	5				
621-BZT52C11S-F	BZT52C11S-F	SOD-323	11	0.2	5				
621-BZT52C12S-F	BZT52C12S-F	SOD-323	12	0.2	5				
621-BZT52C15S-F	BZT52C15S-F	SOD-323	15	0.2	5				
621-BZT52C16S-F	BZT52C16S-F	SOD-323	16	0.2	5				
621-BZT52C18S-F	BZT52C18S-F	SOD-323	18	0.2	5				
621-BZT52C20S-F	BZT52C20S-F	SOD-323	20	0.2	5				
621-BZT52C24S-F	BZT52C24S-F	SOD-323	24	0.2	5				
621-BZT52C27S-F	BZT52C27S-F	SOD-323	27	0.2	2				
621-BZT52C30S-F	BZT52C30S-F	SOD-323	30	0.2	2				
621-BZT52C33S-F	BZT52C33S-F	SOD-323	33	0.2	2				

MOUSER STOCK NO.	Diodes Inc. Part No.	Case Type	Nom. Volt. (V)	Power Rating (W)	Test Curr. (mA)	Price Each			
						1	10	100	500
<b>MMSZ Series; SOD-323</b>									
621-MMSZ5221BS-F	MMSZ5221BS-F	SOD-323	2.4	0.2	20				
621-MMSZ5225BS-F	MMSZ5225BS-F	SOD-323	3	0.2	20				
621-MMSZ5226BS-F	MMSZ5226BS-F	SOD-323	3.3	0.2	20				
621-MMSZ5227BS-F	MMSZ5227BS-F	SOD-323	3.6	0.2	20				
621-MMSZ5228BS-F	MMSZ5228BS-F	SOD-323	3.9	0.2	20				
621-MMSZ5229BS-F	MMSZ5229BS-F	SOD-323	4.3	0.2	20				
621-MMSZ5230BS-F	MMSZ5230BS-F	SOD-323	4.7	0.2	20				
621-MMSZ5231BS-F	MMSZ5231BS-F	SOD-323	5.1	0.2	20				
621-MMSZ5232BS-F	MMSZ5232BS-F	SOD-323	5.6	0.2	20				
621-MMSZ5234BS-F	MMSZ5234BS-F	SOD-323	6.2	0.2	20				
621-MMSZ5235BS-F	MMSZ5235BS-F	SOD-323	6.8	0.2	20				
621-MMSZ5236BS-F	MMSZ5236BS-F	SOD-323	7.5	0.2	20				
621-MMSZ5237BS-F	MMSZ5237BS-F	SOD-323	8.2	0.2	20				
621-MMSZ5239BS-F	MMSZ5239BS-F	SOD-323	9.1	0.2	20				
621-MMSZ5240BS-F	MMSZ5240BS-F	SOD-323	10	0.2	20				
621-MMSZ5241BS-F	MMSZ5241BS-F	SOD-323	11	0.2	20				
621-MMSZ5242BS-F	MMSZ5242BS-F	SOD-323	12	0.2	20				
621-MMSZ5243BS-F	MMSZ5243BS-F	SOD-323	13	0.2	9.5				
621-MMSZ5245BS-F	MMSZ5245BS-F	SOD-323	15	0.2	8.5				
621-MMSZ5248BS-F	MMSZ5248BS-F	SOD-323	18	0.2	7				
621-MMSZ5250BS-F	MMSZ5250BS-F	SOD-323	20	0.2	6.2				
621-MMSZ5251BS-F	MMSZ5251BS-F	SOD-323	22	0.2	5.6				
621-MMSZ5252BS-F	MMSZ5252BS-F	SOD-323	24	0.2	5.2				
621-MMSZ5254BS-F	MMSZ5254BS-F	SOD-323	27	0.2	5				
621-MMSZ5255BS-F	MMSZ5255BS-F	SOD-323	28	0.2	4.5				
621-MMSZ5256BS-F	MMSZ5256BS-F	SOD-323	30	0.2	4.2				
<b>BZX Series; SOT-23</b>									
621-BZX84C2V4-F	BZX84C2V4-F	SOT-23	2.4	0.3	5				
621-BZX84C2V7-F	BZX84C2V7-F	SOT-23	2.7	0.3	5				
621-BZX84C3V0-F	BZX84C3V0-F	SOT-23	3	0.3	5				
621-BZX84C3V3-F	BZX84C3V3-F	SOT-23	3.3	0.3	5				
621-BZX84C3V6-F	BZX84C3V6-F	SOT-23	3.6	0.3	5				
621-BZX84C3V9-F	BZX84C3V9-F	SOT-23	3.9	0.3	5				
621-BZX84C4V3-F	BZX84C4V3-F	SOT-23	4.3	0.3	5				
621-BZX84C5V1-F	BZX84C5V1-F	SOT-23	5.1	0.3	5				
621-BZX84C5V6-F	BZX84C5V6-F	SOT-23	5.6	0.3	5				
621-BZX84C6V2-F	BZX84C6V2-F	SOT-23	6.2	0.3	5				
621-BZX84C6V8-F	BZX84								