


VISHAY Zener Diodes

Products may be RoHS compliant.
Check mouser.com for RoHS status.


VISHAY ZENER DIODES (CONT.)

For quantities of 2000 and up, call for quote.

MOUSER STOCK NO.	Vishay Part No.	Case Type	Nominal Voltage (V)	Power Rating (W)	Test Current (mA)	Price Each			
						1	100	500	1000
Surface Mount									
625-BZX84C6V2-V	BZX84C6V2-V-GS08	SOT-23-3	6.2	0.35	10				
625-BZX84C6V8-V	BZX84C6V8-V-GS08	SOT-23-3	6.8	0.35	15				
625-BZX84C7V5-V	BZX84C7V5-V-GS08	SOT-23-3	7.5	0.35	15				
625-BZX84C8V2-V	BZX84C8V2-V-GS08	SOT-23-3	8.2	0.35	15				
625-BZX84C9V1-V	BZX84C9V1-V-GS08	SOT-23-3	9.1	0.35	15				
625-BZX84C10-V	BZX84C10-V-GS08	SOT-23-3	10	0.35	20				
625-BZX84C11-V	BZX84C11-V-GS08	SOT-23-3	11	0.35	20				
625-BZX84C12-V	BZX84C12-V-GS08	SOT-23-3	12	0.35	25				
625-BZX84C13-V	BZX84C13-V-GS08	SOT-23-3	13	0.35	30				
625-BZX84C15-V	BZX84C15-V-GS08	SOT-23-3	15	0.35	30				
625-BZX84C16-V	BZX84C16-V-GS08	SOT-23-3	16	0.35	40				
625-BZX84C18-V	BZX84C18-V-GS08	SOT-23-3	18	0.35	45				
625-BZX84C20-V	BZX84C20-V-GS08	SOT-23-3	20	0.35	55				
625-BZX84C22-V	BZX84C22-V-GS08	SOT-23-3	22	0.35	55				
625-BZX84C24-V	BZX84C24-V-GS08	SOT-23-3	24	0.35	70				
625-BZX84C27-V	BZX84C27-V-GS08	SOT-23-3	27	0.35	80				
625-BZX84C30-V	BZX84C30-V-GS08	SOT-23-3	30	0.35	80				
625-BZX84C33-V	BZX84C33-V-GS08	SOT-23-3	33	0.35	80				
625-BZX84C36-V	BZX84C36-V-GS08	SOT-23-3	36	0.35	90				
625-BZX84C39-V	BZX84C39-V-GS08	SOT-23-3	39	0.35	130				
625-BZX84C43-V	BZX84C43-V-GS08	SOT-23-3	43	0.35	150				
625-BZX84C47-V	BZX84C47-V-GS08	SOT-23-3	47	0.35	170				
625-BZX84C51-V	BZX84C51-V-GS08	SOT-23-3	51	0.35	180				
78-TZM5221B	TZM5221B-GS08	SOD-80C	2.4	0.5	20				
78-TZM5222B	TZM5222B-GS08	SOD-80C	2.5	0.5	20				
78-TZM5223B	TZM5223B-GS08	SOD-80C	2.7	0.5	20				
78-TZM5224B	TZM5224B-GS08	SOD-80C	2.8	0.5	20				
78-TZM5225B	TZM5225B-GS08	SOD-80C	3.0	0.5	20				
78-TZM5226B	TZM5226B-GS08	SOD-80C	3.3	0.5	20				
78-TZM5227B	TZM5227B-GS08	SOD-80C	3.6	0.5	20				
78-TZM5228B	TZM5228B-GS08	SOD-80C	3.9	0.5	20				
78-TZM5229B	TZM5229B-GS08	SOD-80C	4.3	0.5	20				
78-TZM5230B	TZM5230B-GS08	SOD-80C	4.7	0.5	20				
78-TZM5231B	TZM5231B-GS08	SOD-80C	5.1	0.5	20				
78-TZM5232B	TZM5232B-GS08	SOD-80C	5.6	0.5	20				
78-TZM5233B	TZM5233B-GS08	SOD-80C	6.0	0.5	20				
78-TZM5234B	TZM5234B-GS08	SOD-80C	6.2	0.5	20				
78-TZM5235B	TZM5235B-GS08	SOD-80C	6.8	0.5	20				
78-TZM5236B	TZM5236B-GS08	SOD-80C	7.5	0.5	20				
78-TZM5237B	TZM5237B-GS08	SOD-80C	8.2	0.5	20				
78-TZM5238B	TZM5238B-GS08	SOD-80C	8.7	0.5	20				
78-TZM5239B	TZM5239B-GS08	SOD-80C	9.1	0.5	20				
78-TZM5240B	TZM5240B-GS08	SOD-80C	10	0.5	20				
78-TZM5241B	TZM5241B-GS08	SOD-80C	11	0.5	20				
78-TZM5242B	TZM5242B-GS08	SOD-80C	12	0.5	20				
78-TZM5243B	TZM5243B-GS08	SOD-80C	13	0.5	9.5				
78-TZM5244B	TZM5244B-GS08	SOD-80C	14	0.5	9.0				
78-TZM5245B	TZM5245B-GS08	SOD-80C	15	0.5	8.5				
78-TZM5246B	TZM5246B-GS08	SOD-80C	16	0.5	7.8				
78-TZM5247B	TZM5247B-GS08	SOD-80C	17	0.5	7.4				
78-TZM5248B	TZM5248B-GS08	SOD-80C	18	0.5	7.0				
78-TZM5249B	TZM5249B-GS08	SOD-80C	19	0.5	6.6				
78-TZM5250B	TZM5250B-GS08	SOD-80C	20	0.5	6.2				
78-TZM5251B	TZM5251B-GS08	SOD-80C	22	0.5	5.6				
78-TZM5252B	TZM5252B-GS08	SOD-80C	24	0.5	5.2				
78-TZM5253B	TZM5253B-GS08	SOD-80C	25	0.5	5.0				
78-TZM5254B	TZM5254B-GS08	SOD-80C	27	0.5	4.6				
78-TZM5255B	TZM5255B-GS08	SOD-80C	28	0.5	4.5				
78-TZM5256B	TZM5256B-GS08	SOD-80C	30	0.5	4.2				
78-TZM5257B	TZM5257B-GS08	SOD-80C	33	0.5	3.8				
78-TZM5258B	TZM5258B-GS08	SOD-80C	36	0.5	3.4				
78-TZM5259B	TZM5259B-GS08	SOD-80C	39	0.5	3.2				
78-TZM5260B	TZM5260B-GS08	SOD-80C	43	0.5	3.0				
78-TZM5261B	TZM5261B-GS08	SOD-80C	47	0.5	2.7				
78-TZM5262B	TZM5262B-GS08	SOD-80C	51	0.5	2.5				
78-TZM5263B	TZM5263B-GS08	SOD-80C	56	0.5	2.2				
78-TZM5264B	TZM5264B-GS08	SOD-80C	60	0.5	2.1				
78-TZM5265B	TZM5265B-GS08	SOD-80C	62	0.5	2.0				
78-TZM5266B	TZM5266B-GS08	SOD-80C	68	0.5	1.8				
78-TZM5267B	TZM5267B-GS08	SOD-80C	75	0.5	1.7				
625-ZM4730A	ZM4730A-GS08	MELF	3.9	1	64				
625-ZM4731A	ZM4731A-GS08	MELF	4.3	1	58				
625-ZM4732A	ZM4732A-GS08	MELF	4.7	1	53				
625-ZM4733A	ZM4733A-GS08	MELF	5.1	1	49				
625-ZM4734A	ZM4734A-GS08	MELF	5.6	1	45				
625-ZM4735A	ZM4735A-GS08	MELF	6.2	1	41				
625-ZM4736A	ZM4736A-GS08	MELF	6.8	1	37				
625-ZM4737A	ZM4737A-GS08	MELF	7.5	1	34				
625-ZM4738A	ZM4738A-GS08	MELF	8.2	1	31				
625-ZM4739A	ZM4739A-GS08	MELF	9.1	1	28				
625-ZM4740A	ZM4740A-GS08	MELF	10	1	25				
625-ZM4741A	ZM4741A-GS08	MELF	11	1	23				
625-ZM4742A	ZM4742A-GS08	MELF	12	1	21				
625-ZM4743A	ZM4743A-GS08	MELF	13	1	19				
625-ZM4744A	ZM4744A-GS08	MELF	15	1	17				
625-ZM4745A	ZM4745A-GS08	MELF	16	1	15.5				
625-ZM4746A	ZM4746A-GS08	MELF	18	1	14				
625-ZM4747A	ZM4747A-GS08	MELF	20	1	12.5				
625-ZM4748A	ZM4748A-GS08	MELF	22	1	11.5				
625-ZM4749A	ZM4749A-GS08	MELF	24	1	10.5				
625-ZM4750A	ZM4750A-GS08	MELF	27	1	9.5				
625-ZM4751A	ZM4751A-GS08	MELF	30	1	8.5				



SOT-23-3



MELF/SOD-80C