




LITTELFUSE Fuses



RoHS Compliant This page of product is compliant.

DIMENSIONS: mm (in.)



3AB CERAMIC FUSES

314 Series Fast-Acting Ceramic

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	Littelfuse Part No.	Fig.	Amp (A)	Volts (V)	Price Each			
					1	10	100	250
576-0314003.HXP	0314003.HXP	A	3	250				
576-0314004.HXP	0314004.HXP	A	4	250				
576-0314005.HXP	0314005.HXP	A	5	250				
576-0314006.HXP	0314006.HXP	A	6	250				
576-0314007.HXP	0314007.HXP	A	7	250				
576-0314008.HXP	0314008.HXP	A	8	250				
576-0314010.HXP	0314010.HXP	A	10	250				
576-0314012.HXP	0314012.HXP	A	12	250				
576-0314015.MXP	0314015.MXP	A	15	250				
576-0314020.HXP	0314020.HXP	A	20	250				
576-0314025.HXP	0314025.HXP	A	25	250				
576-0314030.HXP	0314030.HXP	A	30	250				

324 Series Fast-Acting Fuses

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	Littelfuse Part No.	Fig.	Amp (A)	Volts (V)	Price Each			
					1	10	100	250
576-0324010.HXP	0324010.HXP	B	10	250				
576-0324012.HXP	0324012.HXP	B	12	250				
576-0324015.HXP	0324015.HXP	B	15	250				
576-0324020.HXP	0324020.HXP	B	20	250				
576-0324025.HXP	0324025.HXP	B	25	125				
576-0324030.HXP	0324030.HXP	B	30	125				

322 Series Very Fast-Acting Fuses

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	Littelfuse Part No.	Fig.	Amp (A)	Volts (V)	Price Each			
					1	10	100	250
576-0322001.HXP	0322001.HXP	A	1	250				
576-0322002.HXP	0322002.HXP	A	2	250				
576-0322004.HXP	0322004.HXP	A	4	250				
576-0322008.HXP	0322008.HXP	A	8	250				
576-0322020.HXP	0322020.HXP	A	20	65				
576-0322030.HXP	0322030.HXP	A	30	65				

326 Series Slo-Blo® Ceramic

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	Littelfuse Part No.	Fig.	Amp (A)	Volts (V)	Price Each			
					1	10	100	250
576-0326.010HXP	0326.010HXP	A	0.01	250				
576-0326.031HXP	0326.031HXP	A	0.031	250				
576-0326.100HXP	0326.100HXP	A	0.1	250				
576-0326.125HXP	0326.125HXP	A	0.125	250				
576-0326.250HXP	0326.250HXP	A	0.25	250				
576-0326.375HXP	0326.375HXP	A	0.375	250				
576-0326.500HXP	0326.500HXP	A	0.5	250				
576-0326.750HXP	0326.750HXP	A	0.75	250				
576-0326.800HXP	0326.800HXP	A	0.8	250				
576-0326001.HXP	0326001.HXP	A	1	250				
576-032601.5HXP	032601.5HXP	A	1.5	250				
576-0326002.HXP	0326002.HXP	A	2	250				
576-032602.5HXP	032602.5HXP	A	2.5	250				
576-0326003.HXP	0326003.HXP	A	3	250				
576-0326004.HXP	0326004.HXP	A	4	250				
576-0326005.HXP	0326005.HXP	A	5	250				
576-03266.25HXP	03266.25HXP	A	6.25	250				
576-0326007.HXP	0326007.HXP	A	7	250				
576-0326008.HXP	0326008.HXP	A	8	250				
576-0326010.HXP	0326010.HXP	A	10	250				
576-0326012.HXP	0326012.HXP	A	12	250				
576-0326015.HXP	0326015.HXP	A	15	250				
576-0326020.HXP	0326020.HXP	A	20	250				
576-0326025.HXP	0326025.HXP	A	25	125				
576-0326030.HXP	0326030.HXP	A	30	125				

325 Series Slo-Blo® Fuses

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	Littelfuse Part No.	Fig.	Amp (A)	Volts (V)	Price Each			
					1	10	100	250
576-0325010.HXP	0325010.HXP	B	10	250				
576-0325015.HXP	0325015.HXP	B	15	250				
576-0325020.HXP	0325020.HXP	B	30	125				
576-0325030.HXP	0325030.HXP	B	20	250				

SPF SERIES 1000VDC SOLAR FUSES



For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	Littelfuse Part No.	Fig.	Amp (A)	Volts (V)	Price Each			
					1	10	100	250
576-0SPF001.T	0SPF001.T	C	1	1000				
576-0SPF002.T	0SPF002.T	C	2	1000				
576-0SPF003.T	0SPF003.T	C	3	1000				
576-0SPF004.T	0SPF004.T	C	4	1000				
576-0SPF005.T	0SPF005.T	C	5	1000				
576-0SPF006.T	0SPF006.T	C	6	1000				
576-0SPF008.T	0SPF008.T	C	8	1000				
576-0SPF010.T	0SPF010.T	C	10	1000				
576-0SPF012.T	0SPF012.T	C	12	1000				
576-0SPF015.T	0SPF015.T	C	15	1000				
576-0SPF020.T	0SPF020.T	C	20	1000				
576-0SPF025.T	0SPF025.T	C	25	1000				
576-0SPF030.T	0SPF030.T	C	30	1000				

KLK SERIES MIDGET AC FAST-ACTING FUSES



MOUSER STOCK NO.	Littelfuse Part No.	Fig.	Amp (A)	Volts (V)	Price Each			
					1	10	100	250
576-0KLK001.T	KLK001	C	1	600				
576-0KLK01.5T	KLK01.5	C	1.5	600				
576-0KLK002.T	KLK002	C	2	600				
576-0KLK003.T	KLK003	C	3	600				
576-0KLK005.T	KLK005	C	5	600				
576-0KLK006.T	KLK006	C	6	600				
576-0KLK010.T	KLK010	C	10	600				
576-0KLK015.T	KLK015	C	15	600				
576-0KLK020.T	KLK020	C	20	600				
576-0KLK025.T	KLK025	C	25	600				
576-0KLK030.T	KLK030	C	30	600				

FLQ SERIES MIDGET AC SLO-BLO FUSES



MOUSER STOCK NO.	Littelfuse Part No.	Fig.	Amp (A)	Volts (V)	Price Each			
					1	10	100	250
576-0FLQ001.T	FLQ001	C	1	500				
576-0FLQ015.T	FLQ015	C	15	500				
576-0FLQ020.T	FLQ020	C	20	500				
576-0FLQ025.T	FLQ025	C	25	500				

KLKD SERIES MIDGET AC/DC FAST-ACTING FUSES



MOUSER STOCK NO.	Littelfuse Part No.	Fig.	Amp (A)	Volts (V)	Price Each			
					1	10	100	250
576-KLKD.300T	KLKD.300	C	0.3	600				
576-KLKD001.T	KLKD001	C	1	600				
576-KLKD005.T	KLKD005	C	5	600				
576-KLKD008.T	KLKD008	C	8	600				
576-KLKD010.T	KLKD010	C	10	600				
576-KLKD015.T	KLKD015	C	15	600				
576-KLKD020.T	KLKD020	C	20	600				

KLDR SERIES CLASS CC TIME-DELAY FUSES FOR TRANSFORMERS



For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	Littelfuse Part No.	Fig.	Amp (A)	Volts (V)	Price Each			
					1	10	100	250
576-KLDR.100T	KLDR.100	C	0.1	600AC/300DC				
576-KLDR.200T	KLDR.200	C	0.2	600AC/300DC				
576-KLDR.300T	KLDR.300	C	0.3	600AC/300DC				
576-KLDR.500T	KLDR.500	C	0.5	600AC/300DC				
576-KLDR.750T	KLDR.750	C	0.75	600AC/300DC				
576-KLDR001.T	KLDR001	C	1	600AC/300DC				
576-KLDR002.T	KLDR002	C	2	600AC/300DC				
576-KLDR005.T	KLDR005	C	5	600AC/300DC				
576-KLDR009.T	KLDR009	C	9	600AC/300DC				
576-KLDR01.5T	KLDR01.5	C	1.5	600AC/300DC				
576-KLDR010.T	KLDR010	C	10	600AC/300DC				
576-KLDR012.T	KLDR012	C	12	600AC/300DC				
576-KLDR015.T	KLDR015	C	15	600AC/300DC				
576-KLDR020.T	KLDR020	C	20	600AC/300DC				
576-KLDR025.T	KLDR025	C	25	600AC/300DC				
576-KLDR030.T	KLDR030	C	30	600AC/300DC				
576-KLDR2.25T	KLDR2.25	C	2.25	600AC/300DC				

FLM SERIES MIDGET AC TIME-DELAY FUSES



MOUSER STOCK NO.	Littelfuse Part No.	Fig.	Amp (A)	Volts (V)	Price Each			
					1	10	100	250
576-0FLM002.T	FLM002	C	2	250				
576-0FLM6.25T	FLM6.25	C	6.25	250				
576-0FLM010.T	FLM010	C	10	250				
576-0FLM015.T	FLM015	C	15	250				
576-0FLM020.T	FLM020	C	20	250				
576-0FLM030.T	FLM030	C	30	250				