

ETI SYSTEMS High Precision Single Turn Potentiometers

RoHS Compliant This product is RoHS compliant.



EUP1900/1950 SERIES

- 1 watt power rating
- Conductive plastic
- Resistance Tolerance: $\pm 20\%$ Linearity: 2%
- Rotation EUP1900: 360°
- Rotation EUP1950: $340^\circ \pm 5^\circ$

For quantities of 100 and up, call for quote.

MOUSER STOCK NO.	ETI Systems Part No.	Fig.	Ohms	Price Each				
				1	5	10	25	50
882-EUP1900-1K	EUP1900-1K	A	1K					
882-EUP1900-5K	EUP1900-5K	A	5K					
882-EUP1900-10K	EUP1900-10K	A	10K					
882-EUP1950-1K	EUP1950-1K	A	1K					
882-EUP1950-5K	EUP1950-5K	A	5K					
882-EUP1950-10K	EUP1950-10K	A	10K					

EUP1910/1960 SERIES

- 1 watt power rating
- Conductive plastic
- Resistance Tolerance: $\pm 20\%$ Linearity: 2%
- Rotation EUP1910: 360°
- Rotation EUP1960: $330^\circ \pm 5^\circ$

For quantities of 100 and up, call for quote.

MOUSER STOCK NO.	ETI Systems Part No.	Fig.	Ohms	Price Each				
				1	5	10	25	50
882-EUP1910-1K	EUP1910-1K	B	1K					
882-EUP1910-5K	EUP1910-5K	B	5K					
882-EUP1910-10K	EUP1910-10K	B	10K					
882-EUP1960-1K	EUP1960-1K	B	1K					
882-EUP1960-5K	EUP1960-5K	B	5K					
882-EUP1960-10K	EUP1960-10K	B	10K					

EUP120/125 SERIES

- 0.5 watt power rating
- Conductive plastic
- Resistance Tolerance: $\pm 20\%$ Linearity: 5%
- Rotation EUP125: 360°
- Rotation EUP120: $320^\circ \pm 10^\circ$

For quantities of 100 and up, call for quote.

MOUSER STOCK NO.	ETI Systems Part No.	Fig.	Ohms	Price Each				
				1	5	10	25	50
882-EUP120-1K	EUP120-1K	C	1K					
882-EUP120-5K	EUP120-5K	C	5K					
882-EUP120-10K	EUP120-10K	C	10K					
882-EUP125-1K	EUP125-1K	C	1K					
882-EUP125-5K	EUP125-5K	C	5K					
882-EUP125-10K	EUP125-10K	C	10K					

EUP3100/3125 SERIES

- 3 watts power rating
- Wirewound resistive element
- Rotation EUP3100: $280^\circ \pm 5^\circ$
- Resistance Tolerance: $\pm 10\%$ Linearity: 1%
- Rotation EUP3125: 360°

For quantities of 100 and up, call for quote.

MOUSER STOCK NO.	ETI Systems Part No.	Fig.	Ohms	Price Each				
				1	5	10	25	50
882-EUP3100-1K	EUP3100-1K	D	1K					
882-EUP3100-5K	EUP3100-5K	D	5K					
882-EUP3100-10K	EUP3100-10K	D	10K					
882-EUP3125-1K	EUP3125-1K	D	1K					
882-EUP3125-5K	EUP3125-5K	D	5K					
882-EUP3125-10K	EUP3125-10K	D	10K					

EUP3200/3225 SERIES

- 2 watts power rating
- Conductive Plastic
- Rotation EUP3200: $340^\circ \pm 5^\circ$
- Resistance Tolerance: $\pm 20\%$ Linearity: 2%
- Rotation EUP3225: 360°

For quantities of 100 and up, call for quote.

MOUSER STOCK NO.	ETI Systems Part No.	Fig.	Ohms	Price Each				
				1	5	10	25	50
882-EUP3200-2K	EUP3200-2K	D	2K					
882-EUP3200-5K	EUP3200-5K	D	5K					
882-EUP3200-10K	EUP3200-10K	D	10K					
882-EUP3225-2K	EUP3225-2K	D	2K					
882-EUP3225-5K	EUP3225-5K	D	5K					
882-EUP3225-10K	EUP3225-10K	D	10K					

EUP1100/1125 SERIES

- 1 watt power rating
- Wirewound resistive element
- Rotation EUP1100: $285^\circ \pm 5^\circ$
- Resistance Tolerance: $\pm 10\%$ Linearity: 1%
- Rotation EUP1125: 360°

For quantities of 100 and up, call for quote.

MOUSER STOCK NO.	ETI Systems Part No.	Fig.	Ohms	Price Each				
				1	5	10	25	50
882-EUP1100-1K	EUP1100-1K	E	1K					
882-EUP1100-5K	EUP1100-5K	E	5K					
882-EUP1100-10K	EUP1100-10K	E	10K					
882-EUP1125-1K	EUP1125-1K	E	1K					
882-EUP1125-5K	EUP1125-5K	E	5K					
882-EUP1125-10K	EUP1125-10K	E	10K					

EUP1400/1425 SERIES

- 3 watts power rating
- Wirewound resistive element
- Rotation EUP1400: $285^\circ \pm 5^\circ$
- Resistance Tolerance: $\pm 10\%$ Linearity: 0.75%
- Rotation EUP1425: 360°

For quantities of 100 and up, call for quote.

MOUSER STOCK NO.	ETI Systems Part No.	Fig.	Ohms	Price Each				
				1	5	10	25	50
882-EUP1400-1K	EUP1400-1K	F	1K					
882-EUP1400-5K	EUP1400-5K	F	5K					
882-EUP1400-10K	EUP1400-10K	F	10K					
882-EUP1425-1K	EUP1425-1K	F	1K					
882-EUP1425-5K	EUP1425-5K	F	5K					
882-EUP1425-10K	EUP1425-10K	F	10K					

DIMENSIONS: in.

A

B

C

D

E

F

Precision Pots
ETI Systems