

# EPCOS Snap-In Aluminum Electrolytic Capacitors



This page of product is compliant.

## 105°C ALUMINUM ELECTROLYTIC SNAPIN CAPACITORS - LONG LIFE 3000 HOURS

**Features:** • High ripple current capability • Load life of 3000 hours at 105°C • **Applications:** • Switch-mode power supplies in industrial and entertainment electronics **For quantities greater than listed, call for quote.**

Epcos Aluminum Caps, Can

MOUSER STOCK NO.	Epcos Part No.	Voltage (DC)	Value (uF)	Case Size (DxL mm)	Dissipation Factor (tan δ)	Ripple Current (mA)	Price Each			
							1	10	25	50
871-B43254A2157M000	B43254A2157M000	200	150	22x20	0.15	0.63				
871-B43254B2187M000	B43254B2187M000	200	180	25.4x20	0.15	0.76				
871-B43254A2227M000	B43254A2227M000	200	220	22x25	0.15	0.82				
871-B43254B2277M000	B43254B2277M000	200	270	25.4x25	0.15	1.00				
871-B43254A2337M000	B43254A2337M000	200	330	22x30	0.15	1.07				
871-B43254A2397M000	B43254A2397M000	200	390	22x30	0.15	1.17				
871-B43254B2477M000	B43254B2477M000	200	470	25.4x30	0.15	1.40				
871-B43254B2567M000	B43254B2567M000	200	560	25.4x30	0.15	1.53				
871-B43254C2687M000	B43254C2687M000	200	680	30x30	0.15	1.84				
871-B43254A2827M000	B43254A2827M000	200	820	25.4x45	0.15	2.16				
871-B43254B2827M000	B43254B2827M000	200	820	30x30	0.15	2.02				
871-B43254C2108M000	B43254C2108M000	200	1000	35x30	0.15	2.41				
871-B43254A2128M000	B43254A2128M000	200	1200	30x40	0.15	2.50				
871-B43254A2158M000	B43254A2158M000	200	1500	30x50	0.15	3.04				
871-B43254A2188M000	B43254A2188M000	200	1800	35x45	0.15	3.43				
871-B43254A2228M000	B43254A2228M000	200	2200	35x50	0.15	3.68				
871-B43254E2127M000	B43254E2127M000	250	120	22x20	0.15	0.56				
871-B43254E2157M000	B43254E2157M000	250	150	22x25	0.15	0.68				
871-B43254E2187M000	B43254E2187M000	250	180	22x25	0.15	0.74				
871-B43254F2227M000	B43254F2227M000	250	220	25.4x25	0.15	0.90				
871-B43254E2277M000	B43254E2277M000	250	270	22x30	0.15	0.97				
871-B43254F2337M000	B43254F2337M000	250	330	25.4x30	0.15	1.18				
871-B43254G2397M000	B43254G2397M000	250	390	30x25	0.15	1.31				
871-B43254G2477M000	B43254G2477M000	250	470	30x30	0.15	1.53				
871-B43254G2567M000	B43254G2567M000	250	560	30x30	0.15	1.67				
871-B43254G2687M000	B43254G2687M000	250	680	35x30	0.15	1.98				
871-B43254E2827M000	B43254E2827M000	250	820	30x40	0.15	2.23				
871-B43254E2108M000	B43254E2108M000	250	1000	30x50	0.15	2.68				
871-B43254E2128M000	B43254E2128M000	250	1200	30x60	0.15	2.92				
871-B43254E2158M000	B43254E2158M000	250	1500	35x50	0.15	3.25				
871-B43254A9476M000	B43254A9476M000	400	47	22x20	0.15	0.34				
871-B43254A9686M000	B43254A9686M000	400	68	22x25	0.15	0.44				
871-B43254A9107M000	B43254A9107M000	400	100	22x30	0.15	0.57				
871-B43254B9157M000	B43254B9157M000	400	150	25.4x30	0.15	0.76				
871-B43254C9227M000	B43254C9227M000	400	220	30x30	0.15	1.00				
871-B43254C9337M000	B43254C9337M000	400	330	35x30	0.15	1.33				
871-B43254A9477M000	B43254A9477M000	400	470	30x50	0.15	1.76				
871-B43254A9687M000	B43254A9687M000	400	680	35x50	0.15	2.27				
871-B43254A5566M000	B43254A5566M000	450	56	22x25	0.20	0.29				
871-B43254A5686M000	B43254A5686M000	450	68	22x30	0.20	0.34				
871-B43254A5826M000	B43254A5826M000	450	82	22x30	0.20	0.38				
871-B43254B5107M000	B43254B5107M000	450	100	25.4x30	0.20	0.46				
871-B43254B5127M000	B43254B5127M000	450	120	25.4x30	0.20	0.50				
871-B43254C5157M000	B43254C5157M000	450	150	30x30	0.20	0.61				
871-B43254C5187M000	B43254C5187M000	450	180	30x30	0.20	0.67				
871-B43254B5227M000	B43254B5227M000	450	220	30x35	0.20	0.78				
871-B43254B5277M000	B43254B5277M000	450	270	35x30	0.20	0.88				
871-B43254A5337M000	B43254A5337M000	450	330	30x45	0.15	1.04				
871-B43254A5397M000	B43254A5397M000	450	390	30x50	0.15	1.18				
871-B43254A5477M000	B43254A5477M000	450	470	35x45	0.15	1.34				
871-B43254A5567M000	B43254A5567M000	450	560	35x50	0.20	1.52				

## 105°C ALUMINUM ELECTROLYTIC SNAPIN CAPACITORS - LONG LIFE 5000 HOURS

**Features:** • High reliability • High CV product • Long load life of 5000 hours at 105°C • **Applications:** • Professional power supplies in industrial electronics • Frequency converters **For quantities greater than listed, call for quote.**

871-B43255A2227M000	B43255A2227M000	200	220	22x25	0.15	0.82				
871-B43255A2277M000	B43255A2277M000	200	270	25.4x25	0.15	1.00				
871-B43255A2337M000	B43255A2337M000	200	330	25.4x30	0.15	1.18				
871-B43255A2397M000	B43255A2397M000	200	390	25.4x35	0.15	1.35				
871-B43255A2477M000	B43255A2477M000	200	470	25.4x40	0.15	1.56				
871-B43255A2567M000	B43255A2567M000	200	560	30x35	0.15	1.76				
871-B43255A2687M000	B43255A2687M000	200	680	30x40	0.15	2.03				
871-B43255A2827M000	B43255A2827M000	200	820	35x35	0.15	2.29				
871-B43255A2108M000	B43255A2108M000	200	1000	35x35	0.15	2.53				
871-B43255A2128M000	B43255A2128M000	200	1200	35x40	0.15	2.69				
871-B43255A2158M000	B43255A2158M000	200	1500	35x50	0.15	3.25				
871-B43255E2157M000	B43255E2157M000	250	150	22x25	0.15	0.68				
871-B43255E2187M000	B43255E2187M000	250	180	22x30	0.15	0.79				
871-B43255E2227M000	B43255E2227M000	250	220	25.4x30	0.15	0.96				
871-B43255E2277M000	B43255E2277M000	250	270	25.4x35	0.15	1.13				
871-B43255E2337M000	B43255E2337M000	250	330	30x30	0.15	1.28				
871-B43255E2397M000	B43255E2397M000	250	390	30x35	0.15	1.47				
871-B43255E2477M000	B43255E2477M000	250	470	35x30	0.15	1.65				
871-B43255E2567M000	B43255E2567M000	250	560	35x35	0.15	1.89				
871-B43255E2687M000	B43255E2687M000	250	680	35x40	0.15	2.18				
871-B43255E2827M000	B43255E2827M000	250	820	35x45	0.15	2.50				
871-B43255E2108M000	B43255E2108M000	250	1000	35x50	0.15	2.87				
871-B43255A9686M000	B43255A9686M000	400	68	25.4x25	0.15	0.48				
871-B43255A9107M000	B43255A9107M000	400	100	25.4x30	0.15	0.62				
871-B43255A9157M000	B43255A9157M000	400	150	30x30	0.15	0.83				
871-B43255A9227M000	B43255A9227M000	400	220	35x30	0.15	1.08				
871-B43255A9337M000	B43255A9337M000	400	330	35x40	0.15	1.46				
871-B43255A9477M000	B43255A9477M000	400	470	35x50	0.15	1.89				
871-B43255A5476M000	B43255A5476M000	450	47	22x30	0.20	0.39				
871-B43255A5566M000	B43255A5566M000	450	56	25.4x25	0.20	0.44				
871-B43255A5686M000	B43255A5686M000	450	68	25.4x30	0.20	0.51				
871-B43255A5826M000	B43255A5826M000	450	82	30x30	0.20	0.61				
871-B43255A5107M000	B43255A5107M000	450	100	30x30	0.20	0.68				
871-B43255A5127M000	B43255A5127M000	450	120	30x30	0.20	0.74				
871-B43255A5157M000	B43255A5157M000	450	150	35x30	0.20	0.90				
871-B43255A5187M000	B43255A5187M000	450	180	35x35	0.20	1.03				
871-B43255A5227M000	B43255A5227M000	450	220	35x40	0.20	1.19				
871-B43255A5277M000	B43255A5277M000	450	270	35x45	0.20	1.38				
871-B43255A5337M000	B43255A5337M000	450	330	35x50	0.20	1.58				