

EPCOS Power Inductors



This product is RoHS compliant.



SMD SERIES B82554

- Enamel Copper Flat Wire Winding
- High Current Rating
- Magnetically Shielded Ferrite Core
- Low DC Resistance

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Epcos Part No.	Fig.	L (μH)	Idc (A)	Price Each			
					1	10	25	100
871-B82559A112A13	B82559A112A13	A	1.1	20	2.50	2.00	1.90	1.81
871-B82559A222A13	B82559A222A13	A	2.2	15	2.50	2.00	1.90	1.81
871-B82559A501A13	B82559A501A13	A	0.5	30	2.50	2.00	1.90	1.81
871-B82559A142A13	B82559A142A13	A	1.4	22	2.50	2.00	1.90	1.81
871-B82559A242A13	B82559A242A13	A	2.4	16.5	2.50	2.00	1.90	1.81
871-B82559A392A13	B82559A392A13	A	3.9	12	2.50	2.00	1.90	1.81
871-B82559A951A13	B82559A951A13	A	0.95	25	2.50	2.00	1.90	1.81

SMD SERIES B82462-G4

- Enamel Copper Wire Winding Welded to Terminals
- Size: 6mm by 6mm
- High Current Rating
- Magnetically Shielded Ferrite Core
- Wide Temp Range
- Low DC Resistance

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Epcos Part No.	Fig.	L (μH)	Idc (A)	Price Each			
					1	10	25	100
871-B82462G4102M	B82462G4102M	B	1	3.4	1.94	1.92	1.60	1.07
871-B82462G4103M	B82462G4103M	B	10	1.5	1.94	1.92	1.60	1.07
871-B82462G4104M	B82462G4104M	B	100	0.53	1.94	1.92	1.60	1.07
871-B82462G4222M	B82462G4222M	B	2.2	2.55	1.94	1.92	1.60	1.07
871-B82462G4223M	B82462G4223M	B	22	1.05	1.94	1.92	1.60	1.07
871-B82462G4224M	B82462G4224M	B	220	0.35	1.94	1.92	1.60	1.07
871-B82462G4333M	B82462G4333M	B	33	0.85	1.94	1.92	1.60	1.07
871-B82462G4334M	B82462G4334M	B	330	0.27	1.94	1.92	1.60	1.07

SMD SERIES B82464-A4

- Enamel Copper Wire Winding Welded to Terminals
- Size: 10mm by 10mm
- Very High Current Rating
- Ferrite Core
- Wide Temp Range
- Low DC Resistance

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Epcos Part No.	Fig.	L (μH)	Idc (A)	Price Each			
					1	10	25	100
871-B82464A4224K	B82464A4224K	C	220	0.8	2.21	1.94	1.58	1.33
871-B82464A4334K	B82464A4334K	C	330	0.6	2.21	1.94	1.58	1.33
871-B82464G4102M	B82464G4102M	C	1	7.5	3.05	2.74	2.43	1.82
871-B82464G4103M	B82464G4103M	C	10	2.5	3.05	2.74	2.43	1.82
871-B82464G4104M	B82464G4104M	C	100	1	3.05	2.74	2.43	1.82
871-B82464G4105M	B82464G4105M	C	1000	0.3	3.05	2.74	2.43	1.82

SMD SERIES B82471

- Enamel Copper Wire Winding
- Ferrite Core
- High Current Rating
- Welded to Terminals
- Size: 6mm by 6mm
- Low DC Resistance

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Epcos Part No.	Fig.	L (μH)	Idc (A)	Price Each			
					1	10	25	100
871-B82471A1103M	B82471A1103M	D	10	1.44	1.37	1.16	1.03	.872
871-B82471A1104K	B82471A1104K	D	100	0.52	1.37	1.16	1.03	.872
871-B82471A1224K	B82471A1224K	D	220	0.35	1.37	1.16	1.03	.872

SMD SERIES B82472-G4

- Enamel Copper Wire Winding
- Plastic Terminal Carrier
- Very High Current Rating
- Soldered to Terminals
- Size: 7mm by 7mm
- Low DC Resistance
- Magnetically Shielded Ferrite Core
- Wide Temp Range

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Epcos Part No.	Fig.	L (μH)	Idc (A)	Price Each			
					1	10	25	100
871-B82472G4102M	B82472G4102M	E	1	2.9	1.24	1.11	1.00	.836
871-B82472G4103M	B82472G4103M	E	10	1.34	1.24	1.11	1.00	.836
871-B82472G4104M	B82472G4104M	E	100	0.45	1.08	.97	.871	.728
871-B82472G4224M	B82472G4224M	E	220	0.3	1.24	1.11	1.00	.836
871-B82472G4473M	B82472G4473M	E	47	0.65	1.24	1.11	1.00	.836
871-B82472G6102M	B82472G6102M	E	1	3.6	1.24	1.11	1.00	.836
871-B82472G6103M	B82472G6103M	E	10	1.9	1.24	1.11	1.00	.836
871-B82472G6104M	B82472G6104M	E	100	0.67	1.24	1.11	1.00	.836
871-B82472G6105M	B82472G6105M	E	1000	0.2	1.24	1.11	1.00	.836

SMD SERIES B82473

- Enamel Copper Wire Winding Soldered to Terminals
- Plastic Core
- High Current Rating
- Ferrite Core
- Size: 7mm by 7mm
- Low DC Resistance

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Epcos Part No.	Fig.	L (μH)	Idc (A)	Price Each			
					1	10	25	100
871-B82473A1103K	B82473A1103K	F	10	2.3	2.14	1.74	1.44	1.19
871-B82473A1104K	B82473A1104K	F	100	0.72	2.14	1.74	1.44	1.19
871-B82473A1224K	B82473A1224K	F	220	0.49	2.14	1.74	1.44	1.19
871-B82473A1474K	B82473A1474K	F	470	0.34	2.14	1.74	1.44	1.19

SMD SERIES B82475

- Enamel Copper Wire Winding Soldered to Terminals
- Plastic Terminal Carrier
- High Current Rating
- Ferrite Core
- Size: 10mm by 10mm
- Low DC Resistance

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Epcos Part No.	Fig.	L (μH)	Idc (A)	Price Each			
					1	10	25	100
871-B82475A1104K	B82475A1104K	G	100	0.97	2.37	1.93	1.59	1.33
871-B82475A1474K	B82475A1474K	G	470	0.42	2.37	1.93	1.59	1.33

