

PANDUIT Cable Ties and Tools



RoHS Compliant This product is RoHS compliant.

A			RoHS Compliant
B			RoHS Compliant
C			RoHS Compliant
D			RoHS Compliant
E			RoHS Compliant
F			RoHS Compliant
G			RoHS Compliant
H			RoHS Compliant
I			RoHS Compliant
J			RoHS Compliant

NYLON 6.6 MARKER TIES WITH TAGS

- Natural Nylon
- UL94V-2 rating
- Used to fasten and identify bundles at the same time

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Tensile Strength (lbs.)	Length (in.)	Max. Bundle Dia. (in.)	Width (in.)	Price Each			
						1	100	500	1000
Nylon 6.6 (Natural)									
644-PLF1M-M	A	18	4.3	0.87	0.098	.33	.25	.22	.20
644-PLM1M-M	B	18	3.9	0.75	0.098	.39	.259	.228	.207
644-PLM2M-M	B	18	8	2	0.098	.45	.39	.35	.31
644-PLM2S-D	B	18	7.4	1.75	0.098	.48	.436	.395	.353
644-PL2M2S-L	C	50	7.4	1.75	0.185	1.79	1.57	1.50	1.35
Weather (UV) Resistant Nylon 6.6 (Black)									
644-PLF1M-M0	A	18	4.3	0.87	0.098	.38	.32	.249	.21
644-PLM2M-M0	B	18	8	2	0.098	.45	.416	.374	.332
Nylon 6.6 Winged Push Mount Ties									
644-PLWP1M-D	D	18	4.3	.87	.098	.32	.256	.253	.227
644-PLWP1.5I-C	D	40	6.0	1.25	.135	.41	.374	.331	.299
644-PLWP1S-C	D	50	5.2	1.00	.190	.43	.395	.353	.32
644-PLWP2S-C	D	50	7.8	1.75	.190	.47	.373	.31	.278
644-PLWP3H-TL	D	120	12.0	3.00	.300	1.00	.91	.813	.738

TAK-TY® HOOK AND LOOP CABLE TIES

- Black
- Material: Nylon loop, polyethylene hook
- Adjustable, releasable and reusable

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Tensile Strength (lbs.)	Length (in.)	Max. Bundle Dia. (in.)	Width (in.)	Price Each			
						1	100	500	1000
644-HLS1.5S-X0	G	50	6.0	1.5	.75	1.13	.956	.906	.865
644-HLT2I-X0	H	40	8.0	1.9	.50	1.33	1.21	1.07	.977
644-HLT2I-X0	H	40	8.0	1.9	.50	1.84	1.67	1.58	1.50
644-HLC3S-X0	I	50	12.0	3.0	.75	1.90	1.76	1.62	1.49
644-HLTP3I-X0	H	50	12.0	3.0	.75	2.24	1.75	1.41	1.34
644-HLS3S-X0	G	50	12.0	3.2	.75	2.16	2.01	1.87	1.73
644-HLSP3S-X0	G	50	12.0	3.2	.75	3.20	2.50	1.99	1.90
644-HLT3I-X0	H	40	12.0	3.2	.50	1.84	1.58	1.44	1.24
644-HLC5S-X0	I	50	18.0	5.0	.75	2.42	2.21	1.83	1.76
644-HLS5S-X0	G	50	18.0	5.0	.75	2.98	2.64	2.48	2.24
644-HLSP5S-X0	G	50	18.0	5.0	.75	4.00	3.13	2.49	2.37
644-HLS-15R0	G	50	180.0	Various	.75	26.14	24.57	23.09	21.71

PAN-STEEL™ STAINLESS STEEL METAL LOCKING

- General Purpose

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Tensile Strength (lbs.)	Length (in.)	Hole Dia. (in.)	Width (in.)	Price Each			
						1	100	500	1000
644-MLT1S-CP	E	100	5.00	1.00	0.18	1.10	.90	.83	.77
644-MLT2S-CP	E	100	7.90	2.00	0.18	1.21	1.13	1.07	.99
644-MLT4H-LP	E	100	14.30	4.00	0.18	1.74	1.62	1.54	1.42
644-MLT4S-CP	E	100	14.20	4.00	0.18	1.45	1.35	1.29	1.19
644-MLT6H-LP	E	100	20.50	6.00	0.18	2.56	2.38	2.27	2.09
644-MLT6S-CP	E	100	20.40	6.00	0.18	2.13	1.99	1.89	1.74

STAINLESS STEEL MARKER PLATE

- Color: Natural
- Long life



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Size (W x L)	Description	Price Each			
			1	100	500	1000
644-MMP350-C	.75" x 3.50"	304 stainless steel	1.26	1.03	.925	.837

ADHESIVE MOUNT/CABLE TIE COMBO

Adhesive mount & cable tie molded as one piece helps reduce inventory costs.

- Color: White
- Locking cable tie

For quantities greater than listed, call for quote.


MOUSER STOCK NO.	Fig.	Tensile Strength (lbs.)	Length (in.)	Max. Bundle Dia. (in.)	Width (in.)	Price Each			
						1	100	500	1000
644-PLA2S-A-Q	F	50	7.30	1.85	.19	1.57	1.40	1.14	1.07

CABLE TIE INSTALLATION TOOLS

- The preferred tool design in the industry
- Lightweight and balanced
- Requires no special maintenance
- Rugged all-steel construction
- Easy to operate

STS2

- Installer controlled tension and cut-off
- Perfect size for pocket or tool box
- Especially suited to maintenance and construction applications
- Installs miniature, intermediate and standard ties




644-STS2 30.16

GTS

- Installs miniature, intermediate and standard cross section cable ties
- Manual tool/lightweight 8.8oz.
- Meets Mil. std. MS90387-1

644-GTS 175.00



GS2B

- Tool controlled tension and cut-off
- Automatic tension and cut-off by squeezing trigger
- Reduces fatigue and increases productivity
- Especially suited to medium production applications
- Q.P.L. per Mil. Std. MS90387-1
- Installs miniature, intermediate and standard ties

644-GS2B 236.95



RoHS Compliant