

# PANDUIT Wiring Accessories



RoHS Compliant This product is RoHS compliant.

## WIRING ACCESSORIES

### Cable Tie Mounts

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Material	Adhesive Type	Mounting Method	Color	Dimensions W x L (in.)	Price Each			
							1	100	500	1000
644-ABM2S-A-D	A	ABS	Rubber	4-way Adh Backed	White	1.0 x 1.0	.75	.615	.555	.424
644-ABM2S-AT-D	A	ABS	Acrylic	4-way Adh Backed	White	1.0 x 1.0	.70	.57	.54	.49
644-ABM3H-A-L	A	Nylon 6.6	Rubber	4-way Adh Backed	White	1.5 x 1.5	1.90	1.83	1.60	1.33
644-ABM1M-A-M	A	Nylon 6.6	Rubber	4-way Adh Backed	White	.50 x .50	.42	.37	.339	.317
644-ABM1M-AT-M	A	Nylon 6.6	Acrylic	4-way Adh Backed	White	.50 x .50	.48	.453	.419	.385
644-ABM100-A-D	A	Nylon 6.6	Rubber	4-way Adh Backed	White	1.0 x 1.0	.76	.724	.683	.652
644-ABM100-AT-D	A	Nylon 6.6	Acrylic	4-way Adh Backed	White	1.0 x 1.0	.72	.638	.566	.514
644-ABMM-A-D	A	ABS	Rubber	4-way Adh Backed	White	.75 x .75	.78	.626	.424	.393
644-ABMM-AT-D	A	ABS	Acrylic	4-way Adh Backed	White	.75 x .75	.66	.597	.545	.484
644-ABM4H-A-T	A	Nylon 6.6	Rubber	4-way Adh Backed	White	2.0 x 2.0	1.47	1.30	1.24	1.11
644-ABMS-A-D	B	Nylon 6.6	Rubber	2-way Adh Backed	Natural	1.13 x 1.13	.80	.69	.61	.48
644-ABMT-A-C	C	Nylon 6.6	Rubber	Rubber	Natural	1.10 x 1.12	1.94	1.67	1.53	1.41
644-PWMS-H2S-C	D	Nylon 6.6	---	Push Barb	Natural	.37 x .75	.42	.353	.322	.27
644-TM1S4-M	E	Nylon 6.6	---	#4 (M2.5) Screw	Natural	.32 x .51	.22	.209	.198	.176
644-TM2S6-M	E	Nylon 6.6	---	#6 (M3) Screw	Natural	.43 x .63	.30	.19	.148	.137
644-TM2S8-M	E	Nylon 6.6	---	#8 (M4) Screw	Natural	.43 x .63	.30	.19	.169	.148
644-TM3S10-M	E	Nylon 6.6	---	#10 (M5) Screw	Natural	.62 x .86	.33	.292	.282	.252
644-TM3S8-M	E	Nylon 6.6	---	#8 (M4) Screw	Natural	.62 x .86	.75	.587	.525	.257
644-TM3S25-M	E	Nylon 6.6	---	1/4 (M6) Screw	Natural	.62 x .86	.32	.298	.278	.257
644-TM3R6-M	E	Nylon 6.6	---	#6 (M3) Rivet	Natural	.62 x .86	.32	.298	.278	.257

### Wire Mounting Devices

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Material	Adhesive Type	Mounting Method	Color	Dimensions W x L (in.)	Price Each			
							1	100	500	1000
644-ARC-68-A-C	F	Polypro.	Rubber	Rubber Adhesive	Natural	1.0 x 1.0	.85	.76	.62	.58
644-ARC-68-A-C14	F	Polypro.	Rubber	Rubber Adhesive	Gray	1.0 x 1.0	.91	.83	.76	.64
644-ARC-68-S6-C	F	Polypro.	---	#6 (M3) Screw	Natural	1.0 x 1.0	.51	.463	.442	.391
644-ARC-68-S6-C14	F	Polypro.	---	#6 (M3) Screw	Gray	1.0 x 1.0	.58	.473	.401	.391
644-ACC19-A-M	G	Nylon 6.6	Rubber	Adhesive Backed	Natural	.62 x .75	.59	.508	.466	.423
644-ACC38-A-M	G	Nylon 6.6	Rubber	Adhesive Backed	Natural	1.0 x 1.0	.63	.572	.54	.519
644-AJC12-A-C	H	PVC	Rubber	Rubber	Lt. Gray	.86 x 1.0	.47	.425	.337	.271
644-AJC25-A-C	H	PVC	Rubber	Rubber	Lt. Gray	.97 x 1.5	.49	.442	.401	.36
644-CCH12-S10-M	I	Nylon 6.6	---	#10 (M5) Screw	Natural	.50 x $\phi$ .125	.15	.123	.103	.072
644-CCH19-S10-M	I	Nylon 6.6	---	#10 (M5) Screw	Natural	.50 x $\phi$ .187	.15	.123	.102	.082
644-CCH25-S10-M	I	Nylon 6.6	---	#10 (M5) Screw	Natural	.50 x $\phi$ .25	.14	.13	.109	.086
644-CCH31-S10-M	I	Nylon 6.6	---	#10 (M5) Screw	Natural	.50 x $\phi$ .312	.15	.102	.082	.072
644-CCH38-S10-M	I	Nylon 6.6	---	#10 (M5) Screw	Natural	.50 x $\phi$ .375	.15	.113	.102	.082
644-CCH44-S10-M	I	Nylon 6.6	---	#10 (M5) Screw	Natural	.50 x $\phi$ .437	.15	.113	.103	.082
644-CCH50-S10-M	I	Nylon 6.6	---	#10 (M5) Screw	Natural	.50 x $\phi$ .500	.15	.113	.103	.082
644-CCS19-S8-M	I	Nylon 6.6	---	#8 (M4) Screw	Natural	.37 x $\phi$ .187	.10	.082	.072	.061
644-CCS25-S8-M	I	Nylon 6.6	---	#8 (M4) Screw	Natural	.37 x $\phi$ .25	.10	.082	.061	.041
644-CCS31-S8-M	I	Nylon 6.6	---	#8 (M4) Screw	Natural	.37 x $\phi$ .312	.10	.082	.072	.061
644-CCS38-S8-C	I	Nylon 6.6	---	#8 (M4) Screw	Natural	.37 x $\phi$ .375	.14	.133	.103	.082
644-CCS44-S8-M	I	Nylon 6.6	---	#8 (M4) Screw	Natural	.37 x $\phi$ .437	.13	.113	.092	.072
644-CCS50-S8-M	I	Nylon 6.6	---	#8 (M4) Screw	Natural	.37 x $\phi$ .500	.13	.113	.092	.072
644-FCC-A-C8	J	PVC	Rubber	Rubber Adhesive	Gray	1.09 x 1.00	.49	.46	.37	.303
644-WS25-50-C	K	Nylon 6.6	---	Push Barb	Natural	.50 H x $\phi$ .25	.38	.337	.294	.25
644-WS50-25-C	K	Nylon 6.6	---	Push Barb	Natural	.25 H x $\phi$ .50	.42	.37	.304	.261
644-WS50-50-C	K	Nylon 6.6	---	Push Barb	Natural	.50 H x $\phi$ .50	.45	.392	.316	.272
644-CBP12-C	L	Nylon 6.6	---	Push Barb	Natural	.125 standoff H	.24	.228	.174	.141
644-CBP25-C	L	Nylon 6.6	---	Push Barb	Natural	.250 standoff H	.26	.216	.175	.144
644-CBP37-C	L	Nylon 6.6	---	Push Barb	Natural	.375 standoff H	.28	.261	.228	.207
644-CBP50-C	L	Nylon 6.6	---	Push Barb	Natural	.500 standoff H	.24	.228	.185	.162
644-CBLS25-C	M	Nylon 6.6	---	Push Barb	Natural	.250 standoff H	.22	.206	.144	.133
644-CBLS50-C	M	Nylon 6.6	---	Push Barb	Natural	.500 standoff H	.24	.226	.185	.154
644-CBLS75-C	M	Nylon 6.6	---	Push Barb	Natural	.750 standoff H	.27	.236	.195	.175

### Flat Cable Mounting Device

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Material	Adhesive Type	Mounting Method	Color	Dimensions W x L (in.)	Price Each			
							1	100	500	1000
644-FCM1-A-C14	N	Nylon 6.6	Rubber	Rubber Adhesive	Gray	1.05 x 2.90	1.29	1.00	.859	.797
644-FCM1.2-A-C14	N	Nylon 6.6	Rubber	Rubber Adhesive	Gray	1.37 x 3.16	1.60	1.25	.947	.906
644-FCM2-A-C14	N	Nylon 6.6	Rubber	Rubber Adhesive	Gray	2.22 x 5.06	1.43	1.11	1.01	.896
644-FCM3.25-A-L14	N	Nylon 6.6	Rubber	Rubber Adhesive	Gray	3.38 x 7.30	2.62	1.70	1.35	1.26
644-FCM1-S6-C14	N	Nylon 6.6	---	#6 (M3) Screw	Gray	1.00 x 2.90	1.30	1.02	.953	.866
644-FCM1.2-S6-C14	N	Nylon 6.6	---	#6 (M3) Screw	Gray	1.37 x 3.16	1.53	1.20	.978	.916
644-FCM2-S6-C14	N	Nylon 6.6	---	#6 (M3) Screw	Gray	2.22 x 5.06	1.68	1.31	1.08	.993

### Latching Clips

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Material	Adhesive Type	Mounting Method	Color	Dimensions W x L (in.)	Price Each			
							1	100	500	1000
644-LC3-A-C8	O	PVC	Rubber	Adhesive Backed	Lt. Gray	.75 x .75	.65	.576	.546	.504
644-LC5-A-C8	O	PVC	Rubber	Adhesive Backed	Lt. Gray	1.01 x 1.01	.62	.556	.525	.484
644-LC10-A-L8	O	PVC	Rubber	Adhesive Backed	Lt. Gray	1.51 x 1.51	.74	.659	.638	.576

### LWC Type

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Material	Adhesive Type	Mounting Method	Color	Dimensions W x L (in.)	Price Each			
							1	100	500	1000
644-LWC19-A-M14	P	Nylon 6.6	Rubber	Rubber Adhesive	Gray	.61 x .85	.40	.37	.327	.304
644-LWC25-A-C14	P	Nylon 6.6	Rubber	Rubber Adhesive	Gray	1.00 x .88	.75	.679	.607	.545
644-LWC38-A-C14	P	Nylon 6.6	Rubber	Rubber Adhesive	Gray	1.0 x 1.0	.79	.632	.599	.567
644-LWC50-A-L14	P	Nylon 6.6	Rubber	Rubber Adhesive	Gray	1.0 x 1.26	1.25	.988	.762	.721

**DIMENSIONS: in. (mm)**

Technical diagrams A through P showing various wiring accessories with dimensions in inches and millimeters. Diagrams include: A) Cable tie mount; B) Cable tie mount; C) Cable tie mount; D) Cable tie mount with dimensions: .22 (5.6), .23 (5.8), .63 (16.0); E) Cable tie mount; F) Cable tie mount; G) Cable tie mount; H) Cable tie mount; I) Cable tie mount; J) Cable tie mount; K) Cable tie mount with dimensions: Max. Dia. (when closed), .187" (4.7) / .192" (4.9) dia. hole in .03" to .08" thick panel, Standoff Height; L) Cable tie mount with dimensions: .170 (4.3), .140 (3.6), .187 Dia. (4.7), A, B, .140 (3.6); M) Cable tie mount with dimensions: .40 (10.2), A, B, .13 (3.3), .22 (5.6), .56 (14.2); N) Cable tie mount; O) Cable tie mount; P) Cable tie mount.

Panduit Wire & Cable Mgmt.