

BELDEN Flat Cable, Magnet and Bus Bar Wire



This product is RoHS compliant.

BELDEN GRAY RIBBON FLAT CABLE

9L280XX Series .50" Pitch Unshielded

- Gray PVC Insulation, with a Red Polarity stripe for proper circuit alignment
- Voltage Rating: 300V RMS

Tinned Copper 28AWG (7x36) Stranded

Belden Part No.	Number of Conductors	100 ft. Spools			
		MOUSER STOCK NO.	Price Per Spool		
			1	2	
9L28009	9	566-9L28009	46.01	43.02	
9L28010	10	566-9L28010	45.62	44.18	
9L28014	14	566-9L28014	63.63	61.65	
9L28015	15	566-9L28015	68.07	63.65	
9L28016	16	566-9L28016	73.61	69.62	
9L28020	20	566-9L28020	91.73	88.86	
9L28025	25	566-9L28025	121.71	113.82	
9L28026	26	566-9L28026	120.28	116.52	
9L28034	34	566-9L28034	168.93	158.93	
9L28040	40	566-9L28040	187.82	179.79	
9L28050	50	566-9L28050	222.23	215.29	
9L28064	64	566-9L28064	285.59	276.66	

9L260XX Series .050" Pitch

- .010" Nom. Wall Gray PVC Insulation
- 300V RMS

Tinned Copper 26AWG (7x36) Stranded.

Belden Part No.	Number of Conductors	100 ft. Spools			
		MOUSER STOCK NO.	Price Per Spool		
			1	2	
9L26010	10	566-9L26010	46.67	45.21	
9L26016	16	566-9L26016	81.99	77.57	
9L26020	20	566-9L26020	103.63	100.40	
9L26026	26	566-9L26026	131.42	127.32	
9L26034	34	566-9L26034	179.54	173.93	

BELDEN SINGLE BELDSOL™ SOLDERABLE MAGNET WIRE

Dual insulated magnet wire that combines the excellent dielectric characteristics of Polyurethane and the known toughness and solvent resistance of a Nylon overcoat. Rated by IEEE tests for 270°F usage and will solder without insulation removal at 750°F. Half Pound Spools

Belden Part No.	AWG Size	Approximate Length (ft.)	Half Pound Spools			
			MOUSER STOCK NO.	Price Per Spool		
				1	2	
8049	18	100	566-8049	51.42	46.35	
8050	20	160	566-8050	50.66	45.66	
8051	22	254	566-8051	50.79	45.78	
8052	24	404	566-8052	51.73	46.63	
8053	26	645	566-8053	46.11	43.75	
8054	28	1020	566-8054	54.84	49.44	
8055	30	1615	566-8055	63.95	57.64	
8056	32	2515	566-8056	65.79	59.30	
8057	34	4060	566-8057	68.95	62.15	
8058	36	6400	566-8058	77.59	69.95	

BELDEN BUS BAR WIRE

Solid Tinned Copper. Made in accordance with the performance requirements of Federal Spec. QQ-W-343G.

Belden Part No.	AWG	Nominal O.D. (in.)	100 ft. Spools		1000 ft. Spools	
			MOUSER STOCK NO.	Price Per 100' Spool	MOUSER STOCK NO.	Price Per 1000' Spool
8012	14	.065	566-8012	88.40	-	-
8013	16	.052	566-8013	58.30	-	-
8019	18	.041	566-8019	40.89	566-8019-1000	288.97
8020	20	.033	566-8020	32.84	-	-
8021	22	.026	566-8021	25.92	566-8021-1000	196.11
8022	24	.021	566-8022	25.30	-	-
8023	26	.016	566-8023	24.47	-	-
8024	28	.013	566-8024	24.17	-	-
8025	30	.010	566-8025	22.38	-	-

BELDEN SHIELDING AND BONDING CABLE

Belden Part No.	Circular Area (CMA)	Stranded	Tubular I.D. (in.)	50 ft. Spools		
				MOUSER STOCK NO.	Price Per Spool	
					1	2
8662	22900	576x34	.781	566-8662-50	323.38	313.28
8669	13300	336x34	.500	566-8669-50	246.57	231.01
8663	6700	168x34	.219	566-8663-50	123.88	116.28



BELDEN RAINBOW FLAT CABLE

9R280XX Series .050" Pitch

- .010" Nom. Wall Color-Coded PVC Insulation
- Voltage Rating: 300V RMS

Tinned Copper 28AWG (7x36) Stranded

Belden Part No.	Number of Conductors	100 ft. Spools			
		MOUSER STOCK NO.	Price Per Spool		
			1	2	
9R28010	10	566-9R28010	111.86	108.36	
9R28014	14	566-9R28014	159.47	154.49	
9R28016	16	566-9R28016	180.70	175.05	
9R28020	20	566-9R28020	224.36	217.35	
9R28026	26	566-9R28026	309.36	278.78	
9R28034	34	566-9R28034	437.15	393.97	
9R28040	40	566-9R28040	472.64	441.98	
9R28060	60	566-9R28060	777.26	700.46	

BELDEN VARI-TWIST® FLAT CABLE

9V280XX Series .050" Pitch

- .010" Nom. Wall Color-Coded PVC Insulation
- Voltage Rating: 300V RMS

Tinned Copper 28AWG (7x36) Stranded

Designed to reduce crosstalk in the balanced mode by twisting the pairs Standard twist length is 18" followed by a 2" flat section of .050" spaced conductor

Belden Part No.	Number of Pairs	100 ft. Spools			
		MOUSER STOCK NO.	Price Per Spool		
			1	2	
9V28010	5	566-9V28010	100.13	97.00	
9V28014	7	566-9V28014	162.17	146.15	
9V28016	8	566-9V28016	181.84	163.86	
9V28026	13	566-9V28026	264.62	247.46	
9V28034	34	566-9V28034	391.61	352.92	
9V28050	25	566-9V28050	497.60	482.05	

BELDEN HEAVY-ARMORED POLY-THERMALEZE® HIGH-TEMPERATURE MAGNET WIRE

Poly-Thermaleze® is a dual coated magnet wire. Its base coat is a cross-linked, modified Polyester. Its top coat is an Amide-Imide Polyester. Rated for 180°C usage and has exceptional ability to resist solvents and abuse in difficult windings. One pound spools.

Belden Part No.	AWG Size	Approximate Length (ft.)	1 Pound Spools			
			MOUSER STOCK NO.	Price Per Spool		
				1	2	
8073	14	80	566-8073	69.39	65.83	
8074	16	126	566-8074	78.99	76.03	
8076	20	315	566-8076	86.05	77.57	
8079	26	1260	566-8079	94.17	84.89	
8080	28	1990	566-8080	100.11	90.25	