

KOBICONN Banana Plugs/Jacks and Binding Posts

KOBICONN

BANANA JACKS

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Description	Dimensions: in.		Price Each			
			H	Dia.	1	10	100	500
16BJ381	A	Chassis mount, red	.67	.44	1.59	1.22	1.11	1.01
16BJ382	A	Chassis mount, black	.67	.44	1.59	1.22	1.11	1.01
164-R104B-EX	B	With nut and solder tab, black	.67	.47	1.09	.84	.76	.69
164-R104R-EX	B	With nut and solder tab, red	.67	.47	1.09	.84	.76	.69
164-R116B-EX	C	With fibre washer, black	.95	.43	.75	.62	.57	.52
164-R116R-EX	C	With fibre washer, red	.95	.43	.75	.62	.57	.52
164-R122B-EX	D	With fibre washer, black	1.22	.43	.75	.62	.57	.52
164-R122R-EX	D	With fibre washer, red	1.22	.43	.75	.62	.57	.52
164-R124B-EX	E	Safety type, black	1.21	.56	1.94	1.53	1.30	1.18
164-R124R-EX	E	Safety type, red	1.21	.56	1.94	1.53	1.30	1.18

BANANA PLUGS

These banana plugs fit all standard banana jacks and are interchangeable with all standard banana plugs. These plugs are available in a variety of styles and sizes to meet all kinds of industrial, OEM, and consumer applications.

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Description	Dimensions: in.		Price Each			
			H	Dia.	1	10	100	500
171-5462	F	Insulated, soft spring plug, red	1.92	.40	1.41	1.01	.92	.84
174-8103B-EX	G	With safety sleeve, black	2.20	.61	3.16	2.43	2.20	2.01
174-8103R-EX	G	With safety sleeve, red	2.20	.61	3.16	2.43	2.20	2.01
174-R130B-EX	H	Audio power point, black	2.47	.46	3.14	2.09	1.90	1.73
174-R130R-EX	H	Audio power point, red	2.47	.46	3.14	2.09	1.90	1.73
174-R802-EX	I	Metal 30A	1.29	.154	1.29	.901	.829	.745
174-R818B-EX	J	Black 10A	1.87	.37	1.67	1.11	1.01	.92
174-R818R-EX	J	Red 10A	1.87	.37	1.67	1.11	1.01	.92
174-R819B-EX	K	Stackable 10A, black	1.88	.52	1.04	.86	.78	.71
174-R819R-EX	K	Stackable 10A, red	1.88	.52	1.04	.86	.78	.71
174-R820B-EX	L	With strain relief 10A, black	2.36	.43	1.22	1.05	.976	.88
174-R820R-EX	L	With strain relief 10A, red	2.36	.43	1.22	1.06	.984	.888
174-R822B-EX	M	Solder cup 10A, black	1.63	.47	1.07	.71	.64	.58
174-R822R-EX	M	Solder cup 10A, red	1.63	.47	1.07	.71	.64	.58
174-R825B-EX	N	In-line plug with cross hole black	2.32	.35	1.58	1.05	.95	.86
174-R825R-EX	N	In-line plug with cross hole red	2.32	.35	1.58	1.05	.95	.86
174-R884-EX	O	Dual plug with wire guide, black	1.55	1.26	3.14	2.09	1.98	1.80
174-R27AB-EX	P	Black, 10A	2.126	.1575	1.83	1.22	1.11	1.01
174-R27AR-EX	P	Red, 10A	2.126	.1575	1.83	1.22	1.11	1.01
174-R887B-EX	Q	Black, 10A	2.122	.1535	2.19	1.46	1.33	1.21
174-R887R-EX	Q	Red, 10A	2.122	.1535	2.19	1.46	1.33	1.21
174-R8104B-EX	R	Black, 30A	2.2835	.2402	3.24	2.16	1.96	1.78
174-R8104R-EX	R	Red, 30A	2.2835	.2402	3.24	2.16	1.96	1.78
174-R8120-EX	S	Fits 4mm Std. Banana Jack, 30A	1.1417	.1299	1.01	.92	.84	.76


INSULATED BINDING POSTS

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Description	Dimensions: in.		Price Each			
			H	Dia.	1	10	100	500
164-R101B-EX	T	With solder tab, black	1.50	.48	1.16	.89	.82	.74
164-R101R-EX	T	With solder tab, red	1.50	.48	1.33	1.03	.93	.85
164-R109B-EX	U	Insulated with 1 nut and washer black	1.97	.45	1.37	.94	.85	.77
164-R109R-EX	U	Insulated with 1 nut and washer red	1.97	.45	1.37	.94	.85	.77
164-R119B-EX	V	With 2 nuts and washer, black	1.84	.56	1.83	1.28	1.16	1.05
164-R119R-EX	V	With 2 nuts and washer, red	1.84	.56	1.83	1.28	1.16	1.05
164-19B2-EX	W	Dual with base black; red and black	1.85	1.36	3.68	3.07	2.79	2.54
164-R126B-EX	X	Heavy duty 30A, black	1.65	.63	2.87	1.99	1.83	1.66
164-R126R-EX	X	Heavy duty 30A, red	1.65	.63	2.87	1.99	1.83	1.66
164-R134B-EX	Y	Gray with black color ring	1.90	.47	1.76	1.17	1.06	.96
164-R134R-EX	Y	Gray with red color ring	1.90	.47	2.10	1.39	1.26	1.14



RoHS Compliant



Kobiconn Audio/Video Connectors