

# NEUTRIK Professional Jacks and Plugs

RoHS Compliant This product is RoHS compliant.

## timbrePLUG

- Standard timbre of the cable plus three additional sound characteristics
- Slim right-angle plug with industry proven and reliable chuck type strain relief

- Sleek attractive design for convenient handling
  - Gold plug finger, precision machined one piece contacts
- For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Neutrik Part No.	Fig.	Description	Price Each			
				1	10	25	50
568-NP2RX-TIMBRE	NP2RX-TIMBRE	A	1/4" Guitar Plug	24.49	22.33	20.42	19.64

## silentPLUG

The silentPLUG automatically mutes (shorts) an instrument (guitar) cable to avoid pops and squeals when changing the instrument (guitar) under load.

MOUSER STOCK NO.	Neutrik Part No.	Fig.	No. of Cont.	Contact Plating	Description	Price Each			
						1	10	25	100
<b>Straight</b>									
568-NP2X-AU-SILENT	NP2X-AU-SILENT	B	2	Gold	Silent Reed switch, red housing	10.50	9.55	8.90	8.21
<b>Right Angle</b>									
568-NP2RX-AU-SILENT	NP2RX-AU-SILENT	B	2	Gold	Silent Reed switch, red housing	12.02	10.96	10.02	9.27

## 1/4" PROFESSIONAL PHONE PLUGS

- Diecast shell
- Chuck-type strain relief
- Soldering terminations

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Neutrik Part No.	Fig.	No. of Cont.	Contact Plating	Description	Price Each			
						1	10	25	100
<b>Straight</b>									
568-NP2X	NP2X	C	2	Nickel	Nickel satin housing	3.60	3.37	2.98	2.78
568-NP2X-B	NP2X-B	C	2	Gold	Black chrome housing	4.44	4.06	3.64	3.35
568-NP3X	NP3X	C	3	Nickel	Nickel satin housing	5.23	4.79	4.42	4.11
568-NP3X-BAG	NP3X-BAG	C	3	Nickel	Black chrome housing	5.55	5.06	4.63	4.21
568-NP2C	NP2C	D	2	Nickel	Nickel satin housing	3.90	3.48	3.26	2.95
568-NP2C-B	NP2C/B	D	2	Gold	Black chrome housing	4.69	4.26	3.96	3.66
568-NP2C-BAG	NP2C-BAG	D	2	Nickel	Black chrome housing	4.09	3.72	3.41	3.15
568-NP3C	NP3C	D	3	Nickel	Nickel satin housing	5.59	5.13	4.63	4.22
568-NP3C-BAG	NP3C-BAG	D	3	Nickel	Black chrome housing	5.96	5.41	4.96	4.57
<b>Right Angle</b>									
568-NP2RX	NP2RX	E	2	Nickel	Nickel satin	5.54	5.04	4.61	4.25
568-NP3RX	NP3RX	E	3	Nickel	Black chrome	7.64	6.97	6.42	5.93
568-NP2RX-BAG	NP2RX-BAG	E	2	Nickel	Nickel satin	5.47	5.02	4.53	4.13
568-NP3RX-BAG	NP3RX-BAG	E	3	Nickel	Black chrome	8.24	7.48	6.84	6.32

## 3.5MM RIGHT ANGLE PROFESSIONAL PHONE PLUGS

- Chuck-type strain relief and rubber gland
- Accepts cables from 2.0 to 4.5 mm
- Slim design - space saving

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Neutrik Part No.	Fig.	No. of Cont.	Contact Plating	Description	Price Each			
						1	10	25	100
568-NTP3RC	NTP3RC	F	3	Nickel	Nickel satin housing	3.98	3.64	3.37	3.10
568-NTP3RCB	NTP3RCB	F	3	Gold	Black chrome housing	5.47	5.02	4.53	4.13

## LOCKING 1/4" JACKS

- Mates with all 1/4 mono or stereo plugs
- Provides secure lockable interconnection with latch release

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Neutrik Part No.	Fig.	Mount	Contact Plating	Description	Price Each			
						1	10	25	50
568-NJ3FC6	NJ3FC6	G	Cable	Silver	Nickel Metal Housing	7.82	7.17	6.48	6.19
568-NJ3FC6-BAG	NJ3FC6-BAG	G	Cable	Silver	Black Metal Housing	8.62	7.69	7.17	6.79
568-NJ3FP6C	NJ3FP6C	H	Chassis	Silver	Nickel Metal Housing	6.68	5.95	5.72	5.41
568-NJ3FP6P-BAG	NJ3FP6P-BAG	H	Chassis	Silver	Black Plastic Housing	5.94	5.41	4.96	4.76
568-NJ3FP6C-BAG	NJ3FP6C-BAG	H	Chassis	Silver	Black Metal Housing	6.71	6.38	6.19	5.96
568-NJ3FP6C-B	NJ3FP6C-B	H	Chassis	Gold	Black Metal Housing	7.96	7.24	6.99	6.72

## M SERIES 1/4" NYLON STANDARD JACKS

- Body material: heavy duty nylon
- Contact material: solid nickel silver
- Mounting hardware included

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Neutrik Part No.	Fig.	Mono	Stereo	Switched	Terminal Type	Nose Type	Price Each			
								1	10	100	500
550-12001	NMJ2HC-S	I	X	-	No	Solder	1	1.08	.974	.825	.762
550-10021	NMJ2HF-S	I	X	-	No	Solder	2	.62	.564	.521	.489
550-10201	NMJ4HFD2	I	X	-	Yes	PCB	2	.85	.776	.697	.611
550-12202	NMJ4HCD2	I	X	-	Yes	PCB	1	1.22	1.10	.942	.826
550-NMJ6HCS	NMJ6HC-S	J	-	X	Yes	Solder	1	1.14	1.05	.966	.892
550-20301	NMJ6HFD2	J	-	X	Yes	PCB	2	.80	.724	.596	.554
550-22302	NMJ6HCD2	J	-	X	Yes	PCB	1	1.38	1.25	1.05	.949
550-25382	NMJ6HHD2	J	-	X	Yes	PCB	3	.76	.69	.644	.56

\*Mounting hardware must be ordered separately.

## 1/4" NYLON SLIM JACKS

### Features:

- 19% space saving advantage over standard socket
- All SlimLine jacks have 1/4 inch PCB horizontal mount pins
- No mounting nuts and washers included, must be purchased separately.
- Body material: heavy duty nylon
- Contact material: solid nickel silver
- Contact resistance: <0.025 MΩ
- Temperature range: 0°C +70°C

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Neutrik Part No.	Fig.	Mono	Stereo	Switched	Terminal Type	Nose Type	Price Each			
								1	10	100	500
550-10284	NRJ4HF	K	X	-	Yes	PCB	2	.48	.438	.406	.375
550-15284	NRJ4HH	K	X	-	Yes	PCB	3	.50	.448	.423	.391
550-20311	NRJ6HF	K	-	X	Yes	PCB	2	.59	.54	.474	.441
550-20384	NRJ6HF-1	K	-	X	Yes	PCB	2	.59	.54	.474	.441
550-25301	NRJ6HH	K	-	X	Yes	PCB	3	.58	.528	.487	.445
550-20311AU	NRJ6HF-AU	K	-	X	Yes	PCB	2	1.78	1.62	1.35	1.20

\*Chassis Grounding

## Nuts and Washers for Standard and Slim Jack Sockets

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Neutrik Part No.	Description	Price Each			
			1	10	100	500
550-1005	NRJNUT-B	Standard plastic nut	.14	.13	.10	.087
550-1002	NRJ-NUT-MK	Ring nut, knurled, nickel-plated brass	.71	.65	.517	.475
550-MW05	NRJ-WB	16 x 1.2mm Washer	.15	.14	.13	.12

