

REAN Commercial Audio Connectors



This product is RoHS compliant.



TINY XLR PLUGS AND RECEPTACLES

- Robust metal housing with best flex relief
- Shielded system – high noise immunity and EMI protection
- Intuitive and rugged locking mechanism provides secure locking system
- Millionfold proven chuck type strain relief

- Keyed insert and strain relief
- Watertight chassis connector, even in unmated condition



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Neutrik Part No.	Fig.	No. of Cont.	Gender	Description	Price Each		
						1	10	25
Cable Mount								
568-RT3FC-B	RT3FC-B	A	3	Female	Black housing, gold contacts	2.54	2.08	1.91
568-RT3FC-B-W	RT3FC-B-W	B	3	Female	Blk Hsg, Au Cont, with sealing boot	3.15	2.59	2.38
568-RT3FCT-B	RT3FCT-B	C	3	Female	Blk Hsg, Au Cont, Screw Locking	3.02	2.65	2.56
568-RT3MC-B	RT3MC-B	D	3	Male	Black housing, gold contacts	2.09	2.00	1.83
568-RT4FC-B	RT4FC-B	A	4	Female	Black housing, gold contacts	2.84	2.58	2.39
568-RT4FC-B-W	RT4FC-B-W	B	4	Female	Blk Hsg, Au Cont, with sealing boot	2.97	2.87	2.76
568-RT4FCT-B	RT4FCT-B	C	4	Female	Blk Hsg, Au Cont, Screw Locking	3.38	2.97	2.87
568-RT4MC-B	RT4MC-B	D	4	Male	Black housing, gold contacts	2.52	2.42	2.21
568-RT5FC-B	RT5FC-B	A	5	Female	Black housing, gold contacts	3.20	2.89	2.69
568-RT5FC-B-W	RT5FC-B-W	B	5	Female	Blk Hsg, Au Cont, with sealing boot	4.02	3.64	3.33
568-RT5FCT-B	RT5FCT-B	C	5	Female	Blk Hsg, Au Cont, Screw Locking	3.70	3.25	3.14
568-RT5MC-B	RT5MC-B	D	5	Male	Black housing, gold contacts	2.92	2.80	2.56
Chassis Mount								
568-RT3MP-B	RT3MP	E	3	Male	Nickel Hsg, Front Mount, Au Cont	1.86	1.79	1.73
568-RT3MPR	RT3MPR	F	3	Male	Nickel Hsg, Rear Mount, Au Cont	1.91	1.83	1.67
568-RT4MP-B	RT4MP	E	4	Male	Nickel Hsg, Front Mount, Au Cont	2.69	2.20	2.00
568-RT4MPR	RT4MPR	F	4	Male	Nickel Hsg, Rear Mount, Au Cont	2.23	2.13	1.95
568-RT5MP	RT5MP	E	5	Male	Nickel Hsg, Front Mount, Au Cont	3.02	2.75	2.53
568-RT5MPR	RT5MPR	F	5	Male	Nickel Hsg, Rear Mount, Au Cont	2.55	2.44	2.23
Adapters								
568-RA3MT-B	RA3MT-B	G	3	Fem/Male	Tiny Female to XLR Male	6.22	5.96	5.45
568-RA3FT-B	RA3FT-B	G	3	Fem/Fem	Tiny Female to XLR Female	6.29	6.03	5.52



COMMERCIAL 1/4" PHONE PLUGS

- Features large cable clamp with solder tabs
- Housing/shell: Brass Ni/Au/Black plated or Zinc diecast
- Insulation: Thermoplastic
- Contacts: Brass, Ni/Au plated
- Strain relief: Crimp type SnCe plated

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Neutrik Part No.	Fig.	Description	Cable O.D.	Price Each		
					1	10	25
1/4" Phone Plugs							
568-NYS201	NYS201	H	Mono, short handle	6mm	1.28	1.16	1.06
568-NYS202	NYS202	H	Stereo, short handle	6mm	1.69	1.63	1.51
568-NYS208	NYS208	-	Stereo, Right Angle, Metal Housing	6mm	1.60	1.46	1.34
568-NYS203	NYS203	I	Mono, plastic handle	6mm	1.32	1.20	1.09
568-NYS204	NYS204	I	Stereo, plastic handle	6mm	1.37	1.26	1.14
568-NYS224	NYS224	H	Mono, long handle	8mm	1.41	1.36	1.23
568-NYS224L	NYS224L	H	Mono, long handle, outlet D=9.5mm	8mm	1.51	1.37	1.26
568-NYS228	NYS228	H	Stereo, long handle	6mm	1.86	1.82	1.79
568-NYS225	NYS225	J	Mono, Nickel lg. shell for speaker cable	8mm	2.70	2.49	2.27
568-NYS225B	NYS225B	J	Mono, black lg. shell for speaker cable	8mm	2.54	2.31	2.12
3.5MM TRS Phone Plugs							
568-NYS231	NYS231	K	Stereo, Tin Cnts, Nickel Shell	4mm	1.02	.938	.856
568-NYS231BG	NYS231BG	K	Stereo, Gold Cnts, Black Shell	4mm	1.51	1.37	1.26
568-NYS231L	NYS231L	K	Stereo, Tin Cnts, Large Nickel Shell	6mm	1.02	.938	.856

COMMERCIAL 1/4" PHONE JACKS

- Mono and stereo jacks
- Stereo jacks feature all contacts switched
- Can be used with panels as thick as 5.5mm with washer and nut (included)
- Housing/shell: Brass Ni/Au/Black plated or Zinc diecast
- Insulation: Thermoplastic
- Contacts: Brass, Ni/Au plated
- Strain relief: Crimp type SnCe plated

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Neutrik Part No.	Fig.	Description	Price Each		
				1	10	25
With Metal Nut/Washer Mounting Hardware						
568-NYS220	NYS220	L	Mono thick panel - mounts flush - nickel/silver	2.28	2.06	1.92
568-NYS220/3	NYS220/3	L	Stereo thick panel - mounts flush - nickel/silver	2.40	2.17	1.99
568-NYS221	NYS221	L	Phone Connectors 1/4" STEREO REAN	2.40	2.17	1.99
568-NYS229	NYS229	M	Open frame - mono- nickel/silver	1.04	.886	.863
568-NYS229L	NYS229L	M	Open frame-mono-6.5mm pnl thickness-nickel/silver	1.02	.925	.853
568-NYS230	NYS230	M	Open frame - stereo - nickel/silver	1.22	1.10	1.02
568-NYS234	NYS234	N	Stereo PCB vertical-TN and RN contacts-plastic/silver	.96	.899	.815
568-NYS234-3	NYS234-3	N	Stereo PCB vertical - no normals - plastic/silver	.72	.657	.604
With Plastic Nut/Washer Mounting Hardware						
568-NYS212	NYS212	O	Stereo - solder tap version - .450"	.72	.658	.584
568-NYS212/2	NYS212/2	O	Mono - solder tap version	.72	.641	.585
568-NYS216	NYS216	O	Stereo - PC Horizontal - .322" length contacts	.72	.658	.584
568-NYS216/2	NYS216/2	O	Mono - PC Horizontal - .322" length contacts	.72	.641	.585
568-NYS218	NYS218	O	Stereo - PC Horizontal - .590" length contacts	.72	.641	.585
568-NYS218/2	NYS218/2	O	Mono - PC Horizontal - .590" length contacts	.72	.658	.584
568-NYS219	NYS219	O	Stereo - PC Horizontal - .492" length contacts	.72	.658	.584
568-NYS219/2	NYS219/2	O	Mono - PC Horizontal - .492" length contacts	.72	.641	.585
With Chrome Ferrule Mounting Hardware						
568-NYS215	NYS215	O	Stereo - PC Horizontal - chrome ferrule	.82	.745	.682
Inline Cable Mount Jack						
568-NYS2202P	NYS2202P	P	Mono - Cable Mount Inline Jack, Solder, nickel/silver	1.65	1.52	1.39

PHONO (RCA) CONNECTORS

- Heavy duty all metal phono plugs with long handle
- Phono plug accepts cable OD up to 0.25"
- Housing/handle: Brass Ni/Au black plated or Zinc diecast
- Insulation: Thermoplastic
- Contacts: Brass Ni/Au plated

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Neutrik Part No.	Fig.	Description	Contacts	Price Each		
					1	10	25
568-NYS352	NYS352	Q	Plug, Nickel shell	Silver	1.05	.896	.874
568-NYS352G	NYS352G	Q	Plug, Nickel shell	Gold	1.40	1.27	1.18
568-NYS355	NYS355	R	Adapter, Nickel shell	Silver	1.71	1.63	1.52