

TE Modular Jacks and Cat 5e Cables



This product is RoHS compliant.

MULTI-PORT/STACKED R/A MODULAR JACKS WITHOUT PANEL STOPS

Specifications:

- Current Rating: 1.5 amp max. @ 25°C
- Voltage Rating: 150 VAC max.
- Durability: 750 mating cycles
- Operating Temperature: -40°C to 70°C
- Standard Housing: Polysulfone, Black UL 94V-0 rated

Features:

- Meets or exceeds FCC Part 68 rules & regulations

Through-Hole, PCB Termination - Solder

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	Positions-Contacts	Config.	Description	Price Each		
						1	25	50
Standard Profile without Shield								
571-5557785-1	5557785-1	A	8/8	1x1	Cat 3, without Ground Options	1.67	1.63	1.44
571-5558065-1	5558065-1	A	10/10	1x1	Cat 3, without Ground Options	3.42	2.59	2.54
571-5557562-1	5557562-1	A	8/8	1x4	Cat 4, without Ground Options	5.89	5.33	4.70
571-5557566-1	5557566-1	A	8/8	1x8	Cat 4, without Ground Options	15.23	13.85	12.71
571-5557560-1	5557560-1	A	8/8	1x2	Cat 4, without Ground Options	3.17	2.75	2.44
571-5557561-1	5557561-1	A	8/8	1x3	Cat 4, without Ground Options	10.61	9.10	8.03
Standard Profile with Shield								
571-5558503-1	5558503-1	B	8/8	1x4	Cat 5, PCB Ground Options	13.47	12.64	12.15
571-6339169-3	6339169-3	B	8/8	1x8	Cat 5, Panel and PCB Ground Options; 27 Panel Ground Tabs	13.55	11.77	10.40

Low Profile with Shield

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	Positions-Contacts	Config.	Description	Price Each		
						1	25	50
PCB Termination - Solder								
571-5569262-1	5569262-1	C	8/8	2x4	Cat 5, Panel and PCB Ground Options	14.39	13.24	12.10
571-5569264-1	5569264-1	C	8/8	2x8	Cat 5, Panel and PCB Ground Options	34.66	29.64	27.94
571-5569381-1	5569381-1	C	8/8	2x1	Cat 5, Panel and PCB Ground Options	12.01	9.86	8.55
571-6368011-1	6368011-1	C	8/8	2x1	Cat 5, Panel and PCB Ground Options	28.87	23.09	21.00
PCB Termination - Press-Fit								
571-6116317-6	6116317-6	C	8/8	2x8	Cat 5, Panel and PCB Ground Options	73.37	63.09	55.76

Hybrid - RJ45/ Dual USB

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	Positions-Contacts	Config.	LED	Description	Price Each		
							1	25	50
571-6116151-1	6116151-1	D	8/8	2x1	-	Shielded, Cat 3, PCB Ground Options	12.11	10.87	10.28

RJ45 MODULAR JACKS WITH SHIELD

Features:

- Meets the requirements for I/O connectors on Advanced TCA & AMC cards
- Fits in an AMC compact module faceplate
- Panel & PCB Ground Options
- 4.20mm max above PCB
- 7.38mm max below PCB

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	Positions-Contacts	Config.	LED	Description	Price Each		
							1	25	50
571-1888250-1	1888250-1	E	8/8	1X1	Green/Yel	Cat 5e, Solder	4.77	4.34	3.98
571-1888250-3	1888250-3	E	8/8	1X1	-	Cat 5e, Solder	4.93	3.94	3.58

OFFSET, STACKED RJ45 MODULAR JACKS WITH SHIELD

Features:

- Offset designed to meet both AdvancedTCA and AdvancedMC standards
- Category 5 performance
- Press fit termination to the board

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	Positions-Contacts	Config.	LED	Description	Price Each		
							1	25	50
571-1888653-2	1888653-2	F	8/8	2x1	Green	Cat 5, Panel Ground Options	17.56	15.94	14.62
571-1888654-3	1888654-3	F	8/8	2x8	-	Cat 5, Panel Ground Options	70.88	65.97	62.10

CATEGORY 5e PATCH CORD CABLE ASSEMBLIES

Unshielded 4 Pair RJ45 to RJ45

Specifications:

- EIA/TIA-568A wired
- Enhanced performance
- Exceeds Category 5 performance standards
- Cable: 24 AWG, stranded, non-plenum, unshielded

Features:

- Colored boots
- Colored cables

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	Color	Length	Price Each			
					1	25	50	100
571-2192413	219241-3	G	Gray	3 ft.	8.66	8.30	7.71	7.28
571-2192423	219242-3	G	Blue	3 ft.	8.07	7.38	6.81	6.50
571-2192417	219241-7	G	Gray	7 ft.	11.56	10.40	9.82	9.23
571-2192427	219242-7	G	Blue	7 ft.	10.03	9.33	8.46	8.08
571-2192437	219243-7	G	Green	7 ft.	11.27	10.84	10.49	10.04
571-2192447	219244-7	G	Red	7 ft.	11.27	10.85	10.52	10.06
571-12192414	1-219241-4	G	Gray	14 ft.	15.72	14.97	14.27	13.75
571-12192424	1-219242-4	G	Blue	14 ft.	15.73	14.97	14.27	13.75
571-12192434	1-219243-4	G	Green	14 ft.	15.02	13.49	12.75	11.97
571-12192444	1-219244-4	G	Red	14 ft.	15.02	13.49	12.75	11.97

