

TE .100" IDC Headers



FLAT & NARROW FLAT HEADERS

- Housing: UL94V-0 rated, polyester, natural color
- Posts: Copper alloy, tin plated



RoHS Compliant This product is RoHS compliant.

FRICITION LOCK HEADERS

- Posts: Copper alloy, tin plated or gold over nickel
- Housing: UL94V-0 rated, polyester, natural color

For quantities greater than listed, call for quote.

Flat For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	No. of Pos.	Price Each		
				1	10	100
Straight Post						
571-6404522	640452-2	A	2	.38	.357	.249
571-6404523	640452-3	A	3	.35	.249	.21
571-6404524	640452-4	A	4	.37	.333	.319
571-640452-5	640452-5	A	5	.62	.58	.45
571-6404526	640452-6	A	6	.68	.641	.491
571-6404527	640452-7	A	7	.80	.74	.57
571-6404528	640452-8	A	8	.81	.72	.626
571-16404520	1-640452-0	A	10	1.03	.90	.78
571-16404522	1-640452-2	A	12	1.35	1.19	1.15
571-16404524	1-640452-4	A	14	1.56	1.40	1.35
571-16404526	1-640452-6	A	16	2.34	2.08	2.01
Right Angle Post						
571-6404532	640453-2	B	2	.23	.22	.17
571-6404533	640453-3	B	3	.32	.276	.265
571-6404534	640453-4	B	4	.46	.433	.332
571-6404535	640453-5	B	5	.65	.611	.468
571-6404536	640453-6	B	6	.66	.533	.511
571-6404537	640453-7	B	7	.73	.572	.53
571-6404538	640453-8	B	8	.86	.75	.651
571-6404539	640453-9	B	9	.85	.666	.604
571-16404530	1-640453-0	B	10	1.04	.894	.758
571-16404532	1-640453-2	B	12	1.29	1.13	.977
571-16404534	1-640453-4	B	14	1.47	1.31	1.06
571-16404536	1-640453-6	B	16	2.10	1.87	1.52

Narrow Flat For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	No. of Pos.	Price Each		
				1	10	100
Straight Post						
571-3-644456-2	3-644456-2	A	2	.22	.167	.136
571-3-644456-3	3-644456-3	A	3	.21	.183	.17
571-3-644456-4	3-644456-4	A	4	.23	.20	.192
571-3-644456-5	3-644456-5	A	5	.31	.267	.256
571-3-644456-6	3-644456-6	A	6	.35	.30	.288
571-4-644456-0	4-644456-0	A	10	.63	.58	.45
571-4-644456-6	4-644456-6	A	16	1.05	.853	.717
Straight Post with Retentive Leg						
571-3-644695-2	3-644695-2	A	2	.30	.29	.20
571-3-644695-3	3-644695-3	A	3	.44	.42	.29
571-3-644695-4	3-644695-4	A	4	.48	.435	.368
571-3-644695-5	3-644695-5	A	5	.60	.555	.393
571-3-644695-6	3-644695-6	A	6	.75	.70	.54
571-3-644695-9	3-644695-9	A	9	1.05	.915	.753
Right Angle Post						
571-3-644457-2	3-644457-2	B	2	.20	.156	.146
571-3-644457-3	3-644457-3	B	3	.38	.34	.25
571-3-644457-4	3-644457-4	B	4	.38	.302	.279
571-3-644457-5	3-644457-5	B	5	.48	.374	.356
571-3-644457-6	3-644457-6	B	6	.53	.416	.382
571-3-644457-8	3-644457-8	B	8	.70	.624	.52

SHROUDED HEADERS

- Housing: UL94V-0 rated, polyester, natural color
- Posts: Copper alloy, tin plated

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	No. of Pos.	Price Each		
				1	10	100
Straight Post						
571-2-644486-2	2-644486-2	C	2	.66	.65	.49
571-2-644486-3	2-644486-3	C	3	.74	.67	.54
571-2-644486-4	2-644486-4	C	4	.77	.71	.55
571-2-644486-5	2-644486-5	C	5	.94	.77	.71
571-2-644486-6	2-644486-6	C	6	1.02	.89	.75
571-2-644486-7	2-644486-7	C	7	1.17	.946	.839
571-2-644486-8	2-644486-8	C	8	.51	.404	.354
571-2-644486-9	2-644486-9	C	9	1.57	1.28	1.13
571-3-644486-0	3-644486-0	C	10	1.58	1.32	1.19
571-3-644486-4	3-644486-4	C	14	2.43	1.94	1.73
Right Angle Post						
571-2-644488-2	2-644488-2	D	2	.35	.281	.253
571-2-644488-3	2-644488-3	D	3	.60	.55	.42
571-2-644488-4	2-644488-4	D	4	.79	.74	.57
571-2-644488-5	2-644488-5	D	5	.93	.717	.658
571-2-644488-7	2-644488-7	D	7	1.26	1.13	.911

MOUSER STOCK NO.	TE Part No.	Fig.	No. of Pos.	Price Each		
				1	10	100
Straight Post, Tin Plated						
571-6404562	640456-2	E	2	.17	.097	.08
571-6404563	640456-3	E	3	.18	.118	.114
571-6404564	640456-4	E	4	.25	.141	.131
571-6404565	640456-5	E	5	.28	.20	.183
571-6404566	640456-6	E	6	.29	.22	.20
571-6404567	640456-7	E	7	.31	.25	.24
571-6404568	640456-8	E	8	.33	.314	.256
571-6404569	640456-9	E	9	.54	.49	.418
571-16404560	1-640456-0	E	10	.37	.317	.304
571-16404562	1-640456-2	E	12	.61	.494	.474
571-16404564	1-640456-4	E	14	.75	.714	.655
571-16404566	1-640456-6	E	16	1.34	1.18	1.01

MOUSER STOCK NO.	TE Part No.	Fig.	No. of Pos.	Price Each		
				1	10	100
Straight Post, Gold Plated						
571-3-641215-2	3-641215-2	E	2	.58	.546	.417
571-3-641215-3	3-641215-3	E	3	.72	.654	.625
571-3-641215-4	3-641215-4	E	4	1.06	.929	.801
571-3-641215-5	3-641215-5	E	5	1.35	1.22	1.06
571-3-641215-6	3-641215-6	E	6	1.60	1.38	1.19
571-3-641215-7	3-641215-7	E	7	1.80	1.43	1.28
571-3-641215-8	3-641215-8	E	8	1.19	1.08	1.03
571-4-641215-0	4-641215-0	E	10	2.31	2.01	1.72
571-4-641215-2	4-641215-2	E	12	2.79	2.25	1.97
571-4-641215-4	4-641215-4	E	14	3.43	2.99	2.43
571-4-641215-6	4-641215-6	E	16	5.77	5.07	4.11

MOUSER STOCK NO.	TE Part No.	Fig.	No. of Pos.	Price Each		
				1	10	100
Right Angle Post, Tin Plated						
571-6404572	640457-2	F	2	.11	.105	.087
571-6404573	640457-3	F	3	.23	.139	.113
571-6404574	640457-4	F	4	.25	.152	.141
571-6404575	640457-5	F	5	.51	.32	.261
571-6404576	640457-6	F	6	.36	.291	.28
571-6404577	640457-7	F	7	.49	.41	.29
571-6404578	640457-8	F	8	.42	.37	.34
571-6404579	640457-9	F	9	.35	.32	.27
571-16404570	1-640457-0	F	10	.51	.48	.36
571-16404572	1-640457-2	F	12	.40	.38	.31
571-16404574	1-640457-4	F	14	.52	.458	.375
571-16404576	1-640457-6	F	16	.51	.447	.433

MOUSER STOCK NO.	TE Part No.	Fig.	No. of Pos.	Price Each		
				1	10	100
Right Angle Post, Gold Plated						
571-3-641216-5	3-641216-5	F	5	1.80	1.43	1.28
571-4-641216-0	4-641216-0	F	10	2.60	2.27	1.84
571-4-641216-6	4-641216-6	F	16	6.83	6.13	4.88

POLARIZED HEADERS

- Housing: UL94V-0 rated, polyester, natural color
- Posts: Copper alloy, tin plated or gold over nickel
- No 16 Position in Gold

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	No. of Pos.	Price Each		
				1	10	100
Straight Post, Tin Plated						
571-640454-2	640454-2	E	2	.10	.08	.077
571-640454-3	640454-3	E	3	.25	.162	.099
571-640454-4	640454-4	E	4	.21	.14	.114
571-640454-5	640454-5	E	5	.23	.196	.178
571-640454-6	640454-6	E	6	.25	.21	.19
571-640454-7	640454-7	E	7	.36	.29	.24
571-640454-8	640454-8	E	8	.34	.27	.259
571-640454-9	640454-9	E	9	.50	.47	.36
571-16404540	1-640454-0	E	10	.42	.374	.361
571-1640454-2	1-640454-2	E	12	.74	.69	.52
571-1640454-4	1-640454-4	E	14	.74	.69	.53
571-1640454-6	1-640454-6	E	16	.94	.83	.677

MOUSER STOCK NO.	TE Part No.	Fig.	No. of Pos.	Price Each		
				1	10	100
Straight Post, Gold Plated						
571-3-641213-2	3-641213-2	E	2	.52	.42	.367
571-3-641213-3	3-641213-3	E	3	.83	.73	.61
571-3-641213-4	3-641213-4	E	4	1.03	.819	.732
571-3-641213-5	3-641213-5	E	5	1.38	1.21	1.04
571-3-641213-6	3-641213-6	E	6	1.55	1.22	1.10
571-3-641213-8	3-641213-8	E	8	1.11	.956	.79

MOUSER STOCK NO.	TE Part No.	Fig.	No. of Pos.	Price Each		
				1	10	100
Right Angle Post, Tin Plated						
571-6404552	640455-2	F	2	.10	.09	.057
571-6404553	640455-3	F	3	.10	.082	.079
571-6404554	640455-4	F	4	.17	.12	.105
571-6404555	640455-5	F	5	.15	.139	.129
571-6404556	640455-6	F	6	.21	.158	.146
571-640455-7	640455-7					