


HARWIN PCB Receptacles and Pins



RoHS Compliant This product is RoHS compliant.



PCB TURNED TERMINALS

• Material: Brass with tin plating ** Solder Pot

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Harwin Part No.	Fig.	Dimensions: mm							Price Each			
			A	B	C	D	Thru Hole Ø	Panel Thickness	Mounting Hole Ø	1	10	25	
Terminal Pins													
855-H2174-01	H2174-01	A	4.30	-	-	-	-	-	1.60	1.04/1.14	.39	.27	.23
855-H2175-01	H2175-01	A	5.00	-	-	-	-	-	1.60	1.04/1.14	.32	.22	.21
855-H2173-01	H2173-01	A	8.10	-	-	-	-	-	1.60	1.04/1.14	.45	.31	.27
855-H2176-01	H2176-01	A	9.50	-	-	-	-	-	1.60	1.04/1.14	.40	.24	.20
855-H2170-01	H2170-01	A	13.20	-	-	-	-	-	1.60	1.04/1.14	.50	.35	.30
855-H2101A01	H2101A01	B	6.50	2.40	0.96	-	-	-	1.60	1.79/1.87	.43	.26	.20
855-H2105A01	H2105A01	B	4.50	2.40	0.81	-	-	-	1.60	1.33/1.41	.55	.38	.30
855-H2106A01	H2106A01	B	4.50	2.40	0.81	-	-	-	2.40	1.33/1.41	.50	.35	.28
855-H3108-01	H3108-01	C	5.70	1.00	0.50	-	-	-	1.00	.50/.55	.43	.26	.19
855-H2101B01	H2101B01	D	6.75	2.40	0.96	-	-	-	1.60	1.79/1.87	.50	.35	.30
855-H2105B01	H2105B01	D	4.70	2.40	0.81	-	-	-	1.60	1.33/1.41	.55	.38	.30
855-H2157-01	H2157-01	E	1.4 max	2.00	9.80	1.21	-	-	1.60	1.30/1.40	.42	.26	.20
855-H3150-01	H3150-01	E	0.50	1.60	5.40	0.97	-	-	1.60	.99/1.04	.32	.19	.15
855-H3151-01	H3151-01	F	4.40	1.60	4.00	-	-	-	1.60	.99/1.04	.46	.32	.27
855-H2101-01	H2101-01	G	6.00	6.60	2.40	0.91	-	-	1.60	1.79/1.87	.55	.38	.30
855-H2105-01	H2105-01	G	4.50	3.45	2.40	0.81	-	-	1.60	1.33/1.41	.39	.24	.20
Lugs													
855-H9001-01	H9001-01	H	2.40	1.57	-	-	-	-	1.60	1.25/1.33	.48	.30	.25
855-H9004-01	H9004-01	H	4.75	3.18	-	-	-	-	1.60	2.01/2.09	.50	.35	.30
855-H2121-01	H2121-01	I	5.15	3.18	-	-	-	-	1.60	1.69/1.74	.50	.35	.30
855-H9020-01	H9020-01	J	7.65	3.18	-	-	-	-	1.60	2.35/2.45	.60	.42	.37
855-H2071Z01	H2071Z01	K	9.10	4.75	1.70	7.55	1.70	2.40	2.68/2.78	.87	.67	.60	
855-H2072-01	H2072-01	K	6.35	3.95	1.40	5.15	1.40	1.60	2.17/2.27	.48	.45	.435	
855-H2072Z01	H2072Z01	K	6.50	3.95	1.17	5.30	1.17	1.60	2.01/2.11	.65	.50	.45	
855-H2072ZL1	H2072ZL1	K	6.50	3.95	1.17	5.30	1.17	2.40	2.01/2.11	.68	.53	.47	
855-H2073Z01	H2073Z01	K	9.10	4.75	1.70	7.55	1.70	3.20	2.68/2.78	.55	.38	.32	
855-H2074Z01	H2074Z01	K	8.75	6.35	2.77	7.15	2.77	3.20	3.93/4.03	1.11	.91	.80	
855-H2051-01	H2051-01	L	4.80	3.18	0.65	2.40	1.02	1.60	1.60/1.68	.47	.32	.28	
855-H2055-01	H2055-01	L	6.35	3.18	1.20	3.18	1.70	2.40	2.4/2.48	.47	.32	.27	
855-H2039-01	H2039-01	M	12.70	5.55	1.50	7.95	2.18	3.20	3.19/3.27	.70	.64	.573	
855-H9023-01	H9023-01	N	3.95	1.83	0.70	2.25	-	1.60	1.28/1.38	.49	.38	.33	
** 855-H9026-01	H9026-01	O	6.35	3.18	-	3.18	1.10	2.40	1.84/1.94	.51	.40	.37	

PCB SOCKETS

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Harwin Part No.	Fig.	Dimensions: mm							Price Each		
			A	B	C	D	Max. Pin Length	Mating Pin Size Ø	Mounting Hole Ø	1	10	25
Sub Miniature Sockets for Ø0.5mm Pins												
855-H3153-01	H3153-01	P	3.61	1.45	0.43	0.99	3.15	0.46-0.51	1.00/1.10	.43	.27	.20
855-H3155-01	H3155-01	Q	3.61	1.45	1.30	0.99	3.15	0.46-0.51	1.00/1.10	.36	.25	.23
855-H3190-01	H3190-01	R	3.00	1.45	0.43	0.99	2.40	0.46-0.51	1.00/1.10	.48	.33	.27
855-H3191-01	H3191-01	S	4.90	1.45	0.43	0.99	4.70	0.46-0.51	1.00/1.10	.55	.38	.333
855-H3192-01	H3192-01	T	7.54	1.45	0.43	0.99	3.15	0.46-0.51	1.00/1.10	.60	.42	.35
PC Board Sockets for Ø0.8mm Pins												
855-H8505-01	H8505-01	U	3.70	2.67	2.35	1.90	4.35	0.75-0.85	1.91/2.01	.61	.47	.44
855-H8501-01	H8501-01	V	5.00	2.35	1.00	1.90	4.50	0.75-0.85	1.91/1.96	.53	.41	.38
855-H8502-01	H8502-01	W	5.90	2.35	2.25	1.85	4.85	0.60-0.85	1.91/1.96	.55	.38	.33
855-H8504-01	H8504-01	X	5.00	2.35	1.00	1.90	4.50	0.75-0.85	1.91/1.96	.36	.345	.315
PC Board Sockets for 1mm Pins												
855-H3165-01	H3165-01	Y	3.75	2.67	2.20	1.90	4.85	0.90-1.05	1.91/1.96	.55	.38	.33
855-H3182-01	H3182-01	Z	3.75	2.67	2.20	1.90	4.85	0.90-1.05	1.91/2.01	.50	.35	.30
855-H3161-01	H3161-01	AA	4.75	2.35	0.50	1.90	4.60	0.90-1.05	1.91/1.96	.37	.25	.22
855-H3183-01	H3183-01	BB	4.95	2.35	0.60	1.90	4.70	0.90-1.05	1.91/2.01	.49	.34	.30
855-H3163-01	H3163-01	CC	3.28	3.28	4.85	2.18	4.85	0.90-1.05	1.91/1.96	.55	.409	.358
855-H3169-01	H3169-01	DD	5.20	3.28	0.90	2.18	---	0.90-1.05	2.19/2.24	.57	.44	.40
855-H3185-01	H3185-01	EE	5.20	3.28	0.90	2.18	---	0.90-1.05	2.19/2.24	.49	.38	.35
855-H3194-01	H3194-01	FF	4.10	3.28	4.70	1.02	4.50	0.90-1.05	2.37/2.47	1.54	1.27	1.07
PC Board Sockets for 2mm Pins												
855-H3490-01	H3490-01	GG	10.60	4.75	2.60	3.65	8.50	1.9-2.2	3.77/3.67	1.37	1.13	1.05
855-H3492-01	H3492-01	HH	8.00	4.75	0.90	4.00	6.30	1.9-2.2	4.02/4.12	1.33	1.10	1.00