

MOLEX Tools for Terminals and Splices

HAND TOOLS FOR TERMINALS AND SPLICES

Features:

- Premium grade and service grade hand tools
- Service grade ratchet and non-ratchet

For quantities greater than listed, call for quote.

| MOUSER STOCK NO. | Molex Part No. | Description | Price Each | |
|--------------------------------|----------------|---|------------|--------|
| | | | 1 | 5 |
| 538-64001-0100 | 64001-0100 | Premium grade ratchet hand tool for closed barrel, 10-22AWG insulated terminals and splices | 256.76 | 246.13 |
| 538-64003-0100 | 64003-0100 | Premium grade ratchet hand tool for closed barrel, 10-22AWG uninsulated terminals and splices | 248.85 | 238.55 |
| 538-64001-0600 | 64001-0600 | Premium grade ratchet hand tool for 10-22AWG nylon closed end connectors | 395.01 | 378.67 |
| 538-64001-7400 | 64001-7400 | Premium grade ratchet hand tool for closed barrel, 10-22AWG Perma-Seal terminals and splices | 526.68 | 504.90 |
| 538-64001-4500 | 64001-4500 | Premium grade ratchet hand tool for closed barrel, 10-22AWG Perma-Seal step down butt splices and 14-22AWG fully insulated quick disconnect couplers for male and female | 395.01 | 383.15 |
| 538-64016-0038 | 64016-0038 | Service grade ratchet hand tool for closed barrel, 10-22AWG non-insulated terminals and splices | 36.23 | 34.01 |
| 538-64016-0036 | 64016-0036 | Service grade ratchet hand tool for closed barrel, 10-22AWG insulated terminals and splices | 34.50 | 34.20 |
| 538-64016-0042 | 64016-0042 | Service grade ratchet hand tool for closed barrel, step down butt splices 10-22AWG and 14-22AWG male and female fully insulated quick disconnects | 32.00 | 31.00 |
| 538-64016-0041 | 64016-0041 | Service grade ratchet hand tool for closed barrel, 10-22AWG Perma-Seal terminals and splices | 31.00 | 30.90 |
| 538-64016-0039 | 64016-0039 | Service grade non-ratchet multi-function hand tool for 10-22AWG insulated and non-insulated terminals strips and cuts wire 10-22AWG and cuts a variety of screw sizes | 6.40 | 5.47 |
| 538-64001-0200 | 64001-0200 | Premium grade ratchet hand tool for closed barrel, 10-22AWG insulated quick disconnects | 256.76 | 249.05 |
| 538-64001-2300 | 64001-2300 | Premium grade ratchet hand tool for Avikrimp® and InsulKrimp® closed barrel, 18-22AWG snap plug receptacles | 342.34 | 332.06 |
| 538-64003-1100 | 64003-1100 | Premium grade ratchet hand tool for KrimpTite® closed barrel, 14-22AWG non-insulated quick disconnects and bullet receptacles | 312.95 | 295.58 |
| 538-64001-4300 | 64001-4300 | Premium grade ratchet hand tool for Avikrimp® closed barrel, 14-22AWG fully insulated quick disconnect flags | 394.90 | 378.67 |
| 538-64001-2800 | 64001-2800 | Premium grade ratchet hand tool for Avikrimp® closed barrel, 10-12AWG fully insulated quick disconnect flags | 342.34 | 332.06 |
| 538-64001-4700 | 64001-4700 | Premium grade ratchet hand tool for InsulKrimp® closed barrel, 14-22AWG male and female fully insulated quick disconnect couplers, Perma-Seal quick disconnect couplers and snap plug receptacles, conductor only crimp | 342.34 | 332.06 |
| 538-64001-0800 | 64001-0800 | Premium grade ratchet hand tool for Avikrimp® closed barrel, 18-22AWG female fully insulated quick disconnects | 394.90 | 378.67 |
| 538-64001-2600 | 64001-2600 | Premium grade ratchet hand tool for Avikrimp® closed barrel, 14-22AWG male fully insulated quick disconnects | 302.00 | 301.00 |
| 538-64001-0400 | 64001-0400 | Premium grade ratchet hand tool for InsulKrimp® closed barrel, 10-22AWG quick disconnect terminals | 302.84 | 290.31 |
| 538-64001-5200 | 64001-5200 | Premium grade ratchet hand tool for Avikrimp® closed barrel, 24-26AWG female fully insulated quick disconnects, conductor crimp only | 342.34 | 332.06 |
| 538-64001-4600 | 64001-4600 | Premium grade ratchet hand tool for Avikrimp® closed barrel, 10-12AWG male quick disconnects | 316.00 | 302.94 |
| 538-64001-4900 | 64001-4900 | Premium grade ratchet hand tool for Avikrimp® closed barrel, 10-16AWG fully insulated quick disconnect female couplers and Perma-Seal fully insulated snap plug receptacles | 342.34 | 332.06 |
| 538-64016-0037 | 64016-0037 | Service grade ratchet hand tool for closed barrel, 10-22AWG insulated quick disconnects | 30.75 | 30.75 |
| 538-19284-0034 | 19284-0034 | Premium grade ratchet hand tool for heavy duty ring tongue terminals | 125.10 | 115.05 |

Terminals

Molex

TERMINAL TO HAND TOOL MATRIX

| MOUSER STOCK NO. | Molex Premium Grade Ratchet Hand Tool | Molex Service Grade Ratchet Hand Tool | Molex Service Grade Non-Ratchet Hand Tool |
|------------------|---------------------------------------|---------------------------------------|---|
| 538-19069-xxxx | 64003-0100 | 64016-0038 | 64016-0039 |
| 538-19070-xxxx | 64001-0100 | 64016-0036 | 64016-0039 |
| 538-19073-xxxx | 64001-0100 | 64016-0036 | 64016-0039 |
| 538-19099-xxxx | 64001-0100 | 64016-0036 | 64016-0039 |
| 538-19144-xxxx | 64001-0100 | 64016-0036 | 64016-0039 |
| 538-19198-xxxx | 64001-0100 | 64016-0036 | 64016-0039 |
| 538-19121-xxxx | 64001-0100 | 64016-0036 | 64016-0039 |
| 538-19127-xxxx | 64001-0100 | 64016-0036 | 64016-0039 |
| 538-19154-xxxx | 64001-0100 | 64016-0036 | 64016-0039 |
| 538-19160-xxxx | 64001-0600 | - | - |
| 538-19003-0071 | 64001-5200 | - | - |
| 538-19003-0064 | 64001-5200 | - | - |
| 538-19003-0001 | 64001-0400 | 64016-0042 | 64016-0039 |
| 538-19003-0129 | 64001-0400 | 64016-0042 | 64016-0039 |
| 538-19003-0011 | 64001-0400 | 64016-0042 | 64016-0039 |
| 538-19003-0040 | 64001-0400 | 64016-0042 | 64016-0039 |
| 538-19003-0044 | 64001-0400 | 64016-0042 | 64016-0039 |
| 538-19003-0050 | 64001-0400 | 64016-0042 | 64016-0039 |
| 538-19001-0001 | 64001-2600 | 64016-0042 | 64016-0039 |
| 538-19001-0003 | 64001-2600 | 64016-0042 | 64016-0039 |
| 538-19001-0006 | 64001-2600 | 64016-0042 | 64016-0039 |
| 538-19001-0008 | 64001-2600 | 64016-0042 | 64016-0039 |
| 538-19001-0010 | 64001-4600 | - | 64016-0039 |
| 538-19002-0001 | 64001-0800 | 64016-0042 | 64016-0039 |
| 538-19002-0005 | 64001-0800 | 64016-0042 | 64016-0039 |
| 538-19002-0009 | 64001-0800 | 64016-0042 | 64016-0039 |
| 538-19002-0013 | 64001-0800 | 64016-0042 | 64016-0039 |
| 538-19002-0024 | 64001-1100 | 64016-0042 | 64016-0039 |
| 538-19002-0028 | 64001-1100 | 64016-0042 | 64016-0039 |
| 538-19002-0031 | 64001-1100 | 64016-0042 | 64016-0039 |
| 538-19002-0037 | 64001-1100 | 64016-0042 | 64016-0039 |
| 538-19002-0044 | 64001-0200 | 64016-0037 | 64016-0039 |
| 538-19004-0001 | 64001-4700 | - | 64016-0039 |
| 538-19005-0010 | 64001-4900 | - | 64016-0039 |
| 538-19006-0001 | 64001-4300 | - | 64016-0039 |
| 538-19006-0011 | 64001-4300 | - | 64016-0039 |
| 538-19006-0019 | 64001-2800 | - | 64016-0039 |
| 538-19006-0005 | 64001-4300 | - | 64016-0039 |
| 538-19007-0001 | 64001-4100 | - | 64016-0039 |
| 538-19007-0009 | 64001-4100 | - | 64016-0039 |
| 538-19007-0021 | 64001-4100 | - | 64016-0039 |
| 538-19007-0040 | 64001-2800 | - | 64016-0039 |
| 538-19007-0029 | 64001-4100 | - | 64016-0039 |
| 538-19016-xxxx | 64003-1100 | - | 64016-0039 |
| 538-19017-0037 | 64001-0200 | 64016-0037 | 64016-0039 |
| 538-19019-xxxx | 64001-0200 | 64016-0037 | 64016-0039 |
| 538-19022-xxxx | 64003-0100 | 64016-0038 | 64016-0039 |
| 538-19034-xxxx | 64001-0100 | 64016-0036 | 64016-0039 |

| MOUSER STOCK NO. | Molex Premium Grade Ratchet Hand Tool | Molex Service Grade Ratchet Hand Tool | Molex Service Grade Non-Ratchet Hand Tool |
|------------------|---------------------------------------|---------------------------------------|---|
| 538-19036-xxxx | 64001-0100 | 64016-0036 | 64016-0039 |
| 538-19038-xxxx | 64001-2300 | - | 64016-0039 |
| 538-19039-xxxx | 64001-2300 | - | 64016-0039 |
| 538-19211-xxxx | 64003-0100 | 64016-0038 | 64016-0039 |
| 538-19212-xxxx | 64001-0100 | 64016-0036 | 64016-0039 |
| 538-19213-xxxx | 64001-0100 | 64016-0036 | 64016-0039 |
| 538-19221-0223 | 19284-0034 | - | - |
| 538-19221-0224 | 19284-0034 | - | - |
| 538-19221-0225 | 19284-0034 | - | - |
| 538-19221-0424 | 19284-0034 | - | - |
| 538-19221-0495 | 19284-0034 | - | - |
| 538-19221-0452 | 19284-0034 | - | - |
| 538-19221-0230 | 19284-0034 | - | - |
| 538-19221-0232 | 19284-0034 | - | - |
| 538-19221-0231 | 19284-0034 | - | - |
| 538-19221-0418 | 19284-0034 | - | - |
| 538-19221-0235 | 19284-0034 | - | - |
| 538-19221-0233 | 19284-0034 | - | - |
| 538-19221-0420 | 19284-0034 | - | - |
| 538-19221-0238 | 19284-0034 | - | - |
| 538-19221-0237 | 19284-0034 | - | - |
| 538-19221-0241 | 19284-0034 | - | - |
| 538-19221-0240 | 19284-0034 | - | - |
| 538-19221-0242 | 19284-0034 | - | - |
| 538-19221-0244 | 19284-0034 | - | - |
| 538-19221-0243 | 19284-0034 | - | - |
| 538-19221-0245 | 19284-0034 | - | - |
| 538-19221-0247 | 19284-0034 | - | - |
| 538-19221-0250 | 19284-0034 | - | - |
| 538-19221-0412 | 19284-0034 | - | - |
| 538-19221-0251 | 19284-0034 | - | - |

| MOUSER STOCK NO. | Molex Premium Grade Ratchet Hand Tool | Molex Service Grade Ratchet Hand Tool | Molex Service Grade Non-Ratchet Hand Tool |
|--|---------------------------------------|---------------------------------------|---|
| Ring and Spade Tongue Terminals | | | |
| 538-19164-xxxx | 64001-3200 | 64016-0041 | 64016-0039 |
| Butt Splices | | | |
| 538-19164-xxxx | 64001-3200 | 64016-0041 | 64016-0039 |
| Quick Disconnect Couplers | | | |
| 538-19164-0015 | 64001-4500 | 64016-0042 | 64016-0039 |
| 538-19164-0084 | 64001-4500 | 64016-0042 | 64016-0039 |
| 538-19165-0075 | 64001-0100 | 64016-0036 | 64016-0039 |
| 538-19164-0012 | 64001-4500 | 64016-0042 | 64016-0039 |
| 538-19164-0050 | 64001-4500 | 64016-0042 | 64016-0039 |
| 538-19164-0076 | 64001-0100 | 64016-0036 | 64016-0039 |