

MOLEX Eurostyle Terminal Blocks

RoHS Compliant **This product is RoHS compliant.**
EUROSTYLE 3.50MM FIXED PCB TERMINAL BLOCKS

- Features:**
- Insulator: Polyamide, UL94V-0, black
 - Terminal: Brass, tin plated
 - Clamp: Brass, nickel plated
 - Screws: M2 bronze, nickel plated
 - Operating Temp: -30°C to +105°C
 - Wire Range: 16 to 28AWG
 - Voltage: 300V
 - Rating: UL 12A @ 300V

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Molex Part No.	Fig.	No. of Circuits	Dimensions: mm			Price Each			
				H	W	L	1	25	50	100
538-39357-0002	39357-0002	A	2	8.51	7.29	3.50	.84	.79	.648	.564
538-39357-0003	39357-0003	A	3	8.51	7.29	7.00	.85	.824	.74	.66
538-39357-0004	39357-0004	A	4	8.51	7.29	10.50	1.45	1.41	1.23	1.10
538-39357-0005	39357-0005	A	5	8.51	7.29	14.00	1.60	1.51	1.35	1.20
538-39357-0006	39357-0006	A	6	8.51	7.29	17.50	1.93	1.82	1.64	1.45
538-39357-0007	39357-0007	A	7	8.51	7.29	21.00	2.42	2.28	2.05	1.81
538-39357-0008	39357-0008	A	8	8.51	7.29	24.50	2.62	2.45	2.19	1.94
538-39357-0009	39357-0009	A	9	8.51	7.29	28.00	2.90	2.74	2.46	2.18
538-39357-0010	39357-0010	A	10	8.51	7.29	31.50	3.21	3.02	2.71	2.40

EUROSTYLE 5.00MM LOW PROFILE PCB TERMINAL BLOCKS

- Features:**
- Insulator: Polyamide, UL94V-0, gray
 - Terminal: Brass, tin plated
 - Wire Protector: Phosphor bronze, tin plated
 - Screws: Steel, zinc chromate plated
 - Operating Temp: -55°C to +105°C
 - Rating: UL 13.5A @300V

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Molex Part No.	Fig.	No. of Circuits	Dimensions: mm			Price Each			
				H	W	L	1	25	50	100
Horizontal										
538-39890-0302	39890-0302	B	2	10.00	8.20	5.00	.79	.55	.54	.53
538-39890-0303	39890-0303	B	3	10.00	8.20	10.00	.98	.87	.83	.74
35° Entry										
538-39890-0402	39890-0402	C	2	15.00	12.50	5.00	.64	.52	.429	.386
538-39890-0403	39890-0403	C	3	15.00	12.50	10.00	1.25	1.23	1.18	1.01

EUROSTYLE 5.00MM ESE FIXED TERMINAL BLOCKS

- Features:**
- Screw Material: Steel
 - Terminal: Brass
 - Operating Temp: -40°C to +105°C
 - Wire Range: 14-24AWG

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Molex Part No.	Fig.	No. of Circuits	Dimensions: mm			Price Each			
				H	W	L	1	25	50	100
538-39543-0002	39543-0002	D	2	14.50	9.50	10.00	.45	.40	.361	.34
538-39543-0003	39543-0003	D	3	14.50	9.50	15.00	.65	.57	.523	.481
538-39543-0004	39543-0004	D	4	14.50	9.50	20.00	.98	.85	.771	.736
538-39543-0005	39543-0005	D	5	14.50	9.50	25.00	1.38	1.27	1.14	1.06
538-39543-0006	39543-0006	D	6	14.50	9.50	30.00	1.68	1.57	1.42	1.30
538-39543-0007	39543-0007	D	7	14.50	9.50	35.00	1.94	1.78	1.60	1.50
538-39543-0008	39543-0008	D	8	14.50	9.50	40.00	1.32	1.15	1.04	.984
538-39543-0009	39543-0009	D	9	14.50	9.50	45.00	1.73	1.59	1.43	1.34
538-39543-0010	39543-0010	D	10	14.50	9.50	50.00	2.19	2.11	1.97	1.80

EUROSTYLE 5.08MM LOW PROFILE PCB TERMINAL BLOCKS

- Features:**
- Insulator: Polyamide, UL94V-0, black
 - Terminal: Copper Alloy, tin plated
 - Screws: 3mm Copper Alloy
 - Operating Temp: 105°C
 - Voltage: 300V
 - Maximum Current: 13.5A

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Molex Part No.	Fig.	No. of Circuits	Dimensions: mm			Price Each			
				H	W	L	1	25	50	100
Horizontal										
538-39880-0302	39880-0302	E	2	10.00	8.20	5.08	.63	.50	.42	.39
538-39880-0303	39880-0303	E	3	10.00	8.20	10.16	.76	.71	.65	.57
35° Entry										
538-39880-0402	39880-0402	C	2	15.00	12.50	5.08	.68	.62	.573	.542
538-39880-0403	39880-0403	C	3	15.00	12.50	10.16	1.22	1.16	1.06	.99

EUROSTYLE 5.08MM ESE SINGLE-PIECE (FIXED) BLOCKS

- Features:**
- Insulator: Polyamide, UL94V-0, black
 - Pressure Clamp: Brass, nickel plated
 - Contacts: Phosphor bronze, hot tin dip
 - Screws: Steel, zinc chromate plated
 - Wire Range: 12 to 26AWG
 - Single piece (fixed)
 - Rating: UL Class B: 20Amps@300V
 - UL Class C: 10Amps@ 300V
 - CSA: 15Amps@ 300V

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Molex Part No.	Fig.	No. of Circuits	Dimensions: mm			Price Each			
				H	W	L	1	25	50	100
538-39544-3002	39544-3002	F	2	14.40	10.00	10.16	.98	.90	.83	.74
538-39544-3003	39544-3003	F	3	14.40	10.00	15.24	1.45	1.41	1.23	1.10
538-39544-3004	39544-3004	F	4	14.40	10.00	20.32	1.75	1.70	1.48	1.31
538-39544-3005	39544-3005	F	5	14.40	10.00	25.40	2.23	2.13	1.86	1.65
538-39544-3006	39544-3006	F	6	14.40	10.00	30.48	2.63	2.55	2.23	1.97
538-39544-3007	39544-3007	F	7	14.40	10.00	35.58	3.03	2.94	2.56	2.27
538-39544-3008	39544-3008	F	8	14.40	10.00	40.64	3.20	2.96	2.66	2.39
538-39544-3009	39544-3009	F	9	14.40	10.00	45.72	2.63	2.55	2.23	1.97
538-39544-3010	39544-3010	F	10	14.40	10.00	50.80	3.30	3.20	2.79	2.47

DIMENSIONS: mm

A

3.5mm Pitch

B

5.0mm Pitch

C

D

E

F

5.08mm Pitch

Terminal Blocks

Molex