

AVAGO Optocouplers

RoHS Compliant This product is RoHS compliant.



AVAGO OPTOCOUPLERS

PRODUCT NEW

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Avago Part No.	Number of Channels	Package	Forward on Current (mA)	Total Power Dissipation (mW)	Isolation Voltage (V _{RMS})	Price Each			
							1	25	100	500
630-4N25-000E	4N25-000E	-	DIP-6	80	250	2500	.32	.20	.18	.153
630-4N25-W00E	4N25-W00E	-	DIP-6	80	250	2500	.33	.23	.20	.17
630-4N35-000E	4N35-000E	-	DIP-6	80	350	3550	.32	.20	.18	.153
630-4N46-000E	4N46-000E	-	DIP-6	20	100	3750	2.67	2.18	1.94	1.65
630-6N136-000E	6N136-000E	1	DIP-8	8	100	3750	1.49	1.01	.90	.77
630-6N136-300E	6N136-300E	1	SO-8	8	100	3750	1.55	1.06	.94	.80
630-6N137-000E	6N137-000E	1	DIP-8	15	85	3750	1.65	1.13	1.00	.85
630-6N138-000E	6N138-000E	1	DIP-8	20	135	3750	1.49	1.01	.90	.77
630-6N139-000E	6N139-000E	1	DIP-8	20	135	3750	1.49	1.01	.90	.77
630-ACNV4506-000E	ACNV4506-000E	1	DIP-10	10	100	7500	4.84	3.96	3.52	2.99
630-ACNV4506-500E	ACNV4506-500E	1	DIP-10/GW	10	100	7500	4.90	4.01	3.56	3.02
630-ACNV2601-000E	ACNV2601-000E	1	DIP-10	20	85	7500	4.79	3.92	3.48	2.96
630-ACPL-054L-000E	ACPL-054L-000E	2	SO-8	3	36	3750	3.71	3.04	2.70	2.30
630-ACPL-054L-060E	ACPL-054L-060E	2	SO-8	3	36	3750	3.77	3.09	2.74	2.33
630-ACPL-C790-000E	ACPL-C790-000E	2	SSO-8	230	600	5000	8.25	6.75	6.00	5.10
630-ACPL-C79A-000E	ACPL-C79A-000E	2	SSO-8	230	600	5000	10.00	9.00	8.00	6.80
630-ACPL-C79B-000E	ACPL-C79B-000E	2	SSO-8	230	600	5000	12.50	11.25	10.00	8.50
630-ACPL-H342-000E	ACPL-H342-000E	1	SO-8	7	255	3750	2.75	2.25	2.00	1.70
630-ACPL-H342-060E	ACPL-H342-060E	1	SO-8	7	255	3570	2.81	2.30	2.04	1.73
630-ACPL-K342-000E	ACPL-K342-000E	1	SO-8	7	255	5000	3.02	2.48	2.20	1.87
630-ACPL-K342-060E	ACPL-K342-060E	1	SO-8	7	255	5000	3.08	2.52	2.24	1.90
630-ACPL-M49T-000E	ACPL-M49T-000E	1	SO-5	40	100	3750	3.03	2.48	2.20	1.87
630-ACPL-M61L-000E	ACPL-M61L-000E	1	SO-5	8	600	3750	1.93	1.58	1.40	1.19
630-ACPL-M61L-060E	ACPL-M61L-060E	1	SO-5	8	600	3750	1.98	1.62	1.44	1.22
630-ACPL-W611-000E	ACPL-W611-000E	1	SO-6	20	85	3750	2.48	2.03	1.80	1.53
630-ACPL-W611-060E	ACPL-W611-060E	1	SO-6	50	85	3750	2.53	2.07	1.84	1.56
630-ACPL-W61L-000E	ACPL-W61L-000E	1	SSO-6	8	20	5000	2.48	2.03	1.80	1.53
630-ACPL-W61L-060E	ACPL-W61L-060E	1	SSO-6	8	20	5000	2.53	2.07	1.84	1.56
630-ACPL-071L-000E	ACPL-071L-000E	1	SO-8	9	-	3750	3.44	2.81	2.50	2.13
630-ACPL-072L-000E	ACPL-072L-000E	1	SO-8	10	150	3750	4.40	3.60	3.20	2.72
630-ACPL-38JT-500E	ACPL-38JT-500E	2	SO-16	2.5	600	1230	8.35	7.52	6.68	5.67
630-ACPL-782T-000E	ACPL-782T-000E	1	DIP-8	16	600	3750	11.03	9.80	8.82	7.84
630-ACPL-C784-000E	ACPL-C784-000E	1	Stretched SO-8	11	600	5000	7.98	6.53	5.80	4.93
630-ACPL-C78A-000E	ACPL-C78A-000E	1	Stretched SO-8	11	600	5000	13.85	12.47	11.08	9.42
630-ACPL-K73L-000E	ACPL-K73L-000E	2	Stretched SO-8	10	600	5000	6.60	5.40	4.80	4.08
630-ACPL-M46T-000E	ACPL-M46T-000E	1	SO-5	10	130	3750	5.64	4.61	4.10	3.49
630-ACPL-M61T-000E	ACPL-M61T-000E	1	SO-5	20	85	3750	5.64	4.61	4.10	3.49
630-ACPL-M75L-000E	ACPL-M75L-000E	1	SO-5	4	-	3750	3.58	2.93	2.60	2.21
630-ACPL-P340-000E	ACPL-P340-000E	1	Stretched SO-6	25	700	3750	2.48	2.03	1.80	1.53
630-ACPL-P340-060E	ACPL-P340-060E	1	Stretched SO-6	25	700	3750	2.53	2.07	1.84	1.56
630-ACPL-P341-000E	ACPL-P341-000E	1	Stretched SO-6	25	700	3750	2.75	2.25	2.00	1.70
630-ACPL-P341-060E	ACPL-P341-060E	1	Stretched SO-6	25	700	3750	2.81	2.30	2.04	1.73
630-ACPL-P343-000E	ACPL-P343-000E	1	Stretched SO-6	25	700	3750	3.30	2.70	2.40	2.04
630-ACPL-P343-060E	ACPL-P343-060E	1	Stretched SO-6	25	700	3750	3.36	2.75	2.44	2.07
630-ACPL-W340-000E	ACPL-W340-000E	1	Stretched SO-6	25	700	5000	2.61	2.14	1.90	1.62
630-ACPL-W340-060E	ACPL-W340-060E	1	Stretched SO-6	25	700	5000	2.67	2.18	1.94	1.65
630-ACPL-W341-000E	ACPL-W341-000E	1	Stretched SO-6	25	700	5000	3.03	2.48	2.20	1.87
630-ACPL-W341-060E	ACPL-W341-060E	1	Stretched SO-6	25	700	5000	3.08	2.52	2.24	1.90
630-ACPL-W343-000E	ACPL-W343-000E	1	Stretched SO-6	25	700	5000	3.58	2.93	2.60	2.21
630-ACPL-W343-060E	ACPL-W343-060E	1	Stretched SO-6	25	700	5000	3.63	2.97	2.64	2.24
630-ACSL-6210-00RE	ACSL-6210-00RE	2	SO-8	2.7	60	2500	3.85	3.15	2.80	2.38
630-ACSL-6400-00TE	ACSL-6400-00TE	4	SO-16	2.7	60	2500	7.70	6.30	5.60	4.76
630-CNY17-2-000E	CNY17-2-000E	1	DIP-6	0.3	250	5000	.32	.20	.18	.153
630-CNY17-3-000E	CNY17-3-000E	1	DIP-6	0.3	250	5000	.32	.20	.18	.153
630-CNY17-4-000E	CNY17-4-000E	1	DIP-6	0.3	250	5000	.32	.20	.18	.153
630-HCNR200-000E	HCNR200-000E	1	DIP-8	25	60	1414	3.66	2.99	2.66	2.26
630-HCNR200-300E	HCNR200-300E	1	SO-8	25	60	1414	3.71	3.04	2.70	2.30
630-HCNR201-000E	HCNR201-000E	1	DIP-8	25	60	1414	4.87	3.98	3.54	3.01
630-HCNR201-300E	HCNR201-300E	1	SO-8	25	60	1414	4.92	4.03	3.58	3.04
630-HCNW136-000E	HCNW136-000E	1	DIP-8	16	700	5000	2.20	1.80	1.60	1.36
630-HCNW137-000E	HCNW137-000E	1	DIP-8	5	700	5000	3.11	2.54	2.26	1.92
630-HCNW139-000E	HCNW139-000E	1	DIP-8	0.4	700	1414	2.94	2.41	2.14	1.82
630-HCNW139-300E	HCNW139-300E	1	SO-8	0.4	700	5000	3.00	2.45	2.18	1.85
630-HCNW2211-000E	HCNW2211-000E	1	DIP-8	1.6	600	5000	3.85	3.15	2.80	2.38
630-HCNW2211-300E	HCNW2211-300E	1	SO-8	1.6	600	5000	3.91	3.20	2.84	2.41
630-HCNW2611-000E	HCNW2611-000E	1	DIP-8	1.6	600	5000	3.99	3.26	2.90	2.47
630-HCNW2611-300E	HCNW2611-300E	1	SO-8	1.6	600	5000	4.04	3.31	2.94	2.50
630-HCNW3120-000E	HCNW3120-000E	1	DIP-8	10	700	5000	4.26	3.49	3.10	2.64
630-HCNW4502-000E	HCNW4502-000E	1	DIP-8	16	700	5000	2.20	1.80	1.60	1.36
630-HCNW4503-000E	HCNW4503-000E	1	DIP-8	16	700	5000	2.94	2.41	2.14	1.82
630-HCNW4503-300E	HCNW4503-300E	1	SO-8	16	700	5000	3.00	2.45	2.18	1.85
630-HCNW4504-300E	HCNW4504-300E	1	DIP-8	12	100	5000	3.33	2.72	2.42	2.06
630-HCNW4506-300E	HCNW4506-300E	1	SO-8	10	145	3750	3.41	2.79	2.48	2.11
630-HCPL-0201-000E	HCPL-0201-000E	1	DIP-8	1.6	600	3750	3.25	2.66	2.36	2.01
630-HCPL-0201-500E	HCPL-0201-500E	1	SO-8	1.6	600	3750	3.30	2.70	2.40	2.04
630-HCPL-0211-000E	HCPL-0211-000E	1	DIP-8	1.6	600	3750	3.74	3.06	2.72	2.31
630-HCPL-0211-500E	HCPL-0211-500E	1	SO-8	1.6	600	3750	3.80	3.11	2.76	2.35
630-HCPL-0300-000E	HCPL-0300-000E	1	SO-8	0.6	600	3750	8.25	6.75	6.00	5.10
630-HCPL-0314-000E	HCPL-0314-000E	1	SO-8	8	400	3750	2.06	1.69	1.50	1.28
630-HCPL-0370-000E	HCPL-0370-000E	1	SO-8	50	275	3750	3.93	3.22	2.86	2.43
630-HCPL-0452-000E	HCPL-0452-000E	1	SO-8	16	600	3750	1.95	1.33	1.18	1.00
630-HCPL-0453-000E	HCPL-0453-000E	1	SO-8	16	600	3750	2.26	1.85	1.64	1.39
630-HCPL-0454-000E	HCPL-0454-000E	1	SO-8	16	600	3750	2.53	2.07	1.84	1.56
630-HCPL-0500-000E	HCPL-0500-000E	1	SO-8	16	600	3750	1.72	1.17	1.04	.88
630-HCPL-0501-000E	HCPL-0501-000E	1	SO-8	16	600	3750	1.91	1.31	1.16	.99
630-HCPL-0501-500E	HCPL-0501-500E	1	SO-8	16	600	3750	1.80	1.35	1.20	1.02
630-HCPL-0530-000E	HCPL-0530-000E	2	SO-8	16	600	3750	3.71	3.04	2.70	2.30
630-HCPL-0531-000E	HCPL-0531-000E	2	SO-8	16	600	3750	3.85	3.15	2.80	2.38
630-HCPL-053L-000E	HCPL-053L-000E	2	SO-8	16	600	3750	4.18	3.42	3.04	2.58
630-HCPL-0600-000E	HCPL-0600-000E	1	SO-8	5	600	3750	1.93	1.58	1.40	1.19
630-HCPL-0600-500E	HCPL-0600-500E	1	SO-8	5	600	3750	1.98	1.62	1.44	1.22
630-HCPL-0601-000E	HCPL-0601-000E	1	SO-8	5	600	3750	1.93	1.58	1.40	1.19
630-HCPL-0601-500E	HCPL-0601-500E	1	SO-8	5	600	3750	1.98	1.62	1.44	1.22
630-HCPL-060L-000E	HCPL-060L-000E	1	SO-8	5	600	3750	2.20	1.80	1.60	1.36
630-HCPL-0611-000E	HCPL-0611-000E	1	SO-8	5	600	3750	2.48	2.03	1.80	1.53
630-HCPL-0611-500E	HCPL-0611-500E	1	SO-8	5	600	3750	2.53	2.07	1.84	1.56