

PHOENIX CONTACT DIN Rail Mounted Terminal Blocks



DIN RAIL MOUNTED TERMINAL FUSE BLOCKS

DIMENSIONS (mm)

A	B	C	D	E	F	G	H
<ul style="list-style-type: none"> Width: 17.5mm Fuse Size: 10.3x38 18-4AWG (UL) 600V (UL) 30A (UL) Color: Black 	<ul style="list-style-type: none"> Width: 36mm Fuse Size: 20.6x57 18-4AWG (UL) 600V (UL) 30A (UL) Color: Black 	<ul style="list-style-type: none"> Width: 40mm Fuse Size: 27x60 14-1AWG (UL) 600V (UL) 60A (UL) Color: Black 	<ul style="list-style-type: none"> Width: 8.2mm Fuse Size: 5x20mm, 5x25mm, 5x30mm 26-10AWG (UL) 600V (UL) 12A (UL) Color: Black 	<ul style="list-style-type: none"> Width: 10.2mm Fuse Size: 6.3x32mm 26-8 AWG (UL) 600V (UL) 25A (UL) Color: Black 	<ul style="list-style-type: none"> Width: 18mm Fuse Size: 10.3x38mm 16-4AWG (UL) 600V (UL) 30A (UL) Color: Black 	<ul style="list-style-type: none"> Width: 8.2mm Fuse Size: 5x20mm, 6.3x32mm 24-8AWG (UL) 15A upper/30A lower (UL) 600V (UL) Color: Black 	<ul style="list-style-type: none"> Width: 8.2mm Fuse Size: 6.3x32mm 24-8AWG (UL) 15A upper/ 30A lower (UL) 600V (UL) Color: Black

Fuse Terminal Blocks with Disconnect Lever

For quantities greater than listed, call for quote. Accessories (See accessories page for pricing and descriptions)

MOUSER STOCK NO. Mfr. Mfr. Part No.	Fig.	Phoenix Type	Description	Dimensions (mm)		Price Each			Insertion Bridge	Fixed Bridge	Screwdriver	End Bracket	Din Rail Type
				A	B	1	10	50					
Branch Circuit Protection - Class CC and J													
651-3048580	A	UK 10.3-CC HESI	For Class CC fuses	81	73	12.05	10.88	10.77	651-3009299	-	651-1205066	-	NS 35
651-3048616	A	UK 10.3-CC HESI LED	For Class CC fuses w/ LED, 110-600V	81	73	19.88	17.99	17.78	651-3009367	-	651-1205066	-	NS 35
651-3211058	B	UK 20.6-J HESI	For Class J fuses	118	96.5	27.12	25.39	24.23	-	-	651-1205066	-	NS 35
651-3211087	B	UK 20.6-J HESI LED	For Class J fuses w/ LED, 110-600V	118	96.5	34.34	32.16	30.70	-	-	651-1205066	-	NS 35
651-3211113	C	UK 27-J HESI	For Class J fuses	118	96.5	36.29	33.98	32.44	-	-	651-1205066	-	NS 35
651-3211142	C	UK 27-J HESI LED	For Class J fuses w/ LED, 110-600V	118	96.5	43.32	40.98	38.72	-	-	651-1205066	-	NS 35
Fuse Terminal Blocks with Disconnect Lever													
651-3004100	D	UK 5 HESI	Fuse Block	72.5	56.5	7.60	7.00	6.56	651-3118135	-	651-1205053	651-0800886	NS 35
651-3004126	D	UK 5 HESI LED 24	Fuse Block w/ LED, 15-30V	72.5	56.5	10.97	10.27	9.80	651-3118135	-	651-1205053	651-0800886	NS 35
651-3004142	D	UK 5 HESILA 250	Fuse Block w/ LED, 110-250V	72.5	56.5	10.97	10.27	9.80	651-3118135	-	651-1205053	651-0800886	NS 35
651-3004171	E	UK 6.3 HESI	Fuse Block	79	60.5	9.15	8.28	7.99	651-0203137	-	651-1205066	651-0800886	NS 35
651-3004265	E	UK 6.3 HESI LED 24	Fuse Block w/ LED, 15-30V	79	60.5	13.67	12.81	12.22	651-0203137	-	651-1205066	651-0800886	NS 35
651-3004249	E	UK HESILA 250	Fuse Block w/ LED, 110-250V	79	60.5	13.67	12.81	12.22	651-0203137	-	651-1205066	651-0800886	NS 35
651-3048386	F	UK 10.3 HESI N	Fuse Block	81	79	11.48	10.75	10.27	651-3009299	-	651-1205066	651-0800886	NS 35
651-3048399	F	UK 10.3 HESI LED N 690	Fuse Block w/ LED, 220-690V	81	79	19.00	17.79	16.98	651-3009367	-	-	-	-
651-3007204	G	UKK 5 HESI (5x20)	Fuse Block	86.5	79	15.43	14.63	13.49	-	651-2772080	651-1205053	651-0800886	NS 35
651-3026654	G	UKK5 HESI LED 24 (5x20)	Fuse Block w/LED, 15-30V	86.5	79	23.66	21.69	20.05	-	651-2772080	651-1205053	651-0800886	NS 35
651-0711629	G	UKK 5 HESILA 250 (5x20)	Fuse Block w/ LED, 110-250V	86.5	79	23.36	21.89	20.52	-	651-2772080	651-1205053	651-0800886	NS 35
651-3007217	H	UKK 5 HESI (6.3x32)	Fuse Block	86.5	79	17.16	15.51	14.82	-	651-2772080	651-1205053	651-0800886	NS 35
651-0711632	H	UKK 5 HESI LED 24 (6.3x32)	Fuse Block w/ LED for 15-30V	86.5	79	24.67	22.62	20.91	-	651-2772080	651-1205053	651-0800886	NS 35
651-0711616	H	UKK5 HESILA 250 (6.3x32)	Fuse Block w/ LED, 110-250V	86.5	79	26.93	23.02	21.73	-	651-2772080	651-1205053	651-0800886	NS 35

<p>DIKD 1.5TG</p> <ul style="list-style-type: none"> Width: 6.2mm 30-14AWG (UL) 300V (UL) 15A (UL) 3 Levels Color: Gray 	<p>DIK 1.5</p> <ul style="list-style-type: none"> Width: 6.2mm 30-14AWG (UL) 300V (UL) 15A (UL) 3 Levels Color: Gray 	<p>DIKD 1.5</p> <ul style="list-style-type: none"> Requires fuse plug Width: 6.2mm 28-12AWG (UL) 300V (UL) 6.3A (UL) Color: Gray
<p>UK 4-TG</p> <ul style="list-style-type: none"> Requires fuse plug Width: 6.2mm 30-12AWG (UL) 300V (UL) 15A (UL) Color: Gray 	<p>UDK 4-TG</p> <ul style="list-style-type: none"> Requires fuse plug Width: 6.2mm 26-12AWG (UL) 300V (UL) 15A (UL) 15A upper/ 25A lower (UL) Color: Gray 	<p>UKK5-TG</p> <ul style="list-style-type: none"> Requires fuse plug Width: 6.2mm 30-14AWG (UL) 300V (UL) 15A (UL) 3 Levels Color: Gray

Three Level Sensor Terminal Blocks

For quantities greater than listed, call for quote. Accessories (See accessory page for pricing and descriptions)

MOUSER STOCK NO. Mfr. Mfr. Part No.	Fig.	Phoenix Type	Dimensions (mm)		Price Each			Partition Plate	Fixed Bridge	Insertion Bridge	Fuse Plug	Fusle 30V Light	Fuse 250V Light	Screwdriver	End Bracket	Din Rail Type
			A	B	1	10	50									
651-2774237	A	DIKD 1.5 TG	72.5	54.5	8.95	8.03	7.63	651-1413285	-	651-2715940	651-0921011	651-0921037	651-0921053	651-1205053	651-0800886	NS 35
651-2715966	B	DIK 1.5	55.0	54.5	4.92	4.41	4.19	651-1413272	651-2715953 651-0203250	651-2715940	-	-	-	651-1205053	651-0800886	NS 35
651-2715979	C	DIKD 1.5	72.5	54.5	8.58	7.69	7.31	651-1413285	651-0203250	651-2715940	-	-	-	651-1205053	651-0800886	NS 35

Base Terminal Blocks for Cartridge Fuse

For quantities greater than listed, call for quote. Accessories (See accessory page for pricing and descriptions)

MOUSER STOCK NO. Mfr. Mfr. Part No.	Fig.	Phoenix Type	Dimensions (mm)		Price Each			End Cover	Partition Plate	Fixed Bridge	Insertion Bridge	Fuse Plug	Fuse 30V Light	Screwdriver	End Bracket	Din Rail Type
			A	B	1	10	50									
651-2812018	D	UK 4 -TG	42.5	47.0	4.01	3.76	3.59	651-3003020	651-3003224	-	651-0201139	651-0921011	651-0921037	651-0921053	651-0800886	NS 35
651-2777014	E	UDK 4-TG	63.5	47.0	4.14	3.88	3.70	651-2777027	-	651-0203250	651-0201139	651-0921011	651-0921037	651-0921053	651-0800886	NS 35
651-3007042	F	UKK 5-TG	80.0	68.5	11.16	10.45	9.69	-	-	651-0203250	651-0201139	651-0921011	651-0921037	651-0921053	651-0800886	NS 35