

APEM Toggle Switches



600 H SERIES POWER TOGGLE SWITCHES

Specifications:

- Solder terminals

() = Momentary contact

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Apem Part No.	Fig.	Type	Function	Contact Rating	Price Each			
						1	25	100	500
642-631H2	631H2	A	SPST	On-None-Off	15A	3.39	3.02	2.75	2.39
642-636H2	636H2	A	SPDT	On-None-On	15A	5.59	5.05	4.35	4.07
642-637H2	637H2	A	SPDT	(On)-Off-(On)	15A	5.99	5.41	4.66	4.36
642-638H2	638H2	A	SPDT	On-Off-(On)	15A	5.99	5.41	4.66	4.36
642-639H2	639H2	A	SPDT	On-Off-On	15A	5.70	5.15	4.44	4.15
642-641H2	641H2	A	DPST	On-None-Off	15A	7.72	7.03	5.90	5.44
642-644H2	644H2	A	DPDT	On-On-On	15A	11.72	10.59	9.12	8.52
642-646H2	646H2	A	DPDT	On-None-On	15A	9.58	8.65	7.45	6.97
642-647H2	647H2	A	DPDT	(On)-Off-(On)	15A	10.27	9.28	7.99	7.47
642-648H2	648H2	A	DPDT	On-Off-(On)	15A	11.61	10.49	9.03	8.45
642-649H2	649H2	A	DPDT	On-Off-On	15A	9.77	8.83	7.60	7.11
642-651H2	651H2	B	3PST	On-None-Off	15A	15.62	14.23	13.31	12.45
642-656H2	656H2	B	3PDT	On-None-On	15A	17.20	15.68	14.16	13.25
642-657H2	657H2	B	3PDT	(On)-Off-(On)	15A	18.89	17.21	16.10	15.06
642-658H2	658H2	B	3PDT	On-Off-(On)	15A	18.26	16.64	13.96	12.88
642-659H2	659H2	B	3PDT	On-Off-On	15A	18.20	16.58	15.49	14.49

600 NH SERIES POWER TOGGLE SWITCHES

Specifications:

- Contact ratings: Functions: ON-OFF and ON-ON; 15A 250VAC, 20A 125VAC or 10A 24VDC
Functions: ON-OFF-ON; 15A 250VAC, 20A 125VAC or 10A 24VDC
- Operating temp. range: -20°C to +55°C
- Contact resistance: 10mΩ max.
- Solder terminals

() = Momentary contact

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Apem Part No.	Fig.	Type	Function	Contact Rating	Price Each			
						1	25	100	500
642-631NH2	631NH2	C	SPST	On-None-Off	15A	4.52	4.12	3.45	3.19
642-636NH2	636NH2	C	SPDT	On-None-On	15A	5.75	5.19	4.47	4.18
642-637NH2	637NH2	C	SPDT	(On)-Off-(On)	15A	6.93	6.31	5.51	4.95
642-638NH2	638NH2	C	SPDT	On-Off-(On)	15A	6.93	6.31	5.51	4.95
642-639NH2	639NH2	C	SPDT	On-Off-On	15A	5.90	5.33	4.60	4.30

