

MOUNTAIN SWITCH Toggle Switches

RoHS Compliant This product is RoHS compliant.



SEALED MINIATURE TOGGLE SWITCHES

Specifications:

- Rating: 2A/250, 5A/120VAC or 28VDC
- Contact Resistance: 10mΩ max.
- Insulation Resistance: 1000MΩ min.

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Width (W) (in.)	Type	Circuit	Price Each				
					1	50	100	500	1000
108-1AS1T1171-EVX	A	0.26	SPDT	On-On	2.67	2.22	2.02	1.84	1.56
108-1AS2T1172-EVX	A	0.26	SPDT	On-(On)	2.90	2.42	2.20	2.00	1.69
108-1AS3T1173-EVX	A	0.26	SPDT	On-Off-On	3.59	2.99	2.72	2.48	2.10
108-1AS5T1174-EVX	A	0.26	SPDT	On-Off-(On)	3.66	3.05	2.77	2.52	2.13
108-1AD1T1175-EVX	A	0.45	DPDT	On-On	3.66	3.05	2.77	2.52	2.13
108-1AD2T1176-EVX	A	0.45	DPDT	On-(On)	3.59	2.99	2.72	2.48	2.10
108-1AD3T1177-EVX	A	0.45	DPDT	On-Off-On	4.12	3.44	3.12	2.84	2.40
108-1AD5T1179-EVX	A	0.45	DPDT	On-Off-(On)	5.57	4.64	4.22	3.84	3.25
108-1A31T1280-EVX	B	0.642	3PDT	On-On	5.57	4.64	4.22	3.84	3.25
108-1A34T1283-EVX	B	0.642	3PDT	(On)-Off-(On)	6.69	5.58	5.07	4.61	3.90
108-1AS1T2184-EVX	C	0.26	SPDT	On-On	2.99	2.49	2.26	2.06	1.75
108-1AS3T2186-EVX	C	0.26	SPDT	On-Off-On	3.59	2.99	2.72	2.48	2.10
108-1AS5T2187-EVX	C	0.26	SPDT	On-Off-(On)	3.66	3.05	2.77	2.52	2.13
108-1AD1T2188-EVX	C	0.45	DPDT	On-On	3.59	2.99	2.72	2.48	2.10
108-1AD3T2190-EVX	C	0.45	DPDT	On-Off-On	4.12	3.44	3.12	2.84	2.40
108-1AS1T1693-EVX	D	0.26	SPDT	On-On	2.90	2.42	2.20	2.00	1.69
108-1AS3T1695-EVX	D	0.26	SPDT	On-Off-On	3.29	2.99	2.73	2.31	2.18
108-1AD1T1697-EVX	D	0.45	DPDT	On-On	4.12	3.44	3.12	2.84	2.40
108-1AS1T1706-EVX	E	0.26	SPDT	On-On	3.59	2.99	2.72	2.48	2.10
108-1AS3T1708-EVX	E	0.26	SPDT	On-Off-On	4.03	3.35	3.05	2.77	2.34
108-1AS5T1709-EVX	E	0.26	SPDT	On-Off-(On)	4.12	3.44	3.12	2.84	2.40
108-1AD1T1710-EVX	E	0.45	DPDT	On-On	4.12	3.44	3.12	2.84	2.40
108-1AD3T1712-EVX	E	0.45	DPDT	On-Off-On	4.36	3.63	3.31	3.08	2.83
108-1AD4T1713-EVX	E	0.45	DPDT	(On)-Off-(On)	4.36	3.63	3.31	3.08	2.83
108-1A31T2715-EVX	F	0.646	3PDT	On-On	6.33	5.28	4.80	4.36	3.69
108-1A33T2717-EVX	F	0.646	3PDT	On-Off-On	6.69	5.58	5.07	4.61	3.90
108-1AS1T2219-EVX	G	0.26	SPDT	On-On	2.90	2.42	2.20	2.00	1.69
108-1AS2T2220-EVX	G	0.26	SPDT	On-(On)	2.90	2.42	2.20	2.00	1.69
108-1AD1T2223-EVX	G	0.45	DPDT	On-On	3.66	3.05	2.77	2.52	2.13
108-1AD3T2225-EVX	G	0.45	DPDT	On-Off-On	4.12	3.44	3.12	2.84	2.40
108-1A33T2230-EVX	G	0.642	3PDT	On-Off-On	6.33	5.28	4.80	4.36	3.69

SEALED SUB-MINIATURE TOGGLE SWITCHES - SURFACE MOUNT

Specifications:

- Rating: 0.4VA/20VAC or DC
- Contact Resistance: 20mΩ max.
- Insulation Resistance: 1000MΩ min.

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Width (W) (in.)	Type	Circuit	Price Each				
					1	50	100	500	1000
108-2BS1T145-EVX	H	0.244	SPDT	On-On	2.80	2.34	2.12	1.93	1.76

SEALED SUB-MINIATURE TOGGLE SWITCHES - PANEL MOUNT

Specifications:

- Rating: 1A/250, 3A/120VAC or 28VDC
- Contact Resistance: 20mΩ max.
- Insulation Resistance: 1000MΩ min.

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Width (W) (in.)	Type	Circuit	Price Each				
					1	50	100	500	1000
108-2AS1T1203-EVX	I	0.20	SPDT	On-On	2.67	2.22	2.02	1.84	1.56
108-2AS2T1204-EVX	I	0.20	SPDT	On-(On)	2.66	2.42	2.20	1.85	1.72
108-2AS3T1205-EVX	I	0.20	SPDT	On-Off-On	3.95	3.29	2.99	2.73	2.31
108-2AD1T1206-EVX	I	0.36	DPDT	On-On	3.59	2.99	2.72	2.48	2.10
108-2AS1T1609-EVX	J	0.249	SPDT	On-On	2.90	2.42	2.20	2.00	1.69
108-2AD1T1612-EVX	J	0.40	DPDT	On-On	3.59	2.99	2.72	2.48	2.10
108-2AS1T1715-EVX	K	0.232	SPDT	On-On	3.59	2.99	2.72	2.48	2.10
108-2AS3T1717-EVX	K	0.232	SPDT	On-Off-On	4.12	3.44	3.12	2.84	2.40
108-2AD1T1718-EVX	K	0.398	DPDT	On-On	3.59	2.99	2.72	2.48	2.10
108-2AS1T2221-EVX	L	0.20	SPDT	On-On	2.67	2.22	2.02	1.84	1.56
108-2AS3T2223-EVX	L	0.20	SPDT	On-Off-On	3.59	2.99	2.72	2.48	2.10
108-2AD1T2224-EVX	L	0.36	DPDT	On-On	3.59	2.99	2.72	2.48	2.10
108-2AD3T2226-EVX	L	0.36	DPDT	On-Off-On	4.36	3.63	3.31	3.08	2.83
108-2AS1T2627-EVX	M	0.249	SPDT	On-On	2.90	2.42	2.20	2.00	1.69
108-2AD1T2630-EVX	M	0.40	DPDT	On-On	3.59	2.99	2.72	2.48	2.10
108-2AD3T2632-EVX	M	0.40	DPDT	On-Off-On	4.36	3.63	3.31	3.08	2.83
108-2AS1T3233-EVX	N	0.20	SPDT	On-On	2.90	2.42	2.20	2.00	1.69
108-2AS2T3234-EVX	N	0.20	SPDT	On-(On)	3.59	2.99	2.72	2.48	2.10
108-2AS3T3235-EVX	N	0.20	SPDT	On-Off-On	3.66	3.05	2.77	2.52	2.13
108-2AD1T3236-EVX	N	0.36	DPDT	On-On	3.59	2.99	2.72	2.48	2.10
108-2AD3T3238-EVX	N	0.36	DPDT	On-Off-On	4.36	3.63	3.31	3.08	2.83
108-2AS1T3639-EVX	O	0.249	SPDT	On-On	3.59	2.99	2.72	2.48	2.10
108-2AD1T3642-EVX	O	0.40	DPDT	On-On	3.66	3.05	2.77	2.52	2.13

DIMENSIONS: in.

Mountain Switch

Toggle Switches