

C&K Slide Switches



C&K AYZ SERIES MINIATURE SLIDE SWITCHES

Specifications:

- Dielectric Strength: 0.1kV @ 50Hz/1 min.
- Max Switching Voltage: 12VDC
- PC thru-hole termination
- Max Switching Power: 1.2VA
- Max. Switching Current: 100mA
- Sliver plated contacts



For quantities greater than listed, call for quote.

| MOUSER STOCK NO. | C&K Part No. | Fig. | Contact Form | Circuit | Price Each | | | |
|------------------|--------------|------|--------------|---------|------------|------|------|------|
| | | | | | 1 | 25 | 50 | 100 |
| 611-AYZ0102AGRLC | AYZ0102AGRLC | A | SPDT | On-On | 1.00 | .852 | .819 | .784 |
| 611-AYZ0202AGRLC | AYZ0202AGRLC | B | DPDT | On-On | 1.35 | 1.27 | 1.15 | 1.03 |

C&K ES SERIES SEALED TINY SLIDE SWITCHES

Specifications:

- Actuator Height: .121"
- Mechanical and Electrical Life: 40,000 make-and-break cycles at full load
- Contact Rating: 0.4VA max. @ 20VAC or DC max.
- Dielectric Strength: 500Vrms min.
- Lead free



For quantities greater than listed, call for quote.

| MOUSER STOCK NO. | C&K Part No. | Fig. | Contact Form | Circuit | Price Each | | | |
|------------------|--------------|------|--------------|-------------|------------|------|------|------|
| | | | | | 1 | 25 | 50 | 100 |
| 611-ES21MCBE | ES21MCBE | C | DPDT | On-None-On | 7.08 | 6.87 | 6.16 | 5.67 |
| 611-ES22MABE | ES22MABE | D | DPST | Off-None-On | 8.08 | 7.75 | 6.98 | 6.76 |
| 611-ES01MAVBE | ES01MAVBE | E | SPDT | On-None-On | 6.55 | 5.95 | 5.45 | 5.18 |
| 611-ES03MSABE | ES03MSABE | F | SPDT | On-Off-On | 6.56 | 5.74 | 5.49 | 5.10 |

C&K OS SERIES MINIATURE SLIDE SWITCHES

Specifications:

- Dielectric Strength: 500VAC for 1 minute
- Mechanical and Electrical Life: 10,000 cycles
- Contact Rating: 0.2A @ 30VDC
- Shorting or Non-shorting contacts
- PC and panel mounting
- Variety of actuators and terminations
- * Non-Shorting * Shorting



For quantities greater than listed, call for quote.

| MOUSER STOCK NO. | C&K Part No. | Fig. | Contact Form | Circuit | Price Each | | | |
|--------------------------------|----------------|------|--------------|----------|------------|------|------|------|
| | | | | | 1 | 25 | 50 | 100 |
| Vertical Termination | | | | | | | | |
| * 611-OS102011MS2QN1 | OS102011MS2QN1 | G | SPDT | On-On | .48 | .409 | .358 | .332 |
| * 611-OS102011MS2QS1 | OS102011MS2QS1 | G | SPDT | On-On | .42 | .339 | .319 | .288 |
| 611-OS103011MS8QP1 | OS103011MS8QP1 | H | SP3T | On-On-On | .57 | .474 | .417 | .399 |
| 611-OS103012MU1QP1 | OS103012MU1QP1 | I | SP3T | On-On-On | .58 | .556 | .525 | .475 |
| 611-OS103012MU2QP1 | OS103012MU2QP1 | J | SP3T | On-On-On | .57 | .556 | .526 | .495 |
| * 611-OS202011MS2QN1 | OS202011MS2QN1 | K | DPDT | On-On | .66 | .549 | .499 | .472 |
| * 611-OS202011MS2QS1 | OS202011MS2QS1 | K | DPDT | On-On | .67 | .543 | .491 | .479 |
| * 611-OS202011MV4QN1 | OS202011MV4QN1 | L | DPDT | On-On | .64 | .604 | .579 | .554 |
| * 611-OS202013MT5QN1 | OS202013MT5QN1 | N | DPDT | On-On | .54 | .463 | .39 | .339 |
| * 611-OS202013MT8QN1 | OS202013MT8QN1 | M | DPDT | On-On | .57 | .556 | .526 | .471 |
| 611-OS203011MS1QP1 | OS203011MS1QP1 | O | DP3T | On-On-On | .77 | .656 | .605 | .58 |
| * 611-OS203013MT6QN1 | OS203013MT6QN1 | P | DP3T | On-On-On | .47 | .453 | .391 | .362 |
| Right-Angle Termination | | | | | | | | |
| 611-OS102011MA1QN1 | OS102011MA1QN1 | Q | SPDT | On-On | .40 | .352 | .309 | .298 |
| * 611-OS102011MA1QS1 | OS102011MA1QS1 | Q | SPDT | On-On | .45 | .37 | .329 | .308 |
| 611-OS103011MA7QP1 | OS103011MA7QP1 | R | SP3T | On-On-On | .58 | .47 | .40 | .372 |
| * 611-OS202011MA0QN1 | OS202011MA0QN1 | S | DPDT | On-On | .60 | .507 | .444 | .421 |
| 611-OS202011MA0QS1 | OS202011MA0QS1 | S | DPDT | On-On | .47 | .401 | .361 | .284 |
| * 611-OS203011MA2QP1 | OS203011MA2QP1 | T | DP3T | On-On-On | .51 | .495 | .464 | .418 |

C&K LP SERIES: MINIATURE SNAP-IN SLIDE SWITCHES

Specifications:

- Dielectric Strength: 1000Vrms min. @ sea level
- Easy Assembly - Snap-In Mounting
- Contact Rating: 6A @ 125VAC
- Contamination resistant - extended actuator



For quantities greater than listed, call for quote.

| MOUSER STOCK NO. | C&K Part No. | Fig. | Contact Form | Circuit | Price Each | | | |
|-------------------|---------------|------|--------------|---------|------------|------|------|------|
| | | | | | 1 | 25 | 50 | 100 |
| 611-LP02C31T203DQ | LP02C31T203DQ | U | SPDT | On-Off | 3.35 | 2.71 | 2.48 | 2.40 |
| 611-LP22C31T203DQ | LP22C31T203DQ | U | DPDT | On-Off | 4.03 | 3.60 | 3.52 | 3.36 |

C&K SK SERIES: SIDE KNOB SLIDE SWITCHES

Features:

- 10,000 cycles
- Fully automatic assembly and inspection

Typical Applications:

- Volume control switch for phone



For quantities greater than listed, call for quote.

| MOUSER STOCK NO. | C&K Part No. | Fig. | Contact Form | Circuit | Rating | Price Each | | | |
|----------------------|----------------------|------|--------------|-------------|-----------------|------------|------|-----|-----|
| | | | | | | 1 | 25 | 100 | 250 |
| 611-SK12C0405SG1.5RT | SK-12C0405-SG 1.5 RT | V | SPDT | On-On | 0.3 Amp @ 4VDC | .98 | .88 | .84 | .77 |
| 611-SK-12C06-MG4.4NS | SK-12C06-MG 4.4 NS | W | SPDT | On-On | 0.2 Amp @ 30VDC | .66 | .59 | .55 | .47 |
| 611-SK-12F17-G7 | SK-12F17-G 7 | X | SPDT | On-On | 0.3 Amp @ 30VDC | .62 | .49 | .47 | .41 |
| 611-SK-13D08-G5E | SK-13D08-G 5 E | Y | SP3T | On-On-On | 0.3 Amp @ 30VDC | .62 | .49 | .47 | .41 |
| 611-SK-13D26-G6.5KGY | SK-13D26-G 6.5 K GY | Y | SP3T | On-On-On | 0.3 Amp @ 30VDC | .66 | .59 | .55 | .47 |
| 611-SK-14D01-G6 | SK-14D01-G 6 | Z | 4P4T | On-On-On-On | 0.3 Amp @ 30VDC | .42 | .36 | .29 | .26 |
| 611-SK-14D07-VG6 | SK-14D07-VG 6 | Z | SP4T | On-On-On-On | 0.3 Amp @ 30VDC | .54 | .432 | .41 | .34 |
| 611-SK-22D01-MG5NS | SK-22D01-MG 5 NS | AA | DPDT | On-On | 0.3 Amp @ 30VDC | .62 | .49 | .47 | .41 |
| 611-SK-23H11-G9S | SK-23H11-G 9 S | BB | DP3T | On-On | 0.3 Amp @ 30VDC | 1.02 | .92 | .88 | .76 |

C&K SS SERIES: SLIDE SWITCHES

Features:

- Miniature slide switch
- 10,000 cycles

Typical Applications:

- Industrial control, sensor control machine, etc.



For quantities greater than listed, call for quote.

| MOUSER STOCK NO. | C&K Part No. | Fig. | Contact Form | Circuit | Rating | Price Each | | | |
|----------------------|------------------------|------|--------------|-------------|-----------------|------------|------|------|-----|
| | | | | | | 1 | 25 | 100 | 250 |
| 611-SS12D07VG4NSGAPA | SS-12D07-VG 4 NS GA PA | CC | SPDT | On-On | 0.3 Amp @ 6VDC | .54 | .432 | .41 | .34 |
| 611-SS-12D1505-G2 | SS-12D1505-G 2 | DD | SPDT | On-On | 0.3 Amp @ 6VDC | .71 | .64 | .48 | .42 |
| 611-SS-13D16-VG4PA | SS-13D16-VG 4 PA | EE | SP3T | On-On-On | 0.3 Amp @ 30VDC | .64 | .54 | .46 | .40 |
| 611-SS-22D0205-G2 | SS-22D0205-G 2 | FF | DPDT | On-On | 0.3 Amp @ 6VDC | .86 | .81 | .72 | .57 |
| 611-SS-22F02-DG6(L) | SS-22F02-DG 6 (L) | GG | DPDT | On-On | 0.3 Amp @ 30VDC | .71 | .67 | .48 | .42 |
| 611-SS-23D28-G5NS | SS-23D28-G 5 NS | HH | DP3T | On-On-On | 0.3 Amp @ 30VDC | .76 | .69 | .64 | .57 |
| 611-SS-23E06-G5 | SS-23E06-G 5 | II | DP3T | On-On-On | 0.3 Amp @ 30VDC | .73 | .71 | .48 | .42 |
| 611-SS-24E06-TG5P | SS-24E06-TG 5 (P) | JJ | DP4T | On-On-On-On | 0.3 Amp @ 30VDC | .81 | .76 | .704 | .57 |
| 611-SS-44D04-G4 | SS-44D04-G 4 | KK | DP4T | On-On-On-On | 0.3 Amp @ 30VDC | 1.12 | 1.01 | .96 | .83 |



C&K Slide Switches

