

# C&K Slide Switches

## C&K TS SERIES: TINY SLIDE SWITCHES

**Features:**

- Epoxy terminal seal makes these compatible with bottom-wash cleaning

**Applications:**

- Instrumentation
- Computer peripherals

**Specifications:**

- Contact Material: B- Cu alloy, with Au plate over Ni plate, Au plate terminal
- Contact Rating: B- 0.4VA @ 20VAC or DC max.
- Dielectric Strength: 1000 Vrms min. @ sea level
- Electrical Life: TS01 models - 60,000 cycles @ full load  
TS03 models - 30,000 cycles @ full load



RoHS Compliant

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	C&K Part No.	Fig.	Contact Form	Circuit	Contact Material	Price Each			
						1	25	50	100
<b>PC Thru-Hole</b>									
611-TS01CBE	TS01CBE	A	SPDT	On-None-On	B	4.46	4.10	3.85	3.68
<b>Right-Angle PC Thru-Hole</b>									
611-TS01ABE	TS01ABE	B	SPDT	On-None-On	B	4.83	4.35	4.21	4.01

## C&K 1000 SERIES: MINIATURE SLIDE SWITCHES

**Features:**

- Epoxy terminal seal makes these compatible with bottom-wash cleaning

**Applications:**

- Instrumentation
- Computer peripherals

**Specifications:**

- Contact Material: B- Cu alloy, with Au plate over Ni plate, Au plate terminal  
Q- Cu alloy, with Ag plate, Ag plate terminal
- Contact Rating: B- 0.4VA @ 20VAC or DC max.  
Q- 6A @ 120VAC or 28VDC

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	C&K Part No.	Fig.	Contact Form	Circuit	Contact Material	Price Each			
						1	25	50	100
<b>PC Thru-Hole</b>									
611-1101M2S3CBE2	1101M2S3CBE2	C	SPDT	On-None-On	B	4.00	3.88	3.28	3.15
611-1101M2S3CQE2	1101M2S3CQE2	C	SPDT	On-None-On	Q	3.90	3.43	3.32	3.16
611-1201M2S3CBE2	1201M2S3CBE2	D	DPDT	On-None-On	B	8.68	8.09	7.63	7.11
611-1201M2S3CQE2	1201M2S3CQE2	D	DPDT	On-None-On	Q	7.47	7.03	6.61	6.17
<b>Right-Angle PC Thru-Hole</b>									
611-1101M2S3ABE2	1101M2S3ABE2	E	SPDT	On-None-On	B	4.50	4.36	3.90	3.71
611-1101M2S3AQE2	1101M2S3AQE2	E	SPDT	On-None-On	Q	4.50	4.36	3.81	3.67
611-1101M2S3AV2BE2	1101M2S3AV2BE2	F	SPDT	On-None-On	B	5.32	4.48	4.29	3.54
611-1101M2S3AV2QE2	1101M2S3AV2QE2	F	SPDT	On-None-On	Q	4.50	4.36	3.81	3.67
<b>V-Bracket</b>									
611-1101M2S2V3GE2	1101M2S2V3GE2	G	SPDT	On-None-On	B	5.07	4.72	4.49	4.29
<b>Solder Lug</b>									
611-1101M1S3ZQE2	1101M1S3ZQE2	G	SPDT	On-None-On	Q	3.75	3.36	3.22	3.07

## C&K L SERIES: MINIATURE SLIDE SWITCHES

**Features:**

- Positive detent

**Applications:**

- Communications equipment
- Lighting devices

**Specifications:**

- Contact Material: Q- Cu alloy, with Ag plate, Ag plate terminal
- Contact Rating: Q- 4A @ 120VAC or 28VDC
- Actuator Height: PC thru-hole models - 200";  
Right-angle PC thru-hole models - .335"



RoHS Compliant

( ) = Momentary

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	C&K Part No.	Fig.	Contact Form	Circuit	Contact Material	Price Each			
						1	25	100	250
<b>PC Thru-Hole</b>									
611-L202011MS02Q	L202011MS02Q	H	DPDT	On-Off	Q	3.08	2.81	2.43	2.18
611-L203011MS02Q	L203011MS02Q	I	DP3T	On-On-On	Q	3.02	2.79	2.53	2.28
<b>Right-Angle PC Thru-Hole</b>									
611-L102011ML04B	L102011ML04B	I	SPDT	On-None-On	B	2.68	2.51	2.27	2.14
611-L102011ML04Q	L102011ML04Q	I	SPDT	On-None-On	Q	1.84	1.75	1.57	1.50
611-L102011MS02B	L102011MS02B	I	SPDT	On-None-On	B	2.68	2.51	2.27	2.14
611-L204121MS02Q	L204121MS02Q	I	DP4T	On-None-On	Q	3.61	3.36	3.05	2.87
611-L102011ML04Q	L102011ML04Q	J	SPDT	On-None-On	Q	1.87	1.59	1.41	1.32
611-L202011MA04Q	L202011MA04Q	K	DPDT	On-None-On	Q	4.23	3.95	3.46	3.31
611-L212132MV02Q	L212132MV02Q	L	DPDT	(On)-None-On	Q	4.22	3.99	3.50	3.23

## C&K S SERIES: POWER SLIDE SWITCHES

**Features:**

- Enclosed housing

**Applications:**

- Portable tools and small appliances

**Specifications:**

- Contact Material: Q- Cu alloy, with Ag plate, Ag plate terminal
- Dielectric Strength: 1000 Vrms min. @ sea level
- Electrical Life: 10,000 cycles @ full load



RoHS Compliant

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	C&K Part No.	Fig.	Contact Form	Circuit	Contact Material	Price Each			
						1	25	100	250
<b>PC Thru-Hole</b>									
611-S202031MS02Q	S202031MS02Q	M	DPDT	6	Q	2.72	2.50	2.22	1.97
<b>Panel Mount with Mounting Ears</b>									
611-S101031SS03Q	S101031SS03Q	N	SPST	6	Q	1.95	1.86	1.72	1.55
611-S602031SS03Q	S602031SS03Q	N	DPDT	12	Q	3.43	3.20	2.81	2.68

## C&K V SERIES: POWER AND LINE VOLTAGE SELECT

**Applications:**

- Appliances

**Specifications:**

- Contact Material: Q- Cu alloy, w/ Ag plate, Ag plate terminal
- Contact Form: DPDT On-On



RoHS Compliant

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	C&K Part No.	Fig.	Contact Form	Circuit	Price Each			
					1	25	100	250
611-V80212MS02Q	V80212MS02Q	O	DPDT	PC thru-hole	4.17	3.88	3.51	3.06
611-V80212SS05Q	V80212SS05Q	P	DPDT	Mounting ears, QC	4.17	3.88	3.51	3.06
611-V80212MA08Q	V80212MA08Q	Q	DPDT	R/A PC thru-hole	5.34	5.10	3.81	3.49

**DIMENSIONS: in.**

C&K Slide Switches