


Slide Switches

 This product is RoHS compliant.

ALPHA MINIATURE SLIDE SWITCHES

Specifications:

- Contact Resistance: 10mΩ max
- Operating Temperature: -30°C to +85°C
- Electrical Life: 30,000 cycles
- Insulation Resistance: 1000MΩ min.

RoHS Compliant

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Alpha Part No.	Fig.	Type	Rating	Price Each				
					1	50	100	500	1000
106-SS60012F-12	SS60012F-0102-4V-NB	A	SPDT	.3A/125 VAC	.75	.63	.57	.52	.48
106-SS70020F-22-6	SS70020F-0202-6T-NB	B	DPDT	.3A/125 VAC	1.49	1.30	.91	.81	.74
106-SS70020F-22-12	SS70020F-0202-12T-NB	B	DPDT	.3A/125 VAC	1.49	1.30	.91	.81	.74

ALPHA SLIDE SWITCHES

Specifications:

- Contact Resistance: 25mΩ max
- Insulation Resistance: 500VDC-100MΩ min.
- Dielectric Strength: 500VAC/1 minute

RoHS Compliant

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Alpha Part No.	Fig.	Type	Rating	Price Each				
					1	50	100	500	1000
Non-Shorting									
105-SV71030F-13NS	SV71030F-0103-9T-NP	C	SP3T	.1A/30VDC	1.62	1.43	1.04	.95	.88
Free Timing									
105-SV65010F-12FT	SV65010F-0102-6H-FN	D	SPDT	.3A/125VAC	1.62	1.43	1.04	.95	.88
105-SV68010F-23FT	SV68010F-0203-6V-FS	E	DP3T	.3A/125VAC	1.62	1.43	1.04	.95	.88

MOUNTAIN SWITCH TRAVEL SLIDE SWITCHES

2mm Travel Slide Switch

Specifications:

- Rating: Non-Switching-100mA/50VDC Switching-25mA/24VDC
- Operating Temperature: -20°C to +70°C
- Contact Resistance: 100mΩ max.
- Dielectric Strength: 500VAC/1 minute
- Insulation Resistance: 100MΩ min.

RoHS Compliant

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Type	Circuit	Price Each				
				1	50	100	500	1000
Thru-Hole Type								
103-5026-EV	F	SPDT	On-On	1.20	1.00	.91	.83	.76
103-5028-EV	G	SP3T	On-On-On	1.28	1.07	.97	.88	.81
SMD Type								
103-5031-EV	H	SPDT	On-On	1.36	1.13	1.03	.94	.86

Miniature 1.5mm Travel Slide Switches, SMD Type

Specifications:

- Rating: Non-Switching-300mA/4VDC Switching-25mA/24VDC
- Operating Temperature: -20°C to +70°C
- Contact Resistance: 70mΩ max.
- Dielectric Strength: 100VAC/1 minute
- Insulation Resistance: 100MΩ min.

RoHS Compliant

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Type	Circuit	Price Each				
				1	50	100	500	1000
103-5040-EV	I	SPDT	On-On	1.28	1.07	.97	.88	.81
103-5042-EV	J	DPDT	On-On	1.87	1.56	1.42	1.29	1.19
103-5043-EV	K	SP4T	On-On-On	1.87	1.56	1.42	1.29	1.19

SHIN CHIN SLIDE SWITCHES

R13-602 Series

Specifications:

- Rating: 6A/125VAC, 3A/250VAC
- Contact Resistance: 50mΩ max.
- Insulation Resistance: 500VDC 100MΩ min.

 RoHS Compliant


For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Alpha Part No.	Fig.	Type	Circuit	Price Each				
					1	50	100	500	1000
112-R13-602A	R13-602A-05	L	SPST	On-Off	.79	.62	.58	.54	.50
112-R13-602B	R13-602B-05	L	DPDT	On-On	1.18	.97	.88	.80	.74

R13-608 Series

Specifications:

- Rating: 16A/125VAC, 10A/250VAC
- Contact Resistance: 50mΩ max.
- Insulation Resistance: 500VDC 100MΩ min.

 RoHS Compliant

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Alpha Part No.	Fig.	Type	Circuit	Price Each				
					1	50	100	500	1000
112-R13-608A1	R13-608A1-02-BB9	M	SPST	On-Off	3.31	3.01	2.74	2.49	2.29

WELL BUYING SLIDE SWITCH

SS001 Series

Specifications:


- Rating: 0.3A/6VDC
- Operating Force: 200gf-150gf
- Applications:
 - Consumer products
 - Instrumentation
 - Computer products
 - Communication equipment
 - Hand-held devices

RoHS Compliant

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Well Buying Part No.	Fig.	Number of Poles	Number of Positions	Price Each		
					1	50	100
107-SS001-S032NAPA12	SS001-S032NAPA1.2	N	3	2	1.56	1.30	1.18

DIMENSIONS: in.



Dimensional drawings A through N showing various slide switch models with their respective dimensions in inches.

Slide Switches