

MAGNECRAFT Power Relays



CLASS 725 POWER RELAYS

- Applications:**
- Automation Panels
 - Packaging Machinery
 - Appliances
 - HVAC and Refrigeration
 - Food and Beverage



Features	Advantage	Benefit
High ratings (up to 30Amp, 3HP)	Switches high-current loads	Meets demand for high power applications
4,000V dielectric strength (coil to contacts)	Withstands severe voltage surges and spikes	Provides protection for surrounding circuits
Multiple mounting options	Increases functionality and ease of use	Provides solutions for a wide variety of applications
Full featured cover (Plug-in socket mount)	Offers push-to-test button, lock-down door, LED, flag indicators and ID tag	Simplifies and expedites installation and testing
Finger-safe cover and terminals (on relays with screw terminals)	Prevents operator from touching live circuits (IP 20% of protection)	Increases safety in work environment

DIMENSIONS: in. (mm)

Plug-in Socket Mount Full Feature Cover

A

Panel/DIN Mount with quick connect terminals

B

Panel/DIN Mount with screw terminals

C

Relay Wiring Diagrams

70-725-1 Socket

D

Socket Wiring Diagram

General Purpose Relays

MOUSER STOCK NO.	Magnecraft Part No.	Fig.	Contact		Terminal Style	Mount Option	Coil Voltage	Price Each		
			Form	Rating				1	10	25
528-725AXXB4L-120A	725AXXB4L-120A	A	SPST-NO	30A	Quick Connect	Plug-in	120VAC	13.75	13.27	11.77
528-725AXXBC3ML-12D	725AXXBC3ML-12D	B	SPST-NO	30A	Quick Connect	DIN and Flange Cover	12VDC	13.75	13.27	11.77
528-725AXXBC3ML-24D	725AXXBC3ML-24D	B	SPST-NO	30A	Quick Connect	DIN and Flange Cover	24VDC	13.74	13.26	11.76
528-725AXXBC3ML-24A	725AXXBC3ML-24A	B	SPST-NO	30A	Quick Connect	DIN and Flange Cover	24VAC	14.50	13.99	12.41
528-725AXXBC3ML-120A	725AXXBC3ML-120A	B	SPST-NO	30A	Quick Connect	DIN and Flange Cover	120VAC	14.50	13.99	12.41
528-725AXXBC3ML-240A	725AXXBC3ML-240A	B	SPST-NO	30A	Quick Connect	DIN and Flange Cover	240VAC	15.25	14.71	13.05
528-725AXXSC3ML-12D	725AXXSC3ML-12D	C	SPST-NO	30A	Screw Terminal	DIN and Flange Cover	12VDC	18.24	17.60	15.61
528-725AXXSC3ML-24D	725AXXSC3ML-24D	C	SPST-NO	30A	Screw Terminal	DIN and Flange Cover	24VDC	34.19	32.96	29.30
528-725AXXSC3ML-120A	725AXXSC3ML-120A	C	SPST-NO	30A	Screw Terminal	DIN and Flange Cover	120VAC	20.23	19.52	17.32
528-725AXXB4L-24D	725AXXB4L-24D	A	SPST-NO	30A	Quick Connect	Plug-in	24VDC	13.00	12.52	11.12
528-725BXXBC3ML-12D	725BXXBC3ML-12D	B	DPST-NO	25A	Quick Connect	DIN and Flange Cover	12VDC	14.25	13.75	12.20
528-725BXXBC3ML-24D	725BXXBC3ML-24D	B	DPST-NO	25A	Quick Connect	DIN and Flange Cover	24VDC	14.25	13.75	12.20
528-725BXXBC3ML-24A	725BXXBC3ML-24A	B	DPST-NO	25A	Quick Connect	DIN and Flange Cover	24VAC	15.00	14.47	12.84
528-725BXXBC3ML-120A	725BXXBC3ML-120A	B	DPST-NO	25A	Quick Connect	DIN and Flange Cover	120VAC	15.00	14.47	12.84
528-725BXXBC3ML-240A	725BXXBC3ML-240A	B	DPST-NO	25A	Quick Connect	DIN and Flange Cover	240VAC	15.75	15.05	13.47
528-725BXXB4L-24D	725BXXB4L-24D	A	DPST-NO	25A	Quick Connect	Plug-in	24VDC	14.23	13.73	12.18
528-725BXXSC3ML-12D	725BXXSC3ML-12D	C	DPST-NO	25A	Screw Terminal	DIN and Flange Cover	12VDC	19.98	19.27	17.10
528-725BXXSC3ML-24D	725BXXSC3ML-24D	C	DPST-NO	25A	Screw Terminal	DIN and Flange Cover	24VDC	20.00	19.29	17.12
528-725BXXSC3ML-24A	725BXXSC3ML-24A	C	DPST-NO	25A	Screw Terminal	DIN and Flange Cover	24VAC	20.75	20.02	17.76
528-725BXXSC3ML-120A	725BXXSC3ML-120A	C	DPST-NO	25A	Screw Terminal	DIN and Flange Cover	120VAC	20.75	20.02	17.76
528-725BXXSC3ML-240A	725BXXSC3ML-240A	C	DPST-NO	25A	Screw Terminal	DIN and Flange Cover	240VAC	23.76	22.36	21.12

Socket and Hold Down Clip for Class 782/725 Relays

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Magnecraft Part No.	Fig.	Description	Price Each		
				1	10	25
528-70-725-1	70-725-1	D	6 Pin, 30AMPS, 300V Use With 725 Plug-in Models	14.00	13.51	11.89
528-16-725SC-1	16-725SC-1	D	Metal Hold Down Clip For 725 Relays	1.80	1.74	1.54

