

P&B General Purpose Relays

KUHP SERIES: 20 AND 30 AMP ENCLOSED GENERAL PURPOSE RELAYS

RELAYS

Specifications:

- Enclosure: Clear polycarbonate cover
- Expected mechanical life: 10 million operations min.
- Contact material: AgCdO
- Terminals: .250" QC/Solder



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	P&B Part No.	Fig.	Coil Voltage	Contact Form	Contact Rating	Price Each			
						1	25	50	100
Bracket Mount Case									
655-KUHP-5A51-24	KUHP-5A51-24	A1	24VAC	SPDT	30A	29.71	25.98	23.51	20.91
655-KUHP-5A51-120	KUHP-5A51-120	A1	120VAC	SPDT	30A	32.63	28.53	25.82	20.37
655-KUHP-5D51-12	KUHP-5D51-12	A1	12VDC	SPDT	30A	16.20	14.44	13.08	11.90
655-KUHP-5D51-24	KUHP-5D51-24	A1	24VDC	SPDT	30A	29.31	25.64	23.22	18.30
655-KUHP-11A51-24	KUHP-11A51-24	A2	24VAC	DPDT	20A	37.37	32.69	29.58	23.35
655-KUHP-11A51-120	KUHP-11A51-120	A2	120VAC	DPDT	20A	18.84	16.48	14.19	11.77
655-KUHP-11D51-12	KUHP-11D51-12	A2	12VDC	DPDT	20A	17.99	15.74	14.25	11.25
655-KUHP-11D51-24	KUHP-11D51-24	A2	24VDC	DPDT	20A	18.19	15.91	14.40	11.37
Top Flange Case									
655-KUHP-5AT1-120	KUHP-5AT1-120	B1	120VAC	SPDT	30A	32.80	28.68	25.96	20.48
655-KUHP-5DT1-12	KUHP-5DT1-12	B1	12VDC	SPDT	30A	29.49	25.78	23.35	18.43
655-KUHP-5DT1-24	KUHP-5DT1-24	B1	24VDC	SPDT	30A	29.26	25.58	23.15	18.27
655-KUHP-11AT1-120	KUHP-11AT1-120	B2	120VAC	DPDT	20A	16.74	14.64	13.26	11.46
655-KUHP-11DT1-12	KUHP-11DT1-12	B2	12VDC	DPDT	20A	18.19	15.91	14.40	11.37
655-KUHP-11DT1-24	KUHP-11DT1-24	B2	24VDC	DPDT	20A	34.41	30.11	27.25	21.73

KUL SERIES: 10 AMP MAGNETIC LATCHING RELAY

Specifications:

- Enclosure: Clear polycarbonate cover
- Expected mechanical life: 100,000 operations min.
- Contact material: AgCdO
- Terminals: .187" QC/Solder; silver-cadmium oxide, 10Amps



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	P&B Part No.	Fig.	Coil Voltage	Contact Form	Number of Coils	Price Each			
						1	25	50	100
655-KUL-11A15S-120	KUL-11A15S-120	C3	120VAC	DPDT	1	53.64	46.93	42.46	33.52
655-KUL-11D15D-12	KUL-11D15D-12	C4	12VDC	DPDT	2	60.60	53.02	47.98	41.95
655-KUL-11D15D-24	KUL-11D15D-24	C4	24VDC	DPDT	2	60.60	53.02	47.98	41.95
Sockets and Accessories for KUL Series									
655-27E043	27E043			Solder eyelet socket, rated 15A, for 1-3 pole relays		1.95	1.77	1.71	1.59
655-27E067	27E067			PCB terminal socket, rated 15A, for 1-3 pole relays		3.58	3.20	3.08	2.76
655-27E121	27E121			Screw terminal socket, rated 15A, for 1-3 pole relays		7.79	7.07	6.82	5.42
655-27E396	27E396			.187" quick connect socket, rated 15A, for 1-3 pole relays		3.66	3.19	2.89	2.28
655-27E893	27E893			Screw term., DIN rail snap-mnt socket, for 1-3 pole relays		10.44	9.12	8.25	6.52
655-20C247	20C247			Hold down spring for 27E043 and 27E067		1.60	1.40	1.26	1.00
655-20C314	20C314			Hold down spring for 27E121		.43	.37	.34	.31
655-20C318	20C318			Hold down spring for 27E893		.29	.25	.22	.19
655-24A110	24A110			Aluminum DIN rail track, 36"		13.51	11.82	10.70	8.45

KUMP SERIES: 15 AMP ENCLOSED GENERAL PURPOSE RELAYS

Specifications:

- Enclosure: Clear polycarbonate cover
- Expected mechanical life: 100,000 operations min.
- Contact material: AgCdO
- Terminals: .187" QC/solder; silver-cadmium-oxide
- Mounting: #6-32 stud, .218" locating tab



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	P&B Part No.	Fig.	Coil Voltage	Contact Form	Contact Rating	Price Each			
						1	25	50	100
655-KUMP-11A18-24	KUMP-11A18-24	D5	24VAC	DPDT	15A	18.00	15.75	14.24	11.29
655-KUMP-11A18-120	KUMP-11A18-120	D5	120VAC	DPDT	15A	15.59	13.64	12.34	10.66
655-KUMP-11D18-12	KUMP-11D18-12	D5	12VDC	DPDT	15A	14.67	12.41	11.53	10.90
655-KUMP-11D18-24	KUMP-11D18-24	D5	24VDC	DPDT	15A	16.78	14.67	13.28	10.48
655-KUMP-11D18-110	KUMP-11D18-110	D5	110VDC	DPDT	15A	17.91	15.68	14.17	11.24
655-KUMP-14A18-120	KUMP-14A18-120	D6	120VAC	3PDT	15A	16.91	13.74	12.93	12.56
655-KUMP-14D18-12	KUMP-14D18-12	D6	12VDC	3PDT	15A	16.97	13.89	12.92	12.40
655-KUMP-14D18-24	KUMP-14D18-24	D6	24VDC	3PDT	15A	18.12	14.82	13.60	12.67
Sockets and Accessories for KUMP Series									
655-27E043	27E043			Solder eyelet socket, rated 15A, for 1-3 pole relays		1.95	1.77	1.71	1.59
655-27E067	27E067			.187" quick connect, rated 15A, for 1-3 pole relays		3.58	3.20	3.08	2.76
655-27E121	27E121			Screw terminal socket, rated 15A, for 1-3 pole relays		7.79	7.07	6.82	5.42
655-27E396	27E396			.187" quick connect socket, rated 15A, for 1-3 pole relays		3.66	3.19	2.89	2.28
655-27E867	27E867			Screw terminal socket, rated 15A, for 4 pole relays		21.21	18.56	16.78	13.26
655-27E893	27E893			Screw term., DIN rail snap-mnt socket, for 1-3 pole relays		10.44	9.12	8.25	6.52
655-20C228	20C228			Hold down spring with screw for 27E043 and 27E067		.76	.666	.602	.475
655-20C254	20C254			Snap-on hold down spring for 27E043 and 27E067		.31	.267	.235	.192
655-20C318	20C318			Hold down spring for 27E893		.29	.25	.22	.19
655-24A110	24A110			Aluminum DIN rail track, 36"		13.51	11.82	10.70	8.45

MT SERIES: GENERAL PURPOSE MULTIMODE RELAY

Specifications:

- Enclosure: clear polycarbonate cover
- Expected mechanical life: 20 million operations min.
- Contact rating/material: 10A/AgNi (90/10)
- Mechanical indicator (test-button)
- 10Amp



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	P&B Part No.	Fig.	Coil Voltage	Contact Form	Number of Pins	Price Each			
						1	25	50	100
655-MT226024	MT226024	E7	24VAC	DPDT	8 pin	14.81	12.95	11.72	9.25
655-MT226115	MT226115	E7	115VAC	DPDT	8 pin	17.30	15.13	13.69	10.81
655-MT221012	MT221012	E7	12VDC	DPDT	8 pin	16.39	14.34	12.97	10.24
655-MT221024	MT221024	E7	24VDC	DPDT	8 pin	16.42	14.36	12.99	10.26
655-MT326115	MT326115	E8	115VAC	3PDT	11 pin	15.05	13.17	11.91	10.43
655-MT321012	MT321012	E8	12VDC	3PDT	11 pin	17.30	15.13	13.69	10.81
655-MT321024	MT321024	E8	24VDC	3PDT	11 pin	17.30	15.13	13.69	10.81

DIMENSIONS: mm

A

B

C

D

E

Terminal Arrangements

1

SPDT

2

DPDT

3

DPDT

4

DPDT

5

DPDT

6

3PDT

7

DPDT

8

3PDT

General Purpose Relays TE Connectivity