

# EAGLE PLASTIC DEVICES Nylon PCB Hardware



This page of product is compliant.

## FEMALE NYLON CIRCUIT BOARD POSTS

- Molded in Natural Nylon 6/6
- Circuit board hole size - .156 diameter
- Panel Thickness: 1/16

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Description	Price Each		
			1	100	500
561-0375A	A	0.375	.31	.29	.27
561-0500A	A	0.500	.33	.30	.28
561-0625A	A	0.625	.35	.33	.299
561-0750A	A	0.750	.34	.31	.29
561-0875A	A	0.875	.36	.34	.31
561-1000A	A	1.000	.35	.32	.30
561-1125A	A	1.125	.35	.33	.30

## MALE-FEMALE CIRCUIT BOARD SUPPORT

- Molded in Natural Nylon 6/6
- 3/8" board spacing

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Description	Price Each		
			1	100	500
561-F0375	B	3/8"	.11	.10	.09
561-F0625	B	5/8"	.11	.10	.096

## SQUARE STANDOFF LED MOUNT

LED mount provides secure mounting of both two and three lead devices. Nylon mount provides protection from heat, shock, and vibration. Symmetrical design with feet on both sides eliminating need for specific side rotation.

- Molded in Natural Nylon 6/6

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Description	Price Each		
			1	100	500
561-TRM001	C	TRM 001	.17	.16	.149

## POWER TRANSISTOR MOUNTS

Simplify power transistor mountings and insulation, and improve thermal efficiency with molded insulators.

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Description	Price Each		
			1	100	500
<b>Standard - Molded in Natural Nylon 6/6</b>					
561-19PT2	D	TO-66 with barrier	.19	.17	.16
<b>Heavy Duty - Molded in Glassfilled Polyester</b>					
561-20PT11-HD	E	TO-3 with barrier	.21	.19	.18
561-18PT1-HD-WOB	E	TO-3 w/o barrier	.20	.19	.17

## POWER TRANSISTOR COVERS

- Molded in Natural Nylon 6/6

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Description	Price Each		
			1	100	500
<b>TO-3 Configuration</b>					
561-C01032	F	5 hole	.46	.42	.39

## NYLON PUSH SPACERS

- Hole size: .187"

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Dimensions: in.		Panel Depth	Price Each		
		A	B		1	100	500
561-PS250	G	.281	.250	.062	.07	.05	.04
561-PS500	G	.313	.500	.093	.23	.16	.117
561-PS500A	G	.313	.500	.062	.12	.08	.06
561-PS625	G	.281	.625	.062	.08	.05	.042

## COVERED SPACERS

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Dimensions: in.			Price Each		
		A	B	L	1	100	500
561-130001	H	.750	.260	.125	.17	.11	.083
561-130002	H	.843	.257	.156	.24	.159	.124
561-130003	H	.835	.218	.500	.37	.25	.189
561-130004	H	.000	.260	.250	.32	.22	.157
561-130005	H	.000	.325	.250	.31	.21	.15
561-130006	H	.000	.250	.125	.40	.27	.199
561-130007	H	.875	.375	.250	.27	.18	.136

## MINI LOCKING PCB SUPPORTS

- Adhesive Base
- Ideal for smaller sized circuit boards

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Dimension A: in.	Price Each			
			1	100	500	1000
561-187TAB	I	0.187	.53	.35	.27	.22
561-250TAB	I	0.250	.54	.37	.28	.23
561-312TAB	I	0.312	.56	.38	.29	.24
561-375TAB	I	0.375	.55	.37	.28	.23
561-437TAB	I	0.437	.57	.38	.288	.235
561-500TAB	I	0.500	.54	.36	.27	.22
561-562TAB	I	0.562	.57	.38	.288	.246
561-625TAB	I	0.625	.54	.36	.27	.23

## NYLON HEAVY DUTY PCB SUPPORTS

- Snaps into P.C. board from bottom
- Molded in Black Nylon 6/6

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Board Clearance	PCB Hole Dia.	Chassis Hole Size	Price Each		
					1	100	500
561-C00500	J	.430-.460	.157	.312	.23	.21	.203

## NYLON HEAVY DUTY PCB SUPPORTS

- Snaps into P.C. board from bottom
- Molded in Natural Nylon 6/6

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Dimensions: in.				Price Each	
		A	B	C	D	1	100
561-RV250	K	.375	11/32"	.250	.060	.36	.33
561-RV375	K	.375	11/32"	.375	.060	.38	.35
561-RV625	K	.500	13/32"	.625	.063	.22	.20

## REVERSE LOCKING CIRCUIT BOARD SUPPORT STANDOFF

- Molded in Black Nylon 6/6

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Dim "A"	Body Dia.	Head Height	Hole Size	Price Each	
						1	100
561-RVS500	L	.500	.150	.045	.178	.20	.18

## TWO-PIECE NYLON FASTENER

- Molded in Black Nylon 6/6
- For use with edge connector assembly

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Dimensions: in.				Price Each		
		A	B	C	D	1	100	500
<b>Body Item "A"</b>								
561-0003A	M	.110	.480	-	-	.13	.12	.117
561-0004A	M	.096	.340	-	-	.11	.10	.096
<b>Pin Item "B"</b>								
561-0003B	M	-	-	.455	.069	.05	.04	.032
561-0004B	M	-	-	.340	.062	.04	.03	.021

## TRANSISTOR INSULATORS

- Designed to separate the mounting screw from the insulator
- Molded in Natural Nylon 6/6

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Dimensions: in.			Price Each		
		A	B	C	1	100	500
561-T001	N	.680	.476	.219	.17	.16	.149

## KNOCK OUT PLUGS

- Installs with fingertip pressure, no tools required
- Molded in gray nylon
- Head thickness: .125"
- Thickness: .453"

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Dimensions: in.		Price Each			
		Hole Dia.	Dia.	1	100	500	1000
561-0875KOP	O	0.875	1.016	.31	.21	.15	.13
561-1093KOP	O	1.093	1.218	.58	.38	.288	.245
561-1375KOP	O	1.375	1.500	.65	.42	.321	.267
561-1750KOP	O	1.750	1.925	.68	.46	.34	.28
561-2000KOP	O	2.000	2.140	.72	.48	.36	.30

