

HEYCO Liquid Tight Cordgrips



HEYCO LIQUID TIGHT STRAIGHT-THRU CORDGRIPS

Cordgrips are for flexible cords. Install in either clearance or threaded holes.

RoHS Compliant This product is RoHS compliant.

Cable Dia. Range (In.)		Black			Gray			Fig.			Description			Dimensions: in.			Price Each			
Min.	Max.	MOUSER STOCK NO.	Heyco Part No.	MOUSER STOCK NO.	Heyco Part No.	Fig.	Description	A	B	C	1	10	50	100						
Cordgrips for PG Hubs * Locknuts are included																				
0.064	0.210	836-3444	3444	836-3445	3445	A	RLTF 7	0.492	1.170	0.330	.85	.67	.63	.59						
0.114	0.250	836-3207	3207	836-3208	3208	A	LTF 7	0.492	1.170	0.330	.85	.67	.63	.59						
0.069	0.187	836-3446	3446	---	---	A	RLTF 9	0.599	1.300	0.340	.89	.70	.58	.50						
0.181	0.312	836-3210	3210	836-3211	3211	A	LTF 9	0.599	1.300	0.340	.89	.70	.58	.50						
0.069	0.250	836-3448	3448	836-3449	3449	A	RLTF 11	0.733	1.460	0.390	1.07	.85	.70	.61						
0.230	0.395	836-3213	3213	836-3214	3214	A	LTF 11	0.733	1.460	0.390	1.07	.85	.70	.61						
0.170	0.450	836-3216	3216	836-3217	3217	A	LTF 13.5	0.804	1.530	0.410	1.61	1.27	1.04	.89						
0.230	0.530	836-3219	3219	836-3220	3220	A	LTF 16	0.886	1.660	0.450	1.35	1.07	.93	.86						
0.250	0.490	836-3454	3454	---	---	A	RLTF 21	1.115	1.870	0.520	1.89	1.49	1.24	1.07						
0.450	0.705	836-3222	3222	836-3223	3223	A	LTF 21	1.115	1.870	0.520	1.89	1.49	1.24	1.07						
0.590	0.900	836-3225	3225	836-3226	3226	A	LTF 29	1.470	2.230	0.590	3.36	2.65	2.19	1.90						
Cordgrips for NPT Hubs * Locknuts are not included.																				
0.069	0.187	836-3458	3458	---	---	A	RLTF 3/8	0.670	1.490	0.530	.80	.63	.53	.45						
0.181	0.312	836-3228	3228	836-3229	3229	A	LTF 3/8	0.670	1.490	0.530	.80	.63	.58	.54						
0.170	0.470	836-3231	3231	836-3232	3232	A	LTF 1/2	0.875	1.720	0.620	1.07	.85	.70	.65						
0.230	0.546	836-3200	3200	836-3201	3201	A	LLTF 1/2	0.875	1.830	0.620	1.22	.97	.89	.83						
0.450	0.709	836-3234	3234	836-3235	3235	A	LTF 3/4	1.068	1.970	0.630	1.70	1.34	1.20	1.11						
0.250	0.485	836-3460	3460	836-3461	3461	A	RLTF 3/4	1.068	1.970	0.630	1.70	1.34	1.11	.97						
0.590	1.000	836-8437	8437	836-8438	8438	A	LTF 1	1.375	2.420	0.750	3.02	2.38	1.97	1.71						

"HEYCO TITE" LIQUID TIGHT STRAIGHT-THRU CORDGRIPS

"Ratchet design" of sealing nut assembly provides superior anti-vibration protection and ensures a firm grip on the cable. Integral "Sealing Ring" ensures a superior seal at mounting location every time.

Cable Dia. Range (In.)		Black			Gray			Fig.			Description			Dimensions: in.			Price Each			
Min.	Max.	MOUSER STOCK NO.	Heyco Part No.	MOUSER STOCK NO.	Heyco Part No.	Fig.	Description	A	B	C	1	10	50	100						
Cordgrips for PG Hubs * Locknuts are included																				
0.065	0.220	836-M3444	M3444	836-M3445	M3445	B	RLTCG 7	0.492	1.160	0.320	.96	.87	.80	.76						
0.115	0.250	836-M3207	M3207	836-M3208	M3208	B	LTCG 7	0.492	1.160	0.320	.96	.87	.80	.72						
0.105	0.312	836-M3210	M3210	836-M3211	M3211	B	LTCG 9	0.599	1.250	0.320	1.02	.92	.83	.76						
0.230	0.395	836-M3213	M3213	836-M3214	M3214	B	LTCG 11	0.733	1.480	0.380	1.22	1.11	1.02	.92						
0.095	0.260	836-M4500	M4500	---	---	B	RLTCG 13.5	0.804	1.500	0.410	1.34	1.22	1.11	1.02						
0.170	0.450	836-M3216	M3216	836-M3217	M3217	B	LTCG 13.5	0.804	1.500	0.410	1.34	1.22	1.11	1.02						
0.180	0.440	836-M4502	M4502	---	---	B	RLTCG 16	0.886	1.680	0.440	1.54	1.40	1.27	1.16						
0.260	0.546	836-M3219	M3219	836-M3220	M3220	B	LTCG 16	0.886	1.680	0.440	1.54	1.40	1.27	1.16						
0.250	0.485	836-M3454	M3454	836-M3455	M3455	B	RLTCG 21	1.115	1.890	0.520	2.14	1.94	1.77	1.61						
0.485	0.709	836-M3222	M3222	836-M3223	M3223	B	LTCG 21	1.115	1.890	0.520	2.14	1.94	1.77	1.61						
0.490	0.787	836-M4504	M4504	---	---	B	RLTCG 29	1.470	2.230	0.580	3.81	3.47	3.15	2.86						
0.590	1.000	836-M3225	M3225	---	---	B	LTCG 29	1.470	2.230	0.580	3.81	3.47	3.15	2.86						
Cordgrips for NPT Hubs * Locknuts are not included																				
0.105	0.315	836-M3228	M3228	836-M3229	M3229	C	LTCG 3/8	0.680	1.410	0.490	.91	.82	.75	.68						
0.095	0.260	836-M4518	M4518	836-M4519	M4519	C	RLTCG 1/2	0.875	1.700	0.610	1.22	1.11	1.02	.95						
0.170	0.450	836-M3231	M3231	836-M3232	M3232	C	LTCG 1/2	0.875	1.700	0.610	1.22	1.11	1.02	.95						
0.256	0.485	836-M3460	M3460	---	---	C	RLTCG 3/4	1.040	2.000	0.620	1.92	1.75	1.59	1.45						
0.485	0.709	836-M3234	M3234	---	---	C	LTCG 3/4	1.040	2.000	0.620	1.92	1.75	1.59	1.45						
0.490	0.787	836-M8439	M8439	---	---	C	RLTCG 1	1.326	2.410	0.760	3.42	3.11	2.83	2.57						
0.590	1.000	836-M8437	M8437	---	---	C	LTCG 1	1.326	2.410	0.760	3.42	3.11	2.83	2.57						

HYBRID LIQUID TIGHT CORDGRIPS

* Locknuts not included

Cable Dia. Range (In.)		MOUSER			Heyco			Fig.			Thread Size			Dimensions: in.			Price Each			
Min.	Max.	STOCK NO.	Part No.	STOCK NO.	Part No.	Fig.	Thread Size	A	B	C	1	10	50	100						
Cordgrips for PG Hubs																				
0.04	0.20	836-4450	4450	D	PG 7	0.50	0.87	0.20	3.62	3.43	3.27	3.10								
0.12	0.28	836-4451	4451	D	PG 7	0.50	0.87	0.20	3.62	3.43	3.27	3.10								
0.08	0.24	836-4452	4452	D	PG 9	0.61	1.02	0.24	4.66	4.43	4.21	3.99								
0.18	0.39	836-4453	4453	D	PG 9	0.61	1.02	0.24	4.66	4.43	4.21	3.99								
0.14	0.31	836-4454	4454	D	PG 11	0.75	1.22	0.24	6.05	5.75	5.46	5.19								
0.28	0.51	836-4455	4455	D	PG 11	0.75	1.22	0.24	6.05	5.75	5.46	5.19								
0.14	0.31	836-4456	4456	D	PG 13.5	0.83	1.24	0.26	6.05	5.75	5.46	5.19								
0.28	0.51	836-4457	4457	D	PG 13.5	0.83	1.24	0.26	6.05	5.75	5.46	5.19								
0.14	0.31	836-4458	4458	D	PG 16	0.91	1.24	0.26	6.05	5.75	5.46	5.19								
0.28	0.51	836-4459	4459	D	PG 16	0.91	1.24	0.26	10.54	10.00	9.51	9.04								
0.20	0.43	836-4460	4460	D	PG 16	0.91	1.48	0.26	6.05	5.75	5.46	5.19								
0.39	0.67	836-4461	4461	D	PG 16	0.91	1.48	0.26	10.54	10.00	9.51	9.04								
0.28	0.59	836-4462	4462	D	PG 21	1.14	1.57	0.28	15.17	14.41	13.70	13.00								
0.51	0.83	836-4463	4463	D	PG 21	1.14	1.57	0.28	15.17	14.41	13.70	13.00								
0.59	0.91	836-4464	4464	D	PG 29	1.48	1.89	0.31	23.77	22.58	21.45	20.38								
0.75	1.10	836-4465	4465	D	PG 29	1.48	1.89	0.31	23.77	22.58	21.45	20.38								
Cordgrips for Metric Hubs																				
0.04	0.20	836-4472	4472	D	M12 x 1.5	0.50	1.14	0.47	3.90	3.69	3.52	3.34								
0.12	0.28	836-4473	4473	D	M12 x 1.5	0.50	1.14	0.47	3.90	3.69	3.52	3.34								
0.08	0.24	836-4474	4474	D	M16 x 1.5	0.64	1.26	0.47	5.01	4.76	4.52	4.30								
0.18	0.39	836-4475	4475	D	M16 x 1.5	0.64	1.26	0.47	5.01	4.76	4.52	4.30								
0.14	0.31	836-4476	4476	D	M20 x 1.5	0.80	1.46	0.47	6.47	6.15	5.84	5.55								
0.28	0.51	836-4477	4477	D	M20 x 1.5	0.80	1.46	0.47	6.47	6.15	5.84	5.55								
0.20	0.43	836-4478	4478	D	M25 x 1.5	1.00	1.69	0.47	10.93	10.37	9.86	9.37								
0.39	0.67	836-4479	4479	D	M25 x 1.5	1.00	1.69	0.47	10.93	10.37	9.86	9.37								
0.28	0.59	836-4480	4480	D	M32 x 1.5	1.27	1.89	0.59	15.73	14.94	14.20	13.49								
0.51	0.83	836-4481	4481	D	M32 x 1.5	1.27	1.89	0.59	15.73	14.94	14.20	13.49								

Accessories - Locknuts

Thread Size	MOUSER STOCK NO.	Heyco Part No.	Fig.	Description	Dimensions: in.		Price Each			
					Thickness A	Wrenching B	1	10	50	100
PG Thread-Nickel Plated Brass										
PG 7	836-2257	2257	E	PG 7	0.110	0.591	.47	.43	.40	.37
PG 9	836-2258	2258	E	PG 9	0.110	0.709	.70	.66	.63	.60
PG 11	836-2259	2259	E	PG 11	0.118	0.827	.77	.73	.66	.57
PG 13.5	836-2260	2260	E	PG 13.5	0.118	0.906	.80	.74	.68	.63
PG 16	836-2261	2261	E	PG 16	0.118	1.024	.96	.88	.81	.75
PG 21	836-2262	2262	E	PG 21	0.138	1.261	1.32	1.21	1.12	1.03
PG 29	836-2263	2263	E	PG 29	0.158	1.615	2.06	1.89	1.74	1.60
Metric Thread-Nickel Plated Brass										
M12	836-2246	2246	E	LN M12	0.118	0.591	.59	.54	.49	.46
M16	836-2247	2247	E	LN M16	0.118	0.748	.79	.74	.68	.63