

# HEYCO Tight Cordgrrips and Strain Reliefs



## HEYCO LIQUID TIGHT STRAIGHT-THRU CORDGRIPS

RoHS Compliant This product is RoHS compliant.



### Accessories - Locknuts

Black		Gray		Fig.	Description	Price Each						
MOUSER STOCK NO.	MOUSER STOCK NO.	MOUSER STOCK NO.	MOUSER STOCK NO.			1	10	50	100			
<b>Nylon Locknuts, NPT Thread</b>												
836-8461	836-8462			A	NLN 3/8 NPT	.29	.23	.21	.19			
836-8463	836-8464			A	NLN 1/2 NPT	.29	.23	.21	.19			
836-8465	836-8466			A	NLN 3/4 NPT	.35	.31	.28	.26			
836-8467	-----			A	NLN 1 NPT	.75	.61	.51	.46			

## SNAP-IN RATCHETING STRAIN RELIEF

• Installs easily • Black • For Round and Double D Holes

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Heyco Part No.	Fig.	UL Type Designation	Panel Dimensions: In.		Description	Price Each					
				Hole Size	Max. Thickness		1	100	500	1000		
836-1280	1280	B	--	0.875	.125	RSR-875	.34	.32	.312	.296		

## SELF-LOCKING STRAIN RELIEFS

For Flat Cables • Black • 6/6 Nylon • 94V-2

MOUSER STOCK NO.	Heyco Part No.	Fig.	UL Type Designation	Hole Size	Max. Thickness	Description	Price Each					
836-1829	1829	C	SPT-1, SPT-2, HPN	.453 x .512	0.099	ST-100N	.23	.18	.15	.12		
836-1834	1834	C	SPT-2, SPT-3	.689 x .689	0.157	ST-200N	.26	.13	.11	.10		

For Round Cables • Black • 6/6 Nylon • 94V-2

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Heyco Part No.	Fig.	UL Type Designation	Hole Size	Max. Thickness	Description	Price Each					
836-1832	1832	D	SV, SVT, HPD	.453 x .512	0.099	ST-101N	.23	.18	.15	.12		
836-1836	1836	D	SJ, SJO, SJT	.689 x .689	0.157	ST-201N	.26	.16	.14	.12		
836-1848	1848	D	SJT, STO, SEOW-A	.689 x .689	0.157	ST-301N	.26	.13	.11	.10		

For Round and Flat Cables • Black • 6/6 Nylon • 94V-2

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Heyco Part No.	Fig.	UL Type Designation	Hole Size	Max. Thickness	Description	Price Each					
836-1843	1843	E	Round, Flat SPT-3	1.142 x 1.142	0.032	LSR1939-300	.52	.48	.43	.39		

For Round Cables (U-Shape Chassis Slot) • Black • 6/6 Nylon

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Heyco Part No.	Fig.	UL Type Designation	Hole Size	Max. Thickness	Description	Price Each					
836-1839	1839	F	SV, SVT, HPD	.453 x .512	0.062	ST-101A	.23	.18	.15	.12		

## LAY-IN STRAIN RELIEF FOR ROUND, FLAT, OR MULTIPLE CABLES UP TO .600"

MOUSER STOCK NO.	Heyco Part No.	Fig.	UL Type Designation	Panel Dimensions: In.		Description	Price Each					
				Hole Size	Max. Thickness		1	100	500	1000		
836-1266	1266	G	--	.875 x .875	0.100	SR 8R-200	.75	.68	.62	.55		

## STRAIGHT-THRU STRAIN RELIEFS

For Round Cables • Black • 6/6 Nylon

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Heyco Part No.	Fig.	UL Type Designation	Panel Dimensions: In.			Description	Price Each			
				Mounting Hole Dia. (A)	To Prevent Rotation (B)	Max. Thickness		1	100	500	1000
836-1157	1157	H	SV, SVT	0.500	0.450	0.062	SR 5MN-3	.14	.10	.08	.07
836-1150	1150	H	SV, SVT, HPD	.500 x .515	0.450	0.062	SR 5N-4	.13	.09	.07	.06
836-1147	1147	H	SV, SVT, HPD	.500 x .515	0.450	0.100	SR 5P-4	.13	.09	.07	.06
836-1184	1184	H	SJ, SJO, SJT	0.500	0.465	0.090	SR 6W-1	.13	.09	.07	.06
836-1217	1217	H	SJ, SJO, SJT	0.625	0.550	0.062	SR 6N-4	.16	.12	.10	.08
836-1210	1210	H	SJ, SJO, SJT	0.625	0.550	0.125	SR 6P-4	.16	.12	.10	.08
836-1200	1200	H	SJ, SJO, SJT	0.625	0.550	0.062	SR 6N3-4	.16	.12	.10	.08
836-1207	1207	H	SJ, SJO, SJT	0.625	0.550	0.125	SR 6P3-4	.16	.12	.10	.08
836-1214	1214	H	SJ, SJO, SJT	0.625	0.550	0.156	SR 6L-1	.16	.12	.10	.08
836-1240	1240	H	SJ, SJO, SJT	0.875	0.770	0.125	SR 7K-2	.23	.18	.15	.12
836-1244	1244	H	SJ, S, ST	0.750	0.660	0.062	SR 7N-2	.23	.18	.15	.12
836-1237	1237	H	SJT, S, ST	0.750	0.660	0.125	SR 7P-2	.23	.18	.15	.12
836-1247	1247	H	SJT, S, ST	0.875	0.770	0.125	SR 7W-2	.23	.18	.15	.12
836-1250	1250	H	SJT, S, ST	0.875	0.770	0.200	SR 7L-2	.23	.18	.15	.12
836-1497	1497	H	SJT	0.875	0.840	0.125	SR 31-2	.23	.18	.15	.12
836-1254	1254	H	S, ST	0.875	0.840	0.062	SR 8N-2	.23	.18	.15	.12
836-1260	1260	H	S, ST	0.875	0.840	0.125	SR 8P-2	.23	.18	.15	.12
836-1287	1287	H	S, ST, SO	1.093	1.000	0.281	SR 9P-2	.24	.22	.19	.17

For Flat Cables \* Uses Elongated Hole • Black † For flat or round cable

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Heyco Part No.	Fig.	UL Type Designation	Hole Size	Max. Thickness	Description	Price Each				
836-1174	1174	I	HPN, SPT-2	0.562	0.530	0.125	SR 5W-1	.18	.13	.11	.09
836-1484 *	1484	I	SPT-2, SPT-3	0.560	0.700	0.125	SR 30-1	.17	.12	.10	.08
836-1517	1517	I	SPT-3	0.875	0.840	0.125	SR 34-2	.23	.18	.15	.12
836-1497 †	1497	I	SPT-3	0.875	0.840	0.125	SR 31-2	.23	.18	.15	.12

For Flat Cables With Flex-Protecting Internal Radii

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Heyco Part No.	Fig.	UL Type Designation	Hole Size	Max. Thickness	Description	Price Each				
836-1120	1120	I	SPT-1, HSN	0.500	0.465	0.062	SR 4N-4	.11	.07	.06	.05
836-1117	1117	I	SPT-1, HSN	0.500	0.465	0.100	SR 4K-4	.10	.069	.059	.049
836-1127	1127	I	SPT-1, SPT-2, HSN	0.500	0.465	0.156	SR 4L-4	.13	.09	.07	.06
836-1114	1114	I	SPT-1, SPT-2, HSN	0.500	0.460	0.095	SR 4K-1	.10	.069	.059	.049
836-1170	1170	I	SPT-2, SPT-3	0.562	0.530	0.062	SR 5KN-4	.18	.13	.11	.09
836-1167	1167	I	SPT-2, SPT-3	0.562	0.530	0.125	SR 5K-4	.18	.13	.11	.09
836-1160	1160	I	SPT-2	0.625	0.550	0.062	SR 6N4-4	.17	.12	.10	.08
836-1163	1163	I	SPT-2	0.625	0.550	0.125	SR 6P4-4	.17	.12	.10	.08

## RIGHT ANGLE STRAIN RELIEFS

For Flat Cables • Black • 6/6 Nylon • 94V-2

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Heyco Part No.	Fig.	UL Type Designation	Panel Dimensions: In.			Description	Price Each			
				Mounting Hole Dia. (A)	To Prevent Rotation (B)	Max. Thickness		1	100	500	1000
836-1361	1361	J	SPT-2, HSN	0.500	0.450	0.040	SR 14A-1	.22	.15	.12	.10
836-1364	1364	J	SPT-2, HSN	0.500	0.450	0.100	SR 14-1	.22	.15	.12	.10
836-1384	1384	J	SPT-2, SPT-3, HSN	0.562	0.525	0.125	SR 16-1	.23	.15	.14	.13
836-1424	1424	J	SPT-2, SPT-3	0.560	0.730	0.080	SR 20-1	.24	.236	.216	.185
836-1464	1464	J	SPT-3	0.875	0.840	0.125	SR 24-1	.30	.27	.25	.23

For Round Cables

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Heyco Part No.	Fig.	UL Type Designation	Hole Size	Max. Thickness	Description	Price Each				
836-1374	1374	K	SV, SVT, HPD	0.500	0.450	0.100	SR 15-1	.22	.15	.12	.10
836-1320	1320	K	SJ, SJO, SJT	0.625	0.550	0.125	SR 10-2	.23	.15	.14	.13
836-1327	1327	K	SJ, SJO, SJT	0.625	0.550	0.125	SR 11-2	.23	.154	.144	.134
836-1397	1397	K	SJ, S, ST	0.750	0.660	0.125	SR 17-2	.43	.39	.35	.31

