


RAF HARDWARE Hex Standoffs and Handles



RAF ELECTRONIC HARDWARE
a Division of MW Industries, Inc.

RoHS Compliant This product is RoHS compliant.

MALE/FEMALE HEX STANDOFFS (CONT.)



Thread Length Code		
Thread	A	B
2-56	3/16	5/32
4-40	1/4	3/16
6-32	3/8	1/4
8-32	7/16	3/8



"L" (in)	Thread Size	Aluminum Material - Clear Iridite Finish			Stainless Steel Material			Nylon Material		
		MOUSER STOCK NO.	Price Each		MOUSER STOCK NO.	Price Each		MOUSER STOCK NO.	Price Each	
			1	100		1	100		1	100
1/4 Hex										
1/4	4-40	761-4530-440-AL-7	.40	.23	761-4530-440-SS	1.01	.95	761-4530-440-N	.40	.36
5/16	4-40	761-4531-440-AL-7	.47	.36	761-4531-440-SS	1.04	.98	761-4531-440-N	1.40	1.23
3/8	4-40	761-4532-440-AL-7	.35	.27	761-4532-440-SS	1.08	1.02	761-4532-440-N	.45	.39
7/16	4-40	761-4533-440-AL-7	.50	.39	761-4533-440-SS	1.13	1.07	761-4533-440-N	1.50	1.31
1/2	4-40	761-4534-440-AL-7	.50	.39	761-4534-440-SS	1.17	1.10	761-4534-440-N	.47	.41
9/16	4-40	761-4535-440-AL-7	.51	.40	761-4535-440-SS	1.21	1.14	761-4535-440-N	1.58	1.38
5/8	4-40	761-4536-440-AL-7	.53	.41	761-4536-440-SS	1.25	1.19	761-4536-440-N	.48	.42
11/16	4-40	761-4537-440-AL-7	.54	.42	761-4537-440-SS	1.25	1.19	761-4537-440-N	1.67	1.46
3/4	4-40	761-4538-440-AL-7	.55	.43	761-4538-440-SS	1.34	1.27	761-4538-440-N	.49	.42
13/16	4-40	761-4539-440-AL-7	.57	.44	761-4539-440-SS	1.38	1.30	761-4539-440-N	1.76	1.54
7/8	4-40	761-4540-440-AL-7	.58	.45	761-4540-440-SS	1.41	1.34	761-4540-440-N	.49	.43
15/16	4-40	761-4541-440-AL-7	.59	.46	761-4541-440-SS	1.47	1.39	761-4541-440-N	1.85	1.62
1"	4-40	761-4542-440-AL-7	.60	.47	761-4542-440-SS	1.51	1.42	761-4542-440-N	.50	.44
1/4	6-32	761-4530-632-AL-7	.30	.24	761-4530-632-SS	1.18	1.09	761-4530-632-N	.44	.39
5/16	6-32	761-4531-632-AL-7	.48	.37	761-4531-632-SS	1.22	1.12	761-4531-632-N	1.45	1.27
3/8	6-32	761-4532-632-AL-7	.39	.30	761-4532-632-SS	1.27	1.17	761-4532-632-N	.45	.39
7/16	6-32	761-4533-632-AL-7	.50	.39	761-4533-632-SS	1.30	1.20	761-4533-632-N	1.54	1.34
1/2	6-32	761-4534-632-AL-7	.41	.32	761-4534-632-SS	1.35	1.24	761-4534-632-N	.47	.41
9/16	6-32	761-4535-632-AL-7	.53	.41	761-4535-632-SS	1.39	1.28	761-4535-632-N	1.63	1.43
5/8	6-32	761-4536-632-AL-7	.54	.42	761-4536-632-SS	1.47	1.36	761-4536-632-N	.48	.42
11/16	6-32	761-4537-632-AL-7	.55	.43	761-4537-632-SS	1.48	1.37	761-4537-632-N	1.72	1.51
3/4	6-32	761-4538-632-AL-7	.57	.44	761-4538-632-SS	1.52	1.40	761-4538-632-N	.49	.42
13/16	6-32	761-4539-632-AL-7	.58	.45	761-4539-632-SS	1.56	1.44	761-4539-632-N	1.80	1.57
7/8	6-32	761-4540-632-AL-7	.59	.46	761-4540-632-SS	1.61	1.48	761-4540-632-N	.49	.43
15/16	6-32	761-4541-632-AL-7	.60	.47	761-4541-632-SS	1.65	1.52	761-4541-632-N	1.89	1.65
1"	6-32	761-4542-632-AL-7	.61	.47	761-4542-632-SS	1.69	1.56	761-4542-632-N	.50	.44


MALE/MALE HEX STANDOFFS

"L" (in)	Thread Size	Aluminum Material - Clear Iridite Finish			Stainless Steel Material			"L" (in)	Thread Size	Brass Material		
		MOUSER STOCK NO.	Price Each		MOUSER STOCK NO.	Price Each				MOUSER STOCK NO.	Price Each	
			1	100		1	100			1	100	
3/16	4-40	761-4726-AL	2.21	2.03	761-4726-S-12	2.80	2.58	3/16	4-40	761-4726-B-12	3.28	3.02
3/16	4-40	761-4727-AL	2.22	2.04	761-4727-S-12	2.82	2.60	3/16	4-40	761-4727-B-12	3.30	3.04
1/4	6-32	761-4728-AL	2.23	2.05	761-4728-S-12	2.83	2.61	1/4	6-32	761-4728-B-12	3.33	3.06
3/8	8-32	---	---	---	761-4730-S-12	2.96	2.72	3/8	8-32	761-4730-B-12	3.54	3.26

MALE/FEMALE STACKING SPACERS - 3/16"

"L" (in)	Thread Size	MOUSER STOCK NO.	Price Each	
			1	100
Round Profile - Aluminum/Nylon				
.600	4-40	761-4000-440-AL-600	.50	.46
.600	4-40	761-4000-440-NYL-600	1.19	1.10
Hexagonal - Aluminum/Nylon				
.600	4-40	761-4500-440-AL-600	.52	.47
.600	4-40	761-4500-440-NYL-600	2.30	2.11

Thread Length Code		
Thread	A	B
2-56	3/16	5/32
4-40	1/4	3/16
6-32	3/8	1/4
8-32	7/16	3/8



HANDLES

MOUSER STOCK NO.	Thread Size	Dim. A	Outside Diameter	Length	Leg Height	Price Each	
						1	100
Round Handles							
761-8074-440-A-24	4-40	1/4	3/16	2"	1"	2.80	2.60
761-8075-440-A-24	4-40	1/4	3/16	3"	1"	2.97	2.76
761-8076-440-A-24	4-40	1/4	3/16	4"	1"	4.43	4.12
761-8077-440-A-24	4-40	1/4	3/16	5"	1"	4.66	4.34
761-8074-632-A-24	6-32	5/16 - 3/8	3/16	2"	1"	4.04	3.76
761-8075-632-A-24	6-32	5/16 - 3/8	3/16	3"	1"	4.24	3.86
761-8076-632-A-24	6-32	5/16 - 3/8	3/16	4"	1"	4.43	4.12
761-8102-632-A-24	6-32	3/8	1/4	1-1/8	1"	4.11	3.82
761-8103-632-A-24	6-32	3/8	1/4	1-1/4	1"	4.11	3.82
761-8104-632-A-24	6-32	3/8	1/4	1-1/2	1"	4.15	3.86
761-8105-632-A-24	6-32	3/8	1/4	1-3/4	1"	4.20	3.91
761-8106-632-A-24	6-32	3/8	1/4	2"	1"	4.27	3.97
761-8102-832-A-24	8-32	7/16 - 9/16	1/4	1-1/8	1"	4.11	3.82
761-8103-832-A-24	8-32	7/16 - 9/16	1/4	1-1/4	1"	4.11	3.82
761-8104-832-A-24	8-32	7/16 - 9/16	1/4	1-1/2	1"	4.15	3.86
761-8105-832-A-24	8-32	7/16 - 9/16	1/4	1-3/4	1"	4.20	3.91
761-8106-832-A-24	8-32	7/16 - 9/16	1/4	2"	1"	4.27	3.97
Oval Handles							
761-8358-1032-A-24	10-32	5/16 - 5/8	5/8 x 9/32	3"	1-9/32	6.51	6.06
761-8359-1032-A-24	10-32	5/16 - 5/8	5/8 x 9/32	4"	1-9/32	6.85	6.37
761-8360-1032-A-24	10-32	5/16 - 5/8	5/8 x 9/32	4-1/4	1-9/32	6.92	6.44
761-8368-1032-A-24	10-32	5/16 - 5/8	5/8 X 9/32	4"	1-1/2	6.99	6.50
761-8370-1032-A-24	10-32	5/16 - 5/8	5/8 X 9/32	4-1/2	1-1/2	7.24	6.73
761-8371-1032-A-24	10-32	5/16 - 5/8	5/8 X 9/32	4-9/16	1-1/2	7.24	6.73
761-8372-1032-A-24	10-32	5/16 - 5/8	5/8 X 9/32	5"	1-1/2	7.35	6.84
761-8373-1032-A-24	10-32	5/16 - 5/8	5/8 X 9/32	6"	1-1/2	7.73	7.19
761-8376-1032-A-24	10-32	5/16 - 5/8	5/8 X 9/32	3"	1-3/4	6.85	6.37
761-8377-1032-A-24	10-32	5/16 - 5/8	5/8 X 9/32	4"	1-3/4	7.24	6.73

