

RAF HARDWARE Metric Captive Panel and Thumb Screws



This product is RoHS compliant.

STAINLESS STEEL METRIC PLAIN THUMB SCREWS

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	RAF Hardware Part No.	Fig.	Thread Size	A +0.5-0.0	B +0.5-0.5	C +0.5-0.5	D +0.5-0.5	Price Each		
								1	100	500
761-M3465-SS	M3465-SS	A	M3X0.5	8	5	13	8	1.51	1.42	1.23
761-M3466-SS	M3466-SS	A	M3X0.5	8	5	14	9	1.54	1.45	1.25
761-M3467-SS	M3467-SS	A	M3X0.5	8	5	16	11	1.62	1.52	1.32
761-M3468-SS	M3468-SS	A	M3X0.5	8	5	18	13	1.70	1.59	1.38
761-M3469-SS	M3469-SS	A	M3.5X0.6	8	5	13	8	1.53	1.44	1.24
761-M3470-SS	M3470-SS	A	M3.5X0.6	8	5	14	9	1.57	1.47	1.27
761-M3471-SS	M3471-SS	A	M3.5X0.6	8	5	16	11	1.64	1.54	1.34
761-M3473-SS	M3473-SS	A	M4X0.7	10	5	14	9	2.01	1.88	1.63
761-M3474-SS	M3474-SS	A	M4X0.7	10	5	16	11	2.13	2.00	1.73
761-M3476-SS	M3476-SS	A	M4X0.7	10	5	19	14	2.36	2.21	1.92
761-M3477-SS	M3477-SS	A	M4X0.7	10	5	21	16	2.58	2.42	2.10
761-M3478-SS	M3478-SS	A	M5X0.8	11	5	14	9	2.62	2.46	2.13
761-M3479-SS	M3479-SS	A	M5X0.8	11	5	16	11	2.83	2.65	2.30
761-M3481-SS	M3481-SS	A	M5X0.8	11	5	19	14	3.04	2.85	2.47
761-M3482-SS	M3482-SS	A	M5X0.8	11	5	21	16	3.27	3.06	2.66
761-M3483-SS	M3483-SS	A	M6X1	13	6	19	13	3.99	3.74	3.24
761-M3487-SS	M3487-SS	A	M6X1	13	6	25	19	4.70	4.40	3.82

STAINLESS STEEL CAPTIVE SCREWS

Invaluable for equipment panels where mounting hardware is subject to loss, these captive screws and retainers assure easy and secure assembly. In addition to standard models, users choose variations such as slotted, unslotted, or hex heads, washers for oval head styles, plus retainer spring and washer sets.

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	RAF Hardware Part No.	Fig.	Thread Size	H.D. +0.4/-0.4	H.L. +0.4/-0.4	L. +0.4/-0.4	T.L. +0.4/-0.4	S.D. +0.2/-0.2	S.L. +0.3/-0.3	W. +0.2/-0.4	D. +0.3/-0.0	Price Each		
												1	100	500
761-M0100-SS	M0100-SS	B	M3X0.5	8	5	16.5	7	2	9.5	1	1.5	2.20	2.07	1.79
761-M0101-SS	M0101-SS	B	M3X0.5	8	5	18	7	2	11	1	1.5	2.25	2.11	1.83
761-M0102-SS	M0102-SS	B	M3X0.5	8	5	20	7	2	13	1	1.5	2.40	2.25	1.95
761-M0112-SS	M0112-SS	B	M3.5X0.6	9.5	5	20	7	2.5	13	1.2	1.5	2.84	2.67	2.31

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	RAF Hardware Part No.	Fig.	Thread Size	H.D. +0.5/-0.2	H.L. +0.3/-0.3	L. +0.5/-0.5	T.L. +0.0/-0.4	S.D. +0.15/-0.15	S.L. +0.3/-0.3	P.D. +0.0/-0.3	P.L. +0.4/-0.4	W. +0.2/-0.0	D. +0.3/-0.0	Price Each		
														1	100	500
761-M0170-SS	M0170-SS	C	M3X0.5	6.5	6.5	9.5	3.2	2	4.3	2	2	1.2	2	1.44	1.35	1.17
761-M0171-SS	M0171-SS	C	M3X0.5	6.5	6.5	11	3.2	2	5.8	2	2	1.2	2	1.46	1.37	1.19
761-M0172-SS	M0172-SS	C	M3X0.5	6.5	6.5	13	3.2	2	7.8	2	2	1.2	2	1.51	1.42	1.23
761-M0174-SS	M0174-SS	C	M3X0.5	6.5	6.5	16	3.2	2	10.8	2	2	1.2	2	1.77	1.66	1.44
761-M0181-SS	M0181-SS	C	M3X0.5	8	8	9.5	3.2	2	4.3	2	2	1.2	2	1.72	1.61	1.40
761-M0182-SS	M0182-SS	C	M3X0.5	8	8	11	3.2	2	5.8	2	2	1.2	2	1.76	1.65	1.43
761-M0185-SS	M0185-SS	C	M3X0.5	8	8	16	3.2	2	10.8	2	2	1.2	2	2.14	2.01	1.74
761-M0193-SS	M0193-SS	C	M3.5X0.6	8	8	13	5.5	2.5	5	2.5	2.5	1.2	2	1.94	1.82	1.57
761-M0195-SS	M0195-SS	C	M3.5X0.6	8	8	16	5.5	2.5	8	2.5	2.5	1.2	2	2.14	2.01	1.74

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	RAF Hardware Part No.	Fig.	Thread Size	H.D. +0.2/-0.2	H.L. +0.0/-0.4	L. +0.5/-0.5	T.L. +0.3/-0.3	S.D. +0.15/-0.15	S.L. +0.3/-0.3	W.L. +0.0/-0.3	W. +0.0/-0.3	D. +0.0/-0.4	Price Each		
													1	100	500
761-M0274-SS	M0274-SS	D	M2.5X0.45	4	2.5	6.5	4	1.8	2.5	1.8	0.9	1.1	1.12	1.05	.907
761-M0275-SS	M0275-SS	D	M2.5X0.45	4	2.5	8	4	1.8	4	1.8	0.9	1.1	1.14	1.07	.926
761-M0276-SS	M0276-SS	D	M2.5X0.45	4	2.5	9.5	4	1.8	5.5	1.8	0.9	1.1	1.25	1.17	1.02
761-M0277-SS	M0277-SS	D	M2.5X0.45	4	2.5	11	4	1.8	7	1.8	0.9	1.1	1.27	1.19	1.03
761-M0278-SS	M0278-SS	D	M2.5X0.45	4	2.5	13	4	1.8	9	1.8	0.9	1.1	1.30	1.22	1.05
761-M0279-SS	M0279-SS	D	M2.5X0.45	4	2.5	14.5	4	1.8	10.5	1.8	0.9	1.1	1.32	1.24	1.07
761-M0280-SS	M0280-SS	D	M2.5X0.45	4	2.5	16	4	1.8	12	1.8	0.9	1.1	1.33	1.25	1.08
761-M0281-SS	M0281-SS	D	M2.5X0.45	4	2.5	17.5	4	1.8	13.5	1.8	0.9	1.1	1.36	1.27	1.10
761-M0282-SS	M0282-SS	D	M2.5X0.45	4	2.5	19	4	1.8	15	1.8	0.9	1.1	1.67	1.57	1.36
761-M0283-SS	M0283-SS	D	M3X0.5	4.3	2.7	6.5	4.8	2	1.7	2	1	1.2	1.12	1.05	.907
761-M0284-SS	M0284-SS	D	M3X0.5	4.3	2.7	8	4.8	2	3.2	2	1	1.2	1.14	1.07	.926
761-M0285-SS	M0285-SS	D	M3X0.5	4.3	2.7	9.5	4.8	2	4.7	2	1	1.2	1.25	1.17	1.02
761-M0286-SS	M0286-SS	D	M3X0.5	4.3	2.7	11	4.8	2	6.2	2	1	1.2	1.27	1.19	1.03
761-M0288-SS	M0288-SS	D	M3X0.5	4.3	2.7	14.5	4.8	2	9.7	2	1	1.2	1.32	1.24	1.07
761-M0289-SS	M0289-SS	D	M3X0.5	4.3	2.7	16	4.8	2	11.2	2	1	1.2	1.33	1.25	1.08

