


RAF HARDWARE Metric Standoffs and Spacers



RoHS Compliant This product is RoHS compliant.

METRIC HEX FEMALE STANDOFFS 4.5MM



"L" (mm)	Aluminum Material			Stainless Steel Material			Nylon Material		
	MOUSER STOCK NO.	Price Each		MOUSER STOCK NO.	Price Each		MOUSER STOCK NO.	Price Each	
		1	100		1	100		1	100
M2.5x0.45 Thread									
3	761-M1250-2545-AL	.36	.31	761-M1250-2545-SS	.79	.68	761-M1250-2545-N	.61	.52
4	761-M1251-2545-AL	.36	.31	761-M1251-2545-SS	.82	.70	761-M1251-2545-N	.63	.54
5	761-M1252-2545-AL	.37	.32	761-M1252-2545-SS	.84	.72	761-M1252-2545-N	.65	.56
6	761-M1253-2545-AL	.37	.32	761-M1253-2545-SS	.87	.75	761-M1253-2545-N	.69	.59
7	761-M1254-2545-AL	.42	.36	761-M1254-2545-SS	.93	.80	761-M1254-2545-N	.71	.61
8	761-M1255-2545-AL	.42	.36	761-M1255-2545-SS	.96	.82	761-M1255-2545-N	.73	.62
9	761-M1256-2545-AL	.43	.37	761-M1256-2545-SS	.99	.85	761-M1256-2545-N	.76	.65
10	761-M1257-2545-AL	.45	.38	761-M1257-2545-SS	1.02	.87	761-M1257-2545-N	.79	.68
11	761-M1258-2545-AL	.45	.39	761-M1258-2545-SS	1.04	.89	761-M1258-2545-N	.81	.69
12	761-M1259-2545-AL	.46	.39	761-M1259-2545-SS	1.06	.91	761-M1259-2545-N	.84	.72
13	761-M1260-2545-AL	.48	.41	761-M1260-2545-SS	1.09	.94	761-M1260-2545-N	.85	.73
M3x0.5 Thread									
3	761-M1250-3005-AL	.36	.31	761-M1250-3005-SS	.79	.68	761-M1250-3005-N	.61	.52
4	761-M1251-3005-AL	.36	.31	761-M1251-3005-SS	.82	.70	761-M1251-3005-N	.63	.54
5	761-M1252-3005-AL	.37	.32	761-M1252-3005-SS	.84	.72	761-M1252-3005-N	.65	.56
6	761-M1253-3005-AL	.37	.32	761-M1253-3005-SS	.87	.75	761-M1253-3005-N	.69	.59
7	761-M1254-3005-AL	.42	.36	----	---	---	761-M1254-3005-N	.71	.61
8	761-M1255-3005-AL	.42	.36	761-M1255-3005-SS	.96	.82	761-M1255-3005-N	.73	.62
9	761-M1256-3005-AL	.43	.37	761-M1256-3005-SS	.99	.85	761-M1256-3005-N	.76	.65
10	761-M1257-3005-AL	.45	.38	761-M1257-3005-SS	1.02	.87	761-M1257-3005-N	.79	.68
11	761-M1258-3005-AL	.45	.39	761-M1258-3005-SS	1.04	.89	761-M1258-3005-N	.81	.69
12	761-M1259-3005-AL	.46	.39	761-M1259-3005-SS	1.06	.91	761-M1259-3005-N	.84	.72
13	761-M1260-3005-AL	.48	.45	761-M1260-3005-SS	1.03	.94	761-M1260-3005-N	.85	.73

METRIC HEX FEMALE STANDOFFS 6MM

"L" (mm)	Aluminum Material			Stainless Steel Material			Nylon Material		
	MOUSER STOCK NO.	Price Each		MOUSER STOCK NO.	Price Each		MOUSER STOCK NO.	Price Each	
		1	100		1	100		1	100
M3x0.5 Thread									
3	761-M1300-3005-AL	.37	.32	761-M1300-3005-SS	.88	.75	761-M1300-3005-N	.67	.57
4	761-M1301-3005-AL	.38	.33	761-M1301-3005-SS	.91	.78	761-M1301-3005-N	.70	.60
5	----	---	---	761-M1302-3005-SS	.95	.82	761-M1302-3005-N	.74	.63
6	761-M1303-3005-AL	.42	.36	761-M1303-3005-SS	.99	.85	761-M1303-3005-N	.78	.67
7	761-M1304-3005-AL	.43	.37	761-M1304-3005-SS	1.03	.88	761-M1304-3005-N	.81	.69
8	761-M1305-3005-AL	.43	.37	761-M1305-3005-SS	1.06	.91	761-M1305-3005-N	.84	.72
9	761-M1306-3005-AL	.45	.38	761-M1306-3005-SS	1.11	.95	761-M1306-3005-N	.88	.76
10	761-M1307-3005-AL	.46	.39	761-M1307-3005-SS	1.12	.96	761-M1307-3005-N	.92	.79
11	761-M1308-3005-AL	.47	.40	761-M1308-3005-SS	1.13	.97	761-M1308-3005-N	.87	.81
12	761-M1309-3005-AL	.52	.41	761-M1309-3005-SS	1.15	.99	761-M1309-3005-N	.99	.85
13	761-M1310-3005-AL	.52	.44	----	---	---	761-M1310-3005-N	1.03	.88
M4x0.7 Thread									
3	761-M1300-4007-AL	.37	.32	761-M1300-4007-SS	.88	.75	761-M1300-4007-N	.67	.57
4	761-M1301-4007-AL	.38	.33	761-M1301-4007-SS	.91	.78	761-M1301-4007-N	.70	.60
5	761-M1302-4007-AL	.40	.35	761-M1302-4007-SS	.95	.82	761-M1302-4007-N	.74	.63
6	761-M1303-4007-AL	.42	.36	761-M1303-4007-SS	.99	.85	761-M1303-4007-N	.67	.62
7	----	---	---	761-M1304-4007-SS	1.03	.88	761-M1304-4007-N	.69	.65
8	761-M1305-4007-AL	.43	.37	761-M1305-4007-SS	1.06	.91	761-M1305-4007-N	.72	.67
9	761-M1306-4007-AL	.45	.38	761-M1306-4007-SS	1.11	.95	761-M1306-4007-N	.76	.71
10	761-M1307-4007-AL	.46	.39	761-M1307-4007-SS	1.12	.96	761-M1307-4007-N	.79	.74
11	761-M1308-4007-AL	.47	.40	761-M1308-4007-SS	1.13	.97	761-M1308-4007-N	.81	.76
12	761-M1309-4007-AL	.48	.41	----	---	---	----	---	---
13	761-M1310-4007-AL	.52	.44	----	---	---	761-M1310-4007-N	.88	.82

METRIC FEMALE ROUND SPACERS 4.5MM

"L" (mm)	Aluminum Material			Stainless Steel Material			Nylon Material		
	MOUSER STOCK NO.	Price Each		MOUSER STOCK NO.	Price Each		MOUSER STOCK NO.	Price Each	
		1	100		1	100		1	100
M2.5 Thread									
1	761-M0500-25-AL	.36	.31	----	---	---	761-M0500-25-N	.47	.42
2	761-M0501-25-AL	.36	.31	761-M0501-25-SS	.55	.47	761-M0501-25-N	.48	.42
3	761-M0502-25-AL	.37	.32	761-M0502-25-SS	.57	.49	761-M0502-25-N	.49	.43
4	761-M0503-25-AL	.37	.32	761-M0503-25-SS	.58	.50	761-M0503-25-N	.49	.44
5	761-M0504-25-AL	.37	.33	761-M0504-25-SS	.60	.51	761-M0504-25-N	.50	.44
6	761-M0505-25-AL	.40	.35	761-M0505-25-SS	.61	.53	761-M0505-25-N	.51	.45
7	761-M0506-25-AL	.40	.35	----	---	---	761-M0506-25-N	.52	.46
8	761-M0507-25-AL	.41	.36	761-M0507-25-SS	.65	.56	761-M0507-25-N	.53	.47
9	761-M0508-25-AL	.41	.36	----	---	---	761-M0508-25-N	.54	.48
10	761-M0509-25-AL	.42	.36	761-M0509-25-SS	.74	.63	----	---	---
11	761-M0510-25-AL	.42	.37	----	---	---	----	---	---
12	761-M0511-25-AL	.42	.37	----	---	---	761-M0511-25-N	.60	.54
13	761-M0512-25-AL	.45	.40	761-M0512-25-SS	.77	.66	----	---	---
M3 Thread									
1	761-M0500-3-AL	.36	.31	761-M0500-3-SS	.55	.47	761-M0500-3-N	.36	.31
2	761-M0501-3-AL	.36	.31	761-M0501-3-SS	.55	.47	761-M0501-3-N	.37	.32
3	761-M0502-3-AL	.37	.32	----	---	---	761-M0502-3-N	.38	.32
4	761-M0503-3-AL	.37	.32	761-M0503-3-SS	.58	.50	----	---	---
5	761-M0504-3-AL	.37	.33	----	---	---	761-M0504-3-N	.39	.33
6	761-M0505-3-AL	.40	.35	761-M0505-3-SS	.61	.53	761-M0505-3-N	.40	.34
8	761-M0507-3-AL	.41	.36	----	---	---	761-M0507-3-N	.41	.35
10	761-M0509-3-AL	.42	.36	761-M0509-3-SS	.74	.63	----	---	---
11	761-M0510-3-AL	.42	.37	----	---	---	761-M0510-3-N	.43	.37
12	761-M0511-3-AL	.42	.37	761-M0511-3-SS	.76	.65	761-M0511-3-N	.47	.40
13	761-M0512-3-AL	.45	.40	761-M0512-3-SS	.77	.66	----	---	---