

# HAMMOND Consoles and Plastic Enclosures



## SLOPING STYRENE CONSOLES

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Hammond Part No.	Flg.	Dimensions: in.				Price Each			
			L	W	H	D	1	5	10	25
546-1599ESTSGY	1599ESTSGY	A	3.35	6.70	1.33	.72	11.67	10.41	9.72	8.97
546-1599HSTSGY	1599HSTSGY	A	4.33	8.66	1.73	.75	15.16	12.67	11.68	10.85
546-1599KSTSGY	1599KSTSGY	A	5.51	8.66	1.60	.67	13.97	12.50	11.65	10.93
546-1599KSTLGY	1599KSTLGY	A	8.66	5.51	1.60	.71	13.00	10.84	9.99	9.30
546-1599KSTLGYBAT	1599KSTLGYBAT	A	8.66	5.51	1.60	.71	17.50	14.61	13.48	12.51

## PLASTIC DESKTOP CONSOLES

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Hammond Part No.	Flg.	Dimensions: in.				Color	Price Each			
			L	W	H	A		1	5	10	25
546-1595C-GY	1595C-GY	B	6.30	3.80	1.54	2.30	Gray	12.76	11.49	10.62	9.13
546-1595C-BK	1595C-BK	B	6.30	3.80	1.54	2.30	Black	12.76	11.49	10.62	10.29
546-1595EGY	1595E-GY	B	8.50	5.10	1.85	2.90	Gray	15.76	14.09	13.14	12.14
546-1595E-BK	1595E-BK	B	8.50	5.10	1.85	2.90	Black	15.78	14.09	13.14	12.73

## ABS INSTRUMENT ENCLOSURES

For quantities greater than listed, call for quote.

- Two piece "tongue & groove" construction
- UL flammability rating of 94V-0
- Front/rear panels: .064" thick brushed aluminum
- Integral horizontal PC card mounts on Eurocard centers
- Comes with M3 x .5 x 10mm Phillips machine screws that fasten into tapped integral brass bushings
- Two sets of vertical .062" PC board guides provided front /rear

MOUSER STOCK NO.	Hammond Part No.	Flg.	Color	Dimensions: in.			Price Each			
				L	W	H	1	5	10	25
546-1598B-BK	1598B-BK	C	Black	5.28	5.31	1.96	13.54	12.19	11.28	10.92
546-1598A-BK	1598A-BK	C	Black	6.18	3.70	1.42	12.34	10.82	10.28	9.49
546-1598A-GY	1598AGY	C	Gray	6.18	3.70	1.42	12.34	11.02	10.28	9.49
546-1598BB-BK	1598BB-BK	C	Black	7.05	6.06	1.42	13.74	12.05	11.45	10.56
546-1598BBGY	1598BB-GY	C	Gray	7.05	6.06	1.42	13.67	12.27	11.45	10.56
546-1598C-BK	1598C-BK	C	Black	7.09	6.10	2.04	16.94	15.13	14.12	13.66
546-1598C-GY	1598C-GY	C	Gray	7.09	6.10	2.04	16.94	15.13	14.12	13.02
546-1598D-BK	1598D-BK	C	Black	7.09	8.11	2.52	20.68	18.62	17.23	15.93
546-1598DGY	1598D-GY	C	Gray	7.09	8.11	2.52	20.68	18.47	17.23	15.90
546-1598E-BK	1598E-BK	C	Black	6.30	6.30	3.38	20.34	18.31	16.89	15.67
546-1598FGY	1598F-GY	C	Gray	9.84	6.30	1.58	21.59	18.12	16.72	15.52
546-1598G-BK	1598G-BK	C	Black	9.84	6.30	3.00	25.46	22.73	21.21	19.59
546-1598H-BK	1598H-BK	C	Black	11.02	7.87	1.58	26.72	23.85	22.26	20.55
546-1598HGY	1598H-GY	C	Gray	11.02	7.87	1.58	26.57	23.85	22.26	20.55
546-1598J-BK	1598J-BK	C	Black	11.02	7.87	3.00	33.12	29.05	27.60	25.48
546-1598JGY	1598J-GY	C	Gray	11.02	7.87	3.00	33.12	29.05	27.60	25.48

## GENERAL PURPOSE ABS PLASTIC

For quantities greater than listed, call for quote.

- Molded in PC card standoffs and vertical card guides
- Designed to meet IP54
- Positive fit, "tongue & groove" construction requires only 2 mounting screws
- Available in Gray Styrene Plastic
- Easy access to interior via shell type construction

MOUSER STOCK NO.	Hammond Part No.	Flg.	Dimensions: in.			Price Each				
			L	W	H	1	5	10	25	
<b>With Black ABS Plastic End Panels</b>										
546-1598ASGYPBK	1598ASGYPBK	C	6.18	3.70	1.42	8.55	7.68	7.16	6.72	
546-1598BSGYPBK	1598BSGYPBK	C	5.28	5.31	1.96	9.65	8.65	7.97	7.44	
546-1598BBSGYPBK	1598BBSGYPBK	C	7.05	6.06	1.42	10.89	9.79	9.13	8.84	
546-1598CSGYPBK	1598CSGYPBK	C	7.09	6.10	2.04	11.31	10.14	9.34	8.72	
546-1598DSGYPBK	1598DSGYPBK	C	7.09	8.11	2.52	13.53	12.12	11.17	10.43	
546-1598ESGYPBK	1598ESGYPBK	C	6.30	6.30	3.38	13.51	11.84	11.25	10.38	
546-1598FSGYPBK	1598FSGYPBK	C	9.84	6.30	1.58	13.10	11.56	10.98	10.14	
546-1598GSGYPBK	1598GSGYPBK	C	9.84	6.30	3.00	15.47	13.84	12.76	11.91	
546-1598HSGYPBK	1598HSGYPBK	C	11.02	7.87	1.58	14.79	13.57	12.88	11.90	
546-1598JSGYPBK	1598JSGYPBK	C	11.02	7.87	3.00	17.39	14.60	13.43	12.52	
<b>With Aluminum End Panels</b>										
546-1598BSGY	1598BSGY	C	5.28	5.31	1.96	10.14	8.90	8.45	7.80	
546-1598ASGY	1598ASGY	C	6.18	3.70	1.42	9.00	8.09	7.54	6.96	
546-1598ESGY	1598ESGY	C	6.30	6.30	3.38	14.18	12.67	11.81	10.91	
546-1598BBSGY	1598BBSGY	C	7.05	6.06	1.42	10.96	9.61	9.13	8.43	
546-1598CSGY	1598CSGY	C	7.09	6.10	2.04	11.90	10.44	9.91	9.15	
546-1598DS-GY	1598DS-GY	C	7.09	8.11	2.52	14.26	12.51	11.88	10.97	
546-1598GSGY	1598GSGY	C	9.84	6.30	3.00	16.19	14.28	13.57	12.52	
546-1598HSGY	1598HSGY	C	11.02	7.87	1.58	16.17	13.57	12.51	11.61	
546-1598JSGY	1598JSGY	C	11.02	7.87	3.00	18.94	16.61	15.78	14.57	

### Optional Accessories (For 1598 Series Cases)

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Hammond Part No.	Description	Price Each		
			1	5	10
546-1598ATS100	1598ATS100	#6 x 1/4" self-tapping screws, 100 pack	9.43	8.40	7.84
<b>Optional Tilt Handle (Instructions and Mounting Hardware Included)</b>					
546-1598TH1	1598TH1	1598C-BK, E-BK, F-BK, G-BK	14.14	12.40	11.78
546-1598TH2	1598TH2	1598D-BK, H-BK, J-BK	14.14	12.40	11.78

## MG Chemicals SUPER SHIELD CONDUCTIVE COATING

- Flammability rating: UL 94V-0

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	MG Chemicals Part No.	Size	Price Each
590-841-340G	841-340G	Aerosol 340g (12oz.)	31.95

**A**

RoHS Compliant

- Includes removable rear panels for easy modification
- Molded in PCB card standoffs and vertical card guides
- 2 piece, lap joint construction provides protection against dust accumulation and splashing water
- Recessed top panel for membrane keypad

**B**

RoHS Compliant

- Four M3 x .5" x 8mm Phillips pan head screws threaded into integral brass bushings hold recessed panel
- Internal slot: accepts 0.062" PC cards
- 4 self adhesive rubber feet
- 20" dia. stand-off bosses in base
- ABS plastic case, UL 94V-0
- 0.04" thick painted aluminum panel

**C**

RoHS Compliant

- Molded in PC card standoffs and vertical card guides
- Designed to meet IP54
- Positive fit, "tongue & groove" construction requires only 2 mounting screws

Hammond Plastic Boxes