

AULT AC Adapters



This product is RoHS compliant.



AC INTERCHANGEABLE BLADE KIT

For use with medical and commercial wall plug interchangeable For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Description	Price Each		
		1	10	25
831-KT1027K	Includes Europe, United Kingdom, Australian	4.63	4.28	4.13

CENB1010 SERIES, 10-12W SINGLE OUTPUT

- 100-240 VAC Universal
- Meets EISA2007, CEC Efficiency Level V, EU (EC) No 278/2009 Phase II
- 5V to 48V Single Output Models, up to 12W
- No load Power Consumption <0.3W
- Limited Power Source



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each			
					1	10	25	
Wall-Plug Models								
675-CENB1010A0503B01	CENB1010A0503B01	5V	2.00A	10.0W	15.23	14.88	14.53	
675-CENB1010A0903B01	CENB1010A0903B01	9V	1.10A	10.0W	15.23	14.88	14.53	
675-CENB1010A1203B01	CENB1010A1203B01	12V	1.00A	12.0W	15.23	14.88	14.53	
675-CENB1010A2403B01	CENB1010A2403B01	24V	0.50A	12.0W	15.23	14.88	14.53	
Desktop Modules (AC input cord not included)								
675-CENB1010A0503F01	CENB1010A0503F01	5V	2.00A	10.0W	14.80	14.46	14.12	
675-CENB1010A0903F01	CENB1010A0903F01	9V	1.10A	10.0W	14.80	14.46	14.12	
675-CENB1010A1203F01	CENB1010A1203F01	12V	1.00A	12.0W	14.80	14.46	14.12	
675-CENB1010A2403F01	CENB1010A2403F01	24V	0.50A	12.0W	14.80	14.46	14.12	
AC Input Cord								
173-63101-E	7" 6" AC input cord, 3-wire input, 18AWG, Black					6.69	6.09	-

CENB1020 SERIES, 15-20W SINGLE OUTPUT

- 100-240 VAC Universal Input Range
- Meets EISA2007, CEC Efficiency Level V, EU (EC) No 278/2009 Phase II
- 5V to 48V Single Output Models, up to 20W
- Modified and Custom Designs Available
- Regulated Output with Low Ripple
- No load Power Consumption <0.3W
- Limited Power Source



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each			
					1	10	25	
Wall-Plug Models								
675-CENB1020A0503B01	CENB1020A0503B01	5V	3.00A	15.0W	17.22	16.82	16.42	
675-CENB1020A0903B01	CENB1020A0903B01	9V	2.00A	18.0W	17.22	16.82	16.42	
675-CENB1020A1203B01	CENB1020A1203B01	12V	1.50A	18.0W	17.22	16.82	16.42	
675-CENB1020A2403B01	CENB1020A2403B01	24V	0.75A	18.0W	17.22	16.82	16.42	
675-CENB1020A4803B01	CENB1020A4803B01	48V	0.40A	19.20W	17.22	16.82	16.42	
Desktop Modules (AC input cord not included)								
675-CENB1020A0503F01	CENB1020A0503F01	5V	3.00A	15.0W	15.22	14.87	14.52	
675-CENB1020A0903F01	CENB1020A0903F01	9V	2.00A	18.0W	15.22	14.87	14.52	
675-CENB1020A1203F01	CENB1020A1203F01	12V	1.50A	18.0W	15.22	14.87	14.52	
675-CENB1020A2403F01	CENB1020A2403F01	24V	0.75A	18.0W	15.22	14.87	14.52	
675-CENB1020A4803F01	CENB1020A4803F01	48V	0.40A	19.20W	15.22	14.87	14.52	
AC Input Cord								
173-63101-E	7" 6" AC input cord, 3-wire input, 18AWG, Black					6.69	6.09	-

CENB1030 SERIES, 20-32W SINGLE OUTPUT

- 100-240 VAC Universal Input
- Meets EISA2007, CEC Efficiency Level V, EU (EC) No 278/2009 Phase II
- 5V to 48V Single Output Models, up to 32W
- Regulated Output with Low Ripple
- No load Power Consumption <0.3W
- Limited Power Source



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each			
					1	10	25	
Wall-Plug Models								
675-CENB1030A1203C01	CENB1030A1203C01	12V	2.50A	30.0W	17.06	15.65	15.59	
675-CENB1030A2403C01	CENB1030A2403C01	24V	1.33A	31.9W	17.06	15.65	15.59	
Wall-Plug Models (Fixed AC Plug N. America/Japan)								
675-CENB1030A0503B01	CENB1030A0503B01	5V	4.00A	20.0W	20.20	19.74	19.27	
675-CENB1030A0903B01	CENB1030A0903B01	9V	3.00A	27.0W	20.20	19.74	19.27	
675-CENB1030A1203B01	CENB1030A1203B01	12V	2.50A	30.0W	20.20	19.74	19.27	
675-CENB1030A2403B01	CENB1030A2403B01	24V	1.33A	31.9W	20.20	19.74	19.27	
675-CENB1030A4803B01	CENB1030A4803B01	48V	0.67A	32.1W	20.20	19.74	19.27	
Desktop Modules (AC input cord not included)								
675-CENB1030A0503F01	CENB1030A0503F01	5V	4.00A	20.0W	20.20	19.74	19.27	
675-CENB1030A0903F01	CENB1030A0903F01	9V	3.00A	27.0W	20.20	19.74	19.27	
675-CENB1030A1203F01	CENB1030A1203F01	12V	2.50A	30.0W	20.20	19.74	19.27	
675-CENB1030A2403F01	CENB1030A2403F01	24V	1.33A	31.9W	20.20	19.74	19.27	
675-CENB1030A4803F01	CENB1030A4803F01	48V	0.67A	32.1W	20.20	19.74	19.27	
AC Input Cord								
173-63101-E	7" 6" AC input cord, 3-wire input, 18AWG, Black					6.69	6.09	-

CENB1040 SERIES, 25-40W SINGLE OUTPUT

- 100-240 VAC Universal
- Meets EISA2007, CEC Efficiency Level V, EU (EC) No 278/2009 Phase II
- 5V to 48V Single Output Models, up to 40W
- No load Power Consumption <0.3W
- Limited Power Source
- Impact-Resistance Polycarbonate Enclosure
- Regulated Output with Low Ripple



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each			
					1	10	25	
Desktop Modules (AC input cord not included)								
675-CENB1040A0503F01	CENB1040A0503F01	5V	5.00A	25.0W	22.36	21.84	21.33	
675-CENB1040A0903F01	CENB1040A0903F01	9V	4.00A	36.0W	22.36	21.84	21.33	
675-CENB1040A1203F01	CENB1040A1203F01	12V	3.40A	40.8W	22.36	21.84	21.33	
675-CENB1040A2403F01	CENB1040A2403F01	24V	1.70A	40.8W	22.36	21.84	21.33	
675-CENB1040A4803F01	CENB1040A4803F01	48V	0.83A	39.8W	22.36	21.84	21.33	
AC Input Cord								
173-63101-E	7" 6" AC input cord, 3-wire input, 18AWG, Black					6.69	6.09	-

CENB1050 SERIES, 30-53W SINGLE OUTPUT

- 100-240 VAC Universal
- Meets EISA2007, CEC Efficiency Level V, EU (EC) No 278/2009 Phase II
- Desktop and Wall Plug Styles
- 5V to 48V Single Output Models, up to 53W
- No load Power Consumption <0.3W
- Limited Power Source



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each			
					1	10	25	
Desktop Modules (AC input cord not included)								
675-CENB1050A0503F01	CENB1050A0503F01	5V	6A	30W	26.39	25.78	25.17	
675-CENB1050A0903F01	CENB1050A0903F01	9V	5A	45W	26.39	25.78	25.17	
675-CENB1050A1203F01	CENB1050A1203F01	12V	4.2A	50.4W	26.39	25.78	25.17	
675-CENB1050A2403F01	CENB1050A2403F01	24V	2.1A	50.4W	26.39	25.78	25.17	
675-CENB1050A4803F01	CENB1050A4803F01	48V	1.1A	52.8W	26.39	25.78	25.17	
AC Input Cord								
173-63101-E	7" 6" AC input cord, 3-wire input, 18AWG, Black					6.69	6.09	-

CENB1060 SERIES, 35-64W SINGLE OUTPUT

- 100-240 VAC Universal
- Meets EISA2007, CEC Efficiency Level V, EU (EC) No 278/2009 Phase II
- 5V to 48V Single Output Models, up to 64W
- No load Power Consumption <0.5W
- Modified and Custom Designs Available
- 2.5 Barrel Type Connector



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each			
					1	10	25	
Desktop Modules (AC input cord not included)								
675-CENB1060A0551F01	CENB1060A0551F01	5V	7A	35W	29.25	28.57	27.90	
675-CENB1060A0903F01	CENB1060A0903F01	9V	6A	54W	29.25	28.57	27.90	
675-CENB1060A1203F01	CENB1060A1203F01	12V	5A	60W	29.25	28.57	27.90	
675-CENB1060A2403F01	CENB1060A2403F01	24V	2.7A	64.8W	29.25	28.57	27.90	
675-CENB1060A4803F01	CENB1060A4803F01	48V	1.3A	62.4W	29.25	28.57	27.90	
AC Input Cord								
173-63101-E	7" 6" AC input cord, 3-wire input, 18AWG, Black					6.69	6.09	-

CENB1080 & CENB1090 SERIES, 78-90W SINGLE OUTPUT

- 100-240 VAC Universal
- Meets EISA2007, CEC Efficiency Level V, EU (EC) No 278/2009 Phase II
- 12V to 48V Single Output Models, up to 90W
- No load Power Consumption <0.5W
- Limited Power Source
- Modified and Custom Designs Available
- 2.5 Barrel Type Connector



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each			
					1	10	25	
Desktop Modules (AC input cord not included)								
675-CENB1080A1251F01	CENB1080A1251F01	12V	6.5A	78W	50.21	49.05	47.89	
675-CENB1080A2403F01	CENB1080A2403F01	24V	3.25A	78W	50.21	49.05	47.89	
675-CENB1080A4803F01	CENB1080A4803F01	48V	1.65A	79.2W	50.21	49.05	47.89	
675-CENB1090A1251F01	CENB1090A1251F01	12V	7A	84W	61.18	59.77	58.36	
675-CENB1090A2403F01	CENB1090A2403F01	24V	3.75A	90W	61.18	59.77	58.36	
675-CENB1090A4803F01	CENB1090A4803F01	48V	1.9A	90W	61.18	59.77	58.36	
AC Input Cord								
173-63101-E	7" 6" AC input cord, 3-wire input, 18AWG, Black					6.69	6.09	-

CENB1100 SERIES, 90-101W SINGLE OUTPUT

- 100-240 VAC Universal
- Meets EISA2007, CEC Efficiency Level V, EU (EC) No 278/2009 Phase II
- Desktop Styles
- 12V to 48V Single Output Models, up to 120W
- No load Power Consumption <0.5W
- IPX Compliant
- 2.5 Barrel Type Connector



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each			
					1	10	25	
Desktop Modules (AC Input Cord Not Included)								
675-CENB1100A1251F01	CENB1100A1251F01	12V	7.50A	90.0W	66.67	65.13	63.59	
675-CENB1100A2403F01	CENB1100A2403F01	24V	4.20A	101.0W	66.67	65.13	63.59	
675-CENB1100A4803F01	CENB1100A4803F01	48V	2.10A	101.0W	66.67	65.13	63.59	
AC Input Cord								
173-63101-E	7" 6" AC input cord, 3-wire input, 18AWG, Black					6.69	6.09	-

CENB1120 SERIES, 120W SINGLE OUTPUT

- 100-240VAC Universal Input
- IPX1 Compliant
- Complies with EMI/RFI Regulations
- Impact Resistant, Non-Vented Polycarbonate Enclosure
- 3 year warranty
- Meets ENERGY STAR Criteria level IV and EISA Requirements
- 2.5 Barrel Type Connector



For quantities greater than listed, call for quote.

|--|