

AULT Medical AC Adapters

RoHS Compliant This product is RoHS compliant.



NEW FROM AULT

MENB1010 SERIES, 10-12 WATTS, SINGLE OUTPUT

- Features:**
- 100-240VAC Universal Input
 - 5V to 24V Single Output Models, up to 12W
 - Impact-Resistant Polycarbonate Enclosure
 - Limited Power Source
 - Meets EISA2007, CEC Efficiency Level V, EU (EC) No 278/2009 Phase II
 - Desktop & Wall Plug Styles
 - No load power consumption <0.3W
 - Regulated Output with Ripple
 - Certified to UL/EN/IEC60601-1
 - Desktop models AC Input: N01 = IEC320-C8 F01 = IEC320-C14



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each		
					1	10	25
Wall-Plug Models							
675-MENB1010A0503B01	MENB1010A0503B01	5V	2A	10W	15.95	13.96	13.69
675-MENB1010A0903B01	MENB1010A0903B01	9V	1.1A	10W	15.95	13.96	13.69
675-MENB1010A1203B01	MENB1010A1203B01	12V	1A	12W	15.95	13.96	13.69
675-MENB1010A2403B01	MENB1010A2403B01	24V	.5A	12W	15.95	13.96	13.69

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each		
					1	10	25
Desktop Models (AC Input cord not included)							
675-MENB1010A0503F01	MENB1010A0503F01	5V	2A	10W	13.36	11.70	11.47
675-MENB1010A0903F01	MENB1010A0903F01	9V	1.1A	10W	13.36	11.70	11.47
675-MENB1010A1203F01	MENB1010A1203F01	12V	1A	12W	13.36	11.70	11.47
675-MENB1010A2403F01	MENB1010A2403F01	24V	.5A	12W	13.36	11.70	11.47

MENB1020 SERIES, 15-20 WATTS, SINGLE OUTPUT

- Features:**
- 100-240VAC Universal Input Range
 - 5V to 48V Single Output Models, up to 20W
 - Impact-Resistant Polycarbonate Enclosure
 - Limited Power Source
 - No load Power Consumption <0.3W
 - Meets EISA2007, CEC Efficiency Level V, EU (EC) No 278/2009 Phase II
 - Certified to UL/EN/IEC60601-1
 - Desktop models AC Input: N01 = IEC320-C8 F01 = IEC320-C14



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each		
					1	10	25
Wall-Plug Models							
675-MENB1020A0503B01	MENB1020A0503B01	5V	3A	15W	16.84	14.74	14.45
675-MENB1020A0703B01	MENB1020A0703B01	7.5V	2A	15W	13.58	13.17	12.90
675-MENB1020A0903B01	MENB1020A0903B01	9V	2A	18W	16.84	14.74	14.45
675-MENB1020A1203B01	MENB1020A1203B01	12V	1.5A	18W	16.84	14.74	14.45
675-MENB1020A2403B01	MENB1020A2403B01	24V	.75A	18W	16.84	14.74	14.45
Desktop Models (AC Input cord not included)							
675-MENB1020A0503F01	MENB1020A0503F01	5V	3A	15W	15.15	13.26	13.00
675-MENB1020A0903F01	MENB1020A0903F01	9V	2A	18W	15.15	13.26	13.00
675-MENB1020A1203F01	MENB1020A1203F01	12V	1.5A	18W	15.15	13.26	13.00
675-MENB1020A2403F01	MENB1020A2403F01	24V	.75A	18W	15.15	13.26	13.00



MENB1030 SERIES, 20-32 WATTS, SINGLE OUTPUT

- Features:**
- 100-240VAC Universal Input
 - 5V to 24V outputs models, up to 32W
 - No load Power Consumption <0.3W
 - Regulated Output with Low Ripple
 - Meets EISA2007, CEC Efficiency Level V, EU (EC) No 278/2009 Phase II
 - Certified to UL/EN/IEC60601-1
 - Desktop models AC Input: N01 = IEC320-C8 F01 = IEC320-C14



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each		
					1	10	25
Wall-Plug Models (AC Plug N. America/Japan)							
675-MENB1030A0503B01	MENB1030A0503B01	5V	4A	22W	21.47	18.96	18.48
675-MENB1030A0903B01	MENB1030A0903B01	9V	3A	27W	21.47	18.96	18.48
675-MENB1030A1203B01	MENB1030A1203B01	12V	2.5A	30W	21.47	18.96	18.48
675-MENB1030A2403B01	MENB1030A2403B01	24V	1.33A	31.9W	21.47	18.96	18.48

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each		
					1	10	25
Desktop Models (AC Input cord not included)							
675-MENB1030A0503F01	MENB1030A0503F01	5V	4A	22W	21.68	18.98	18.61
675-MENB1030A0903F01	MENB1030A0903F01	9V	3A	27W	21.68	18.98	18.61
675-MENB1030A1203F01	MENB1030A1203F01	12V	2.5A	30W	21.68	18.98	18.61
675-MENB1030A2403F01	MENB1030A2403F01	24V	1.33A	31.9W	21.68	18.98	18.61

MENB1040 SERIES, 25-41 WATTS, SINGLE OUTPUT

- Features:**
- 100-240VAC Universal Input
 - 5V to 24V Single Output Models, up to 40W
 - Desktop Style
 - Meets EISA2007, CEC Efficiency Level V, EU (EC) No 278/2009 Phase II
 - Certified to UL/EN/IEC60601-1
 - Desktop models AC Input: N01 = IEC320-C8 F01 = IEC320-C14



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Ault Part No.	Output Voltage	Max. Current	Max. Power	Price Each		
					1	10	25
Desktop Models (AC Input cord not included)							
675-MENB1040A1203F01	MENB1040A1203F01	12V	3.4A	40.8W	25.69	22.49	22.05
675-MENB1040A2403F01	MENB1040A2403F01	24V	1.7A	40.8W	25.69	22.49	22.05

AC INTERCHANGEABLE BLADE KIT

- For use with medical and commercial wall plug interchangeable

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Description	Price Each		
		1	10	25
831-KT1027K	Includes Europe, United Kingdom, Australian	4.63	3.83	3.76

AC INPUT CORD

- For use with adapters shown

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Description	Price Each
173-0602-E	Kobiconn - 6'7" AC input cord, 3-wire input, 18AWG, Black	7.52