

POMONA Test Clips and Accessories



BANANA PLUGS AND JACKS

Replace blank with 0 for Black, 2 for Red *LAP = Lucel Acetal Polymer P = Polycarbonate For quantities greater than listed, call for quote.

| MOUSER STOCK NO. | | Fig. | Description | Insulation * | Price Each | | |
|------------------|---------------|------|-------------------------------------------------------------------|--------------|------------|-------|-------|
| Mfr. | Mfr. Part No. | | | | 1 | 25 | 50 |
| Plugs | | | | | | | |
| 565-1825- | | A | Solderless stackup banana plug | ABS | 1.76 | 1.68 | 1.56 |
| 565-1325- | | B | Do-it-yourself sldrless stackup banana plug | ABS | 1.65 | 1.58 | 1.46 |
| 565-5169- | | C | Insul. banana plug w/flexible boot 18-22AWG | PVC | 2.70 | 2.59 | 2.40 |
| 565-5170- | | C | Insul. banana plug w/flexible boot 14-16AWG | PVC | 2.70 | 2.59 | 2.40 |
| 565-MDP- | | D | Double banana with wire guide | ABS | 2.78 | 2.67 | 2.47 |
| 565-MDP-S- | | D | Double banana with shorting bar | ABS | 4.75 | 4.56 | 4.22 |
| 565-122505A | | E | Retractable sheath banana plug Black | LAP | 5.10 | 4.89 | 4.53 |
| 565-122506A | | E | Retractable sheath banana plug Red | LAP | 5.10 | 4.89 | 4.53 |
| 565-4513 | | F | Mini. banana plug with threaded stud .48" | - | 2.21 | 2.11 | 1.96 |
| 565-3276 | | F | Mini. banana plug with threaded stud .23" | - | 1.59 | 1.35 | 1.30 |
| 565-3268 | | G | Mini. rivet type banana plug .062" panel | - | 1.40 | 1.30 | 1.15 |
| 565-2035- | | H | Mini. double banana plug with shorting bar | ABS | 6.40 | 6.15 | 5.69 |
| Jacks | | | | | | | |
| 565-1581- | | I | Panel mount banana jack | P | 1.57 | 1.51 | 1.40 |
| 565-2854- | | I | Panel mount banana jack | P | 2.47 | 2.37 | 2.20 |
| 565-2269-0 | | J | Double panel mount banana jacks w/black mounting base | P | 3.46 | 3.32 | 3.07 |
| 565-4243- | | K | Binding post with double mounting base | P | 6.92 | 6.65 | 6.16 |
| 565-2142- | | L | Miniature banana jack, panel mount | P | 1.57 | 1.51 | 1.40 |
| 565-2143- | | J | Miniature banana jack in double mounting base, panel mount | P | 4.30 | 4.12 | 3.82 |
| 565-3542- | | L | Pin tip jack | P | 3.10 | 2.97 | 2.75 |
| 565-5168- | | I | Insulated banana jack with flexible boot 14-16 AWG | PVC | 2.70 | 2.59 | 2.40 |
| 565-3267 | | M | Uninsulated banana jack | - | 1.17 | 1.11 | .984 |
| 565-6728- | | N | 4mm Safety ban. jack to ban. plug adapter | Nylon 6 | 3.90 | 3.75 | 3.47 |
| 565-6720- | | O | 4mm Safety ban. jack to 6/32 thread adapter | Nylon 6 | 3.90 | 3.75 | 3.47 |
| 565-3452- | | P | Dual pin tip jack with shorting bar | P | 5.90 | 5.67 | 5.25 |
| 565-4995- | | Q | Spring loaded binding post | Nylon | 22.50 | 21.60 | 20.01 |
| 565-72911 | | R | Insulated BNC to 2 Male Banana | Polymide | 19.96 | 19.38 | 18.40 |
| 565-72908 | | S | Insulated BNC to Stackable/Retractable 4mm Plugs | Nylon | 16.52 | 16.05 | 15.24 |
| 565-72912- | | T | Panel mount IEC1010 banana jack for sheathed plugs, threaded stud | - | 3.25 | 3.12 | 2.89 |
| 565-72913- | | T | Panel mount IEC1010 banana jacks for sheathed plugs, solder tab | - | 2.80 | 2.68 | 2.49 |

BINDING POSTS

For quantities greater than listed, call for quote.

| MOUSER STOCK NO. | | Fig. | Description | Price Each | | |
|------------------|---------------|------|---------------------------------|------------|------|------|
| Mfr. | Mfr. Part No. | | | 1 | 25 | 50 |
| 565-6883 | | U | Dual binding posts | 2.18 | 2.12 | 2.02 |
| 565-6884 | | V | Dual binding posts, raised base | 2.11 | 2.07 | 1.90 |

TEST LEADS

Replace blank with 0 for Black, 2 for Red • Current rating: 5A For quantities greater than listed, call for quote.

| MOUSER STOCK NO. | | Fig. | Description | Length (In.) | Price Each | | |
|-------------------|---------------|------|-----------------------------------------------|--------------|------------|-------|-------|
| Mfr. | Mfr. Part No. | | | | 1 | 25 | 50 |
| Plugs | | | | | | | |
| 565-AL-B-12- | | W | Alligator clip patch cord | 12 | 5.50 | 5.28 | 4.89 |
| 565-AL-B-24- | | W | Alligator clip patch cord | 24 | 5.80 | 5.56 | 5.15 |
| 565-AL-B-36- | | W | Alligator clip patch cord | 36 | 5.90 | 5.67 | 5.25 |
| 565-AL-B-48- | | W | Alligator clip patch cord | 48 | 6.80 | 6.52 | 6.04 |
| 565-AL-B-60- | | W | Alligator clip patch cord | 60 | 6.80 | 6.52 | 6.04 |
| 565-B4- | | X | Stacking standard banana plug each end | 4 | 4.70 | 4.51 | 4.18 |
| 565-B8- | | X | Stacking standard banana plug each end | 8 | 4.80 | 4.60 | 4.26 |
| 565-B12- | | X | Stacking standard banana plug each end | 12 | 4.80 | 4.60 | 4.26 |
| 565-B18- | | X | Stacking standard banana plug each end | 18 | 4.90 | 4.71 | 4.36 |
| 565-B24- | | X | Stacking standard banana plug each end | 24 | 5.10 | 4.89 | 4.53 |
| 565-B36- | | X | Stacking standard banana plug each end | 36 | 5.10 | 4.89 | 4.53 |
| 565-B48- | | X | Stacking standard banana plug each end | 48 | 5.30 | 5.08 | 4.71 |
| 565-B72- | | X | Stacking standard banana plug each end | 72 | 5.50 | 5.28 | 4.89 |
| 565-1440-24- | | X | Cross stacking banana plug patch cord | 24 | 7.60 | 7.29 | 6.75 |
| 565-1440-36- | | X | Cross stacking banana plug patch cord | 36 | 7.60 | 7.29 | 6.75 |
| 565-1440-48- | | X | Cross stacking banana plug patch cord | 48 | 7.60 | 7.29 | 6.75 |
| 565-1440-60- | | X | Cross stacking banana plug patch cord | 60 | 9.00 | 8.64 | 8.00 |
| 565-4613-12- | | Y | Micrograbber test clip patch cord | 12 | 7.30 | 7.00 | 6.49 |
| 565-4613-24- | | Y | Micrograbber test clip patch cord | 24 | 7.50 | 7.20 | 6.67 |
| 565-4613-36- | | Y | Micrograbber test clip patch cord | 36 | 7.60 | 7.29 | 6.75 |
| 565-3781-8 | | Y | Minigrabber test clip each end | 8 | 4.60 | 4.41 | 4.08 |
| 565-3781-12- | | Y | Minigrabber test clip each end | 12 | 4.70 | 4.51 | 4.18 |
| 565-3781-24- | | Y | Minigrabber test clip each end | 24 | 4.70 | 4.51 | 4.18 |
| 565-3781-36- | | Y | Minigrabber test clip each end | 36 | 4.80 | 4.60 | 4.26 |
| 565-3781-48- | | Y | Minigrabber test clip each end | 48 | 5.10 | 4.89 | 4.53 |
| 565-5301-12- | | Z | SMD Grabber test clip patch cord | 12 | 9.20 | 8.83 | 8.18 |
| 565-5301-24- | | Z | SMD Grabber test clip patch cord | 24 | 9.30 | 8.92 | 8.27 |
| 565-4911A-12- | | AA | Retractable sheath banana plug patch cord | 12 | 11.75 | 11.28 | 10.45 |
| 565-4911A-24- | | AA | Retractable sheath banana plug patch cord | 24 | 12.00 | 11.52 | 10.67 |
| 565-4911A-36- | | AA | Retractable sheath banana plug patch cord | 36 | 12.50 | 12.00 | 11.12 |
| 565-4911A-48- | | AA | Retractable sheath banana plug patch cord | 48 | 12.50 | 12.00 | 11.12 |
| 565-4911A-60- | | AA | Retractable sheath banana plug patch cord | 60 | 12.75 | 12.24 | 11.34 |
| Test Clips | | | | | | | |
| 565-3782-12- | | BB | Minigrabber test clip to stacking banana plug | 12 | 6.20 | 5.95 | 5.51 |
| 565-3782-24- | | BB | Minigrabber test clip to stacking banana plug | 24 | 6.30 | 6.04 | 5.60 |
| 565-3782-36- | | BB | Minigrabber test clip to stacking banana plug | 36 | 6.30 | 6.04 | 5.60 |
| 565-3782-48- | | BB | Minigrabber test clip to stacking banana plug | 48 | 6.40 | 6.15 | 5.69 |
| 565-1166-24- | | CC | Multi-stacking banana plug to alligator clip | 24 | 5.60 | 5.37 | 4.97 |
| 565-1166-36- | | CC | Multi-stacking banana plug to alligator clip | 36 | 5.60 | 5.37 | 4.97 |
| 565-1166-48- | | CC | Multi-stacking banana plug to alligator clip | 48 | 6.10 | 5.85 | 5.42 |
| 565-1368-A-18 | | DD | Multi-stacking double to single banana plugs | 18 | 29.50 | 28.32 | 26.24 |
| 565-1368-A-24 | | DD | Multi-stacking double to single banana plugs | 24 | 29.50 | 28.32 | 26.24 |
| 565-1368-A-30 | | DD | Multi-stacking double to single banana plugs | 30 | 29.50 | 28.32 | 26.24 |
| 565-1368-A-36 | | DD | Multi-stacking double to single banana plugs | 36 | 29.50 | 28.32 | 26.24 |
| 565-1368-A-48 | | DD | Multi-stacking double to single banana plugs | 48 | 29.50 | 28.32 | 26.24 |
| 565-1368-A-60 | | DD | Multi-stacking double to single banana plugs | 60 | 29.50 | 28.32 | 26.24 |

