

# SILVERTRONIC Test Clips



## TEST CLIPS

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Description	Price Each		
			1	25	50
Mfr. Mfr. Part No.					
835-501789	A	Multi-Colored 10 Leads	4.00	3.80	3.61
835-502012/B	B	Heavy Duty, 500A	17.00	16.15	15.34
835-502012/R	B	Heavy Duty, 500A	17.00	16.15	15.34
835-502013/B	B	Kelvin Clamp, 500A	23.00	21.85	20.76
835-502013/R	B	Kelvin Clamp, 500A	23.00	21.85	20.76
835-502003/B	C	Solid Copper, 500A	17.00	16.15	15.34
835-502003/R	C	Solid Copper, 500A	17.00	16.15	15.34
835-501790	D	Heavy Duty Steel, 50A	1.65	1.57	1.49
835-501790C	D	HD Clip Copper, 100A	5.58	5.30	5.04
835-400020/B	E	Insulator 501790, Black	.92	.87	.83
835-400020/R	E	Insulator 501790, Red	.92	.87	.83
835-502002	F	HD Clip Steel, 25A	.72	.68	.65
835-501997	G	Auto Clip Steel, 40A	.90	.83	.77
835-501997C	G	Solid Copper, 75A	2.32	2.21	2.09
835-400023/B	H	Insulator 501790, Black	.67	.64	.60
835-400023/R	H	Insulator 501790, Red	.67	.64	.60
835-501996	I	GP Clip Steel, 20A	.52	.49	.47
835-501996C	I	GP Clip Copper, 40A	.92	.87	.83
835-501793	J	Clip Steel, 5A	.16	.15	.14
835-501795	K	Clip with Barrel, 5A	.17	.16	.15
835-501793C	J	Solid Copper, 5A	.26	.25	.23
835-502007	L	6-32 Barrel, 5A	.38	.36	.34
835-400016/B	M	Insulator 501795, Black	.16	.15	.14
835-400016/R	M	Insulator 501795, Red	.16	.15	.14
835-400015/B	N	Insulator 501793, Black	.13	.12	.11
835-400015/R	N	Insulator 501793, Red	.13	.12	.11
835-502008	O	Clip Steel, 5A	.30	.29	.27
835-502008C	O	Solid Copper, 5A	.43	.41	.39
835-400025/B	P	Insulator 502008, Black	.16	.15	.14
835-400025/R	P	Insulator 502008, Red	.16	.15	.14
835-502009/B	Q	Plier Clip Steel, 15A	.54	.51	.49
835-502009/R	Q	Plier Clip Steel, 15A	.54	.51	.49
835-501849	R	Large Clip Steel	2.40	2.28	2.17
835-501849C	R	Large Clip Solid Copper	8.50	8.08	7.67
835-400012/B	S	Insulator 501849, Black	.43	.41	.39
835-400012/R	S	Insulator 501849, Red	.43	.41	.39
835-501994	T	Clip Steel, 5A	.32	.30	.29
835-501994C	T	Solid Copper, 10A	.58	.55	.52
835-501774	U	Small Clip Steel, 50A	.46	.44	.42
835-501774Z	U	Zinc Plated, 50A	.50	.48	.46
835-501774C	U	Small Clip Solid Copper, 75A	1.51	1.43	1.36
835-400010/B	V	Insulator 501774, Black	.16	.15	.14
835-400010/R	V	Insulator 501774, Red	.16	.15	.14
835-400018/B	W	Insulator 501994, Black	.17	.16	.15
835-400018/R	W	Insulator 501994, Red	.17	.16	.15
835-501797	X	Clip Steel, 10A	.47	.45	.42
835-501797C	X	Solid Copper, 20A	.69	.66	.62
835-400019/B	Y	Insulator 501797, Black	.40	.38	.36
835-400019/R	Y	Insulator 501797, Red	.40	.38	.36
835-501958	Z	Ground Clamp Steel, 50A	8.00	7.60	7.22
835-501784	AA	With Barrel, 10A	.20	.19	.18
835-501784C	AA	Copper with Barrel, 10A	.60	.57	.54
835-502000C/B	BB	Solid Copper, 10A	.74	.70	.67
835-502000C/R	BB	Solid Copper, 10A	.74	.70	.67
835-501784CS	CC	Solid Copper, 10A	.55	.52	.50
835-502000/B	BB	Clip Steel, 10A	.47	.45	.42
835-502000/R	BB	Clip Steel, 10A	.47	.45	.42
835-501784S	CC	Clip Steel, 10A	.29	.28	.26
835-501785	DD	8-32 Barrel, 10A	.44	.42	.40
835-501784U	EE	With U-Shape Tail, 10A	.25	.24	.23
835-501784X	FF	SS with Barrel, 10A	.59	.56	.53
835-400017/B	GG	Insulator 501784-5, Black	.17	.16	.15
835-400017/R	GG	Insulator 501784-5, Red	.17	.16	.15
835-501993/B	HH	Clip Steel, 10A	.73	.69	.66
835-501993/R	HH	Clip Steel, 10A	.73	.69	.66
835-502005	II	Clip Steel, 5A	.33	.31	.30
835-502005C	II	Solid Copper, 10A	.47	.45	.42
835-400024/B	JJ	Insulator 502005, Black	.20	.19	.18
835-400024/R	JJ	Insulator 502005, Red	.20	.19	.18
835-502001	KK	Kelvin Clip Gold, 10A	7.40	7.03	6.68
835-501995	LL	Zinc Plate, 5A	.40	.38	.36
835-501995C	LL	Solid Copper, 10A	.88	.84	.79
835-400021/B	MM	Insulator 501995, Black	.29	.28	.26
835-400021/R	MM	Insulator 501995, Red	.29	.28	.26
835-400013/B	NN	Insulator 501791, Black	.47	.45	.42
835-400013/R	NN	Insulator 501791, Red	.47	.45	.42
835-501791-L	OO	Bed of Nails Spike	4.00	3.80	3.61
835-501791	PP	Bed of Nails Spike	4.00	3.80	3.61

