

ESD Safe Cutters and Tweezers

Erem "N" SERIES DIAGONAL CUTTERS

- Swiss made
- ESD safe
- Guaranteed for over 1 million openings
- High grade tool steel
- Low fatigue operation



For quantities greater than listed, call for quote.

MOUSER STOCK NO.		Fig.	Size	Cut	Price Each	
Mfr.	Mfr. Part No.				1	5
578—512N		A	4 1/2"	Small oval head, Semi-Flush		56.00
578—522N		A	4 1/2"	Medium oval head, Full-Flush		56.00
578—612N		A	4 1/4"	Small oval head, Semi-Flush		53.00
578—622N		A	4 1/4"	Small oval head, Full-Flush		53.00
578—622NA		A	4 1/4"	Tapered head, Full-Flush		52.00
578—622NB		A	4 1/4"	Tapered relieved head, Full-Flush		52.00
578—632N		A	4 1/4"	Small head, Super Full-Flush		54.00

ESD SAFE CUTTERS

- Cutting edges are induction hardened at a hardness of Approx. 64°HRC.
- Two component non-slip soft grip handle



For quantities greater than listed, call for quote.

MOUSER STOCK NO.		Fig.	Description	Length	Price Each	
Mfr.	Mfr. Part No.				1	5
596—32703		B	Side cutters, Small Tapered Head, Form 1-Semi Flush	115mm	45.04	31.83
596—32705		B	Side cutters, Small Tapered Head, Form 2 Flush	115mm	45.72	32.32
596—32702		B	Side Cutters Small Tapered Head with Hollow Ground Back, Form 3- Semi Flush	115mm	46.18	33.49
596—32704		B	Side cutters, Small Tapered Head with Hollow Ground Back, Form 4-Flush	115mm	46.18	33.49
596—32710		B	Side Cutters, Wide Tapered Head, Form 3-Full Flush	115mm	49.54	35.92
596—32712		C	Side cutters, Slim Oval Head, Form 1-Flush	115mm	46.16	33.45
596—32714		C	Side cutters, Slim Oval Head, Form 2-Full Flush	115mm	50.14	36.35
596—32718		C	Side cutters, Wide Oval Head Carbide Cutting Edges, Form 2-Bevel	110mm	105.60	76.57
596—32720		C	Side cutters, Wide Oval Head, Form 3-Flush	115mm	45.60	33.07
596—32728		D	Oblique Front Cutters, Very Small Head, 40°, Form 4-Flush	110mm	50.77	36.81
596—32732		E	End Cutters, Extra Slim, Form 1-Flush	110mm	50.70	36.75
596—32734		F	End Cutters, Wide Head, Form 2-Flush	115mm	50.70	36.77

ESD SAFE TWEEZERS

- ESD Safe
- Hypo Allergenic Coated
- Anti Magnetic
- Made from Vommelloy
- Anti Static Conductive
- Textured Gripping Surface
- Acid Resistant



For quantities greater than listed, call for quote.

MOUSER STOCK NO.		Fig.	Description	Length	Price Each	
Mfr.	Mfr. Part No.				1	5
596—44501		G	Universal Fine Point	130mm	15.74	11.41
596—44503		H	Long Narrow Body Low Force	135mm	20.07	14.56
596—44505		I	Flat Round Tip Smooth Sides ESD safe	120mm	19.75	14.33
596—44506		G	Fine Round Points for Assembly	120mm	20.07	14.56
596—44508		J	Very Fine Points/Tapered to Tip ESD Safe	110mm	20.67	14.99
596—44509		J	Extra Fine Points/Tapered To Tip ESD Safe	110mm	20.10	14.57
596—49379		J	Extra Fine Points/Tapered To Tip	110mm	24.73	17.93
596—44510		K	Curved Extra Fine Rounded Tips	120mm	26.86	25.52
596—44518		L	Narrow Rounded Tip Serrated, Guide Pin	150mm	20.24	14.67
596—44523		G	Long Rounded to 1.0mm Wide Serrated	125mm	19.98	18.98
596—44525		M	Curved Extra Fine, 3mm Long Straight Tip	120mm	31.04	21.64
596—44529		N	MicroTip Bent 30° 1mm Wide	120mm	27.48	19.93
596—44531		G	General Purpose Fine Point	120mm	20.68	14.99
596—44532		G	Heavy Duty Strong Tapered to Strong Point	120mm	26.28	19.06

Erem TWEEZERS

- Material: "non-magnetic", anti-acid alloy
- Temperature resistance: 300°C

For quantities greater than listed, call for quote.

MOUSER STOCK NO.		Fig.	Description	Length	Price Each	
Mfr.	Mfr. Part No.				1	5
578—2SA		O	4.5" medium point	-	20.50	20.50
578—EROP2ASA		P	4.5" round point	-	3.50	3.50
578—3SA		G	4.75" popular fine point for microelectronics	-	24.80	24.80
578—EROP3SA		G	4.5" popular fine point for microelectronics	-	3.50	3.50
578—EROP3CSA		G	4.25" popular fine point for microelectronics	-	3.50	3.50
578—5SA		G	4.5" superfine point, special shaping	-	29.40	29.40
578—EROP5SA		G	4.5" superfine point, special shaping	-	3.50	3.50
578—7SA		K	4.75" curved point easy access-confined areas	-	26.80	26.80
578—EROP7SA		K	4.75" curved point easy access-confined areas	-	3.50	3.50
578—AASA		G	5.0" straight point, hardened tips	-	10.50	10.50
578—EROPAASA		G	4.75" strong but fine point	-	3.50	3.50
578—OOSA		G	4.75" flat inside edges, general purpose	-	19.40	19.40
578—EROPPOOSA		G	4.75" flat inside edges, general purpose	-	3.50	3.50

Erem CUTTING TWEEZERS

For quantities greater than listed, call for quote.

MOUSER STOCK NO.		Fig.	Description	Length	Price Each	
Mfr.	Mfr. Part No.				1	5
578—15AGW		Q	4.5" oblique head, long life, soft wire cutting	-	29.00	29.00
578—15AGS		Q	4.25" oblique fine head, long life, soft wire cutting	-	31.60	31.60

