

VECTOR Extender Cards and Prototype Accessories

VECTORBORD® GENERAL PURPOSE EXTENDER CARDS

- Low insertion force
- Gold-plated contacts
- Current Rating: 5 amps @ 10°F rise
- Voltage Rating: 200 RMS or 300 VDC

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Vector Part No.	Fig.	Extension Length (In.)	Description		Price Each	
				Contacts	Spacing	1	10
574-3690	3690	A	6.5	22 each side	.156"	40.43	37.80
574-3690-16	3690-16	B	6.5	28 each side	.125"	48.04	44.91
Bus Extenders							
574-3690-22	3690-22	C	5.7	IBM PC, XT, 31 contacts each side	.100"	77.82	72.95
574-3690-26	3690-26	D	5.6	IBM AT-ISA, 18/31 contacts ea. side	.100"	76.98	71.98

PROTOTYPE ACCESSORIES

Pins and Terminals

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Vector Part No.	Fig.	Description	Package Quantity	Price Each
Press-In Terminals for .042" Holes Insertion Tool: 574-P133A					
574-T46-2-9/M	T46-2-9/M	E	A=.36", B=.42"	1000	95.85
574-T46-3-9/C	T46-3-9/C	E	A=.46", B=.60"	100	16.63
574-T46-3-9/M	T46-3-9/M	E	A=.46", B=.60"	1000	113.79
574-T46-4-9/C	T46-4-9/C	E	A=.04", B=.42"	100	10.45
574-T46-4-9/M	T46-4-9/M	E	A=.04", B=.42"	1000	104.45
Bifurcated Miniwrap Terminals for .042" Holes Insertion Tool: 574-A13 or 574-A13-1					
574-T44/C	T44/C	F	Max. .021" leads or 24 AWG wires	100	11.55
574-T44/M	T44/M	F	Max. .021" leads or 24 AWG wires	1000	66.50
574-T68/C	T68/C	G	Max. .032" leads or 20 AWG wires	100	10.71
574-T68/M	T68/M	G	Max. .032" leads or 20 AWG wires	1000	63.14
Trifurcated Klipwrap Terminals for .042" Holes Insertion Tool: 574-P156					
574-T49/C	T49/C	H	Wirewrap tail with 3-prong receptacle	100	16.09
Press-In Pins for .042" Holes Insertion Tool: 574-P133A					
574-K24A/M	K24A/M	I	A=.255", B=.375", gold plated	1000	110.69
574-K24C/M	K24C/M	I	A=.255", B=.375", tin plated	1000	69.65
574-K30C/M	K30C/M	J	A=.255", B=.305", tin plated	1000	59.75
574-K31C/M	K31C/M	J	A=.160", B=.195", tin plated	1000	46.50
Push-In Terminals for .042" Holes Insertion Tool: 574-P149 or 574-P149A					
574-T42-1/C	T42-1/C	K	Horizontal slot holds up to 7 wires	100	11.19
574-T42-1/M	T42-1/M	K	Horizontal slot holds up to 7 wires	1000	62.90
Push-In Terminals for .062" Holes Insertion Tool: 574-P91A					
574-T28/C	T28/C	L	Vert. slot holds .025" leads/22 AWG wires	100	10.97
574-T28/M	T28/M	L	Vert. slot holds .025" leads/22 AWG wires	1000	71.42
Wire-wrap Socket Pins for .042" Holes Insertion Tool: 574-P158					
574-R32/C	R32/C	M	Pressfit mounting, 4-finger contacts	100	40.00

Insertion Tools for Pins and Terminals

MOUSER STOCK NO.	Vector Part No.	For Use With	Price Each
574P133A	P133A	Press-In Terminals and Pins for .042" Holes	88.59
574-A13	A13	Bifurcated Miniwrap Terminals for .042" Holes	26.94
574-P149	P149	Push-In Terminals for .042" Holes	27.99
574-P149A	P149A	Push-In Terminals for .042" Holes	40.25

Tefzel Insulated Silver Plated Wire

This wire is designed to be used with wire wrap terminals. Spool diameter is 1".

- Two 50' Spools Per Package

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Vector Part No.	AWG	Color	Price Per Package
574-W28-6A	W28-6A	28	Green	22.28
574-W28-6B	W28-6B	28	Red	25.91
574-W28-6D	W28-6D	28	Blue	22.38
574-W28-6E	W28-6E	28	White	23.37
574-W28-6F	W28-6F	28	Yellow	21.11
574-W28-6H	W28-6H	28	Black	22.28

Solder Eyelets and Bus Strips

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Vector Part No.	Fig.	Description	Package Quantity	Price Per Package
574-T123/500	T123/500	N	Solder eyelets for .055" holes	500	33.18
574-T107/C	T107/C	O	.08" x 14" solder-coated bus strips	100	108.92

