

STANDARD LINEAR AMPLIFIERS (CONT.)

RoHS Compliant This product is RoHS compliant.

NEW PRODUCT

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	National Products Part No.	Package Style	No. of Channels	Total Supply Voltage (Min./Max.) (+5V=5, ±5V=10)	Supply Current Per Channel (Max.) (mA)	GBW (Typ.) (MHz)	Slew Rate (Typ.) (V/μs)	V _{os} (25°C) (Max.) (mV)	Price Each		
									1	25	100
Low Power, Rail-to-Rail (Cont.)											
926-LM6132BIN/NOPB	LM6132BIN/NOPB	DIP-14	2	2.7/24	0.36	10	14	6	3.33	2.67	2.43
926-LMC6462BIMX/NOPB	LMC6462BIMX/NOPB	SOIC-8	2	3/15.5	0.02	50	8	3	2.62	2.10	1.91
926-LMC6482AIM/NOPB	LMC6482AIM/NOPB	SOIC-8	2	3/15.5	0.5	1.5	1.3	0.75	2.33	1.87	1.68
926-LMC6482AIMX/NOPB	LMC6482AIMX/NOPB	SOIC-8	2	3/15.5	0.5	1.5	1.3	0.75	2.63	2.02	1.83
926-LMC6482AIN/NOPB	LMC6482AIN/NOPB	DIP-8	2	3/15.5	0.5	1.5	1.3	0.75	2.21	1.78	1.60
926-LMC6482IM/NOPB	LMC6482IM/NOPB	SOIC-8	2	3/15.5	0.5	1.5	1.3	3	1.95	1.57	1.41
926-LMC6482IMX/NOPB	LMC6482IMX/NOPB	SOIC-8	2	3/15.5	0.5	1.5	1.3	3	1.95	1.57	1.41
926-LMC6482IMM/NOPB	LMC6482IMM/NOPB	MiniSOIC-8	2	3/15.5	0.5	1.5	1.3	3	2.21	1.70	1.54
926-LMC6482IMMX/NOPB	LMC6482IMMX/NOPB	MiniSOIC-8	2	3/15.5	0.5	1.5	1.3	3	1.95	1.57	1.41
926-LMC6482IN/NOPB	LMC6482IN/NOPB	DIP-8	2	3/15.5	0.5	1.5	1.3	3	1.95	1.57	1.41
926-LMC6482IM	LMC6482IM	SOIC-8	2	3/15.5	1.4	1.5	1.3	3.7	1.95	1.57	1.41
926-LMV934MA/NOPB	LMV934MA/NOPB	SOIC-8	4	1.8/5.5	0.116	1.5	0.42	5.5	1.86	1.50	1.35
926-LMV934MAX/NOPB	LMV934MAX/NOPB	SOIC-14	4	1.8/5.5	0.116	1.5	0.42	5.5	2.10	1.62	1.47
926-LMV934MT/NOPB	LMV934MT/NOPB	TSSOP-14	4	1.8/5.5	0.116	1.5	0.42	5.5	1.86	1.50	1.35
926-LM6134AIMX/NOPB	LM6134AIMX/NOPB	SOIC-14	4	1.8/24	1.6	10	14	4	3.90	3.51	3.19
926-LM6134BIM	LM6134BIM	SOIC-14	4	1.8/24	1.6	10	14	4	3.75	3.01	2.74
926-LMV824M/NOPB	LMV824M/NOPB	SOIC-8	4	2.5/5.5	0.25	5.6	2	3.5	1.55	1.25	1.12
926-LPV324MTX/NOPB	LPV324MTX/NOPB	TSSOP-14	4	2.7/5	0.042	1.52	0.1	7	1.29	1.02	.918
926-LMV324M/NOPB	LMV324M/NOPB	SOIC-14	4	2.7/5.5	0.1025	1	1	7	1.05	.84	.735
926-LMV324MT/NOPB	LMV324MT/NOPB	TSSOP-14	4	2.7/5.5	0.1025	1	1	7	1.30	1.03	.906
926-LMV324MX/NOPB	LMV324MX/NOPB	SOIC-14	4	2.7/5.5	0.1025	1	1	7	1.14	.90	.81
926-LMV344MA/NOPB	LMV344MA/NOPB	SOIC-14	4	2.7/5.5	0.107	1	1	5	1.26	1.00	.882
926-LMV344MT/NOPB	LMV344MT/NOPB	TSSOP-14	4	2.7/5.5	0.107	1	1	5	1.50	1.14	1.05
926-LM6134AIM/NOPB	LM6134AIM/NOPB	SOIC-14	4	2.7/24	0.36	10	14	2	4.37	3.51	3.19
926-LM6134BIM/NOPB	LM6134BIM/NOPB	SOIC-14	4	2.7/24	0.36	10	14	6	3.75	3.01	2.74
926-LM6134BIMX/NOPB	LM6134BIMX/NOPB	SOIC-14	4	2.7/24	0.36	10	14	6	4.02	3.28	2.94
926-LM6134BIN/NOPB	LM6134BIN/NOPB	DIP-14	4	2.7/24	0.36	10	14	6	4.06	3.26	2.97
926-LMC6484AIM/NOPB	LMC6484AIM/NOPB	SOIC-14	4	3/15	0.5	1.5	1.3	3	3.67	2.94	2.68
926-LMC6484AIMX/NOPB	LMC6484AIMX/NOPB	SOIC-14	4	3/15	0.5	1.5	1.3	3	3.93	3.20	2.88
926-LMC6484AIN/NOPB	LMC6484AIN/NOPB	DIP-14	4	3/15	0.5	1.5	1.3	3	4.34	3.48	3.17
926-LMC6484IM/NOPB	LMC6484IM/NOPB	SOIC-14	4	3/15	0.5	1.5	1.3	3	3.02	2.43	2.21
926-LMC6484IMX/NOPB	LMC6484IMX/NOPB	SOIC-14	4	3/15	0.5	1.5	1.3	3	3.02	2.43	2.21
926-LMC6484IN/NOPB	LMC6484IN/NOPB	DIP-14	4	3/15	0.5	1.5	1.3	3	3.61	2.90	2.64
926-LMC6484AIM	LMC6484AIM	SOIC-14	4	3/15.5	2.8	1.5	1.3	1.35	4.04	3.24	2.95
926-LMC6484IM	LMC6484IM	SOIC-14	4	3/15.5	2.8	1.5	1.3	3.7	3.24	2.64	2.37
Low Voltage											
926-LM10CLN/NOPB	LM10CLN/NOPB	DIP-8	1	1.1/7	0.3	0.09	0.2	4	3.39	2.72	2.48
926-LM10CN/NOPB	LM10CN/NOPB	DIP-8	1	1.1/45	0.28	0.09	0.2	2	3.16	2.54	2.31
926-LM10CWM/NOPB	LM10CWM/NOPB	SOIC-14	1	1.1/45	0.28	0.09	0.2	2	3.00	2.40	2.19
Low Voltage, Rail-to-Rail											
926-LMV321M7/NOPB	LMV321M7/NOPB	SC-70-5	1	2.7/5.5	0.13	1	1	7	.97	.748	.66
926-LMV116MF/NOPB	LMV116MF/NOPB	SOT-23-5	1	2.7/12	0.6	45	40	5	1.79	1.41	1.26
926-LMV841MG/NOPB	LMV841MG/NOPB	SC-70-5	1	2.7/12	1.02	4.5	2.5	0.5	2.33	1.79	1.62
926-LMV842MA/NOPB	LMV842MA/NOPB	SOIC-8	2	2.7/12	1.02	4.5	2.5	0.5	3.05	2.45	2.23
926-LM6152ACM/NOPB	LM6152ACM/NOPB	SOIC-8	2	2.7/24	1.4	75	30	2	4.93	3.96	3.60
926-LM6152BCM/NOPB	LM6152BCM/NOPB	SOIC-8	2	2.7/24	1.4	75	30	5	3.98	3.19	2.91
926-LMV844MA/NOPB	LMV844MA/NOPB	SOIC-8	4	2.7/12	1.02	4.5	2.5	0.5	5.07	4.07	3.71
926-LMV844QMA/NOPB	LMV844QMA/NOPB	SOIC-8	4	2.7/12	1.02	4.5	2.5	0.5	5.71	4.59	4.19
926-LM6154BCM/NOPB	LM6154BCM/NOPB	SOIC-14	4	2.7/24	1.4	75	30	5	6.44	5.17	4.71
Micropower											
926-LMP2231AMFE/NOPB	LMP2231AMFE/NOPB	SOT-23	1	1.6/5.5	0.016	0.13	0.042	150	4.57	3.73	3.35
926-LMV641MGE/NOPB	LMV641MGE/NOPB	SC-70-5	1	2.7/12	0.158	10	1.6	0.5	2.06	1.59	1.44
926-LMC6041AIM/NOPB	LMC6041AIM/NOPB	SOIC-8	1	4.5/15.5	0.014	0.075	0.02	3	2.33	1.87	1.68
926-LMC6041IN/NOPB	LMC6041IN/NOPB	DIP-8	1	4.5/15.5	0.014	0.075	0.02	6	2.02	1.62	1.46
926-LMC6061AIM/NOPB	LMC6061AIM/NOPB	SOIC-8	1	4.5/15.5	0.02	0.1	0.035	0.35	1.90	1.53	1.37
926-LMC6061IM/NOPB	LMC6061IM/NOPB	SOIC-8	1	4.5/15.5	0.02	0.1	0.035	0.8	1.40	1.11	.978
926-LMC6442AIM/NOPB	LMC6442AIM/NOPB	SOIC-8	2	1.8/11	0.00095	0.01	0.0041	3	2.70	2.17	1.95
926-LMC6442IM/NOPB	LMC6442IM/NOPB	SOIC-8	2	1.8/11	0.00095	0.01	0.0041	7	2.70	2.17	1.95
926-LMC6442IN/NOPB	LMC6442IN/NOPB	DIP-8	2	1.8/11	0.00095	0.01	0.0041	7	2.70	2.17	1.95
926-LMC6042AIM/NOPB	LMC6042AIM/NOPB	SOIC-8	2	4.5/15.5	0.01	0.1	0.02	3	2.94	2.36	2.15
926-LMC6042AIN/NOPB	LMC6042AIN/NOPB	DIP-8	2	4.5/15.5	0.01	0.1	0.02	3	2.94	2.36	2.15
926-LMC6042IM/NOPB	LMC6042IM/NOPB	SOIC-8	2	4.5/15.5	0.01	0.1	0.02	6	2.76	2.22	2.00
926-LMC6042IN/NOPB	LMC6042IN/NOPB	DIP-8	2	4.5/15.5	0.01	0.1	0.02	6	2.25	1.81	1.63
926-LMC6062AIM/NOPB	LMC6062AIM/NOPB	SOIC-8	2	4.5/15.5	0.016	0.1	0.035	0.35	3.84	3.08	2.80
926-LMC6062IM/NOPB	LMC6062IM/NOPB	SOIC-8	2	4.5/15.5	0.016	0.1	0.035	0.8	3.01	2.42	2.18
926-LMC6062IN/NOPB	LMC6062IN/NOPB	DIP-8	2	4.5/15.5	0.016	0.1	0.035	0.8	2.88	2.31	2.11
926-LMC6042IMX/NOPB	LMC6042IMX/NOPB	SOIC-8	2	4.5/15.5	0.034	10	0.02	6.3	2.54	1.95	1.77
926-LMC6042AIMX/NOPB	LMC6042AIMX/NOPB	SOIC-8	2	4.5/15.5	0.034	10	0.02	3.3	2.98	2.29	2.08
926-LMC6082AIM/NOPB	LMC6082AIM/NOPB	SOIC-8	2	4.5/15.5	0.45	1.3	1.5	0.35	5.82	4.68	4.26
926-LPC662AIM/NOPB	LPC662AIM/NOPB	SOIC-8	2	5/15	0.043	0.35	0.11	3	2.86	2.29	2.09
926-LP2902M/NOPB	LP2902M/NOPB	SOIC-14	4	3/26	0.02125	0.1	0.05	10	1.61	1.29	1.13
926-LP324M/NOPB	LP324M/NOPB	SOIC-14	4	3/32	0.02125	0.1	0.05	9	.93	.74	.649
926-LP324MX/NOPB	LP324MX/NOPB	SOIC-14	4	3/32	0.02125	0.1	0.05	9	1.25	.99	.891
926-LMC6044AIM/NOPB	LMC6044AIM/NOPB	SOIC-14	4	4.5/15.5	0.01	0.1	0.02	3	3.08	2.47	2.25
926-LMC6044IM/NOPB	LMC6044IM/NOPB	SOIC-14	4	4.5/15.5	0.01	0.1	0.02	6	2.33	1.87	1.68
926-LMC6064AIM/NOPB	LMC6064AIM/NOPB	SOIC-14	4	4.5/15.5	0.016	0.1	0.035	0.35	6.08	4.88	4.44
926-LMC6064IM/NOPB	LMC6064IM/NOPB	SOIC-14	4	4.5/15.5	0.092	10	0.035	13	4.48	3.60	3.28
926-LPC660AIM/NOPB	LPC660AIM/NOPB	SOIC-14	4	5/15	0.04	0.35	0.11	3	3.42	2.74	2.50
926-LPC660IM/NOPB	LPC660IM/NOPB	SOIC-14	4	5/15	0.04	0.35	0.11	6	2.98	2.40	2.16
Micropower, Rail-to-Rail											
926-LPV521MGE/NOPB	LPV521MGE/NOPB	SC-70-5	1	1.6/5.5	0.0004	0.0062	0.0024	1	2.16	1.66	1.51
926-LMV551MF/NOPB	LMV551MF/NOPB	SOT-23-5	1	2.7/5.5	0.037	3	1	3	1.44	1.14	1.02
926-LMV551MG/NOPB	LMV551MG/NOPB	SC-70-5	1	2.7/5.5	0.037	3	1	3	1.44	1.14	1.02
926-LPV511MG/NOPB	LPV511MG/NOPB	SC-70-5	1	2.7/12	0.00097	0.027	0.0077	3	1.63	1.28	1.15
926-LMC7111BIM5/NOPB	LMC7111BIM5/NOPB	SOT-23-5	1	2.7/11	0.025	0.05	0.027	7	1.44	1.14	1.02
926-LMC7111BIM5XNOPB	LMC7111BIM5XNOPB	SOT-23-5	1	2.7/11	0.025	0.05	0.027	7	1.44	1.14	1.02
926-LMC6462AIM/NOPB	LMC6462AIM/NOPB	SOIC-8	2	3/15.5	0.02	0.05	0.015	0.5	3.02	2.43	2.21
926-LMC6462BIM/NOPB	LMC6462BIM/NOPB	SOIC-8	2	3/15.5	0.02	0.05	0.015	3	2.66	2.14	1.93
926-LPV324M/NOPB	LPV324M/NOPB	SOIC-14	4	2.7/5	0.0075	0.152	0.1	7	1.19	.952	.833