

PANASONIC SEMICONDUCTOR Diodes **Panasonic**



This product is RoHS compliant.

SWITCHING DIODES (CONT.)

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Panasonic Part No.	Package	VR (Max) (V)	IF (AV) (Max) (mA)	IR (Max) (μA)	trr (Max) (ns)	Price Each		
							1	25	100
667-DA3J103E0L	DA3J103E0L	SMMini3-F2-B	80	100	0.1	10	.12	.11	.107
667-DA3S101A0L	DA3S101A0L	SSMini3-F3-B	80	100	0.1	3	.10	.093	.091
667-DA3S101F0L	DA3S101F0L	SSMini3-F3-B	80	100	0.1	3	.18	.174	.169
667-DA3S101K0L	DA3S101K0L	SSMini3-F3-B	80	100	0.1	3	.10	.093	.091
667-DA3S102D0L	DA3S102D0L	SSMini3-F3-B	80	100	0.1	10	.13	.12	.117
667-DA3S103E0L	DA3S103E0L	SSMini3-F3-B	80	100	0.1	10	.13	.12	.117
667-DA3X101A0L	DA3X101A0L	Mini3-G3-B	80	100	0.1	3	.08	.079	.077
667-DA3X101F0L	DA3X101F0L	Mini3-G2-B	80	100	0.1	3	.12	.112	.109
667-DA3X101K0L	DA3X101K0L	Mini3-G3-B	80	100	0.1	3	.08	.079	.077
667-DA3X102D0L	DA3X102D0L	Mini3-G3-B	80	100	0.1	10	.10	.092	.09
667-DA3X103E0L	DA3X103E0L	Mini3-G3-B	80	100	0.1	10	.10	.092	.09
667-DA4J101K0R	DA4J101K0R	SMMini4-F3-B	80	100	0.1	3	.18	.178	.173
667-DA4X101F0R	DA4X101F0R	Mini4-G4-B	80	100	0.1	3	.27	.269	.262
667-DA4X101K0R	DA4X101K0R	Mini4-G4-B	80	100	0.1	3	.19	.189	.184
667-DA4X106U0R	DA4X106U0R	Mini4-G4-B	80	100	0.1	10	.40	.394	.384
667-DA5S101K0R	DA5S101K0R	SSMini5-F4-B	80	100	0.1	3	.23	.228	.222
667-DA6J101K0R	DA6J101K0R	SMMini6-F3-B	80	100	0.1	3	.30	.29	.283
667-DA6X101K0R	DA6X101K0R	Mini6-G4-B	80	100	0.1	3	.21	.201	.196
667-DA6X102P0R	DA6X102P0R	Mini6-G4-B	80	100	0.1	10	.34	.332	.323
667-DA6X102S0R	DA6X102S0R	Mini6-G4-B	80	100	0.1	10	.19	.182	.178
667-DA6X103Q0R	DA6X103Q0R	Mini6-G4-B	80	100	0.1	10	.34	.332	.323
667-DA6X103T0R	DA6X103T0R	Mini6-G4-B	80	100	0.1	10	.18	.178	.174
667-DA6X106U0R	DA6X106U0R	Mini6-G4-B	80	100	0.1	10	.34	.332	.323
667-DA6X109W0R	DA6X109W0R	Mini6-G4-B	80	100	0.1	3	.36	.35	.341
667-DA2J10400L	DA2J10400L	SMMini2-F5-B	80	200	0.5	10	.13	.126	.123
667-DA4J104K0R	DA4J104K0R	SMMini4-F3-B	80	200	0.5	10	.12	.115	.112
667-DA3J107K0L	DA3J107K0L	SMMini3-F2-B	300	100	1	60	.27	.262	.256
667-DA3X107K0L	DA3X107K0L	Mini3-G3-B	300	100	1	60	.25	.245	.238
667-DA3X108K0L	DA3X108K0L	Mini3-G3-B	300	100	1	-	.23	.211	.205
667-DA2J10800L	DA2J10800L	SMMini2-F5-B	300	200	0.2	-	.31	.307	.299
667-DA6X108K0R	DA6X108K0R	Mini6-G4-B	300	200	1	-	.38	.373	.364

ZENER DIODES

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Panasonic Part No.	Package	VZ (V)			IR (Max) (μA)	PD (Max) (mW)	Price Each		
			Min.	Nom.	Max.			1	25	100
667-DZ2W02400L	DZ2W02400L	Mini2-F3-B	2.28	2.4	2.52	20	1000	.32	.249	.226
667-DZ2J02400L	DZ2J02400L	SMMini2-F5-B	2.28	2.4	2.52	120	200	.15	.107	.104
667-DZ2S02400L	DZ2S02400L	SSMini2-F5-B	2.28	2.4	2.52	120	150	.15	.134	.131
667-DZ4J024K0R	DZ4J024K0R	SMMini4-F3-B	2.28	2.4	2.52	120	200	.15	.11	.107
667-DZ2W02700L	DZ2W02700L	Mini2-F3-B	2.57	2.7	2.84	20	1000	.32	.249	.226
667-DZ2J02700L	DZ2J02700L	SMMini2-F5-B	2.57	2.7	2.84	120	200	.15	.107	.104
667-DZ2J027M0L	DZ2J027M0L	SMMini2-F5-B	2.57	2.7	2.84	120	200	.15	.107	.104
667-DZ2S02700L	DZ2S02700L	SSMini2-F5-B	2.57	2.7	2.84	120	150	.15	.134	.131
667-DZ2W03000L	DZ2W03000L	Mini2-F3-B	2.85	3	3.15	20	1000	.32	.249	.226
667-DZ2J03000L	DZ2J03000L	SMMini2-F5-B	2.85	3	3.15	50	200	.15	.107	.104
667-DZ2J030M0L	DZ2J030M0L	SMMini2-F5-B	2.85	3	3.15	50	200	.15	.107	.104
667-DZ2S03000L	DZ2S03000L	SSMini2-F5-B	2.85	3	3.15	50	150	.15	.134	.131
667-DZ2S030M0L	DZ2S030M0L	SSMini2-F5-B	2.85	3	3.15	50	150	.15	.134	.131
667-DZ4J030K0R	DZ4J030K0R	SMMini4-F3-B	2.85	3	3.15	50	200	.15	.11	.107
667-DZ2W03300L	DZ2W03300L	Mini2-F3-B	3.14	3.3	3.47	20	1000	.32	.249	.226
667-DZ2J03300L	DZ2J03300L	SMMini2-F5-B	3.14	3.3	3.47	20	200	.15	.095	.092
667-DZ2J033M0L	DZ2J033M0L	SMMini2-F5-B	3.14	3.3	3.47	20	200	.15	.107	.104
667-DZ2S03300L	DZ2S03300L	SSMini2-F5-B	3.14	3.3	3.47	20	150	.15	.134	.131
667-DZ2S033M0L	DZ2S033M0L	SSMini2-F5-B	3.14	3.3	3.47	20	150	.15	.134	.131
667-DZ2J03600L	DZ2J03600L	SMMini2-F5-B	3.42	3.6	3.78	10	200	.15	.107	.104
667-DZ2J036M0L	DZ2J036M0L	SMMini2-F5-B	3.42	3.6	3.78	10	200	.15	.107	.104
667-DZ2S03600L	DZ2S03600L	SSMini2-F5-B	3.42	3.6	3.78	10	150	.15	.134	.131
667-DZ2S036M0L	DZ2S036M0L	SSMini2-F5-B	3.42	3.6	3.78	10	150	.15	.134	.131
667-DZ4J036K0R	DZ4J036K0R	SMMini4-F3-B	3.42	3.6	3.78	10	200	.15	.11	.107
667-DZ2W03600L	DZ2W03600L	Mini2-F3-B	3.42	3.6	3.78	20	1000	.32	.249	.226
667-DZ2J03900L	DZ2J03900L	SMMini2-F5-B	3.71	3.9	4.1	10	200	.15	.107	.104
667-DZ2J039M0L	DZ2J039M0L	SMMini2-F5-B	3.71	3.9	4.1	10	200	.15	.107	.104
667-DZ2S03900L	DZ2S03900L	SSMini2-F5-B	3.71	3.9	4.1	10	150	.15	.134	.131
667-DZ2S039M0L	DZ2S039M0L	SSMini2-F5-B	3.71	3.9	4.1	10	150	.15	.134	.131
667-DZ4J039K0R	DZ4J039K0R	SMMini4-F3-B	3.71	3.9	4.1	10	200	.15	.11	.107
667-DZ2W03900L	DZ2W03900L	Mini2-F3-B	3.71	3.9	4.1	20	1000	.32	.249	.226
667-DZ2J05100L	DZ2J05100L	SMMini2-F5-B	4.85	4.1	5.36	1	200	.15	.107	.104
667-DZ2J051M0L	DZ2J051M0L	SMMini2-F5-B	4.85	4.1	5.36	1	200	.15	.107	.104
667-DZ2J04300L	DZ2J04300L	SMMini2-F5-B	4.09	4.3	4.52	10	200	.15	.107	.104
667-DZ2J043M0L	DZ2J043M0L	SMMini2-F5-B	4.09	4.3	4.52	10	200	.15	.107	.104
667-DZ2W04300L	DZ2W04300L	Mini2-F3-B	4.09	4.3	4.52	20	1000	.32	.249	.226
667-DZ2J04700L	DZ2J04700L	SMMini2-F5-B	4.47	4.7	4.94	2	200	.15	.107	.104
667-DZ2J047M0L	DZ2J047M0L	SMMini2-F5-B	4.47	4.7	4.94	2	200	.15	.107	.104
667-DZ2S04700L	DZ2S04700L	SSMini2-F5-B	4.47	4.7	4.94	2	150	.15	.134	.131
667-DZ2S047M0L	DZ2S047M0L	SSMini2-F5-B	4.47	4.7	4.94	2	150	.15	.134	.131
667-DZ4J047K0R	DZ4J047K0R	SMMini4-F3-B	4.47	4.7	4.94	2	200	.15	.107	.104
667-DZ2404700L	DZ2404700L	TMiniP2-F2-B	4.47	4.7	4.94	20	2000	.42	.323	.294
667-DZ2W04700L	DZ2W04700L	Mini2-F3-B	4.47	4.7	4.94	20	1000	.32	.249	.226
667-DZ2705100L	DZ2705100L	SSSMini2-F4-B	4.85	5.1	5.36	1	120	.16	.157	.153
667-DZ2S05100L	DZ2S05100L	SSMini2-F5-B	4.85	5.1	5.36	1	150	.15	.134	.131
667-DZ2S051M0L	DZ2S051M0L	SSMini2-F5-B	4.85	5.1	5.36	1	150	.15	.134	.131
667-DZ2405100L	DZ2405100L	TMiniP2-F2-B	4.85	5.1	5.36	20	2000	.42	.323	.294
667-DZ2W05100L	DZ2W05100L	Mini2-F3-B	4.85	5.1	5.36	20	1000	.32	.249	.226
667-DZ2705600L	DZ2705600L	SSSMini2-F4-B	5.32	5.6	5.88	0.5	120	.16	.157	.153
667-DZ2J05600L	DZ2J05600L	SMMini2-F5-B	5.32	5.6	5.88	0.5	200	.15	.107	.104
667-DZ2J056M0L	DZ2J056M0L	SMMini2-F5-B	5.32	5.6	5.88	0.5	200	.15	.107	.104
667-DZ2S05600L	DZ2S05600L	SSMini2-F5-B	5.32	5.6	5.88	0.5	150	.15	.134	.131
667-DZ2S056M0L	DZ2S056M0L	SSMini2-F5-B	5.32	5.6	5.88	0.5	150	.15	.134	.131
667-DZ4J056K0R	DZ4J056K0R	SMMini4-F3-B	5.32	5.6	5.88	0.5	200	.15	.107	.104
667-DZ2405600L	DZ2405600L	TMiniP2-F2-B	5.32	5.6	5.88	20	2000	.42	.323	.294
667-DZ2W05600L	DZ2W05600L	Mini2-F3-B	5.32	5.6	5.88	20	1000	.32	.249	.226
667-DZ37062D0L	DZ37062D0L	SSSMini3-F2-B	5.89	6.2	6.51	0.02	150	.08	.077	.075
667-DZ2706200L	DZ2706200L	SSSMini2-F4-B	5.89	6.2	6.51	0.2	120	.25	.222	.216
667-DZ2J06200L	DZ2J06200L	SMMini2-F5-B	5.89	6.2	6.51	0.2	200	.15	.107	.104
667-DZ2J062M0L	DZ2J062M0L	SMMini2-F5-B	5.89	6.2	6.51	0.2	200	.15	.107	.104
667-DZ2S06200L	DZ2S06200L	SSMini2-F5-B	5.89	6.2	6.51	0.2	150	.15	.134	.131
667-DZ2S062M0L	DZ2S062M0L	SSMini2-F5-B	5.89	6.2	6.51	0.2	150	.15	.134	.131